

300mA, LOW QUIESCENT CURRENT, FAST TRANSIENT LOW DROPOUT LINEAR REGULATOR

Description


The AP7331 is a 300mA, adjustable and fixed output voltage, low dropout linear regulator. The device included pass element, error amplifier, band-gap, current limit and thermal shutdown circuitry. The device is turned on when EN pin is set to logic high level.

The characteristics of low dropout voltage and low quiescent current make it suitable for low power applications, for example, battery powered devices. The typical quiescent current is approximately 65µA.

Built-in current-limit and thermal-shutdown functions prevent IC from damage in fault conditions.

The AP7331 is available in SOT25 and DFN2020-6 packages.

Pin Assignments



Features

- 300mA Low Dropout Regulator with EN
- Very low l_Q over full load: 65µA
- Wide input voltage range: 2V to 6V
- Wide adjustable output: 0.8V to 5.0V
- Fixed output options: 1.0V to 3.3V
- PSRR: 65dB typical at 100Hz
- Fast start-up time: 80µs
- Stable with low ESR, 1µF ceramic output capacitor
- Excellent Load/Line Transient Response
- Low dropout: 300mV typical at 300mA
- Current limit protection
- Short circuit protection
- Thermal shutdown protection
- Ambient temperature range: -40°C to 85°C
- SOT25 and DFN2020-6: Available in "Green" Molding Compound (No Br, Sb)
- Lead Free Finish/RoHS Compliant (Note 1)

Notes: 1. EU Directive 2002/95/EC (RoHS). All applicable RoHS exemptions applied. Please visit our website at http://www.diodes.com/products/lead_free.html


Applications

- XDSL Routers
- Wireless LAN Cards
- Desktop and Notebook Computers
- Battery Powered Equipments



300mA, LOW QUIESCENT CURRENT, FAST TRANSIENT LOW DROPOUT LINEAR REGULATOR


Typical Application Circuit



Pin Descriptions

	Pin Number					
Pin Name	SOT25 (fixed)	DFN2020-6 (fixed)	SOT25 (adj)	DFN2020-6 (adj)	Description	
IN	1	3	1	3	Voltage input pin. Bypass to ground through at least 1µF capacitor	
GND	2	2	2	2	Ground	
EN	3	1	3	1	Enable input, active high	
ADJ	-	-	4	6	Output feedback pin	
NC	4	5, 6	-	5	No connection	
OUT	5	4	5	4	Voltage output pin. Bypass to ground through 1µF ceramic capacitor	

Functional Block Diagram





Absolute Maximum Ratings

Symbol	Parameter	Ratings	Units	
ESD HBM	Human Body Model ESD Protection		6	kV
ESD MM	Machine Model ESD Protection		400	V
VIN	Input Voltage	7	V	
	EN Voltage	V _{IN} + 0.3	V	
	Continuous Load Current	Internal Limited		
T _{OP}	Operating Junction Temperature Range	-40 ~ 125	°C	
T _{ST}	Storage Temperature Range		-65 ~150	°C
D		SOT25	640	mW
PD	Power Dissipation (Note 2)	740	mW	
TJ	Maximum Junction Temperature		150	°C

Recommended Operating Conditions

Symbol	Parameter	Min	Max	Unit
V _{IN}	Input voltage	2	6	V
IOUT	Output Current (Note 3)	0	300	mA
T _A	Operating Ambient Temperature	-40	85	°C

Notes:

Ratings apply to ambient temperature at 25°C
 The device maintains a stable, regulated output voltage without a load current.



Electrical Characteristics

Symbol	Parameter	Test Conditions	Min	Тур.	Max	Unit
1.	Input Quicecont Current	$V_{EN} = V_{IN}, I_{OUT} = 0mA$		55	75	
Ιq	Input Quiescent Current	$V_{EN} = V_{IN}, I_{OUT} = 300 \text{mA}$		65 85	μA	
I _{SHDN}	Input Shutdown Current	$V_{EN} = 0V, I_{OUT} = 0mA$			1	μA
I _{LEAK}	Input Leakage Current	$V_{EN} = 0V$, OUT grounded	_		1	μA
V _{Dropout}	Dropout Voltage (Note 4)	I _{OUT} = 300mA		300	550	mV
V_{REF}	ADJ Reference Voltage (Adjustable version)	I _{OUT} = 0mA		0.4		V
I _{ADJ}	ADJ Leakage (Adjustable version)				1	μA
V _{OUT}	Output Voltage Accuracy	$T_A = -40^{\circ}$ C to 85° C, $I_{OUT} = 30$ mA	-2		2	%
ΔV_{OUT} / $\Delta V_{IN}/V$	Line Regulation	$V_{IN} = (V_{OUT} + 1V)$ to V_{IN-Max} , $V_{EN} = V_{IN}$, $I_{OUT} = 1mA$		0.01	0.20	%/V
ΔV _{OUT} /V _{OUT}	Load Regulation	$V_{IN} = (V_{OUT} + 1V)$ to V_{IN-Max} , I_{OUT} from 1mA to 300mA	-0.6		0.6	%
t _{ST}	Start-up Time	$V_{EN} = 0V$ to 2.0V, $V_{OUT} = 1V$, $I_{OUT} = 300$ mA		80		μs
PSRR	PSRR	$V_{\text{IN}} = [V_{\text{OUT}} + 1V]V_{\text{DC}} + 0.5V_{\text{ppAC}},$ f = 100Hz, I _{OUT} =30mA		65		dB
I _{SHORT}	Short-circuit Current	$V_{IN} = V_{IN-Min}$ to V_{IN-Max} , $V_{OUT} < 0.2V$		100		mA
ILIMIT	Current Limit	V _{OUT} /R _{OUT} = 1A	400	600		mA
VIL	EN Input Logic Low Voltage	$V_{IN} = V_{IN-Min}$ to V_{IN-Max}			0.4	V
VIH	EN Input Logic High Voltage	$V_{IN} = V_{IN-Min}$ to V_{IN-Max}	1.4			V
I _{EN}	EN Input Current	$V_{IN} = 0V \text{ or } V_{IN-Max}$	-1		1	μA
T _{SHDN}	Thermal Shutdown Threshold			140		°C
T _{HYS}	Thermal Shutdown Hysteresis			15		°C
θ_{JA}	Thermal Resistance Junction-to-Ambient	SOT25 (Note 5)		190		°C/W
UJA		DFN2020-6 (Note 6)		167		°C/W

$(T_A = 25^{\circ}C, V_{IN} = V_{OII}$	+1V Cm = 10F C	OUT = 1 UE VEN = 2V	unless otherwise stated)


 Dropout voltage is the voltage difference between the input and the output at which the output voltage drops 2% below its nominal value. This parameter only applies to output voltages above 1.8V.
 Test conditions for SOT25: Device mounted on FR-4 substrate PCB, with minimum recommended pad layout, 2oz copper, single sided
 Test conditions for DFN2020-6: Device mounted on FR-4 substrate PCB, with minimum recommended pad layout, 2oz copper, double sided, Notes:

bottom layer is a copper plane.



AP7331


Typical Characteristics






AP7331


Typical Characteristics (Continued)







Typical Characteristics (Continued)





Application Note

Input Capacitor


A 1μ F ceramic capacitor is recommended to connect between V_{IN} and GND pins to decouple input power supply glitch and noise. The amount of the capacitance may be increased without limit. This input capacitor must be located as close as possible to the device to assure input stability and less noise. For PCB layout, a wide copper trace is required for both V_{IN} and GND. A lower ESR capacitor allows the use of less capacitance, while higher ESR type requires more capacitance.

Output Capacitor

The output capacitor is required to stabilize and help transient response for LDO. The AP7331 is stable with very small ceramic output capacitors. The recommended capacitance is from 1μ F to 4.7μ F, Equivalent Series Resistance (ESR) is from $10m\Omega$ to $200m\Omega$, and temperature characteristic is X7R or X5R. Higher capacitance values help to improve load/line transient response. The output capacitance may be increased to keep low undershoot/overshoot. Place output capacitor as close as possible to OUT and GND pins, and keep the leads as short as possible.

Adjustable Operation

The AP7331 provides output voltage from 0.8V to 5.0V through external resistor divider as shown below.



The output voltage is calculated by:

$$V_{OUT} = V_{REF} \left(1 + \frac{R_1}{R_2} \right)$$

Where $V_{REF}=0.4V$ (the internal reference voltage)

Rearranging the equation will give the following that is used for adjusting the output to a particular voltage:

$$R_1 = R_2 \left(\frac{V_{OUT}}{V_{REF}} - 1 \right)$$

To maintain the stability of the internal reference voltage, R_2 need to be kept smaller than $125k\Omega$.

No Load Stability

Other than external resistor divider, no minimum load is required to keep the device stable. The device will remain stable and regulated in no load condition.

ON/OFF Input Operation

The AP7331 is turned on by setting the EN pin high, and is turned off by pulling it low. If this feature is not used, the EN pin should be tied to IN pin to keep the regulator output on at all time. To ensure proper operation, the signal source used to drive the EN pin must be able to swing above and below the specified turn-on/off voltage thresholds listed in the Electrical

AP7331

Characteristics section under V_{IL} and V_{IH} .

Current Limit Protection

When output current at OUT pin is higher than current limit threshold, the current limit protection will be triggered and clamp the output current to approximately 600mA to prevent over-current and to protect the regulator from damage due to overheating.

Short Circuit Protection

When OUT pin is short-circuit to GND or OUT pin voltage is less than 200mV, short circuit protection will be triggered and clamp the output current to approximately 100mA. This feature protects the regulator from overcurrent and damage due to overheating.

Thermal Shutdown Protection

Thermal protection disables the output when the junction temperature rises to approximately +140°C, allowing the device to cool down. When the junction temperature reduces to approximately +125°C the output circuitry is enabled again. Depending on power dissipation, thermal resistance, and ambient temperature, the thermal protection circuit may cycle on and off. This cycling limits the heat dissipation of the regulator, protecting it from damage due to overheating.

Ultra Fast Start-up

After enabled, the AP7331 is able to provide full power in as little as tens of microseconds, typically 80µs, without sacrificing low ground current. This feature will help load circuitry move in and out of standby mode in real time, eventually extend battery life for mobile phones and other portable devices.

Fast Transient Response

Fast transient response LDOs can extend battery life. TDMA-based cell phone protocols such as Global System for Mobile Communications (GSM) have a transmit/receive duty factor of only 12.5 percent, enabling power savings by putting much of the baseband circuitry into standby mode in between transmit cycles. In baseband circuits, the load often transitions virtually instantaneously from 100 μ A to 100mA. To meet this load requirement, the LDO must react very quickly without a large voltage drop or overshoot — a requirement that cannot be met with conventional, general-purpose LDOs.



300mA, LOW QUIESCENT CURRENT, FAST TRANSIENT LOW DROPOUT LINEAR REGULATOR

Application Note (Continued)

Fast Transient Response (Continued)

The AP7331's fast transient response from 0 to 300mA provides stable voltage supply for fast DSP and GSM chipset with fast changing load.

Small Overshoot and Undershoot

The AP7331 has small and controlled overshoot and undershoot in load and line transitions. This helps to protect supplied circuit from damage and operation error caused by glitches. This feature also permits the usage of small value output decoupling capacitor with AP7331.


Low Quiescent Current

The AP7331, consuming only around 65µA for all input range and output loading, provides great power saving in portable and low power applications.

Wide Output Range

The AP7331, with a wide output range of 0.8V to 5.0V, provides a versatile LDO solution for many portable applications.

Ordering Information



Γ	Device	Package Code	Packaging	7" Tape and Reel		
	Device	Fachage Code	(Note 7)	Quantity	Part Number Suffix	
Pb ,	AP7331-XXWG-7	W	SOT25	3000/Tape & Reel	-7	
Pb ,	AP7331-XXSNG-7	SN	DFN2020-6	3000/Tape & Reel	-7	


Note: 7. Pad layout as shown on Diodes Inc. suggested pad layout document AP02001, which can be found on our website at http://www.diodes.com/datasheets/ap02001.pdf.

Marking Information

1. SOT25



300mA, LOW QUIESCENT CURRENT, FAST TRANSIENT LOW DROPOUT LINEAR REGULATOR



Device	Package	Identification Code
AP7331-ADJ	SOT25	QJ
AP7331-10	SOT25	QK
AP7331-12	SOT25	QL
AP7331-15	SOT25	QM
AP7331-18	SOT25	QN
AP7331-20	SOT25	QT
AP7331-25	SOT25	QP
AP7331-28	SOT25	QQ
AP7331-30	SOT25	QR
AP7331-33	SOT25	QS

2. DFN2020-6

(Top View)



XX : Identification Code

<u>Y</u> : Year : 0~9

 \underline{W} : Week : A~Z : 1~26 week; a~z : 27~52 week; z represents 52 and 53 week X : A~Z : Green


Device	Package	Identification Code
AP7331-ADJ	DFN2020-6	QJ
AP7331-10	DFN2020-6	QK
AP7331-12	DFN2020-6	QL
AP7331-15	DFN2020-6	QM
AP7331-18	DFN2020-6	QN
AP7331-20	DFN2020-6	QT
AP7331-25	DFN2020-6	QP
AP7331-28	DFN2020-6	QQ
AP7331-30	DFN2020-6	QR
AP7331-33	DFN2020-6	QS

Package Outline Dimensions (All Dimensions in mm)


1. Package Type: SOT25







2. Package Type: DFN2020-6




Tape Orientation (Note 8)

DFN2020-6



300mA, LOW QUIESCENT CURRENT, FAST TRANSIENT LOW DROPOUT LINEAR REGULATOR



Notes: 8. The taping orientation of the other package type can be found on our website at http://www.diodes.com/datasheets/ap02007.pdf



300mA, LOW QUIESCENT CURRENT, FAST TRANSIENT LOW DROPOUT LINEAR REGULATOR

IMPORTANT NOTICE

DIODES INCORPORATED MAKES NO WARRANTY OF ANY KIND, EXPRESS OR IMPLIED, WITH REGARDS TO THIS DOCUMENT, INCLUDING, BUT NOT LIMITED TO, THE IMPLIED WARRANTIES OF MERCHANTABILITY AND FITNESS FOR A PARTICULAR PURPOSE (AND THEIR EQUIVALENTS UNDER THE LAWS OF ANY JURISDICTION).

Diodes Incorporated and its subsidiaries reserve the right to make modifications, enhancements, improvements, corrections or other changes without further notice to this document and any product described herein. Diodes Incorporated does not assume any liability arising out of the application or use of this document or any product described herein; neither does Diodes Incorporated convey any license under its patent or trademark rights, nor the rights of others. Any Customer or user of this document or products described herein in such applications shall assume all risks of such use and will agree to hold Diodes Incorporated and all the companies whose products are represented on Diodes Incorporated website, harmless against all damages.

Diodes Incorporated does not warrant or accept any liability whatsoever in respect of any products purchased through unauthorized sales channel.

Should Customers purchase or use Diodes Incorporated products for any unintended or unauthorized application, Customers shall indemnify and hold Diodes Incorporated and its representatives harmless against all claims, damages, expenses, and attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized application.

Products described herein may be covered by one or more United States, international or foreign patents pending. Product names and markings noted herein may also be covered by one or more United States, international or foreign trademarks.

LIFE SUPPORT

Diodes Incorporated products are specifically not authorized for use as critical components in life support devices or systems without the express written approval of the Chief Executive Officer of Diodes Incorporated. As used herein:

- A. Life support devices or systems are devices or systems which:
 - 1. are intended to implant into the body, or
 - 2. support or sustain life and whose failure to perform when properly used in accordance with instructions for use provided in the labeling can be reasonably expected to result in significant injury to the user.
- B. A critical component is any component in a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or to affect its safety or effectiveness.

Customers represent that they have all necessary expertise in the safety and regulatory ramifications of their life support devices or systems, and acknowledge and agree that they are solely responsible for all legal, regulatory and safety-related requirements concerning their products and any use of Diodes Incorporated products in such safety-critical, life support devices or systems, notwithstanding any devices- or systems-related information or support that may be provided by Diodes Incorporated. Further, Customers must fully indemnify Diodes Incorporated and its representatives against any damages arising out of the use of Diodes Incorporated products or systems.

Copyright © 2011, Diodes Incorporated

www.diodes.com

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Diodes Incorporated:

 AP7331-10SNG-7
 AP7331-10WG-7
 AP7331-12SNG-7
 AP7331-12WG-7
 AP7331-15SNG-7
 AP7331-15WG-7

 AP7331-18SNG-7
 AP7331-18WG-7
 AP7331-20SNG-7
 AP7331-20WG-7
 AP7331-25SNG-7
 AP7331-25WG-7

 AP7331-28SNG-7
 AP7331-28WG-7
 AP7331-30SNG-7
 AP7331-30WG-7
 AP7331-33SNG-7
 AP7331-33WG-7

 AP7331-SNG-7
 AP7331-WG-7
 AP7331-SNG-7
 AP7331-WG-7