CCS Series 291 Precision, Long-life 12mm Optical Encoder

- Available with 4, 6, 8, 24,32, 64 Pulses per Revolution
- Optional Momentary Switch
- Multiple options for terminations, resolution, cable lengths, and operating voltage



Sense

Description

The 291 Series allows versatility in design applications by providing

highly reliable, precise digital output and long rotational life with our non-contacting design. This product provides flexibility in resolution, power consumption, and operating temperatures. The options of Schmitt trigger, detents, momentary switch, shaft & bushing length, dual shaft, termination styles, torque, operating voltage, and IP ratings provide flexibility to meet your exacting design requirements.

Ordering Information

Serie	Bush s Termination Leng	ing gth	Shaft Length	Shaf Trim	t (Outp Combi	ut ination	Operating Voltage	Swi	itch	Schmitt Ti & Locatin	igger g Lug
291	V1	C	22		F		832	А		В		4
	•					•				V		
Code	Termination	Code	Shaft Long	,	C	Code	Spec.		Code	ò	Spec.	
	.050" pitch pins		Jidit Len			F	Flat	.	A		None	
V1	Rear facing .132" length(not for 64 PPR	22 .68	7"	ure		S	Slotted		В		(not for 64 P	
	.10" pitch pins	24 .87	5″		0	utnut	Comb	ination				↓
Ρ1	Rear facing		uter shaft: .685	ire	8	332	8 PPR.	32 Detents	C	ode	S	pec.
	.236" length 4" ribbon cable	lr Ir	ner shaft: 1.05	9″	6	524	6 PPR,	24 Detents			Without Sc	nmitt trigger,
*~ 4	With .050" pitch	050" pitch (Not av			4	416	4 PPR,	16 Detents	BL	ANK	With locating lug (not for	
*C4	connector terminals (not	lug, 32 a	and 64 PPR, see	e page	8	300	8 PPR,	No Detents			Without Sc	nmitt trigger.
	for 64 PPR)	<u> </u>			6	500	6 PPR,	No Detents		A	Without loo	ating lug (not
	5" ribbon cable				4	100	4 PPR,	No Detents			for 32, 64 P	PR)
*C5	connector terminals (not for 64 PPR)					(00	24 PPR	, No Detents	S		With Schmi	tt trigger,
					Х	(00	(Only a Schmit	t trigger)		-	Without loo	ating lug
	6" ribbon cable						24 PPR	. 24 Detents		В	With Schmi	tt trigger,
*~~	With .050" pitch	hinals (not			X24	<24	(only a	vailable with			with locati	ig iug
CO	connector terminals (not						Schmitt trigger)					
	for 64 PPR)	-					32 PPR	, No Detents	-	Cod	e Snec	
		V			Y	(00	(only a	vailable with	-	A	5.0V	
			"D"				64 PPR	No Detents	_		3.3V (nc	t for
		ing Lengtr	B B		Z	200	(only available with		В		64 PPR)	
	U .312 FOF 256" For	dual shaft co					Schmit	t trigger)				
	D (not for 32	2, 64 PPR)		No	te: * 0	Cable co	onnector	for C4, C5, C6	is AMP	P/N 2	15083-6 or Ec	juivalent

2017-07-24 Rev. D

www.ctscorp.com

Electrical Specifications

Encoder Function					
Parameter	Conditions & Remarks	Min	Nominal	Max	Unit
Voltage (4, 6, 8, 24, 32 PPR)		4.75 3 175	5.0 3.3	5.25 3.425	VDC
Voltage (64 PPR)		4.5	5.0	5.5	VDC
Output Code	2-Bit Quadrature Channel A leads Channel B by 90° during clockwise rotation				
Sink Current	5.0 VDC 3.3 VDC	2.0mA 1.0mA			
Power Consumption	5.0 VDC 3.3 VDC			150 80	mW mW
Resolution	4, 6, 8, 24, 32, 64				Pulses per Revolution

Mechanical and Environmental

Manual Soldering	Maximum temperature of 350°C for 5 seconds				
RoHS	Lead-Free. Fully compliant to RoHS Directive				
Shock :	Per MIL-STD-883F (100G's)				
Vibration :	Per MIL-STD-883F (15G's)				
IP Rating (4, 6, 8, 24, 32 PPR):	IP 50				
IP Rating (64 PPR):	IP 40				
Packaging :	Standard anti-static tray packaging				
Operating Temperature:	-40°C to +85°C				
Storage Temperature:	-55°C to +100°C				
Storage Temperature: (32, 64 PPR)	-40°C to +100°C				
Detetional Life	No detent @ 30 RPM 3 Million Cycles				
Rotational Life	With detent @ 30 RPM 1 Million Cycles				
Push-Pull Strength of Shaft (4,6,8,24, 32 PPR) (64 PPR)	10 seconds20 kg10 seconds13.6 kg				
Terminal Pull-out Strength	10 seconds 6 kg				
Rotational Torque					
(4, 6, 8, 24 PPR) (32 PPR)	Running10 to 30 gf-cmRunning30 gf-cm Max.				
(64 PPR)	Running 100 gf-cm Max.				
Potational Torque	24 Detents 90 to 190 gf-cm				
Kotational rorque	16, 32 Detents 50 to 150 gf-cm				
Detent Options	0, 16, 24, 32				

Optional Momentary Switch Function:

Parameter	Conditions & Remarks	Min.	Nominal	Max	Unit
Switch contact resistance				10	ohms
Switch rating	5 VDC @10 mA				
Switch travel		0.25	0.5	0.75	mm
Actuation Force		400	510	620	grams
Switch Life	Standard	1 Millio	ı		Actuations
Switch Life		Consult CTS for custom life requirements			ements

Mechanical Specifications

Figure 1 – 291V1... – Without Schmitt Trigger, With Left Locating Lug, .050" Pitch Pins Facing Rear



2017-07-24 Rev. D

www.ctscorp.com

Page 3 of 13





GENERAL TOLERANCE: $\frac{\pm.010 \text{ inch}}{\pm 0.25 \text{ mm}}$





GENERAL TOLERANCE: ±.010 inch ±0.25 mm

www.ctscorp.com

Page 5 of 13



Figure 4 – 291V1...B – With Schmitt Trigger, With Locating Lug, .050" Pitch Pins Facing Rear

GENERAL TOLERANCE: $\frac{\pm.010 \text{ inch}}{\pm 0.25 \text{ mm}}$

www.ctscorp.com

Page 6 of 13



Figure 5 – 291P1...A – Without Schmitt Trigger, Without Locating Lug, .100" Pitch Pins Facing Rear 291P1...S – With Schmitt Trigger, Without Locating Lug, .100" Pitch Pins Facing Rear

GENERAL TOLERANCE : $\frac{\pm.010 \text{ inch}}{\pm 0.25 \text{ mm}}$

www.ctscorp.com

Page 7 of 13





GENERAL TOLERANCE: $\frac{\pm.010 \text{ inch}}{\pm 0.25 \text{ mm}}$

www.ctscorp.com

Page 8 of 13

Figure 7 –291C... – Without Schmitt Trigger, With Locating Lug, With Ribbon Cable 291C...B – With Schmitt Trigger, With Locating Lug, With Ribbon Cable



GENERAL TOLERANCE: ±.010 inch ±0.25 mm

Page 9 of 13





www.ctscorp.com

Figure 9 – 291P1...Z00AA – 64 PPR, With Schmitt Trigger, With Locating Lug, .100" Pitch Pins Facing Rear, Without Momentary Switch



GENERAL TOLERANCE: $\frac{\pm .010 \text{ inch}}{\pm 0.25 \text{ mm}} \frac{\text{inch}}{\text{mm}}$



2017-07-24 Rev. D

www.ctscorp.com

Page 11 of 13

Series 291 **Compact Optical Encoder**

Electric Circuit And Waveform (Without Schmitt Trigger Design)



*Product will function properly with external 2.2KΩ pull up resistors



Standard Quadrature 2-Bit Code

Standard Quadrature 2-Bit Code

Nominal Detent Position **POSITION NUMBER**

8 PPR/32 detents is shown 2. Code repeats every 4 positions

3. Channel A Leads Channel B in CW direction and lags in CCW direction

8 PPR/ 32 DETENTS



POSITION NUMBER Position

1. 24 PPR/24 detents is shown 2. The nominal detent position is located when both Channel A and B are low 3. Channel A Leads Channel B in CW direction and lags in CCW direction

Nominal

4, 6, 8, 24, 32 PPR





*Schmitt trigger and pull-up resitor (4.7KΩ) are integrated inside CTS optical encoder, so it's not necessary to have external pull-up resistors for application circuit.



POSITION NUMBER

8 PPR/32 detents is shown 1. 2. Code repeats every 4 positions 3. Channel A Leads Channel B in CW direction and lags in CCW direction



POSITION NUMBER

1. 24 PPR/24 detents is shown 2. The nominal detent position is located when both Channel A and B are low 3. Channel A Leads Channel B in CW direction and lags in CCW direction

64 PPR





1. 64 PPR/0 detents is shown

2. Code repeats every 4 positions

3. Channel A Leads Channel B in CW

direction and lags in CCW direction

2017-07-24 Rev. D

resistors for application circuit.

www.ctscorp.com

Page 12 of 13

Dual Shaft Construction





D - DUAL

	Х	Y	Ζ	В
Imperial	.125"	.094"	.250"	.256"
Metric	3.18	2.40	6.35	6.50

Single Shaft Trim Options

FLATTED



Shaft Trim	Diameter	х	Y	
F	.250" (6.35 mm)	.250" (6.35 mm)	.218" (5.53 mm)	

SD SLOT



Shaft Trim	Diameter	х	Y	
S	.250" (6.35 mm)	.059" (1.5mm)	.039" (1.0mm)	

Page 13 of 13

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

CTS:

<u>291C6022F624AB</u> <u>291C6022F832AB</u> <u>291V1022F624AB</u> <u>291V1022F832AB</u> <u>291P1024SZ00AAB</u> 291P1022FX24ABB <u>291P1022FY00ABB</u>