


N=Number of contacts



P.C.B. LAYOUT

**Technical Data:**  
**Electrical**  
 Pitch: 3.81mm  
 Voltage rating: 300V  
 Current rating: 12 Amps  
 Withstanding Voltage: 2500VAC(1min)  
**Mechanical:**  
 Operating temperature: -40°C to +105°C  
 Soldering temperature:  
 Temperature= 250°C±10°C / 5 seconds max  
 Safety approval:   
 RoHS Compliance

Part No.: **OSTOQXX3250**

- No. of Poles**
- 02 2 Poles
  - 03 3 Poles
  - ... ..
  - 24 24 Poles
- COLOR**
- 0: Black
  - 2: Red
  - 3: Orange
  - 4: Yellow
  - 5: Green (Standard)
  - 6: Blue
  - 8: Grey
- Nonstandard colors  
 Mins could apply

2	Pin	Copper Alloy	Tin plated	1xN
1	Body	PA66-30%GF UL94 V		1
ITEM	NAME OF PART	MATERIAL	NOTES	Q'TY
DWG	DATE	UNITS:	SHEET: 1 OF 1	Tolerance
CHK.	DATE	SCALE:	NONE 4:1 (.)	X. ±0.50
APP.	DATE	TITLE:	OSTOQ SERIES 3.81MM	X.X ±0.30
				X.XX ±0.10
				X° ±1°
				Ⓢ
		PART NO.	OSTOQXX3250	
		DWG NO.	OSTOQXX3250.DWG	
<b>OST</b>				
ON-SHORE TECHNOLOGY, INC.				

REV	SIGN	DESCRIPTION	CHK.	DATE