

NOTES:

1. MATERIALS AND FINISHES:

SMA STR PLUG - P/N: 132144
 CABLE - RG-316/U COAXIAL CABLE

2. ELECTRICAL:

A. IMPEDANCE: 50 OHM



3. PACKAGING:

A. QUANTITY: SINGLE PACK
 B. BAG TO BE MARKED: AMPHENOL RF, 135101-01-XX.XX, AND DATE CODE

THIRD ANGLE PROJ.

REVISIONS

REV	DESCRIPTION	DATE	ECN	APPR
NC	INITIAL RELEASE	03-Feb-09	--	--
C	SYNC, UPDATED DRAWING FORMAT\N/A	12-Aug-16	01541	SH
D	60.00", 72.00" & M2.00 LENGTHS ADDED	13-Dec-18	9961	VR



DRAWING NO.	PART NO. (IMPERIAL)	PART NO. (METRIC)	'L' METERS [INCHES]
SMAM-316U-SMAM002-16-02	-	135101-01-M0.10	0.100±0.006 [3.94±0.250]
SMAM-316U-SMAM002-16-03	135101-01-06.00	-	0.152±0.006 [6.00±0.250]
SMAM-316U-SMAM002-16-04	-	135101-01-M0.25	0.250±0.006 [9.84±0.250]
SMAM-316U-SMAM002-16-05	135101-01-12.00	-	0.305±0.006 [12.00±0.250]
SMAM-316U-SMAM002-16-01	135101-01-18.00	-	0.457±0.006 [18.00±0.250]
SMAM-316U-SMAM002-16-06	-	135101-01-M0.50	0.500±0.006 [19.69±0.250]
SMAM-316U-SMAM002-16-07	135101-01-24.00	-	0.610±0.013 [24.00±0.500]
SMAM-316U-SMAM002-16-08	-	135101-01-M0.75	0.750±0.013 [29.53±0.500]
SMAM-316U-SMAM002-16-09	135101-01-36.00	-	0.914±0.013 [36.00±0.500]
SMAM-316U-SMAM002-16-10	-	135101-01-M1.00	1.000±0.013 [39.37±0.500]
SMAM-316U-SMAM002-16-11	135101-01-48.00	-	1.219±0.013 [48.00±0.500]
SMAM-316U-SMAM002-16-12	135101-01-60.00	-	1.524±0.038 [60.00±1.500]
SMAM-316U-SMAM002-16-13	135101-01-72.00	-	1.829±0.046 [72.00±1.800]
SMAM-316U-SMAM002-16-14	-	135101-01-M2.00	2.000±0.050 [78.74±1.970]

DESIGN REQUIREMENTS:

- | | |
|---|--|
| <input checked="" type="checkbox"/> FREQUENCY: DC - 3 GHz | <input checked="" type="checkbox"/> CONTINUITY |
| <input type="checkbox"/> VSWR: ----1 MAX. | <input checked="" type="checkbox"/> HI-POT: 500 VRMS |
| <input type="checkbox"/> INS. LOSS: ----dBMAX. | <input type="checkbox"/> OTHER |

CUSTOMER OUTLINE DRAWING

ALL OTHER SHEETS ARE FOR INTERNAL USE ONLY

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN METRIC AND TOLERANCES ARE: <0.5mm ±0.05mm 0.5 - 6mm ±0.1mm 6 - 30mm ±0.2mm 30 - 120mm ±0.3mm ANGLES ±1°	MATERIAL	DRAWN	DATE	TITLE	Amphenol RF www.amphenolrf.com	
	SEE NOTES	M. ZHANG	09-Jul-16	SMA STR PLUG TO SMA STR PLUG USING COAXIAL RG-316/U CABLE VARIOUS LENGTHS		
NOTICE - These drawings, specifications, or other data (1) are, and remain the property of Amphenol corp. (2) must be returned upon request; and (3) are confidential and not to be disclosed to any person other than those to whom they are given by Amphenol Corp. the furnishing of these drawings, specifications, or other data by Amphenol Corp., or to any other person to anyone for any purpose is not to be regarded by implication or otherwise in any manner licensing, granting rights to permitting such holder or any other person to manufacture, use or sell any product, process or design, patented or otherwise, that may in any way be related to or disclosed by said drawings, specifications, or other data.	REFERENCE	KARTHIK R	DATE	08-Jul-16	DRAWING NO. SMAM-316U-SMAM002-16-XX	
	EAR# 7297	APPROVED	K. CAPOZZI	DATE	13-Dec-18	ITEM NO. 11M3611M00216XX
	REF:	CONFIGURATION LEVEL: In Work	CAD FILE	SCALE: 3.3:1.0	SHEET 2 OF 2	PART NO. 135101-01-XX.XX
FINISH				DWG SIZE B	REV D	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[135101-01-72.00](#) [135101-01-60.00](#) [135101-01-M2.00](#)