

POLYAMIDE (PA) RECOIL TUBING

[✉ Email](#)[🖨 Print](#)

Parker Legris recoil tubing has a lasting memory after multiple uses, offering an alternative to reels for excellent ergonomics and space saving.

The pre-assembled tubes are equipped with a protection spring, preventing damage to the ends.

PART NUMBER:

1471P08 07 13

TUBING MATERIAL:

PA

TUBE I.D. (MM):

6

TUBE O.D. (MM):

8

CONNECTION 1 THREAD SIZE (METRIC):

R1/4

COLOR:

ORANGE

LENGTH (M):

4

[Reset Attributes](#)

WHERE TO BUY

PRODUCT OVERVIEW	-
TECH SPECIFICATIONS	+

[Print Tech Specifications](#)

PERFORMANCE CHARACTERISTICS

MAXIMUM PRESSURE (BARG)

20

MINIMUM WORKING TEMPERATURE (°C)

-20

MAXIMUM WORKING TEMPERATURE (C)

80

VACUUM RATING (MM OF HG)

755

WEIGHT (KG/PACKAGE)

0.249

NUMBER OF TUBES

1

APPLICATION

MRO, Pneumatic Tools, Transportation, Lubrication, Industrial Cleaning, Robotics, Car Washing

MEDIA

Compressed air, lubricants, Other fluids: please consult us

CERTIFICATES

DI: 97/23/EC (PED), RG: 1907/2006 (REACH), DI: 2002/95/EC (RoHS), 2011/65/EC

[Print Tech Specifications](#)

CAD	+
------------	---

PRODUCT SUPPORT +

RECOMMENDED



C 9000 Polymer Quick-Acting Safety Couplers



Polyurethane (PU) Recoil Tubing



Braided Polyurethane (PU) Recoil Hose



CONTACT US

Parker Hannifin Manufacturing France SAS

Fluid System Connectors Division Europe
Parc Alcyone - Bat. D
1 rue André et Yvonne Meynier - CS 46911
35069 Rennes Cedex France

Phone

Phone: +33 (0) 2-99-25-55-00

Parker Hannifin +

[Products](#)

[About Parker](#)

[Investors](#)

[Community](#)

[Careers](#)

Global Operations +

[Divisions](#)

[Sales Companies](#)

[Worldwide Locations](#)

[Distribution Network](#)