
CMD270P3

4-8 GHz Low Noise Amplifier

Product Overview

The CMD270P3 is a broadband MMIC low noise amplifier housed in a leadless 3x3 mm plastic surface mount package. The CMD270P3 is ideally suited for EW and communications systems where small size and low power consumption are needed. The broadband device delivers greater than 16 dB of gain with a corresponding output 1 dB compression point of +18 dBm and a noise figure of 1.7 dB. The CMD270P3 is a 50 ohm matched design eliminating the need for external DC blocks and RF port matching.

Functional Block Diagram





Key Features

- Ultra Low Noise Figure
- High Gain Broadband Performance
- Single Supply Voltage: +4.0 V @ 60 mA
- Pb-free RoHs Compliant 3x3 QFN Package

Ordering Information

Part No.	Description
CMD270P3	100 pcs on 7" reel

Electrical Performance ($V_{dd} = 4.0 V$, $T_A = 25^{\circ}C$, F = 6 GHz)

Parameter	Min	Тур	Мах	Units
Frequency Range		4 - 8		GHz
Gain		16		dB
Noise Figure		1.7		dB
Input Return Loss		15		dB
Output Return Loss		11		dB
Output P1dB		18		dBm
Supply Current		60		mA

CMD270P3 4-8 GHz Low Noise Amplifier

Absolute Maximum Ratings

Parameter	Rating
Drain Voltage, V _{dd}	5 V
RF Input Power	+20 dBm
Channel Temperature, Tch	150°C
Power Dissipation, Pdiss	523 mW
Thermal Resistance, Q _{JC}	124.3°C/W
Operating Temperature	-40 to 85°C
Storage Temperature	-55 to 150°C

Exceeding any one or combination of the maximum ratings may cause permanent damage to the device.

Recommended Operating Conditions

Parameter	Min	Тур	Max	Units
V _{dd}	2.0	4.0	5.0	V
l _{dd}		60		mA


Electrical performance is measured at specific test conditions. Electrical specifications are not guaranteed over all recommended operating conditions.


Electrical Specifications (V_{dd} = 4.0 V, T_A = 25°C)


Parameter	Min	Тур	Max	Min	Тур	Max	Units
Frequency Range		4 - 6			6 - 8		GHz
Gain	13.5	17.5	20	11	15.5	19	dB
Noise Figure		1.8	2.6		1.8	2.4	dB
Input Return Loss		11			12		dB
Output Return Loss		15			15		dB
Output P1dB		18			19		dBm
Output IP3		28			31		dBm
Supply Current	40	60	80	40	60	80	mA
Gain Temperature Coefficient		0.008			0.008		dB/°C
Noise Figure Temperature Coefficient		0.008			0.008		dB/°C




Typical Performance












Typical Performance



Gain vs. Temperature, V_{dd} = 4.0 V

4.5

5

3

2

1

0

4

6

Frequency/GHz

6.5

7


7.5

8

. 5.5



Typical Performance




P1dB vs. Temperature, V_{dd} = 4.0 V

CMD270P3 4-8 GHz Low Noise Amplifier

Mechanical Information

Package Information and Dimensions



	DIMENSIONS IN MILLIMETERS				
SYMBOLS	MIN	NOM	MAX		
А	0.80	0.90	1.00		
A1	0	0.02	0.05		
A3		0.25REF.			
b	0.18	0.23	0.30		
D	2.85	3.00	3.15		
D1		1.5BSC			
Е	2.85	3.00	3.15		
E1		1.5BSC			
e		0.50BSC			
L	0.30	0.40	0.50		
θ	0		12		
aaa		0.25			
bbb		0.10			
ссс		0.10			
М			0.05		

Notes:

- 1. Dimensions are in millimeters
- 2. RoHS compliant mold compound
- 3. Lead frame material: Copper alloy
- 4. Lead finish: 100% matte Sn
- 5. Indicated dimension/tolerance applies to leads and exposed pad

Recommended PCB Land Pattern

Qorvo recommends that the user develop the land pattern that will provide the best design for proper solder reflow and device attach for their specific application. Please review Qorvo Application Note AN 105 for a recommended land pattern approach.


Recommended Solder Reflow Profile

Qorvo recommends screen printing with belt furnace reflow to ensure proper solder reflow and device attach. Please review Qorvo Application Note AN 102 for a recommended solder reflow profile.

CMD270P3 4-8 GHz Low Noise Amplifier

Pin Description

Pin Diagram




Functional Description

Pin	Function	Description	Schematic
1, 5 - 8, 12, 13, 15, 16	N/C	No connection required These pins may be connected to RF / DC ground	
2, 4, 9, 11 and die paddle	Ground	Connect to RF / DC ground	GND =
3	RF in	DC blocked and 50 ohm matched	RF in
10	RF out	DC blocked and 50 ohm matched	O RF out
14	V _{dd}	Power supply voltage Decoupling and bypass caps required	Vdd =



Applications Information

Application Circuit



Biasing and Operation

The CMD270P3 is biased with a single 4.0 V positive drain supply.

RF power can be applied at any time.


GaAs MMIC devices are susceptible to damage from Electrostatic Discharge. Proper precautions should be observed during handling, assembly and test.



Applications Information

Evaluation Board

The circuit board shown has been developed for optimized assembly at Qorvo. A sufficient number of via holes should be used to connect the top and bottom ground planes. As surface mount processes vary, careful process development is recommended.



Bill of Material

Designator	Value	Description			
J1, J2		SMA End Launch Connector			
P1		10 Pin Header			
C1	0.33 µF	Capacitor, Tantalum			
C2	1000 pF	Capacitor, 0603			
C3	100 pF	Capacitor, 0402			
U1		CMD270P3 Low Noise Amplifier			
PCB		CM1118A Evaluation PCB			

CMD270P3 4-8 GHz Low Noise Amplifier

Handling Precautions

Parameter	Rating	Standard		On the l
ESD – Human Body Model (HBM)	Class 1A	ESDA / JEDEC JS-001-2012		Caution! ESD-Sensitive Device
MSL-Moisture Sensitivity Level	Level 1	IPC/JEDEC J-STD-020	JE .	ESD-Sensitive Device

RoHS Compliance

This part is compliant with 2011/65/EU RoHS directive (Restrictions on the Use of Certain Hazardous Substances in Electrical and Electronic Equipment) as amended by Directive 2015/863/EU.

This product also has the following attributes:

- Lead Free
- Antimony Free
- TBBP-A (C15H12Br402) Free
- SVHC Free
- PFOS Free
- Halogen Free

Contact Information

For the latest specifications, additional product information, worldwide sales and distribution locations:

Web: www.qorvo.com

Tel: 1-844-890-8163

Email: customer.support@qorvo.com

Important Notice

The information contained in this Data Sheet and any associated documents ("Data Sheet Information") is believed to be reliable; however, Qorvo makes no warranties regarding the Data Sheet Information and assumes no responsibility or liability whatsoever for the use of said information. All Data Sheet Information is subject to change without notice. Customers should obtain and verify the latest relevant Data Sheet Information before placing orders for Qorvo[®] products. Data Sheet Information or the use thereof does not grant, explicitly, implicitly or otherwise any rights or licenses to any third party with respect to patents or any other intellectual property whether with regard to such Data Sheet Information itself or anything described by such information.

DATA SHEET INFORMATION DOES NOT CONSTITUTE A WARRANTY WITH RESPECT TO THE PRODUCTS DESCRIBED HEREIN, AND QORVO HEREBY DISCLAIMS ANY AND ALL WARRANTIES WITH RESPECT TO SUCH PRODUCTS WHETHER EXPRESS OR IMPLIED BY LAW, COURSE OF DEALING, COURSE OF PERFORMANCE, USAGE OF TRADE OR OTHERWISE, INCLUDING THE IMPLIED WARRANTIES OF MERCHANTABILITY AND FITNESS FOR A PARTICULAR PURPOSE. Without limiting the generality of the foregoing, Qorvo[®] products are not warranted or authorized for use as critical components in medical, life-saving, or life-sustaining applications, or other applications where a failure would reasonably be expected to cause severe personal injury or death. Applications described in the Data Sheet Information are for illustrative purposes only. Customers are responsible for validating that a particular product described in the Data Sheet Information is suitable for use in a particular application.

© 2020 Qorvo US, Inc. All rights reserved. This document is subject to copyright laws in various jurisdictions worldwide and may not be reproduced or distributed, in whole or in part, without the express written consent of Qorvo US, Inc. | QORVO[®] is a registered trademark of Qorvo US, Inc.



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Qorvo: CMD270P3