



SPECIFICATION FOR APPROVAL

CUSTOMER: CHIP

EVERCOOL MODEL NO: AL6025H12BA

CUSTOMER MODEL NO: AL6025H12BA

DESCRIPTION: DC12V FAN

APPROVED BY (AUTHORISED)	APPROVED
	Alex
	CHECKED
	Guoruihua
	DRAWN
	Libingbing
	SALES
	Teddy

* Please confirm your acceptance by return fax or mail.

SPEC NO	ISSUE DATE	EDITION	REVISED DATE
20151118A03	2015/11/18	A0	2015/11/18

THE PRODUCTION ACCORD WITH EUROPE UNION ROHS STANDARD

EVERCOOL THERMAL CO., LTD

NO. 123-8, HSING DE RD., SAN-CHUNG CITY,

TAIPEI HSIEN, TAIWAN, R.O.C.

TEL: 886-2-8512-2889 FAX: 886-2-8512-2890

[URL:www.evercool.com.tw](http://www.evercool.com.tw)

[EMAIL: coolest@ms14.hinet.net](mailto:coolest@ms14.hinet.net)

I. GENERAL SPECIFICATION

Item	Specification
1.Part NO.	AL6025H12BA
2.Outline Dimension	60*60*25
3.Rated Voltage	12 VDC
4.Starting Voltage	7 VDC
5.Operating Voltage Range	7 VDC~ 13.8 VDC
6.Rated Current*	0.24 A(Max)
7.Rated Power Consumption*	2.88 W
8.Rated Speed*	5000 RPM±15%
9.Max. Airflow**	26.63 CFM(ft3/min)
10.Max. Static Pressure**	0.28 In-H2O
11.Noise Level***	<36 dB(A)
12.Life Expectancy	50000 hrs at 45°C
13.No of Polarity	4 Poles
14.Direction of Rotation	Counter-Clockwise

Noted:

***Input Current Speed Power Consumption**

Measured after continuous 30 minutes operation at rated voltage in free air at ambient temperature of 25 °C, 65% relative humidity

****Performance**

Measured with use of double chamber. The value are recorded when the fan speed is stabilized at rated voltage.

*****Noise Level**

Measured at rated voltage in a semi-anechoic chamber with background noise below than 17 dB(A). The measuring distance is in one meter from microphone to inlet of the fan.

II. ELECTRICAL SPECIFICATION

Item		Specification
1.Polarity Protection	✓ YES	Be capable of endurance when Vcc & GRD are exchanged
	NO	
2.Auto restart	YES	Locked motor protection
	✓ NO	
3.Insulation Resistance		10MΩ/b/w unshielded wire and frame at 500 VDC/min
4.Dielectric Strength		5Ma Max./Measured b/w lead wire and frame at 500VAC/min

III. MAIN MATERIALS / PARTS SPECIFICATION

Item		Specification				
1.Materials of Frame		Aluminum				
2.Materials of Fan Blade		Thermoplastic PBT of UL 94V-0(BK)				
3.Bobbin						
4.Bearing	✓	Dual ball bearing				
		1 ball & 1 sleeve bearing				
		Sleeve bearing				
		EL bearing				
5.Lead wire	✓	Red (+)	UL#	1007	24	AWG
	✓	Black (-)	UL#	1007	24	AWG
	✓	Blue(FG)	UL#	1007	24	AWG

6.Connector		2510 3P				


IV. ENVIRONMENT SPECIFICATION

Item	Specification
1.Operation Temperature	-10°C ~+80°C/66%(RH), high / low temperature test for 24 hours, temperature change: 30°C /hours.
2.Storage Temperature	-40°C ~+70°C/66%(RH), high / low temperature test for 24 hours, temperature change: 30°C /hours.


V. DROPPING TEST

Prepared in minimum packing condition, fan will withstand one drop each on three surfaces from 30 cm height onto a 10mm thick hard wooden board.

VI. LABEL MARKING





VII. OUTLINE DIMENSION




UNIT $\frac{\text{MM}}{\text{INCH}}$

VIII. Sensor Circuit System

Speed Sensor / Tachometer (FG/F)



IX. P/Q Performance



	Q(cfm)	Ps(InchH ₂ o)
1	0.000	0.276
2	8.789	0.139
3	12.498	0.087
4	15.255	0.081
5	17.758	0.075
6	19.854	0.072
7	21.663	0.063
8	23.371	0.045
9	24.961	0.025
10	26.627	0.000