

Specification Sheet

Part Number: 151-02501



The 360 degree enclosure ensures the entire bundle is secure when being routed by this clip.

Locking tab on this clip is small enough that it will not interfere with any other portion of the wire routing, but is significant enough to allow for manual disengagement if service is needed.

Disc around the fir tree eliminates potential debris and water to enter the panel hole.

LOC Locking Clamp, 10–14 mm Bundle Dia with FT9X12 Fir Tree, PA66HIRHSUV, Black, 500/pkg

Article Number	151-02501
Type	LOC1014FT9x12
Color	Black (BK)
Quantity Per	bag
Product Description	The Locking Omega Clip creates a full and secure lock completely around a wire bundle ranging from 5-25 mm. The fixating fir tree on this clip allows for the clip to be secured into a panel by utilizing a round or oval hole.
Short Description	LOC Locking Clamp, 10–14 mm Bundle Dia with FT9X12 Fir Tree, PA66HIRHSUV, Black, 500/pkg

Global Part Name

LOC1014FT9x12-PA66HIRHSUV-BK

Minimum Tensile Strength (Imperial)

50.0

Minimum Tensile Strength (Metric)

225.0

Length L (Imperial)

1.37

Length L (Metric)

35.0

Fixation Method

Fir Tree

Width W (Imperial)

0.47

Width W (Metric)

12.0

Bundle Diameter Min (Imperial)

0.39

Bundle Diameter Min (Metric)

10.0

Bundle Diameter Max (Imperial)

0.55

Bundle Diameter Max (Metric)

14.0

Cable Ties

T50R

Height H (Imperial)

2.30

Height H (Metric)

58.75

Panel Thickness Min (Imperial)

0.02

Panel Thickness Max (Imperial)	0.27
Panel Thickness Min (Metric)	0.60
Panel Thickness Max (Metric)	6.75
Mounting Hole Diameter D (Imperial)	0.35 x 0.47 " 0.35 x 0.55
Mounting Hole Diameter D (Metric)	9.0 x 14.0 mm 9.0 x 12.0 mm
Mounting Hole Diameter D Min (Imperial)	0.35
Mounting Hole Diameter D Max (Imperial)	0.55
Mounting Hole Diameter D Max (Metric)	14.0
Disc Diameter (Metric)	23.63
Disc Diameter (Imperial)	0.93
Material	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)
Material Shortcut	PA66HIRHSUV
Flammability	UL 94 HB
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Reach Compliant (Article 33)	Yes

ROHS Compliant Yes

UL Listed (US and Canada) Yes

UL Listed (US) Yes

Package Quantity (Imperial) 500

Package Quantity (Metric) 500

Customs Number 3926909988