

Specification Sheet

Part Number: 156-00882



Friction tab inside the fir tree allows the tie to sit in mount without falling out prior to installation.

Fir tree provides low insertion effort yet demonstrates high extraction resistance.

Disc feature prevents rattling in high-vibration applications and protects against debris ingress.

2-Piece Cable Tie/Fir Tree Mount, 8.0"L, .20"-.22" Mounting Hole Diameter, PA66HS, Black, 500/pkg

Article Number 156-00882

Type T50RFT5.5SD

Color Black (BK)

Quantity Per carton

Product Description HellermannTyton's fir tree mounts provide a secure grip in a mounting hole. The mount can slide along the cable tie to adjust orientation as needed. Fir tree mounts are designed to provide a low insertion force and high extraction force. This mount is sold as an assembly with the cable tie.

Short Description 2-Piece Cable Tie/Fir Tree Mount, 8.0"L, .20"-.22" Mounting Hole Diameter, PA66HS, Black, 500/pkg

Global Part Name

T50RFT5.5SD-PA66HS/PA66HIRHS-BK

Minimum Tensile Strength (Imperial) 50.0

Minimum Tensile Strength (Metric) 225

Length L (Imperial) 8.0

Length L (Metric) 203.2

Fixation Method Fir Tree

Identification Plate Position none

Releasable Closure No

Tie Closure plastic pawl

Width W (Imperial) 0.18

Width W (Metric) 4.6

Bundle Diameter Min (Imperial) 0.20

Bundle Diameter Min (Metric) 5.0

Bundle Diameter Max (Imperial) 2.0

Bundle Diameter Max (Metric) 45.0

Thickness T (Imperial) 0.05

Thickness T (Metric)	1.2
Height H (Imperial)	0.05
Panel Thickness Min (Imperial)	0.03
Panel Thickness Max (Imperial)	0.18
Panel Thickness Min (Metric)	0.7
Panel Thickness Max (Metric)	4.5
Mounting Hole Diameter D (Imperial)	0.2 - 0.22
Mounting Hole Diameter D (Metric)	5.0 - 5.7 mm
Mounting Hole Diameter D Min (Imperial)	0.224
Mounting Hole Diameter D Max (Imperial)	0.196
Mounting Hole Diameter D Max (Metric)	5.7
Disc Diameter (Metric)	16.0
Disc Diameter (Imperial)	0.63
Material	Polyamide 6.6 heat stabilized (PA66HS) Polyamide 6.6, high impact modified, heat stabilized (PA66HIRHS)
Material Shortcut	PA66HS PA66HIRHS

Material Cable Tie Polyamide 6.6 heat stabilized (PA66HS)

Operating Temperature -40°F to +221°F (-40°C to +105°C)

ROHS Compliant Yes

Package Quantity (Imperial) 500

Package Quantity (Metric) 500

Customs Number 3926909988