

A. System Overview

## Conductor Identification Labels











B1. Cable Ties

### Material Chart

| Material  | Print Method | Temperature Range                  | Features   |
|-----------|--------------|------------------------------------|--|
| Polyester | Pre-Printed  | -40°F to 250°F<br>(-40°C to 121°C) | Indoor/outdoor rated; laminated label material protects legend from abrasion and chemicals; resistant to UV light, chemical atmosphere, and abrasion; excellent life and adhesion properties |

B2. Cable Accessories

B3. Stainless Steel Ties

| Part Number | Symbol  | Legend                    | Marker Diameter |       | Labels Per Sheet | Std. Pkg. Sheet(s) | Std. Ctn. Sheet(s) |
|-------------|---|---------------------------|-----------------|-------|------------------|--------------------|--------------------|
|             |   |                           | In.             | mm    |                  |                    |                    |
| PESS-A-CE   |    | CE SYMBOL                 | 0.49            | 12.50 | 20               | 10                 | 100                |
| PESS-B-CE   |   |                           | 0.63            | 16.00 | 20               | 10                 | 100                |
| PESS-C-CE   |   |                           | 0.79            | 20.00 | 10               | 10                 | 100                |
| PESS-D-CE   |   |                           | 0.98            | 25.00 | 10               | 10                 | 100                |
| PESS-E-CE   |   |                           | 1.24            | 31.50 | 10               | 10                 | 100                |
| PESS-A-ES   |    | EARTH (GROUND)            | 0.49            | 12.50 | 20               | 10                 | 100                |
| PESS-B-ES   |   |                           | 0.63            | 16.00 | 20               | 10                 | 100                |
| PESS-C-ES   |   |                           | 0.79            | 20.00 | 10               | 10                 | 100                |
| PESS-D-ES   |   |                           | 0.98            | 25.00 | 10               | 10                 | 100                |
| PESS-E-ES   |   |                           | 1.24            | 31.50 | 10               | 10                 | 100                |
| PESS-A-L1   |   | OUTER CONDUCTOR – L1      | 0.49            | 12.50 | 20               | 10                 | 100                |
| PESS-B-L1   |   |                           | 0.63            | 16.00 | 20               | 10                 | 100                |
| PESS-C-L1   |   |                           | 0.79            | 20.00 | 10               | 10                 | 100                |
| PESS-D-L1   |   |                           | 0.98            | 25.00 | 10               | 10                 | 100                |
| PESS-E-L1   |   |                           | 1.24            | 31.50 | 10               | 10                 | 100                |
| PESS-A-L2   |  | OUTER CONDUCTOR 2 – L2    | 0.49            | 12.50 | 20               | 10                 | 100                |
| PESS-B-L2   |   |                           | 0.63            | 16.00 | 20               | 10                 | 100                |
| PESS-C-L2   |   |                           | 0.79            | 20.00 | 10               | 10                 | 100                |
| PESS-D-L2   |   |                           | 0.98            | 25.00 | 10               | 10                 | 100                |
| PESS-E-L2   |   |                           | 1.24            | 31.50 | 10               | 10                 | 100                |
| PESS-A-L3   |  | OUTER CONDUCTOR 3 – L3    | 0.49            | 12.50 | 20               | 10                 | 100                |
| PESS-B-L3   |   |                           | 0.63            | 16.00 | 20               | 10                 | 100                |
| PESS-C-L3   |   |                           | 0.79            | 20.00 | 10               | 10                 | 100                |
| PESS-D-L3   |   |                           | 0.98            | 25.00 | 10               | 10                 | 100                |
| PESS-E-L3   |   |                           | 1.24            | 31.50 | 10               | 10                 | 100                |
| PESS-A-LF   |  | LEAD FREE SYMBOL          | 0.49            | 12.50 | 20               | 10                 | 100                |
| PESS-A-N    |  | NEUTRAL CONDUCTOR – N     | 0.49            | 12.50 | 20               | 10                 | 100                |
| PESS-B-N    |   |                           | 0.63            | 16.00 | 20               | 10                 | 100                |
| PESS-C-N    |   |                           | 0.79            | 20.00 | 10               | 10                 | 100                |
| PESS-D-N    |   |                           | 0.98            | 25.00 | 10               | 10                 | 100                |
| PESS-A-PE   |  | PROTECTIVE CONDUCTOR – PE | 0.49            | 12.50 | 20               | 10                 | 100                |
| PESS-A-ROHS |  | RoHS WHEELED BIN SYMBOL   | 0.49            | 12.50 | 20               | 10                 | 100                |
| PESS-A-SS   |  | SAFETY FUNCTION           | 0.49            | 12.50 | 20               | 10                 | 100                |
| PESS-B-SS   |   |                           | 0.63            | 16.00 | 20               | 10                 | 100                |
| PESS-C-SS   |   |                           | 0.79            | 20.00 | 10               | 10                 | 100                |
| PESS-D-SS   |   |                           | 0.98            | 25.00 | 10               | 10                 | 100                |

F. Index

Order number of cards required.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

## Panduit:

[PESS-A-ES](#) [PESS-A-ROHS](#) [PESS-A-SS](#) [PESS-C-ES](#) [PESS-A-PE](#) [PESS-A-CE](#) [PESS-A-L1](#) [PESS-A-L2](#) [PESS-A-L3](#) [PESS-A-LF](#) [PESS-D-L3](#) [PESS-E-ES](#) [PESS-B-L3](#) [PESS-B-CE](#) [PESS-D-ES](#) [PESS-C-CE](#) [PESS-C-SS](#) [PESS-E-L2](#) [PESS-D-SS](#) [PESS-C-L1](#) [PESS-C-N](#) [PESS-B-N](#) [PESS-C-L3](#) [PESS-E-L3](#) [PESS-D-L1](#) [PESS-C-L2](#) [PESS-D-CE](#) [PESS-B-L1](#) [PESS-E-CE](#) [PESS-B-L2](#) [PESS-E-L1](#) [PESS-D-N](#) [PESS-D-L2](#) [PESS-A-N](#) [PESS-B-ES](#) [PESS-B-SS](#) [PESS-A-RC10](#) [PESS-A-RC25](#) [PESS-A-RC50](#) [PESS-A-RCE](#)