

Surface Mount Type **SP-Cap**

Series: **SX** (Low ESR Products)




■ Features

- Large capacitance (560 μ F max.)
- Low ESR (4.5 m Ω to 9 m Ω)
- RoHS directive compliant

■ Specifications


Series & Size Code	SX			
Category Temp. Range	-40 °C to +105 °C			
Rated W.V.Range	2 V.DC to 6.3 V.DC			
Nominal Cap.Range	82 μ F to 560 μ F			
Capacitance Tolerance	\pm 20 %			
DC Leakage Current	$I \leq 0.1 CV (\mu A)$ 2 minutes			
tan δ	≤ 0.06 (120 Hz/+20 °C)			
Surge Voltage	Rated Working Voltage \times 1.25 (15 °C to 35 °C)			
Endurance	After applying rated working voltage for 2000 hours at 105 °C \pm 2 °C, and then being stabilized at +20 °C, capacitor shall meet the following limits.			
	Capacitance change	\pm 20% of initial measured value		
	tan δ	≤ 200 % of initial specified value		
Moisture resistance	DC leakage current	≤ 300 % of initial specified value		
	After storing for 500 hours at 60 °C, 90 %			
	Capacitance change of initial measured value	2, 2.5 V.DC	4 V.DC	6.3 V.DC
		+70, -20 %	+60, -20 %	+50, -20 %
	tan δ	≤ 200 % of initial specified value		
DC leakage current	\leq Initial specified value			

■ Marking



■ Dimensions in mm(not to scale)

(Unit : mm)



Design and specifications are each subject to change without notice. Ask factory for the current technical specifications before purchase and/or use. Should a safety concern arise regarding this product, please be sure to contact us immediately.

■ Low ESR Products

Series & Size Code	Rated W.V. (V.DC)	Capacitance (±20%) (μF)	Case Size			Specification		Part number Reflow condition : 260 °C ^{*3}	Min. Packaging Q'ty (pcs) ^{*4}
			L (mm)	W (mm)	H (mm)	Ripple current (Ar.m.s.) ^{*1}	ESR (mΩ max.) ^{*2}		
SX	2	180	7.3	4.3	1.9	6.3	9	EEFSX0D181ER	3500
		220	7.3	4.3	1.9	6.3	9	EEFSX0D221ER	3500
		270	7.3	4.3	1.9	6.3	9	EEFSX0D271ER	3500
			7.3	4.3	1.9	7.5	6	EEFSX0D271XE	3500
			7.3	4.3	1.9	8.5	4.5	EEFSX0D271E4	3500
		330	7.3	4.3	1.9	6.3	9	EEFSX0D331ER	3500
			7.3	4.3	1.9	7.5	6	EEFSX0D331XE	3500
			7.3	4.3	1.9	8.5	4.5	EEFSX0D331E4	3500
		390	7.3	4.3	1.9	6.3	9	EEFSX0D391ER	3500
			7.3	4.3	1.9	7.5	6	EEFSX0D391XE	3500
			7.3	4.3	1.9	8.5	4.5	EEFSX0D391E4	3500
		470	7.3	4.3	1.9	6.3	9	EEFSX0D471ER	3500
			7.3	4.3	1.9	7.5	6	EEFSX0D471XE	3500
			7.3	4.3	1.9	8.5	4.5	EEFSX0D471E4	3500
		560	7.3	4.3	1.9	8.5	4.5	EEFSX0D561E4	3500
	2.5	150	7.3	4.3	1.9	6.3	9	EEFSX0E151ER	3500
		180	7.3	4.3	1.9	6.3	9	EEFSX0E181ER	3500
		220	7.3	4.3	1.9	6.3	9	EEFSX0E221ER	3500
			7.3	4.3	1.9	7.0	7	EEFSX0E221E7	3500
		270	7.3	4.3	1.9	7.0	7	EEFSX0E271E7	3500
			7.3	4.3	1.9	6.3	9	EEFSX0E331ER	3500
		330	7.3	4.3	1.9	7.5	6	EEFSX0E331XE	3500
			7.3	4.3	1.9	8.5	4.5	EEFSX0E331E4	3500
			7.3	4.3	1.9	6.3	9	EEFSX0E391ER	3500
		390	7.3	4.3	1.9	7.5	6	EEFSX0E391XE	3500
			7.3	4.3	1.9	8.5	4.5	EEFSX0E391E4	3500
			7.3	4.3	1.9	6.3	9	EEFSX0E471ER	3500
		470	7.3	4.3	1.9	7.5	6	EEFSX0E471XE	3500
			7.3	4.3	1.9	8.5	4.5	EEFSX0E471E4	3500
			82	7.3	4.3	1.9	6.3	9	EEFSX0G820ER
	4	100	7.3	4.3	1.9	6.3	9	EEFSX0G101ER	3500
		150	7.3	4.3	1.9	6.3	9	EEFSX0G151ER	3500
			7.3	4.3	1.9	7.0	7	EEFSX0G151E7	3500
180		7.3	4.3	1.9	6.3	9	EEFSX0G181ER	3500	
220		7.3	4.3	1.9	6.3	9	EEFSX0G221ER	3500	
6.3	120	7.3	4.3	1.9	7.0	7	EEFSX0J121E7	3500	
	150	7.3	4.3	1.9	6.3	9	EEFSX0J151ER	3500	

*1: Ripple current (100 kHz/ +45 °C), *2: ESR (100 kHz/+20 °C)

*3: Please refer to the page of "Mounting Specifications".

*4: Please contact us when 500 pcs packing is necessary.

Temperature Compensation Multipliers for Ripple Current		
≤ 45 °C	45 °C < T ≤ 85 °C	85 °C < T ≤ 105 °C
1.0	0.7	0.25