



CGS

TE Part # 1623746-5

TE Internal #: ER7412RJT

[View on TE.com >](#)

Passive Components > Resistors > Fixed Resistors > Through-Hole Resistors



Resistor Type: **Power Resistor**

Dimensions: **13.5 x 6 mm**

Number of Terminations: **2**

Packaging Method: **Ammo Packed**

Tolerance: **5%**

Features

Product Type Features

Product Type	Fixed Resistor
Resistor Type	Power Resistor
Element Type	Wirewound

Configuration Features

Number of Resistors	1
---------------------	---

Electrical Characteristics

Voltage Rating	100 V
Tolerance	5%
Resistance Class	Up to 1kΩ
Resistance	12 Ω
Power Rating	3 W

Body Features

Lead Type	Axial Leaded
-----------	--------------

Termination Features

Number of Terminations	2
Termination Type	Tinned Copper Leads

Mechanical Attachment

Mount Style	Axial Leaded
-------------	--------------

Dimensions

Dimensions	13.5 x 6 mm
------------	-------------

Usage Conditions

Operating Temperature Range	-55 – 200 °C
Temperature Coefficient	0 – 60 ppm/°C

Packaging Features

Packaging Method	Ammo Packed
------------------	-------------

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2019 (197) Candidate List Declared Against: JUL 2017 (174)
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Wave solder capable to 265°C


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulations, TE's information on SVHC in articles for this part number is still based on the European Chemical Agency (ECHA) 'Guidance on requirements for substances in articles' (Version: 2, April 2011), applying the 0.1% weight on weight concentration threshold at the finished product level. TE is aware of the European Court of Justice ruling of September 10th, 2015 also known as O5A (Once An Article Always An Article) stating that, in case of 'complex object', the threshold for a SVHC must be applied to both the product as a whole and simultaneously to each of the articles forming part of its composition. TE has evaluated this ruling based on the new ECHA "Guidance on requirements for substances in articles" (June 2017, version 4.0) and will be updating its statements accordingly.


Compatible Parts

ER74 12R 5% AMMO PK

TE Part # 1623746-5
TE Internal #: ER7412RJT




TE Part # 4-1623750-7
ER58 R22 5% AMMO



TE Part # 1623749-6
ER17 22K 5% LOOSE




TE Part # 6-1623746-9
ER74 R05 10% AMMO PK



TE Part # 1-1623746-3
ER74 1R0 5% AMMO PK

Customers Also Bought



TE Part #1623746-3
ER74 10R 5% AMMO PK



TE Part #1-1478996-5
Cable Boot Red RG174,
179, 187



TE Part #3-1879073-2
THS10 82R 5%



TE Part #3-1879074-9
THS15 2K2 5%



TE Part #6-1879224-8
CPF 0603 17K4 0.1%
25PPM 1K RL



TE Part #1623714-2
FCB4 10K 5% HP




TE Part #2176216-1
CPF A 0603 10R 0.1%
25PPM 1K RL



TE Part #1-2176185-1
CRGH0805 1% 3K3 0.33W



TE Part #4-1879314-7
DPL12S 24P 24DET 21F RD
/GRN



TE Part #4-1623746-9
ER74 6R8 5% AMMO PK

Documents

Product Drawings

[ER74 12R 5% AMMO PK](#)

English

CAD Files

[3D PDF](#)

[3D](#)

[Customer View Model](#)

[ENG_CVM_CVM_1623746-5_BA.2d_dxf.zip](#)



English

Customer View Model

[ENG_CVM_CVM_1623746-5_BA.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1623746-5_BA.3d_stp.zip](#)

English

Datasheets & Catalog Pages

[4-1773460-6_RESISTIVE_SOLUTIONS_RAIL](#)

English

[1309350_PASSIVE_COMPONENT](#)

English

[Type ER/ERV Series High Power Resistors](#)

English

[8-1773459-4_POWER_FILTERING_AND_RESISTIVE_SOLUTIONS_FOR_ELEVATORS_AND_ESCALATORS](#)

English