

CP Series

Cold Plate Four-pass Heatsink



FEATURES

- Designed for Ohmite products, Pre drilled hole patterns for standard Ohmite planar resistors TAP600/TAP800 and TAP1K0/TAP2K0.
- Design flexibility, Chill Plate lengths can be configured as well as mounting hole patterns to accept a multitude of devices.
- Thermally efficient copper mounting surface for the most efficient heat transfer.

The Ohmite CP4 series Liquid Coldplates are designed for Ohmite heatsinkable type resistors, such as TAP600, TAP800, TA1K0, TA2K0, and various SOT-227 resistor packages. The CP series also provides maximum heat removal for SCRs, rectifiers, diodes, thyristors, and other high-power semiconductor devices. The CP series is customizable to fit multiple applications. Length and mounting hole patterns can be specified.

SERIES SPECIFICATIONS

Part Number	Mounting Surface Area (in ² /mm ²)	Weight (oz/g)	Ohmite Resistor Series	Thermal Resistance* (°C/W)
CP4-114A	19.13/12339	28.4/805		0.018
CP4-114B	19.13/12339	28.4/805	TAP600/TAP800	0.018
CP4-114C	19.13/12339	28.4/805	TAP1K0/TAP2K0	0.018

* @ flow of 1.5 GPM

CHARACTERISTICS

Tubing Copper, 0.375" OD, nominal wall thickness of 0.050"

Plate Aluminum 6063-T5


Weight 805 g

CP Series


Cold Plate Four-pass Heatsink

HEAT DISSIPATION

Graph data produced using Ohmite TAP2K0.



DIMENSIONS



HOW TO ORDER

Custom sizes and bolt configurations are subject to minimums.

Four Pass
CP4A-114A-108E
 Cold Plate Length (mm) Hole Pattern Width (mm) RoHS Compliant
 A = no holes
 B = TAP600/800
 C = TA1K0/TA2K0
 (assigned sequentially for custom patterns)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Ohmite:](#)

[CP4A-114B-108E](#) [CP4A-114C-108E](#) [CP4A-114A-108E](#)