



Smart Highside Power Switch

Reversave™

 Reverse battery protection by self turn on of power MOSFET

Features

- Short circuit protection
- Current limitation
- Overload protection
- Thermal shutdown
- Overvoltage protection (including load dump)
- Loss of ground protection
- Loss of V_{bb} protection (with external diode for charged inductive loads)
- Very low standby current
- Fast demagnetisation of inductive loads
- Electrostatic discharge (ESD) protection
- Optimized static electromagnetic compatibility (EMC)
- Green product (RoHS compliant)
- AEC qualified

Diagnostic Function


• Proportional load current sense (with defined fault signal during thermal shutdown)


Application


- Power switch with current sense diagnostic feedback for 12V and 24 V DC grounded loads
- All types of resistive, capacitive and inductive loads (no PWM with inductive loads)
- Replaces electromechanical relays, fuses and discrete circuits

General Description

N channel vertical power FET with charge pump, current controlled input and diagnostic feedback with load current sense, integrated in Smart SIPMOS® chip on chip technology. Providing embedded protective functions.









PROFET® BTS 443 P

| Pin | Symbol | | Function |
|---------|--------|---|---|
| 1 | OUT | 0 | Output to the load. The pin 1 and 5 must be shorted with each |
| | | | other especially in high current applications!*) |
| 2 | IN | Ι | Input, activates the power switch in case of short to ground |
| Tab/(3) | Vbb | + | Positive power supply voltage, the tab is shorted to this pin. |
| 4 | IS | S | Diagnostic feedback providing a sense current proportional to the load current; high current on failure (see Truth Table on page 6) |
| 5 | OUT | 0 | Output to the load. The pin 1 and 5 must be shorted with each |
| | | | other especially in high current applications!*) |

^{*)} Not shorting all outputs will considerably increase the on-state resistance, reduce the peak current capability and decrease the current sense accuracy

Maximum Ratings at $T_j = 25$ °C unless otherwise specified

| Parameter | Symbol | Values | Unit |
|--|--------------------------------------|--------------|------|
| Supply voltage (overvoltage protection see page 4) | $V_{ m bb}$ | 36 | V |
| Supply voltage for full short circuit protection | $V_{ m bb}$ | 241) | V |
| (see also diagram on page 9) T_j =-40150 °C: | | | |
| Load dump protection $V_{\text{LoadDump}} = U_{\text{A}} + V_{\text{S}}$, $U_{\text{A}} = 13.5 \text{ V}$ $R_{\text{I}} = 2 \Omega$, $R_{\text{L}} = 2.7 \Omega$, $t_{\text{d}} = 200 \text{ ms}$, IN= low or high | V _{Load dump} ²⁾ | 60 | V |
| Load current (Short-circuit current, see page 4) | <i>I</i> L | self-limited | Α |
| Operating temperature range | $T_{\rm j}$ | -40+150 | °C |
| Storage temperature range | T_{stg} | -55+150 | |
| Power dissipation (DC) TC ≤ 25°C | P _{tot} | 42 | W |
| Inductive load switch-off energy dissipation, single pulse U=12V, I=10A, L=3mH T_j =150 °C: | E _{AS} | 0.15 | J |
| Electrostatic discharge capability (ESD) (Human Body Model) acc. ESD assn. std. S5.1-1993; R=1.5kΩ; C=100pF | V _{ESD} | 4.0 | kV |
| Current through input pin (DC) | I _{IN} | +15, -100 | mA |
| Current through current sense pin (DC) | IIS | +15, -100 | |
| see internal circuit diagrams page 7 | | | |

Data Sheet Page 2 of 13 Rev. 1.0, 2007-02

¹⁾ Short circuit is tested with $100m\Omega$ and $20\mu H$

²⁾ V_{Load dump} is set-up without the DUT connected to the generator per ISO 7637-1 and DIN 40839



Thermal Characteristics

| Parameter and Conditions | Symbol | Values | | | Unit | |
|--------------------------|-----------------------|---------------------|-----|-----|------|-----|
| | | _ | min | typ | max | |
| Thermal resistance | chip - case: | $R_{\rm thJC}^{3)}$ | | - | 1.5 | K/W |
| • | | R_{thJA} | | 80 | | |
| SMD versi | ion, device on PCB4): | | | 45 | | |

Electrical Characteristics

| Parameter and Conditions | Symbol | ol Values | | ; | Unit |
|---|--------|-----------|-----|-----|------|
| at T_j = -40°C150°C, V_{bb} = 12 V unless otherwise specified | | min | typ | max | · |

Load Switching Capabilities and Characteristics

| 9 1 | | | | | |
|---|------------------------|-----|-----|-----|------|
| On-state resistance (pin 3 to pin 1,5) | | | | | |
| $V_{\text{IN}} = 0, I_{\text{L}} = 5 \text{ A}$ $T_{\text{j}} = 25 ^{\circ}\text{C}$: | Ron | | 13 | 16 | mΩ |
| <i>T</i> j=150 °C: | | | 25 | 31 | |
| Output voltage drop limitation at small load currents (Tab to pin 1,5) $T_{j=-40150}$ °C: | V _{ON(NL)} | | 50 | | mV |
| Nominal load current (Tab to pin 1,5) | | | | | Α |
| ISO Proposal: T_C =85°C, $V_{ON} \le 0.5 \text{V}$, $T_j \le 150$ °C | I _{L(ISO)} | 21 | 25 | | |
| SMD 4): T_A =85°C, $V_{ON} \le 0.5 \text{V}$, $T_j \le 150$ °C | $I_{L(nom)}$ | 6.2 | 7.6 | | |
| Turn-on time I _{IN} to 90% V _{OUT} : | <i>t</i> on | 150 | | 410 | μs |
| Turn-off time $I_{IN} \perp$ to 10% V_{OUT} : | $t_{ m off}$ | 70 | | 410 | |
| $R_{L} = 2.5\Omega$, T_{j} =-40150 °C | | | | | |
| Slew rate on | dV/dt _{on} | 0.1 | | 1 | V/µs |
| 10 to 30% V_{OUT} , $R_{\text{L}} = 2.5 \Omega$, T_{j} =-40150 °C | | | | | |
| Slew rate off 70 to 40% V_{OUT} , $R_{\text{L}} = 2.5 \ \Omega$, $T_{\text{j}} = -40150 \ ^{\circ}\text{C}$ | -d V/dt _{off} | 0.1 | | 1 | V/μs |

Data Sheet Page 3 of 13 Rev. 1.0, 2007-02

 $^{^{3)}}$ Thermal resistance R_{thCH} case to heatsink (about 0.5 ... 0.9 K/W with silicone paste) not included!

⁴⁾ Device on 50mm*50mm*1.5mm epoxy PCB FR4 with 6cm² (one layer, 70μm thick) copper area for V_{bb} connection. PCB is vertical without blown air.

| Parameter and Conditions | Symbol | | Values | } | Unit |
|---|--------|-----|--------|-----|------|
| at T_j = -40°C150°C, V_{bb} = 12 V unless otherwise specified | | min | typ | max | |

Operating Parameters

| Operating voltage (V _{IN} =0V) | | $V_{ m bb(on)}$ | 5.0 | | 36 | V |
|---|----------------------------------|----------------------|-----|-----|-----|----|
| Undervoltage shutdown 5) | | $V_{bIN(u)}$ | 1.5 | 3.0 | 4.5 | V |
| Undervoltage restart of charge pump (V _{IN} =0V) | | $V_{ m bb(ucp)}$ | 3.0 | 4.5 | 6.0 | V |
| Overvoltage protection 6) Ibb=15 mA | | $V_{Z,IN}$ | 61 | 68 | | V |
| Standby current | <i>T</i> _j =-40+25°C: | I _{bb(off)} | | 2 | 5 | μΑ |
| / _{IN} =0 | <i>T</i> _j =150°C: | | | 4 | 8 | |

Protection Functions 7)

| Short circuit current limit (Tab to pin 1,5) | | | | | |
|--|---------------------|----------------|----------------|-------------------|----|
| $V_{\rm ON}$ =8V, time until limitation max. 300 μ s | | | | | |
| τ _j =-40°C: τ _j =25°C: τ _j =+150°C: | I _{L(SC)} | 35 35 35 | 75 65 65 | 110 110 125 | Α |
| Repetitive short circuit current limit, $T_j = T_{jt}$ | I _{L(SCr)} | | 65 | | Α |
| Output clamp (inductive load switch off) at $V_{\text{OUT}} = V_{\text{bb}} - V_{\text{ON(CL)}}$ (e.g. overvoltage) $I_{\text{L}} = 40 \text{ mA}^{8}$ | $V_{ON(CL)}$ | 38 | 42 | 48 | V |
| Thermal overload trip temperature | T_{jt} | 150 | | | °C |
| Thermal hysteresis | $\Delta T_{\rm jt}$ | | 10 | | K |

Reverse Battery

| Reverse battery voltage | $-V_{ m bb}$ | - | 20 | V |
|--|----------------------|---------|----|-----------|
| On-state resistance (pin 1,5 to pin 3) | | | | |
| $V_{\rm bb} = -8V$, $V_{\rm IN} = 0$, $I_{\rm L} = -5$ A, $R_{\rm IS} = 1$ k Ω , $T_{\rm i} = 25$ °C: | R _{ON(rev)} | | 22 | $m\Omega$ |
| $V_{\rm bb}$ = -12V, $V_{\rm IN}$ = 0, $I_{\rm L}$ = -5 A, $R_{\rm IS}$ = 1 k Ω , $T_{\rm i}$ =25 °C: | | 16 | 19 | |
| <i>T</i> _j =150 °C: | | 25 | 32 | |
| Integrated resistor in $V_{\rm bb}$ line | R _{bb} | 200 | | Ω |

⁵⁾ VbIN=Vbb-VIN see diagram on page 11.

 $^{^{6)}}$ see also $V_{\mathrm{ON(CL)}}$ in circuit diagram on page 7.

⁷⁾ Integrated protection functions are designed to prevent IC destruction under fault condition described in the data sheet. Fault conditions are considered as "outside" normal operating range. Protection functions are not for continuous repetitive operation.

⁸⁾ see also page 12.



Diagnostic Characteristics

| Biagnostic Characteristics | | | | | | |
|---|---|---------------------------|--------------|--------------|---------------|----|
| Current sense ratio, static on- | condition | k _{ILIS} | | 8200 | | |
| $k_{\text{ILIS}} = I_{\text{L}} : I_{\text{IS}}$ $V_{\text{ON}} < 1.5 \text{ V}, V_{\text{IS}} < V_{\text{OUT}} - 5 \text{ V}, V_{\text{bin}}$ | ~ 1 E V 9) | | | | | |
| VON<1.5 V, VIS< VOUT-5 V, VIN | √>4.3 V °/ | | | | | |
| | $IL = 20A, Tj = -40^{\circ}C$: | | 7400 | 8300 | 9100 | |
| | Tj = +25°C: Tj = +150°C: | | 7500 7500 | 8300 8200 | 9100 8800 | |
| | $I_{J} = +150 \text{ C}$: $IL = 5A, T_{j} = -40 ^{\circ}\text{C}$: | | 6800 | 8300 | 9700 | |
| | $T_j = +25^{\circ}C$: | | 7200 | 8300 | 9300 | |
| | Tj = +150°C: | | 7200 | 8200 | 9000 | |
| I | L = 2.5A, $Tj = -40$ °C: | | 6800 | 8500 | 10000 | |
| | Tj = +25°C: | | 6800 | 8500 | 9800 | |
| | $Tj = +150^{\circ}C$: | | 6800 6800 | 8100 | 9200 10500 | |
| | IL = 1A, Tj = -40°C: Tj = +25°C: | | 6800 | 8600 8600 | 10500 | |
| | Tj = +150°C: | | 6800 | 8600 | 10500 | |
| $I_{IN} = 0$ (e.g. during de-energ | gising of inductive loads): | | | n.a. | | |
| Sense current under fault con- | ditions; | | | | | |
| <i>V</i> _{DS} >1.5V, typ. | T_{j} = -40+150°C: | I _{IS,fault} | 2.5 | 4 | | mA |
| Fault-Sense signal delay after | negative input slope | t _{delay(fault)} | | | 0.8 | ms |
| Current sense leakage current | t | | | | | |
| | $I_{IN} = 0$: | $I_{\rm IS(II)}$ | | | 0.5 | μΑ |
| | $V_{\rm IN} = 0, I_{\rm L} = 0$: | l ' ' | | 4 | 12 | |
| Current sense settling time to | | - () | | | | |
| positive input slope, $I_L = 0 \ \Box$ | | t _{son(IS)} | | | 400 | μs |
| | $T_{\rm j}$ = -40+150°C: | , , | | | | · |
| Overvoltage protection | | | | | | |
| $I_{bb} = 15 \mathrm{mA}$ | $T_{\rm j}$ = -40+150°C: | $V_{bIS(Z)}$ | 61 | 68 | | V |
| - | | | | | | |
| Input | | | | | ı | |
| Required current capability of | input switch $T_j = -40+150$ °C: | I _{IN(on)} | | 0.7 | 1.2 | mA |
| Maximum input current for turn | n-off T_j =-40+150°C: | I _{IN(off)} | | | 50 | μΑ |
| · | | | | | | |

Data Sheet Page 5 of 15 Rev. 1.0, 2007-02

⁹⁾ If V_{ON} is higher, the sense current is no longer proportional to the load current due to sense current saturation.

¹⁰) Not subject to production test, specified by design.




Truth Table

| | Input | Output | Current |
|----------------------|---------|--------|-------------------------------|
| | Current | | Sense |
| | level | level | lis |
| Normal | L | L | 0 |
| operation | Н | Н | nominal |
| Overload | L | L | 0 |
| | Н | Н | I _{ISfault} |
| Short circuit to GND | L | L | 0 |
| | Н | L | I _{ISfault} |
| Overtemperature | L | L | 0 |
| | Н | L | I _{ISfault} |
| Short circuit to Vbb | L | Н | 0 |
| | Н | Н | <nominal<sup>11</nominal<sup> |
| Open load | L | Z | 0 |
| | Н | Н | 0 |

L = "Low" Level H = "High" Level Z = high impedance, potential depends on external circuit

Terms




Two or more devices can easily be connected in parallel to increase load current capability.

Data Sheet Page 6 of 15 Rev. 1.0, 2007-02

¹¹⁾ Low ohmic short to $V_{
m bb}$ may reduce the output current $I_{
m L}$ and therefore also the sense current $I_{
m IS}$.




Input circuit (ESD protection)



ESD-Zener diode: 68 V typ., max 15 mA;

Current sense output

Normal operation




 $V_{\rm Z,IS}$ = 68 V (typ.), $R_{\rm IS}$ = 1 k Ω nominal (or 1 k Ω /n, if n devices are connected in parallel). $I_{\rm S} = I_{\rm L}/k_{\rm ilis}$ can be only driven by the internal circuit as long as $V_{\rm out}$ - $V_{\rm IS}$ > 5V. If you want to measure load currents

up to
$$I_{\rm L(M)}$$
, R_{IS} should be less than $\frac{V_{bb}-5V}{I_{L(M)}/K_{ilis}}$.


Note: For large values of $R_{\rm IS}$ the voltage $V_{\rm IS}$ can reach almost $V_{\rm bb}$. See also overvoltage protection. If you don't use the current sense output in your application, you can leave it open.

Inductive and overvoltage output clamp



 V_{ON} is clamped to $V_{ON(Cl)} = 42 \text{ V typ.}$


Overvoltage protection of logic part



 R_{bb} = 200 Ω typ., $V_{Z,IN}$ = $V_{Z,IS}$ = 68 V typ., R_{IS} = 1 k Ω nominal. Note that when overvoltage exceeds 73 V typ. a voltage above 5V can occur between IS and GND, if $R_{V},\,V_{Z,VIS}$ are not used.



Reversave™ (Reverse battery protection)



 $R_{V} \ge 1 k\Omega$, $R_{IS} = 1 k\Omega$ nominal. Add R_{IN} for reverse battery protection in applications with V_{bb} above 16V;


recommended value:
$$\frac{1}{R_{\text{IN}}} + \frac{1}{R_{\text{IS}}} + \frac{1}{R_{\text{V}}} = \frac{0.05A,}{|V_{bb}| - 12V}$$

To minimise power dissipation at reverse battery operation, the summarised current into the IN and IS pin should be about 50mA. The current can be provided by using a small signal diode D in parallel to the input switch, by using a MOSFET input switch or by proper adjusting the current through $R_{\rm IS}$ and $R_{\rm V.}$ Since the current through $R_{\rm bb}$ generates additional heat in the device, this has to be taken into account in the overall thermal considerations.


V_{bb} disconnect with energised inductive load

Provide a current path with load current capability by using a diode, a Z-diode, or a varistor. ($V_{\rm ZL}$ < 73 V or $V_{\rm Zb}$ < 30 V if R_{IN}=0). For higher clamp voltages currents at IN and IS have to be limited to 250 mA.

Version a:




Version b:



Note that there is no reverse battery protection when using a diode without additional Z-diode V_{ZL} , V_{Zb} .


Version c:

Sometimes a necessary voltage clamp is given by non inductive loads R_L connected to the same switch and eliminates the need of clamping circuit:





Inductive load switch-off energy dissipation



Energy stored in load inductance:

$$E_{L} = \frac{1}{2} \cdot L \cdot I_{L}^{2}$$

While demagnetising load inductance, the energy dissipated in PROFET is

$$E_{AS} = E_{bb} + E_L - E_R = \int V_{ON(CL)} \cdot i_L(t) dt$$


with an approximate solution for $R_L > 0 \Omega$:

$$E_{\text{AS}} = \frac{I_{\text{L}} \cdot L}{2 \cdot R_{\text{L}}} \left(V_{\text{bb}} + |V_{\text{OUT(CL)}}| \right) \ ln \ (1 + \frac{I_{\text{L}} \cdot R_{\text{L}}}{|V_{\text{OUT(CL)}}|} \right)$$

The device is not suitable for permanent PWM with inductive loads if active clamping occurs every cycle.

Maximum allowable load inductance for a single switch off


$$L = f(I_L)$$
; T_{j,start} = 150°C, V_{bb} = 12 V, R_L = 0 Ω





Timing diagrams

Figure 1a: Switching a resistive load, change of load current in on-condition:



The sense signal is not valid during a settling time after turn-on/off and after change of load current.

Figure 1b: typical behaviour of sense output:





Figure 2a: Switching motors and lamps:



Sense current above $I_{IS,fault}$ can occur at very high inrush currents.

Figure 2b: Switching an inductive load:






Figure 3a: Short circuit:




Figure 4a: Overtemperature Reset if $T_i < T_{jt}$




Figure 5a: Undervoltage restart of charge pump, overvoltage clamp






Figure 6a: Current sense versus load current:






Figure 6b: Current sense ratio¹²⁾:



 $^{^{12\,)}}$ This range for the current sense ratio refers to all devices. The accuracy of the $k_{\scriptscriptstyle \rm ILIS}$ can be raised by means of calibration the value of $k_{\scriptscriptstyle \rm ILIS}$ for every single device.

Figure 7a: Output voltage drop versus load current:






Package Outlines

All dimensions in mm

D-Pak-5 Pin: PG-TO252-5-11

Sales Code BTS 443P



Green Product

To meet the world-wide customer requirements for environmentally friendly products and to be compliant with government regulations the device is available as a green product. Green products are RoHS-Compliant (i.e Pbfree finish on leads and suitable for Pb-free soldering according to IPC/JEDEC J-STD-020).



PROFET® BTS 443 P

Revision History

| Version | Date | Changes |
|----------|------------|--|
| Rev. 1.0 | 2007-02-21 | RoHS-compliant version of BTS443P |
| | | Page 1, page 13: RoHS compliance statement and Green product feature added |
| | | Page 1, page 13: Change to RoHS compliant package PG-TO252-5-11 |
| | | Legal disclaimer updated |

Edition 2007-02

Published by
Infineon Technologies AG
81726 Munich, Germany
© Infineon Technologies AG 2007.
All Rights Reserved.

Legal Disclaimer

The information given in this document shall in no event be regarded as a guarantee of conditions or characteristics ("Beschaffenheitsgarantie"). With respect to any examples or hints given herein, any typical values stated herein and/or any information regarding the application of the device, Infineon Technologies hereby disclaims any and all warranties and liabilities of any kind, including without limitation warranties of non-infringement of intellectual property rights of any third party.

Information

For further information on technology, delivery terms and conditions and prices please contact your nearest Infineon Technologies Office (www.infineon.com).

Warnings

Due to technical requirements components may contain dangerous substances. For information on the types in question please contact your nearest Infineon Technologies Office.

Infineon Technologies Components may only be used in life-support devices or systems with the express written approval of Infineon Technologies, if a failure of such components can reasonably be expected to cause the failure of that life-support device or system, or to affect the safety or effectiveness of that device or system. Life support devices or systems are intended to be implanted in the human body, or to support and/or maintain and sustain and/or protect human life. If they fail, it is reasonable to assume that the health of the user or other persons may be endangered.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Infineon:

BTS443P BTS443PAUMA1