

#### Is Now Part of



## ON Semiconductor®

# To learn more about ON Semiconductor, please visit our website at www.onsemi.com

Please note: As part of the Fairchild Semiconductor integration, some of the Fairchild orderable part numbers will need to change in order to meet ON Semiconductor's system requirements. Since the ON Semiconductor product management systems do not have the ability to manage part nomenclature that utilizes an underscore (\_), the underscore (\_) in the Fairchild part numbers will be changed to a dash (-). This document may contain device numbers with an underscore (\_). Please check the ON Semiconductor website to verify the updated device numbers. The most current and up-to-date ordering information can be found at <a href="www.onsemi.com">www.onsemi.com</a>. Please email any questions regarding the system integration to Fairchild <a href="guestions@onsemi.com">guestions@onsemi.com</a>.

ON Semiconductor and the ON Semiconductor logo are trademarks of Semiconductor Components Industries, LLC dba ON Semiconductor or its subsidiaries in the United States and/or other countries. ON Semiconductor owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of ON Semiconductor's product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marking.pdf. ON Semiconductor reserves the right to make changes without further notice to any products herein. ON Semiconductor makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does ON Semiconductor assume any liability of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using ON Semiconductor products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by ON Semiconductor. "Typical" parameters which may be provided in ON Semiconductor data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. ON Semiconductor does not convey any license under its patent rights nor the rights of others. ON Semiconductor products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use ON Semiconductor products for any such unintended or unauthorized application, Buyer shall indemnify and hold ON Semiconductor and its officers, employees



June 1993 Revised April 2005

#### 74LVX573

### Low Voltage Octal Latch with 3-STATE Outputs

#### **General Description**

The LVX573 is a high-speed octal latch with buffered common Latch Enable (LE) and buffered common Output Enable ( $\overline{\text{OE}}$ ) inputs. The LVX573 is functionally identical to the LVX373 but with inputs and outputs on opposite sides of the package. The inputs tolerate up to 7V allowing interface of 5V systems to 3V systems.

#### **Features**


- Input voltage translation from 5V to 3V
- Ideal for low power/low noise 3.3V applications
- Guaranteed simultaneous switching noise level and dynamic threshold performance

#### **Ordering Code:**

Order Number	Package Number	Package Description
74LVX573M	M20B	20-Lead Small Outline Integrated Circuit (SOIC), JEDEC MS-013, 0.300" Wide
74LVX573SJ	M20D	Pb-Free 20-Lead Small Outline Package (SOP), EIAJ TYPE II, 5.3mm Wide
74LVX573MTC	MTC20	20-Lead Thin Shrink Small Outline Package (TSSOP), JEDEC MO-153, 4.4mm Wide

Devices also available in Tape and Reel. Specify by appending suffix letter "X" to the ordering code. Pb-Free package per JEDEC J-STD-020B.

#### **Logic Symbols**




#### **Connection Diagram**



### **Pin Descriptions**

Pin Names	Description
D <sub>0</sub> –D <sub>7</sub>	Data Inputs
LE	Latch Enable Input
ŌĒ	3-STATE Output Enable Input
O <sub>0</sub> -O <sub>7</sub>	3-STATE Latch Outputs



#### **Functional Description**


The LVX573 contains eight D-type latches. When the enable (LE) input is HIGH, data on the  $\ensuremath{D_n}$  inputs enters the latches. In this condition the latches are transparent, i.e., a latch output will change state each time its D input changes. When LE is LOW the latches store the information that was present on the D inputs a setup time preceding the HIGH-to-LOW transition of LE. The  $\underline{\mbox{ 3-STATE}}$ buffers are controlled by the Output Enable (OE) input. When  $\overline{OE}$  is LOW, the buffers are enabled. When  $\overline{OE}$  is HIGH the buffers are in the high impedance mode but this does not interfere with entering new data into the latches.

#### **Truth Table**

	Inputs					
ŌĒ	LE	D	O <sub>n</sub>			
L	Н	Н	Н			
L	Н	L	L			
L	L	X	O <sub>0</sub>			
Н	X	X	Z			

- H = HIGH Voltage
- L = LOW Voltage Z = High Impedance
- $O_0 = \hbox{Previous} \ O_0 \ \hbox{before HIGH-to-LOW transition of Latch Enable}$

#### **Logic Diagram**



Please note that this diagram is provided only for the understanding of logic operations and should not be used to estimate propagation delays

#### **Absolute Maximum Ratings**(Note 1)

Supply Voltage ( $V_{CC}$ ) -0.5V to +7.0V

DC Input Diode Current (I<sub>IK</sub>)

 $V_{I} = -0.5 V \\ DC \ Input \ Voltage \ (V_{I}) \\ -0.5 V \ to \ 7 V$ 

DC Output Diode Current (I<sub>OK</sub>)

 $\begin{array}{ll} \mbox{V}_{\mbox{O}} = -0.5 \mbox{V} & -20 \mbox{ mA} \\ \mbox{V}_{\mbox{O}} = \mbox{V}_{\mbox{CC}} + 0.5 \mbox{V} & +20 \mbox{ mA} \end{array}$ 

DC Output Voltage ( $V_{O}$ ) -0.5V to  $V_{CC} + 0.5V$ 

DC Output Source

or Sink Current ( $I_O$ )  $\pm 25$  mA

DC V<sub>CC</sub> or Ground Current

 $\begin{array}{ll} (I_{CC} \mbox{ or } I_{GND}) & \pm 75 \mbox{ mA} \\ \mbox{Storage Temperature } (T_{STG}) & -65 \mbox{°C to } +150 \mbox{°C} \end{array}$ 

Power Dissipation 180 mW

# Recommended Operating Conditions (Note 2)

Note 1: The "Absolute Maximum Ratings" are those values beyond which the safety of the device cannot be guaranteed. The device should not be operated at these limits. The parametric values defined in the Electrical Characteristics tables are not guaranteed at the absolute maximum ratings. The "Recommended Operating Conditions" table will define the conditions for actual device operation.

Note 2: Unused inputs must be held HIGH or LOW. They may not float.

#### **DC Electrical Characteristics**

Symbol	Parameter	v <sub>cc</sub>	T <sub>A</sub> = +25°C		$T_A = -40^{\circ}C \text{ to } +85^{\circ}C$		Units	Conditions		
Cymbol	i di dilletei		Min	Тур	Max	Min	Max	Office	Conditions	
V <sub>IH</sub>	HIGH Level	2.0	1.5			1.5				
	Input Voltage	3.0	2.0			2.0		V		
		3.6	2.4			2.4				
V <sub>IL</sub>	LOW Level	2.0			0.5		0.5			
	Input Voltage	3.0			0.8		0.8	V		
		3.6			0.8		0.8			
V <sub>OH</sub>	HIGH Level	2.0	1.9	2.0		1.9			$V_{IN} = V_{IH} \text{ or } V_{IL}   I_{OH} = -50  \mu\text{A}$	
	Output Voltage	3.0	2.9	3.0		2.9		V	$V_{IN} = V_{IH}$ or $V_{IL}$ $I_{OH} = -50$ μA $I_{OH} = -50$ μA	
		3.0	2.58			2.48			$I_{OH} = -4 \text{ mA}$	
V <sub>OL</sub>	LOW Level	2.0		0.0	0.1		0.1		$V_{IN} = V_{IH} \text{ or } V_{IL}  I_{OL} = 50  \mu\text{A}$	
	Output Voltage	3.0		0.0	0.1		0.1	V	$I_{OL} = 50 \mu A$	
		3.0			0.36		0.44		I <sub>OL</sub> = 4 mA	
I <sub>OZ</sub>	3-STATE Output	3.6			±0.25		±2.5	μΑ	$V_{IN} = V_{IH}$ or $V_{IL}$	
	Off-State Current								V <sub>OUT</sub> = V <sub>CC</sub> or GND	
I <sub>IN</sub>	Input Leakage Current	3.6			±0.1		±1.0	μΑ	V <sub>IN</sub> = 5.5V or GND	
I <sub>CC</sub>	Quiescent Supply Current	3.6			4.0		40.0	μΑ	V <sub>IN</sub> = V <sub>CC</sub> or GND	

#### **Noise Characteristics** (Note 3)

Symbol	Parameter	V <sub>CC</sub>	T <sub>A</sub> = 25°C		Units	C <sub>L</sub> (pF)	
	1 414.110151		Тур	Limit			
V <sub>OLP</sub>	Quiet Output Maximum Dynamic V <sub>OL</sub>		0.5	0.8	V	50	
V <sub>OLV</sub>	Quiet Output Minimum Dynamic V <sub>OL</sub>		-0.5	-0.8	V	50	
V <sub>IHD</sub>	Minimum HIGH Level Dynamic Input Voltage	3.3		2.0	V	50	
V <sub>ILD</sub>	Maximum LOW Level Dynamic Input Voltage			0.8	V	50	

Note 3: (Input  $t_r = t_f = 3ns$ )

www.fairchildsemi.com

#### **AC Electrical Characteristics**

Symbol	Parameter	v <sub>cc</sub>	T <sub>A</sub> = +25°C		$T_A = -40$ °C to $+85$ °C		Units	Conditions	
Cyb01		(V)	Min	Тур	Max	Min	Max	Units	Conditions
t <sub>PLH</sub>	Propagation	2.7		7.6	14.5	1.0	17.5		C <sub>L</sub> = 15 pF
t <sub>PHL</sub>	Delay Time			10.1	18.0	1.0	21.0	ns	C <sub>L</sub> = 50 pF
	D <sub>n</sub> to O <sub>n</sub>	$3.3 \pm 0.3$		5.9	9.3	1.0	11.0	115	C <sub>L</sub> = 15 pF
				8.4	12.8	1.0	14.5		C <sub>L</sub> = 50 pF
t <sub>PLH</sub>	Propagation	2.7		8.2	15.6	1.0	18.5		C <sub>L</sub> = 15 pF
t <sub>PHL</sub>	Delay Time			10.7	19.1	1.0	22.0	ns	C <sub>L</sub> = 50 pF
	LE to O <sub>n</sub>	$3.3 \pm 0.3$		6.4	10.1	1.0	12.0	ns	C <sub>L</sub> = 15 pF
				8.9	13.6	1.0	15.5		C <sub>L</sub> = 50 pF
$t_{PZL}$	3-STATE Output	2.7		7.8	15.0	1.0	18.5		$C_L = 15 \text{ pF}, R_L = 1 \text{ k}\Omega$
t <sub>PZH</sub>	Enable Time	Ī		10.3	18.5	1.0	22.0	ns	$C_L = 50 \text{ pF}, R_L = 1 \text{ k}\Omega$
		$3.3 \pm 0.3$		6.1	9.7	1.0	12.0	115	$C_L = 15 \text{ pF}, R_L = 1 \text{ k}\Omega$
				8.6	13.2	1.0	15.5		$C_L = 50 \text{ pF}, R_L = 1 \text{ k}\Omega$
t <sub>PLZ</sub>	3-STATE Output	2.7		12.1	19.1	1.0	22.0	ns	$C_L = 50 \text{ pF}, R_L = 1 \text{ k}\Omega$
t <sub>PHZ</sub>	Disable Time	$3.3 \pm 0.3$		10.1	13.6	1.0	15.5	115	$C_L = 50 \text{ pF}, R_L = 1 \text{ k}\Omega$
t <sub>W</sub>	LE Pulse	2.7	6.5			7.5		ns	
	Width	$3.3 \pm 0.3$	5.0			5.0		115	
t <sub>S</sub>	Setup Time	2.7	5.0			5.0		ns	
	D <sub>n</sub> to LE	$3.3 \pm 0.3$	3.5			3.5		115	
t <sub>H</sub>	Hold Time	2.7	1.5			1.5		ns	
	D <sub>n</sub> to LE	$3.3 \pm 0.3$	1.5			1.5		115	
t <sub>OSHL</sub>	Output to Output	2.7			1.5		1.5	ns	C <sub>L</sub> = 50 pF
toslh	Skew (Note 4)	2.3			1.5		1.5	115	


Note 4: Parameter guaranteed by design.  $t_{OSLH} = |t_{PLHm} - t_{PLHn}|, t_{OSHL} = |t_{PHLm} - t_{PHLn}|.$ 

#### Capacitance


Symbol	Parameter		T <sub>A</sub> = +25°C		T <sub>A</sub> = -40°0	Units	
		Min	Тур	Max	Min	Max	Oilles
C <sub>IN</sub>	Input Capacitance		4	10		10	pF
C <sub>OUT</sub>	Output Capacitance		6				pF
C <sub>PD</sub>	Power Dissipation		27				pF
	Capacitance (Note 5)						

Note 5: C<sub>PD</sub> is defined as the value of the internal equivalent capacitance which is calculated from the operating current consumption without load.


Average operating current can be obtained by the equation:  $I_{CC(opr.)} = \frac{C_{PD} \times V_{CC} \times f_{|N} + I_{CC}}{8 \text{ (per latch)}}$ 









#### Physical Dimensions inches (millimeters) unless otherwise noted (Continued)









DIMENSIONS ARE IN MILLIMETERS

A. CONFORMS TO JEDEC REGISTRATION MO-153, VARIATION AC, REF NOTE 6. DATE 7/93.

- B. DIMENSIONS ARE IN MILLIMETERS.
- C. DIMENSIONS ARE EXCLUSIVE OF BURRS, MOLDS FLASH, AND TIE BAR EXTRUSIONS.
- D. DIMENSIONS AND TOLERANCES PER ANSI Y14.5M, 1982.

# 

DETAIL A

MTC20REVD1

NOTES:

### 20-Lead Thin Shrink Small Outline Package (TSSOP), JEDEC MO-153, 4.4mm Wide Package Number MTC20

Fairchild does not assume any responsibility for use of any circuitry described, no circuit patent licenses are implied and Fairchild reserves the right at any time without notice to change said circuitry and specifications.

#### LIFE SUPPORT POLICY

FAIRCHILD'S PRODUCTS ARE NOT AUTHORIZED FOR USE AS CRITICAL COMPONENTS IN LIFE SUPPORT DEVICES OR SYSTEMS WITHOUT THE EXPRESS WRITTEN APPROVAL OF THE PRESIDENT OF FAIRCHILD SEMICONDUCTOR CORPORATION. As used herein:

7

- Life support devices or systems are devices or systems which, (a) are intended for surgical implant into the body, or (b) support or sustain life, and (c) whose failure to perform when properly used in accordance with instructions for use provided in the labeling, can be reasonably expected to result in a significant injury to the user.
- A critical component in any component of a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or system, or to affect its safety or effectiveness.

www.fairchildsemi.com

ON Semiconductor and in are trademarks of Semiconductor Components Industries, LLC dba ON Semiconductor or its subsidiaries in the United States and/or other countries. ON Semiconductor owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of ON Semiconductor's product/patent coverage may be accessed at <a href="www.onsemi.com/site/pdf/Patent-Marking.pdf">www.onsemi.com/site/pdf/Patent-Marking.pdf</a>. ON Semiconductor reserves the right to make changes without further notice to any products herein. ON Semiconductor makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does ON Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using ON Semiconductor products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by ON Semiconductor. "Typical" parameters which may be provided in ON Semiconductor data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. ON Semiconductor does not convey any license under its patent rights nor the rights of others. ON Semiconductor products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use ON Semiconductor products for any such unintended or unauthorized application, Buyer shall indemnify and hol

#### **PUBLICATION ORDERING INFORMATION**

#### LITERATURE FULFILLMENT:

Literature Distribution Center for ON Semiconductor 19521 E. 32nd Pkwy, Aurora, Colorado 80011 USA Phone: 303-675-2175 or 800-344-3860 Toll Free USA/Canada Fax: 303-675-2176 or 800-344-3867 Toll Free USA/Canada Email: orderlit@onsemi.com N. American Technical Support: 800–282–9855 Toll Free USA/Canada
Europe, Middle East and Africa Technical Support:
Phone: 421 33 790 2910

Phone: 421 33 790 2910

Japan Customer Focus Center

Phone: 81–3–5817–1050

ON Semiconductor Website: www.onsemi.com

Order Literature: http://www.onsemi.com/orderlit

For additional information, please contact your local Sales Representative

© Semiconductor Components Industries, LLC

www.onsemi.com