HUBER+SUHNER[®] DATA SHEET Between Series Adapter: 31_N-SMA-50-51/1--_N



Description

Adaptor jack/jack N-precision jack (female) / SMA-precision

Interface standards IEC 60169-16_MIL-STD-348A/402_CECC 22210

Technical Data

Electrical Data

Electrical Length

Mechanical Data

Number of matings Weight 500 0.0331 kg

13 °C to 33 °C

compliant

32.97 mm +/- 0.1

Environmental Data

Operating Temperature 2002/95/EC (RoHS)

Material Data

Piece Parts (N-precision) Centre contact Outer contact Body Insulator

Piece Parts (SMA-precision) Centre contact Outer contact Body Insulator

Related Documents

Ordering Information

Single package

Material Copper Beryllium Alloy Stainless Steel Stainless Steel PFA / PTFE

Material Copper Beryllium Alloy Copper Beryllium Alloy Copper Beryllium Alloy

31 N-SMA-50-51/1-- NE



Surface Plating

Gold Plating (Nickel underplated) Passivated (Plating) Passivated (Plating)

Surface Plating

Gold Plating (Nickel underplated) Gold Plating (Nickel underplated)

HUBER+SUHNER is certified according to ISO 9001 and ISO 14001

WAIVER!

It is exclusively in written agreements that we provide our customers with warrants and representations as to the technical contained specifications and/or the fitness for any particular purpose. The facts and figures herein are carefully compiled to the best of our knowledge, but they are intended for general informational purposes only.

HUBER+SUHNER – Excellence in Connectivity Solutions

Document: DOC-0000195561 L



Uncontrolled Copy

 HUBER+SUHNER AG

 RF Technology

 9100 Herisau, Switzerland

 Phone
 +41 (0)71 353 41 11

 Fax
 +41 (0)71 353 45 90

 www.hubersuhner.com