

G1/2 Electric Solenoid Valve



This is a normally open G1/2 12VDC electric solenoid valves with barbed inlet and outlet ports, great for projects involving low viscosity fluid control. You can find it ubiquitous on applications like automatic faucets, foot operated faucets, drinking fountains etc.

Features

- Durable
- Stainless steel inlet filter
- Wide operation temperature range

Specifications

- Working voltage: 12VDC
- Max current: 450mA
- Inlet/Outlet ports: G1/2"
- Materials: nylon/ stainless steel/Polyoxymethylene
- Valve type: diaphragm valve (operated by servo)
- Filter screen: stainless steel inlet filter
- Max operating temperature: 120°C
- Operating pressure range: 0.02 – 0.8 MPa