

3,500 to 4,500

5.5



BERGQUIST SIL PAD TSP 900

Dielectric Breakdown Voltage, ASTM D149, Vac

Dielectric Constant, ASTM D150 @ 1,000 Hz

Electrical Properties

Known as BERGQUIST SIL-PAD 400 October 2018

PRODUCT DESCRIPTION

The Original Sil-Pad® Material.

Technology	Silicone
Appearance	Gray
Reinforcement Carrier	Fiberglass
Total Thickness	0.178, 0.229mm
Application	Thermal management, Thermally conductive adhesive
Operating Temperature Range	-60 to 180°C

FEATURES AND BENEFITS

- Thermal impedance: 1.13°C-in²/W @ 50 psi
- Original Sil-Pad material
- Excellent mechanical and physical characteristics
- Flame retardant

TYPICAL APPLICATIONS

- Power supplies
- Automotive electronics
- Power semiconductors
- Motor controls

BERGQUIST SIL PAD TSP 900 is a composite of silicone rubber and fiberglass. The material is flame retardant and is specially formulated for use as a thermally conductive insulator . The primary use for BERGQUIST SIL PAD TSP 900 is to electrically isolate power sources from heat sinks.

BERGQUIST SIL PAD TSP 900 has excellent mechanical and physical characteristics. Surfaces are pliable and allow complete surface contact with excellent heat dissipation.

BERGQUIST SIL PAD TSP 900 actually improves its thermal resistance with age. The reinforcing fiberglass provides excellent cut-through resistance. In addition, BERGQUIST SIL PAD TSP 900 is non-toxic and resists damage from cleaning agents.

TYPICAL PROPERTIES

Physical Properties

Hardness, Shore A, ASTM D2240	
Breaking Strength, ASTM D1458, KN/m	5
Elongation , 45° to warp and fill, ASTM D412,%	54
Tensile Strength, ASTM D412, MPa	20
Flammability Rating, UL 94	V-0

Volume Resistivity, ASTM D257, ohm-meter	1×10 ¹¹
Thermal Properties Thermal Conductivity , ASTM D5470, W/(m-K)	0.9
Thermal Performance vs. Pressure TO-220 Thermal Performance, °C/W @ 0.007":	
@ 10 psi @ 25 psi	6.62 5.93
@ 50 psi @ 100 psi	5.14 4.38
@ 200 psi @ 0.009":	3.61
@ 10 psi @ 25 psi	8.51 7.62
@ 50 psi @ 100 psi @ 200 psi	6.61 5.63 4.64
@ 200 psi	4.04

hermal Impedance, ASTM D5470, °C-in²/W (1)	
@ 0.007":	
@ 10 psi	1.82
@ 25 psi	1.42
@ 50 psi	1.13
@ 100 psi	0.82
@ 200 psi	0.54
@ 0.009":	
@ 10 psi	2.34
@ 25 psi	1.83
@ 50 psi	1.45
@ 100 psi	1.05
@ 200 psi	0.69

I) The ASTM D5470 test fixture was used. The recorded value includes interfacial thermal resistance. These values are provided for reference only. Actual application performance is directly related to the surface roughness, flatness and pressure applied.

GENERAL INFORMATION

For safe handling information on this product, consult the Safety Data Sheet, (SDS).



Not for product specifications

The technical data contained herein are intended as reference only. Please contact your local quality department for assistance and recommendations on specifications for this product.

CONFIGURATIONS AVAILABLE

BERGQUIST SIL PAD TSP 900 are supplied in:

 Sheet form, die-cut parts and roll form; with or without pressure sensitive adhesive

Conversions

(°C x 1.8) + 32 = °F kV/mm x 25.4 = V/mil mm / 25.4 = inches N x 0.225 = lb N/mm x 5.71 = lb/in psi x 145 = N/mm² MPa = N/mm² N·m x 8.851 = lb·in N·m x 0.738 = lb·ft N·mm x 0.142 = oz·in mPa·s = cP

Disclaimer

Note:

The information provided in this Technical Data Sheet (TDS) including the recommendations for use and application of the product are based on our knowledge and experience of the product as at the date of this TDS. The product can have a variety of different applications as well as differing application and working conditions in your environment that are beyond our control. Henkel is, therefore, not liable for the suitability of our product for the production processes and conditions in respect of which you use them, as well as the intended applications and results. We strongly recommend that you carry out your own prior trials to confirm such suitability of our product.

Any liability in respect of the information in the Technical Data Sheet or any other written or oral recommendation(s) regarding the concerned product is excluded, except if otherwise explicitly agreed and except in relation to death or personal injury caused by our negligence and any liability under any applicable mandatory product liability law.

In case products are delivered by Henkel Belgium NV, Henkel Electronic Materials NV, Henkel Nederland BV, Henkel Technologies France SAS and Henkel France SA please additionally note the following:

In case Henkel would be nevertheless held liable, on whatever legal ground, Henkel's liability will in no event exceed the amount of the concerned delivery.

In case products are delivered by Henkel Colombiana, S.A.S. the following disclaimer is applicable:

The information provided in this Technical Data Sheet (TDS) including the recommendations for use and application of the product are based on our knowledge and experience of the product as at the date of this TDS. Henkel is, therefore, not liable for the suitability of our product for the production processes and conditions in respect of which you use them, as well as the intended applications and results. We strongly recommend that you carry out your own prior trials to confirm such suitability of our product.

Any liability in respect of the information in the Technical Data Sheet or any other written or oral recommendation(s) regarding the concerned product is excluded, except if otherwise explicitly agreed and except in relation to death or personal injury caused by our negligence and any liability under any applicable mandatory product liability law.

In case products are delivered by Henkel Corporation, Resin Technology Group, Inc., or Henkel Canada Corporation, the following disclaimer is applicable:

The data contained herein are furnished for information only and are believed to be reliable. We cannot assume responsibility for the results obtained by others over whose methods we have no control. It is the user's responsibility to determine suitability for the user's purpose of any production methods mentioned herein and to adopt such precautions as may be advisable for the protection of property and of persons against any hazards that may be involved in the handling and use thereof. In light of the foregoing, Henkel Corporation specifically disclaims all warranties expressed or implied, including warranties of merchantability or fitness for a particular purpose, arising from sale or use of Henkel Corporation's products. Henkel Corporation specifically disclaims any liability for consequential or incidental damages of any kind, including lost profits. The discussion herein of various processes or compositions is not to be interpreted as representation that they are free from domination of patents owned by others or as a license under any Henkel

Corporation patents that may cover such processes or compositions. We recommend that each prospective user test his proposed application before repetitive use, using this data as a guide. This product may be covered by one or more United States or foreign patents or patent applications.

Trademark usage: [Except as otherwise noted] All trademarks in this document are trademarks and/or registered trademarks of Henkel and its affiliates in the U.S. and elsewhere.

Reference 1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Bergquist Company:

SP400-0.007-00-05 SP400-0.007-00-104 SP400-0.007-00-51 SP400-0.007-00-54 SP400-0.007-00-58 SP400-0.007-00-90 SP400-0.009-00-02 SP400-0.009-00-03 SP400-0.009-00-04 SP400-0.009-00-05 SP400-0.009-00-09 SP400-0.009-00-51 SP400-0.009-00-54 SP400-0.009-00-58 SP400-0.009-00-90 SP400-0.009-AC-54 SP400-0.009-00-45 3223-07FR-50 SP400-0.009-AC-102 SP400-0.009-AC-1212 SP400-0.007-00-1212 SP400-0.009-00-1212 SP400-0.009AC-44 SP400-0.007-AC-53 SP400-0.007-00-92 7403-09FR-85 SP400-0.007-AC-1212 7403-09FR-26 SP400-0.009-00-35 3223-07AC-54 SP400-0.007-00-5 SP400-0.009-00-3 SP400-0.009-00-9 SP400-0.007-00-10 SP400-0.007-00-100 SP400-0.007-00-101 SP400-0.007-00-102 SP400-0.007-AC-101 SP400-0.007-AC-102 SP400-0.007-AC-103 SP400-0.007-AC-104 SP400-0.007-AC-105 SP400-0.007-AC-11 SP400-0.007-AC-110 SP400-0.007-AC-111 SP400-0.007-AC-112 SP400-0.007-AC-113 SP400-0.007-AC-114 SP400-0.007-AC-115 SP400-0.007-AC-116 SP400-0.007-AC-117 SP400-0.007-AC-118 SP400-0.007-AC-119 SP400-0.007-AC-12 SP400-0.007-AC-120 SP400-0.007-AC-121 SP400-0.007-AC-122 SP400-0.007-AC-123 SP400-0.007-AC-124 SP400-0.007-AC-125 SP400-0.007-AC-126 SP400-0.007-AC-127 SP400-0.007-AC-128 SP400-0.007-AC-129 SP400-0.007-AC-13 SP400-0.007-AC-130 SP400-0.007-AC-131 SP400-0.007-AC-132 SP400-0.007-AC-133 SP400-0.007-AC-134 SP400-0.007-AC-135 SP400-0.007-AC-136 SP400-0.007-AC-137 SP400-0.007-AC-138 SP400-0.007-AC-15 SP400-0.007-AC-16 SP400-0.007-AC-17 SP400-0.007-AC-18 SP400-0.007-AC-19 SP400-0.007-AC-2 SP400-0.007-AC-20 SP400-0.007-AC-21 SP400-0.007-AC-22 SP400-0.007-AC-23 SP400-0.007-AC-24 SP400-0.007-AC-25 SP400-0.007-AC-26 SP400-0.007-AC-27 SP400-0.007-AC-28 SP400-0.009-AC-37 SP400-0.009-AC-38 SP400-0.009-AC-39 SP400-0.009-AC-4 SP400-0.009-AC-40 SP400-0.009-AC-41 SP400-0.009-AC-42 SP400-0.009-AC-43 SP400-0.009-AC-45 SP400-0.009-AC-46 SP400-0.009-AC-47