

General Information

ZK2.5-D2 **Extended Product Type:**

Product ID: 1SNK705210R0000 EAN: 3472597052101

Catalog Description: ZK2.5-D2 PI-Spring clamp Terminal Block - Double deck - Grey

Long Description: Combine high performance with compact dimensions: - 800 V IEC 600 V UL, - 2 jumper

channels and a large input and output marker zone on each deck.

Categories

Products » Low Voltage Products and Systems » Connection Devices » Terminal Blocks » SNK Series

Ordering

Minimum Order Quantity: 50 piece **Customs Tariff Number:** 85369010 Color: Grey

Dimensions

78.5 mm **Product Net Height: Product Net Length:** 60.2 mm **Product Net Depth:** 60.2 mm **Product Net Weight:** 11.2 g **Product Net Width:** 5.2 mm

Technical

Spacing: 5.2 mm **Connection Type:** PI Spring Function: Feed-through

Number of Levels:

Connecting Capacity Main Circuit: Spring Clamp / Flexible 1x 0.22 ... 2.5 mm²

Spring Clamp / Rigid 1x 0.2 ... 4 mm²

Spring Clamp / With Insulated Ferrrule 1x 0.22 ... 2.5 mm² Spring Clamp / Without Insulated Ferrule 1x 0.22 ... 2.5 mm² Spring Clamp / With Twin Ferrule 2x 0.22 ... 0.5 mm²

Gauge Type: A2 / 2.3 mm Dia. Rated Current (In): Main Circuit 24 A

Rated Short-time Withstand Current for 1 s 300 A

(I_{cw}):

800 V Rated Voltage (Ur): 8000 V Rated Impulse Withstand Voltage

(U_{imp}):

Pollution Degree: Power Loss: 1.6 W

Degree of Protection: acc. to IEC 60529, IEC 60947-1, EN 60529 Main Terminals IP20

Insulation Material: Polyamide

TH35-7.5 (35 x 7.5 mm Mounting Rail) acc. to IEC 60715 Mounting on DIN Rail: TH35-15 (35 x 15 mm Mounting Rail) acc. to IEC 60715

Wire Stripping Length: 11.0 mm Rated Cross-Section: 2.5 mm²

Technical UL/CSA

Spring Clamp / Rigid 1x 26 ... 12 AWG **Connecting Capacity Main Circuit**

UL/CSA: Spring Clamp / With Insulated Ferrule 1x 26 ... 14 AWG

Spring Clamp / Without Insulated Ferrule 1x 26 ... 14 AWG

Stranded 12 AWG Connecting Capacity UL/CSA:

Flammability According to UL94: Short-Circuit Current Rating (SCCR): 100 kA

Maximum Operating Voltage Main Circuit 600 V

UL/CSA:

Environmental

Resistance to Vibrations acc. to IEC Compliant

60068-2-6:

RoHS Status: Following EU Directive 2011/65/EC Ambient Air Temperature: Operation -55 ... +110 °C Storage -55 ... +110 °C

Certificates and Declarations (Document Number)

Instructions and Manuals:	1SNK160027C0201
ATEX Certificate:	1SND162009A1701
BV Certificate:	1SND162013A0202
CB Certificate:	1SND162020A0200
CSA Certificate:	1SND162014A0203
cUL Certificate:	1SND162012A0203
Data Sheet, Technical Information:	1SNK162037D0201
Declaration of Conformity - CE:	1SND225112U1000
DNV Certificate:	1SND162023A0200
EAC Certificate:	1SND161010A1100
RoHS Information:	1SND230535F0201

Classifications

ETIM 4:	EC000897 - Feed-through terminal block
ETIM 5:	EC000897 - Feed-through terminal block
ETIM 6:	EC000897 - Feed-through terminal block
Object Classification Code:	X

Container Information

Package Level 1 Width:	82 mm
Package Level 1 Length:	265 mm
Package Level 1 Height:	65 mm
Package Level 1 Gross Weight:	0.61 kg
Package Level 1 EAN:	3472597052101
Package Level 2 Units:	400 piece
Package Level 2 Width:	300 mm
Package Level 2 Length:	400 mm
Package Level 2 Height:	200 mm
Package Level 2 Gross Weight:	4.880 kg
Package Level 3 Units:	19200 piece
Product Packing Type:	Box
Package Level 1 Units:	50 piece

