

Customer Specification

PART NO. 6715

Construction

| | | Diameters (In) |
|----------------|---|----------------|
| 1) Component 1 | 1 X 1 HOOKUP | |
| a) Conductor | 18 (16/30) AWG Tinned Copper | 0.048 |
| b) Insulation | 0.0095" Wall, Nom. Modified Polyphenylene Ether | 0.067+/- 0.002 |
| (1) Print | ALPHA WIRE ECOWIRE TM 18 AWG E163869-DB RU AWM 11028 105C 600V VW-1 --- CRU AWM I A/B 105C 600V FT1 CE ROHS | |
| (2) Color(s) | WHITE, BLACK, RED, GREEN, YELLOW, BLUE, BROWN ORANGE, SLATE, VIOLET, GREEN/YELLOW, DARK BLUE WHITE/BLUE | |

Applicable Specifications

| | | |
|----------------------|-------------------------------------|------------------------------|
| 1) UL | AWM/STYLE 11028 | 105°C / 600 V _{RMS} |
| | VW-1 | |
| 2) CSA International | C(RU) AWM I A/B FT1 | 105°C / 600 V _{RMS} |
| 3) Other | Halogen-Free | |
| | IEC 60332-2 Flame Behavior | |
| 4) CE: | EU Low Voltage Directive 2006/95/EC | |

Environmental

| | |
|------------------------------------|--|
| 1) EU Directive 2011/65/EU(RoHS2): | |
| | All materials used in the manufacture of this part are in compliance with European Directive 2011/65/EU regarding the restriction of use of certain hazardous substances in electrical and electronic equipment. Consult Alpha |

| | |
|-------------------------------------|---|
| | Wire's web site for RoHS C of C. |
| 2) REACH Regulation (EC 1907/2006): | |
| | This product does not contain Substances of Very High Concern (SVHC) listed on the European Union's REACH candidate list in excess of 0.1% mass of the item. For up-to-date information, please see Alpha's REACH SVHC Declaration. |

Properties

| | |
|---|-----------------------------|
| Physical & Mechanical Properties | |
| 1) Temperature Range | -40 to 105°C |
| 2) Bend Radius | 10X Cable Diameter |
| 3) Pull Tension | 12.6 Lbs, Maximum |
| Electrical Properties (For Engineering purposes only) | |
| 1) Voltage Rating | 600 V _{RMS} |
| 2) Inductance | 0.04 µH/ft, Nominal |
| 3) Conductor DCR | 7.1 Ω/1000ft @20°C, Nominal |

Other

| | |
|---|---|
| Packaging | Flange x Traverse x Barrel (inches) |
| a) 25000 DR | 23 x 30 x 0 Max. 2 separate pieces; Min length/piece 5000 FT. |
| b) 5000 FT | 12 x 6 x 3.5 Continuous length |
| c) 1000 FT | 9 x 4.5 x 3.5 Continuous length |
| d) 100 FT | 3.75 x 2 x 1.75 Continuous length |
| | <i>[Spool dimensions may vary slightly]</i> |
| Notes: | |
| a) Certain colors and put-up combinations may only be available by special order, minimums may apply. | |

www.alphawire.com

Alpha Wire | 711 Ligerwood Avenue, Elizabeth, NJ 07207

Tel: 1-800-52 ALPHA (25742)

Although Alpha Wire ("Alpha") makes every reasonable effort to ensure there accuracy at the time of publication, information and specifications described herein are subject to errors or omissions and to changes without notice, and the listing of such information and specifications does not ensure product availability.

Alpha provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Alpha be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary) whatsoever, even if Alpha had been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

ALPHA WIRE - CONFIDENTIAL AND PROPRIETARY Notice to persons receiving this document and/or technical information. This document is confidential and is the exclusive property of ALPHA WIRE, and is merely on loan and subject to recall by ALPHA WIRE at any time. By taking possession of this document, the recipient acknowledges and agrees that this document cannot be used in any manner adverse to the interests of ALPHA WIRE, and that no portion of this document may be copied or otherwise reproduced without the prior written consent of ALPHA WIRE. In the case of conflicting contractual provisions, this notice shall govern the status of this document.

©2019 ALPHA WIRE - all rights reserved.



EU/China ROHS CERTIFICATE OF COMPLIANCE

To Whom It May Concern:

Alpha Wire Part Number: 6715

6715, RoHS-Compliant Commencing With 7/1/2009 Production

Note: all colors and put-ups

This document certifies that the Alpha part number cited above is manufactured in accordance with Directive 2011/65/EU of the European Parliament, better known as the RoHS Directive (commonly known as RoHS 2), with regards to restrictions of the use of certain hazardous substances used in the manufacture of electrical and electronic equipment. This certification extends to amending Directive 2015/863/EU which expanded the list of restricted substances to 10 items (commonly known as RoHS 3) The reader is referred to these Directives for the specific definitions and extents of the Directives. **No Exemptions are required for RoHS Compliance on this item.** Additionally, Alpha certifies that the listed part number is in compliance with China RoHS "Marking for Control of Pollution by Electronic Information Products" standard SJ/T 11364-2014.

| Substance | Maximum Control Value |
|---|---------------------------|
| Lead | 0.1% by weight (1000 ppm) |
| Mercury | 0.1% by weight (1000 ppm) |
| Cadmium | 0.01% by weight (100 ppm) |
| Hexavalent Chromium | 0.1% by weight (1000 ppm) |
| Polybrominated Biphenyls (PBB) | 0.1% by weight (1000 ppm) |
| Polybrominated Diphenyl Ethers (PBDE) , Including Deca-BDE | 0.1% by weight (1000 ppm) |
| Bis(2-ethylhexyl) phthalate (DEHP) | 0.1% by weight (1000 ppm) |
| Butyl benzyl phthalate (BBP) | 0.1% by weight (1000 ppm) |
| Dibutyl phthalate (DBP) | 0.1% by weight (1000 ppm) |
| Diisobutyl phthalate (DIBP) | 0.1% by weight (1000 ppm) |

The information provided in this document and disclosure is correct to the best of Alpha Wire's knowledge, information and belief at the date of its release. The information provided is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it will become part of. The intent of this document is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Authorized Signatory for the Alpha Wire:

Dave Watson, Director of Engineering & QA

9/29/2020

Alpha Wire

711 Lidgerwood Ave.

Elizabeth, NJ 07207

Tel: 1-908-925-8000

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Alpha Wire:

[6715 WH013](#) [6715 RD013](#) [6715 BR005](#) [6715 BK013](#) [6715 SL005](#) [6715 BR001](#) [6715 OR013](#) [6715 YL013](#) [6715 SL001](#) [6715 GR001](#) [6715 WH005](#) [6715 GR005](#) [6715 BR013](#) [6715 BK005](#) [6715 GR013](#) [6715 YL001](#) [6715 RD005](#) [6715 BL005](#) [6715 VI005](#) [6715 OR005](#) [6715 SL013](#) [6715 RD001](#) [6715 BL013](#) [6715 WH001](#) [6715 OR001](#) [6715 GY001](#) [6715 GY005](#) [6715 BK001](#) [6715 VI001](#) [6715 DB005](#) [6715 GY013](#) [6715 VI013](#) [6715 DB013](#) [6715 BL001](#) [6715 DB001](#) [6715 YL005](#) [6715 BK190](#) [6715 BL190](#) [6715 BR190](#) [6715 DB190](#) [6715 GR190](#) [6715 GY190](#) [6715 OR190](#) [6715 RD190](#) [6715 SL190](#) [6715 VI190](#) [6715 WH190](#) [6715 YL190](#) [6715 WU001](#) [6715 WU005](#) [6715 WU190](#) [6715 WU013](#)