

#### Important notice

Dear Customer,

On 7 February 2017 the former NXP Standard Product business became a new company with the tradename **Nexperia**. Nexperia is an industry leading supplier of Discrete, Logic and PowerMOS semiconductors with its focus on the automotive, industrial, computing, consumer and wearable application markets

In data sheets and application notes which still contain NXP or Philips Semiconductors references, use the references to Nexperia, as shown below.

Instead of <a href="http://www.nxp.com">http://www.nxp.com</a>, <a href="http://www.semiconductors.philips.com/">http://www.nxp.com</a>, <a href="http://www.nexperia.com/">http://www.nexperia.com/</a>, <a href="http://www.nexperia.com/">http://www.nexperia.com/</a>, <a href="http://www.nexperia.com/">use http://www.nexperia.com/</a>

Instead of sales.addresses@www.nxp.com or sales.addresses@www.semiconductors.philips.com, use salesaddresses@nexperia.com (email)

Replace the copyright notice at the bottom of each page or elsewhere in the document, depending on the version, as shown below:

- © NXP N.V. (year). All rights reserved or © Koninklijke Philips Electronics N.V. (year). All rights reserved

Should be replaced with:

- © Nexperia B.V. (year). All rights reserved.


If you have any questions related to the data sheet, please contact our nearest sales office via e-mail or telephone (details via **salesaddresses@nexperia.com**). Thank you for your cooperation and understanding,

Kind regards,

Team Nexperia

### **DISCRETE SEMICONDUCTORS**

# DATA SHEET



# BC856W; BC857W; BC858W PNP general purpose transistors

Product data sheet Supersedes data of 1999 Apr 12 2002 Feb 04



## PNP general purpose transistors

BC856W; BC857W;

**BC858W** 

#### **FEATURES**

• Low current (max. 100 mA)

• Low voltage (max. 65 V).

### **APPLICATIONS**

• General purpose switching and amplification.

#### **DESCRIPTION**

PNP transistor in a SOT323 plastic package. NPN complements: BC846W, BC847W and BC848W.

#### **MARKING**


TYPE NUMBER	MARKING CODE <sup>(1)</sup>
BC856W	3D*
BC856AW	3A*
BC856BW	3B*
BC857W	3H*
BC857AW	3E*
BC857BW	3F*
BC857CW	3G*
BC858W	3M*

#### Note

1. \* = -: made in Hong Kong.

### **PINNING**

PIN	DESCRIPTION		
1	base		
2	emitter		
3	collector		



<sup>\* =</sup> t: made in Malaysia.

# PNP general purpose transistors

BC856W; BC857W; BC858W

### **LIMITING VALUES**

In accordance with the Absolute Maximum System (IEC 60134).

SYMBOL	PARAMETER	CONDITIONS	MIN.	MAX.	UNIT
V <sub>CBO</sub>	collector-base voltage	open emitter			
	BC856W		_	-80	V
	BC857W		_	-50	V
	BC858W		_	-30	V
$V_{CEO}$	collector-emitter voltage	open base			
	BC856W		_	-65	V
	BC857W		_	-45	V
	BC858W		_	-30	V
V <sub>EBO</sub>	emitter-base voltage	open collector	_	-5	V
I <sub>C</sub>	collector current (DC)		_	-100	mA
I <sub>CM</sub>	peak collector current		_	-200	mA
I <sub>BM</sub>	peak base current		_	-200	mA
P <sub>tot</sub>	total power dissipation	T <sub>amb</sub> ≤ 25 °C; note 1	_	200	mW
T <sub>stg</sub>	storage temperature		-65	+150	°C
Tj	junction temperature		_	150	°C
T <sub>amb</sub>	operating ambient temperature		-65	+150	°C

### Note

### THERMAL CHARACTERISTICS

SYMBOL	PARAMETER	PARAMETER CONDITIONS		UNIT	
R <sub>th j-a</sub>	thermal resistance from junction to ambient	in free air; note 1	625	K/W	

### Note

1. Refer to SOT323 standard mounting conditions.

<sup>1.</sup> Refer to SOT323 standard mounting conditions.

# PNP general purpose transistors

BC856W; BC857W; BC858W

### **CHARACTERISTICS**

 $T_{amb}$  = 25 °C; unless otherwise specified.

SYMBOL	PARAMETER CONDITIONS		MIN.	TYP.	MAX.	UNIT
I <sub>CBO</sub>	collector-base cut-off current	$V_{CB} = -30 \text{ V}; I_E = 0$	-	-1	-15	nA
		$V_{CB} = -30 \text{ V}; I_{E} = 0;$ $T_{j} = 150 \text{ °C}$	_	_	-4	μΑ
I <sub>EBO</sub>	emitter-base cut-off current	$V_{EB} = -5 \text{ V}; I_C = 0$	_	_	-100	nA
h <sub>FE</sub>	DC current gain	$I_C = -2 \text{ mA}; V_{CE} = -5 \text{ V}$				
	BC856W		125	_	475	
	BC857W; BC858W		125	_	800	
	BC856AW; BC857AW		125	_	250	
	BC856BW; BC857BW		220	_	475	
	BC857CW		420	_	800	
V <sub>CEsat</sub>	collector-emitter saturation voltage	$I_C = -10 \text{ mA}; I_B = -0.5 \text{ mA}$	_	-75	-300	mV
		$I_C = -100 \text{ mA}; I_B = -5 \text{ mA};$ note 1	_	-250	-600	mV
V <sub>BEsat</sub>	base-emitter saturation voltage	$I_C = -10 \text{ mA}; I_B = -0.5 \text{ mA}$	_	-700	_	mV
		$I_C = -100 \text{ mA}; I_B = -5 \text{ mA};$ note 1	-	-850	_	mV
V <sub>BE</sub>	base-emitter voltage	$I_C = -2 \text{ mA}; V_{CE} = -5 \text{ V}$	-600	-650	-750	mV
		$I_C = -10 \text{ mA}; V_{CE} = -5 \text{ V}$	_	_	-820	mV
C <sub>c</sub>	collector capacitance	$V_{CB} = -10 \text{ V}; I_E = I_e = 0;$ f = 1 MHz	_	_	3	pF
C <sub>e</sub>	emitter capacitance $V_{EB} = -0.5 \text{ V}; I_C = I_c = f = 1 \text{ MHz}$		_	_	12	pF
f <sub>T</sub>	transition frequency	V <sub>CE</sub> = -5 V; I <sub>C</sub> = -10 mA; f = 100 MHz	100	_	-	MHz
F	noise figure	$\begin{split} I_{C} &= -200 \; \mu A; \; V_{CE} = -5 \; V; \\ R_{S} &= 2 \; k \Omega; \; f = 1 \; k Hz; \\ B &= 200 \; Hz \end{split}$	_	-	10	dB


### Note

1. Pulse test:  $t_p \le 300~\mu s;~\delta \le 0.02.$ 

2002 Feb 04

### PNP general purpose transistors


### BC856W; BC857W; BC858W



**BC857AW**;  $V_{CE} = -5 \text{ V}.$ 

- (1)  $T_{amb} = 150 \, ^{\circ}C$ .
- (2)  $T_{amb} = 25 \, ^{\circ}C$ .
- (3)  $T_{amb} = -55 \, ^{\circ}C$ .


Fig.2 DC current gain as a function of collector current; typical values.



**BC857AW**;  $V_{CE} = -5 \text{ V}$ .

- (1)  $T_{amb} = -55 \, ^{\circ}C$ .
- (2)  $T_{amb} = 25 \, ^{\circ}C$ .
- (3)  $T_{amb} = 150 \, ^{\circ}C$ .


Fig.3 Base-emitter voltage as a function of collector current; typical values.



**BC857AW**;  $I_C/I_B = 20$ .

- (1) T<sub>amb</sub> = 150 °C.
- (2)  $T_{amb} = 25 \, ^{\circ}C$ .
- (3)  $T_{amb} = -55 \,^{\circ}\text{C}$ .

Fig.4 Collector-emitter saturation voltage as a function of collector current; typical values.




**BC857AW**;  $I_C/I_B = 20$ .

- (1)  $T_{amb} = -55 \, ^{\circ}C$ .
- (2)  $T_{amb} = 25 \, ^{\circ}C$ .
- (3)  $T_{amb} = 150 \, ^{\circ}C$ .

Fig.5 Base-emitter saturation voltage as a function of collector current; typical values.

### PNP general purpose transistors


### BC856W; BC857W; BC858W



**BC857BW**;  $V_{CE} = -5 \text{ V}.$ 

- (1)  $T_{amb} = 150 \, ^{\circ}C$ .
- (2)  $T_{amb} = 25 \, ^{\circ}C$ .
- (3)  $T_{amb} = -55 \, ^{\circ}C$ .


Fig.6 DC current gain as a function of collector current; typical values.



**BC857BW**;  $V_{CE} = -5 \text{ V}$ .

- (1)  $T_{amb} = -55 \, ^{\circ}C$ .
- (2)  $T_{amb} = 25 \, ^{\circ}C$ .
- (3)  $T_{amb} = 150 \, ^{\circ}C$ .


Fig.7 Base-emitter voltage as a function of collector current; typical values.



**BC857BW**;  $I_C/I_B = 20$ .

- (1)  $T_{amb} = 150 \, ^{\circ}C$ .
- (2)  $T_{amb} = 25 \, ^{\circ}C$ .
- (3)  $T_{amb} = -55 \, ^{\circ}C$ .

Fig.8 Collector-emitter saturation voltage as a function of collector current; typical values.




BC857BW;  $I_C/I_B = 20$ .

- (1)  $T_{amb} = -55 \, ^{\circ}C$ .
- (2)  $T_{amb} = 25 \, ^{\circ}C$ .
- (3)  $T_{amb} = 150 \,^{\circ}\text{C}$ .

Fig.9 Base-emitter saturation voltage as a function of collector current; typical values.

### PNP general purpose transistors


### BC856W; BC857W; BC858W



**BC857CW**;  $V_{CE} = -5 \text{ V}.$ 

- (1)  $T_{amb} = 150 \, ^{\circ}C$ .
- (2)  $T_{amb} = 25 \, ^{\circ}C$ .
- (3)  $T_{amb} = -55 \, ^{\circ}C$ .


Fig.10 DC current gain as a function of collector current; typical values.



**BC857CW**;  $V_{CE} = -5 \text{ V}.$ 

- (1)  $T_{amb} = -55 \, ^{\circ}C$ .
- (2)  $T_{amb} = 25 \, ^{\circ}C$ .
- (3)  $T_{amb} = 150 \, ^{\circ}C$ .


Fig.11 Base-emitter voltage as a function of collector current; typical values.



**BC857CW**;  $I_C/I_B = 20$ .

- (1)  $T_{amb} = 150 \, ^{\circ}C$ .
- (2)  $T_{amb} = 25 \, ^{\circ}C$ .
- (3)  $T_{amb} = -55 \,^{\circ}\text{C}$ .

Fig.12 Collector-emitter saturation voltage as a function of collector current; typical values.



BC857CW;  $I_C/I_B = 20$ .

- (1)  $T_{amb} = -55 \, ^{\circ}C$ .
- (2)  $T_{amb} = 25 \, ^{\circ}C$ .
- (3)  $T_{amb} = 150 \, ^{\circ}C$ .

Fig.13 Base-emitter saturation voltage as a function of collector current; typical values.


# PNP general purpose transistors

BC856W; BC857W; BC858W

### **PACKAGE OUTLINE**

Plastic surface mounted package; 3 leads

**SOT323** 



OUTLINE	REFERENCES		EUROPEAN	ISSUE DATE		
VERSION	IEC	JEDEC	EIAJ		PROJECTION	1330E DATE
SOT323			SC-70			97-02-28

0.45

0.15

0.23 0.13

0.2

2002 Feb 04 8

0.25

0.10

0.4

1.1

mm

0.1

2.2

1.8

1.35

1.15

1.3

0.65

### PNP general purpose transistors

BC856W; BC857W; BC858W

#### **DATA SHEET STATUS**

DOCUMENT STATUS <sup>(1)</sup>	PRODUCT STATUS <sup>(2)</sup>	DEFINITION
Objective data sheet	Development	This document contains data from the objective specification for product development.
Preliminary data sheet	Qualification	This document contains data from the preliminary specification.
Product data sheet	Production	This document contains the product specification.

#### **Notes**

- 1. Please consult the most recently issued document before initiating or completing a design.
- The product status of device(s) described in this document may have changed since this document was published
  and may differ in case of multiple devices. The latest product status information is available on the Internet at
  URL http://www.nxp.com.

#### **DISCLAIMERS**

**General** — Information in this document is believed to be accurate and reliable. However, NXP Semiconductors does not give any representations or warranties, expressed or implied, as to the accuracy or completeness of such information and shall have no liability for the consequences of use of such information.

Right to make changes — NXP Semiconductors reserves the right to make changes to information published in this document, including without limitation specifications and product descriptions, at any time and without notice. This document supersedes and replaces all information supplied prior to the publication hereof.

Suitability for use — NXP Semiconductors products are not designed, authorized or warranted to be suitable for use in medical, military, aircraft, space or life support equipment, nor in applications where failure or malfunction of an NXP Semiconductors product can reasonably be expected to result in personal injury, death or severe property or environmental damage. NXP Semiconductors accepts no liability for inclusion and/or use of NXP Semiconductors products in such equipment or applications and therefore such inclusion and/or use is at the customer's own risk.

**Applications** — Applications that are described herein for any of these products are for illustrative purposes only. NXP Semiconductors makes no representation or warranty that such applications will be suitable for the specified use without further testing or modification.

Limiting values — Stress above one or more limiting values (as defined in the Absolute Maximum Ratings System of IEC 60134) may cause permanent damage to the device. Limiting values are stress ratings only and operation of the device at these or any other conditions

above those given in the Characteristics sections of this document is not implied. Exposure to limiting values for extended periods may affect device reliability.

Terms and conditions of sale — NXP Semiconductors products are sold subject to the general terms and conditions of commercial sale, as published at http://www.nxp.com/profile/terms, including those pertaining to warranty, intellectual property rights infringement and limitation of liability, unless explicitly otherwise agreed to in writing by NXP Semiconductors. In case of any inconsistency or conflict between information in this document and such terms and conditions, the latter will prevail.

No offer to sell or license — Nothing in this document may be interpreted or construed as an offer to sell products that is open for acceptance or the grant, conveyance or implication of any license under any copyrights, patents or other industrial or intellectual property rights.

**Export control** — This document as well as the item(s) described herein may be subject to export control regulations. Export might require a prior authorization from national authorities.

**Quick reference data** — The Quick reference data is an extract of the product data given in the Limiting values and Characteristics sections of this document, and as such is not complete, exhaustive or legally binding.

### **NXP Semiconductors**

### **Customer notification**

This data sheet was changed to reflect the new company name NXP Semiconductors. No changes were made to the content, except for the legal definitions and disclaimers.

### **Contact information**

For additional information please visit: http://www.nxp.com

For sales offices addresses send e-mail to: salesaddresses@nxp.com

© NXP B.V. 2009

All rights are reserved. Reproduction in whole or in part is prohibited without the prior written consent of the copyright owner.

The information presented in this document does not form part of any quotation or contract, is believed to be accurate and reliable and may be changed without notice. No liability will be accepted by the publisher for any consequence of its use. Publication thereof does not convey nor imply any license under patent- or other industrial or intellectual property rights.

Printed in The Netherlands 613514/04/pp10 Date of release: 2002 Feb 04 Document order number: 9397 750 09168



# **Mouser Electronics**

**Authorized Distributor** 

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

### Nexperia:

BC856AW /T3 BC856AW T/R BC856BW /T3 BC856BW /T3 BC856BW /T3 BC857AW /T3 BC857AW /T3 BC857BW /T3 BC857BW /T3 BC857BW T/R BC857CW /T3 BC857CW /T3 BC857W /T3 BC857W /T3 BC856AW,135 BC856AW,135 BC856BW,135 BC856BW,135 BC856W,135 BC856W,135 BC857W,135 BC857W,135 BC857W,135 BC857W,135 BC857W,135 BC857W,135 BC857W,135 BC857W,135 BC858W,135 BC858W