## Specification sheet

# VEGA

# **VEGABAR 18**

# Two-wire 4 ... 20 mA

# Pressure sensor with ceramic measuring cell



#### **Application area**

The VEGABAR 18 pressure transmitter with ceramic measuring cell can be used universally for measurement of gases, vapours and liquids. The VEGABAR 18 is an economical solution for a multitude of applications in all areas of industry.

# Your benefit

- · Low-cost version with very small mounting dimensions
- High plant availability through maximum overload and vacuum resistance of the ceramic measuring cell

## Function

The heart of the pressure transmitter is the pressure measuring cell transforming the pressure into an electrical signal. This pressure-dependent signal is convereted by the integrated electronics into a standardized output signal.

Sensor element is the ceramic CERTEC® measuring cell with excellent long-term stability and high overload resistance.

## **Technical data**

Measuring ranges -1 ... +25 bar/-100 ... +2500 kPa

(-14.5 ... +300 psig)

Smallest measuring range +0.1 bar/+10 kPa (+1.45 psig)

 $\begin{array}{ll} \mbox{Deviation} & < 0.5 \ \% \\ \mbox{Output signal} & 4 \dots 20 \ \mbox{mA} \end{array}$ 

Process fitting Thread from G½, ½ NPT Process temperature  $-40 \dots +100 \,^{\circ}\text{C} \, (-40 \dots +212 \,^{\circ}\text{F})$  Ambient, storage and  $-40 \dots +70 \,^{\circ}\text{C} \, (-40 \dots +140 \,^{\circ}\text{F})$ 

transport temperature

Operating voltage 12 ... 35 V DC

Protection rating up to IP66/IP67 acc. to EN 60529/IEC 529,

up to Type 6P UL 50

#### **Materials**

The wetted parts of the instrument are made of 316L as well as sapphire-ceramic<sup>®</sup>. The process seal is available in FKM.

A complete overview of the available materials and seals can be found on our homepage under "Products" and "Configure & Order".

## **Housing versions**

The housing is equipped with plug connectors acc. to ISO 4400 or  $M12 \times 1$ .

It is available with protection ratings up to IP66/IP67.

# **Electronics versions**

The instrument has a 4  $\dots$  20 mA signal output.

### **Approvals**


Worldwide approvals are available for VEGA instruments, e.g. for use in hazardous areas, on ships or in hygienic applications.

The technical data in the respective safety instructions are valid for approved instruments (e.g. with Ex approval). In some cases, these data can differ from the data listed herein.

You can find detailed information on the existing approvals with the appropriate product on our homepage.




#### **Electrical connection**



Wiring plan - two-wire 4 ... 20 mA - M12 x 1 plug

1 Voltage supply and signal output




Wiring plan - two-wire 4 ... 20 mA - plug according to ISO 4400

1 Voltage supply and signal output

You can find details on electrical connection in the instrument operating instructions at <a href="https://www.vega.com/downloads">www.vega.com/downloads</a>.

#### **Dimensions**



Dimensions VEGABAR 18

- 1 Thread G½ (EN 837), manometer connection
- 2 Thread ½ NPT, inside ¼ NPT (ASME B1.20.1)
- 3 Thread G½, inside G¼ (ISO 228-1)

## Information

You can find further information on the VEGA product line on our home-

In the download section on our homepage you'll find operating instructions, product information, brochures, approval documents, instrument drawings and much, much more.

Software accessories such as the current device software and the appropriate operating software are also available there.

# Instrument selection

On our homepage under "Products" you can select the suitable measuring principle and instrument for your application.

There you will also find detailed information on the available device versions.

# Contact

You can find your personal contact person at VEGA on our homepage under "Contact".