

The design of the ACS resistor provides a good balance of power density, stability and resistance to environment for a broad range of industrial power applications, such as drives and controls.

- Good ratio between power capability and physical size
- Wound to maximise high pulse capability
- Low inductive versions available
- Available on tape and reel 1W to 5W or bulk
- RoHS Compliant




Characteristics

Tolerance (Code):	Standard F ($\pm 1\%$), J ($\pm 5\%$) and K ($\pm 10\%$); other tolerances available on request
Temperature coefficient:	$<1R \pm 90\text{ppm}/^\circ\text{C}$, $1R-10R \pm 50\text{ppm}/^\circ\text{C}$, $>10R \pm 20\text{ppm}/^\circ\text{C}$
Insulation resistance:	1, 000M ohms minimum dry, 100M ohms minimum after moisture test
Dielectric withstand voltage:	500V AC
MIL types:	Available upon request.

Electrical Specifications

Type	Wattage	Max working voltage (V)	Resistance range for 5% tolerance	
			Inductive	Non Inductive (N)
ACS 1	1	50	R01 - 8K	R01 - 3K
ACS 2	2	100	R01 - 10K	R01 - 4K
ACS 3	3	200	R02 - 18K	R02 - 9K
ACS 5S	5	157	R05 - 22K	R05 - 10K
ACS 5L	5	400	R05 - 35K	R05 - 17K
ACS 7	7	450	R06 - 50K	R06 - 25K
ACS 10S	10	700	R1 - 70K	R1 - 35K
ACS 10L	10	800	R3 - 100K	R5 - 50K

Derating Curve



Ordering Procedure

Standard Resistor To specify standard: Series, Wattage Rating, Winding Type, Resistance and Tolerance Code, e.g.: ACS3 18K F

ACS3N 18K F (non-inductive)

Tolerance (Code) $\pm 1\%$ (F), $\pm 5\%$ (J), $\pm 10\%$ (K)

Typical Inductance

Type	<50 ohms	>50 ohms
ACS 1 - ACS2	0.2 μH	0.37 μH
ACS 3 - ACS5L	0.3 μH	0.6 μH
ACS 7 - ACS 10L	0.65 μH	1.2 μH

As specified by MIL-R-39007. Max series inductance at 0.5MHz.


ARCOL UK Limited,
Threemilestone Ind. Estate,
Truro, Cornwall, TR4 9LG, UK.
T +44 (0) 1872 277431
F +44 (0) 1872 222002
E sales@arcolresistors.com

www.arcolresistors.com

The information contained herein does not form part of a contract and is subject to change without notice. Arcol operate a policy of continual product development, therefore, specifications may change.

It is the responsibility of the customer to ensure that the component selected from our range is suitable for the intended application. If in doubt please ask Arcol.

Dimensions (mm)



Type	B ± 1.5	C ± 1.0	D ± 0.02	E ± 0.8
ACS 1	12	37.0	0.8	4
ACS 2	13.8	35.0	0.8	4.7
ACS 3	15.7	35.0	0.8	5.9
ACS 5S	13	35.0	0.8	3.5
ACS 5L	22.5	44.0	1.0	8.52
ACS 7	24.5	44.0	1.0	8.52
ACS 10S	43.7	35	1.0	8.52
ACS 10L	46.2	33.0	1.0	10.5

ARCOL UK Limited,
 Threemilestone Ind. Estate,
 Truro, Cornwall, TR4 9LG, UK.
 T +44 (0) 1872 277431
 F +44 (0) 1872 222002
 E sales@arcolresistors.com

www.arcolresistors.com

The information contained herein does not form part of a contract and is subject to change without notice. Arcol operate a policy of continual product development, therefore, specifications may change.

It is the responsibility of the customer to ensure that the component selected from our range is suitable for the intended application. If in doubt please ask Arcol.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Ohmite:

[ACS 5s 22K J T&R](#) [ACS 5s 15K J T&R](#) [ACS 5s 10K J T&R](#) [ACS 5s 18K J T&R](#) [ACS 5s 12K J T&R](#) [ACS 5s 8R2 J T&R](#) [ACS 5s 820R J T&R](#) [ACS 5s R4 K T&R](#) [ACS 5s R8 K T&R](#) [ACS 5s R6 K T&R](#) [ACS 5s R2 K T&R](#) [ACS 5s R3 K T&R](#) [ACS 5s R7 K T&R](#) [ACS 5s R5 K T&R](#) [ACS 5s R9 K T&R](#) [ACS 5s R1 K T&R](#) [ACS 5s 270R J T&R](#) [ACS 5s 220R J T&R](#) [ACS 5s 2R7 J T&R](#) [ACS 5s 2R2 J T&R](#) [ACS 5s 6R8 J T&R](#) [ACS 5s 680R J T&R](#) [ACS 5s 1K5 J T&R](#) [ACS 5s 1K8 J T&R](#) [ACS 5s 1K2 J T&R](#) [ACS 5s 5K6 J T&R](#) [ACS 5s 330R J T&R](#) [ACS 5s 390R J T&R](#) [ACS 5s 4K7 J T&R](#) [ACS5S10RJ](#) [ACS 5s 1K J T&R](#) [ACS 5s 3R3 J T&R](#) [ACS 5s 3R9 J T&R](#) [ACS 5s 82R J T&R](#) [ACS 5s 47R J T&R](#) [ACS 5s 68R J T&R](#) [ACS 5s 22R J T&R](#) [ACS 5s 27R J T&R](#) [ACS 5s 56R J T&R](#) [ACS 5s 18R J T&R](#) [ACS 5s 10R J T&R](#) [ACS 5s 12R J T&R](#) [ACS 5s 15R J T&R](#) [ACS 5s 39R J T&R](#) [ACS 5s 33R J T&R](#) [ACS 5s 3K3 J T&R](#) [ACS 5s 3K9 J T&R](#) [ACS 5s 100R J T&R](#) [ACS 5s 180R J T&R](#) [ACS 5s 2K7 J T&R](#) [ACS 5s 1R5 J T&R](#) [ACS 5s 1R2 J T&R](#) [ACS 5s 1R J T&R](#) [ACS 5s 1R8 J T&R](#) [ACS 5s 120R J T&R](#) [ACS 5s 2K2 J T&R](#) [ACS 5s 150R J T&R](#) [ACS 5s 560R J T&R](#) [ACS 5s 5R6 J T&R](#) [ACS 5s 4R7 J T&R](#) [ACS 5s 470R J T&R](#) [ACS 5s R12 K T&R](#) [ACS 5s R15 K T&R](#) [ACS 5s R56 K T&R](#) [ACS 5s R33 K T&R](#) [ACS 5s R39 K T&R](#) [ACS 5s R47 K T&R](#) [ACS 5s R82 K T&R](#) [ACS 5s R68 K T&R](#) [ACS 5s R22 K T&R](#) [ACS 5s 8K2 J T&R](#) [ACS 5s 6K8 J T&R](#) [ACS 5s R4 K BULK](#) [ACS5S 560R J TA](#)