

Datasheet

Twist Drill Bit

RS Stock number [768-3242](#)



Features

- Twin drill bit made of high speed steel
- Right-hand cutting twist drill bit, Type N, 135° drill bit tip, split point manufactured to DIN 1412 C, diameter tolerance h 8
- Two-cutter, cylindrical, two flutes
- Suitable for alloyed and non-alloyed steel up to a tensile strength of 900 N/mm², cast steel, cast iron, sintered iron, malleable cast iron, non-ferrous metals and hard plastics
- Precision ground - enables up to 40% faster drilling rate and up to 50% lower feed pressure than standard-ground HSS drill bits with a chisel edge
- Self centring split point drill tip means there is no need to pre-punch or pilot drill up to 10mm diameter

Specification

Diameter (mm): 4

Working length (mm): 43

Total length (mm): 75

Colour: Polished