


150 mA low noise high PSRR linear voltage regulator

Datasheet - production data



Features

- Input voltage from 2.4 to 5.5 V
- Very low quiescent current (31 μA typ. at noload, 75 μA typ. at 150 mA load, 1 μA max. in OFF mode)
- Very low noise (20 μV_{RMS} at V_{OUT} = 1.5 V)
- Output voltage tolerance: ± 1.8% at 25 °C
- 150 mA guaranteed output current
- Wide range of output voltages available on request: 1.2 V to 3.3 V in 100 mV steps
- Logic-controlled electronic shutdown
- Compatible with ceramic capacitors
- Very high PSRR (80 dB @ 100 Hz, 76 @ 10 kHz, 54 @ 100 kHz)
- Internal current and thermal limit
- Package: SOT323-5L
- Temperature range: -40 °C to 125 °C

Description

The LD59015 provides 150 mA maximum current with an input voltage range from 2.4 V to 5.5 V, and a typical dropout voltage of 150 mV. It is stable with ceramic capacitors. High PSRR, low quiescent current and low noise features make it suitable for low power battery-powered applications. Power supply rejection is 80 dB at low frequency and starts to roll off at 10 kHz. The enable logic control function puts the LD59015 in shutdown mode, allowing a total current consumption lower than 1 µA. The device also includes short-circuit constant current limiting and thermal protection. Typical applications are mobile phones, personal digital assistants (PDAs), cordless phones and similar batterypowered systems.

Table 1. Device summary

| Order code | Output voltages |
|-------------|-----------------|
| LD59015C12R | 1.2 V |
| LD59015C15R | 1.5 V |
| LD59015C18R | 1.8 V |
| LD59015C25R | 2.5 V |
| LD59015C30R | 3.0 V |
| LD59015C33R | 3.3 V |

July 2017 DocID17488 Rev 5 1/18

Contents LD59015

Contents

| 1 | Block diagram 3 |
|---|-------------------------------------|
| 2 | Pin configuration |
| 3 | Typical application5 |
| 4 | Maximum ratings |
| 5 | Electrical characteristics |
| 6 | Typical performance characteristics |
| 7 | Package information |
| | 7.1 SOT323-5L package information |
| | 7.2 SOT323-5L packing information |
| 8 | Revision history |



LD59015 Block diagram

1 Block diagram

IN

BandGap
0.8 V

Trimming

Thermal
Protection

Enable

EN

GND

Figure 1. LD59015 block diagram

Pin configuration LD59015

2 Pin configuration

Figure 2. Pin connection (top view)




Table 2. Pin description

| Pin | Symbol | Function |
|-----|--------|---|
| 1 | IN | Input voltage |
| 2 | GND | Ground |
| 3 | EN | Enable input Set $V_{EN} > 0.9$ to turn on the device Set $V_{EN} < 0.4$ to turn off the device |
| 4 | N.C. | Not connected |
| 5 | OUT | Output voltage |

LD59015 Typical application

3 Typical application

V_{IN} IN OUT V_{OUT} 1 μF Load V_{OUT} Load V_{EN} EN GND

Figure 3. Typical application circuit



Maximum ratings LD59015

4 Maximum ratings

Table 3. Absolute maximum ratings

| Symbol | Parameter | Value | Unit |
|------------------|--------------------------------------|--|------|
| V_{IN} | DC input voltage | - 0.3 to 7 | V |
| V _{OUT} | DC output voltage | - 0.3 to V _I + 0.3 (max. 7) | V |
| V_{EN} | Enable input voltage | - 0.3 to V _I + 0.3 (max. 7) | V |
| I _{OUT} | Output current | Internally limited | mA |
| P_{D} | Power dissipation | Internally limited | mW |
| Human body model | | ± 3 | kV |
| ESD | Machine model | ± 300 | V |
| T _{STG} | Storage temperature range | -65 to 150 | °C |
| T _{OP} | Operating junction temperature range | -40 to 125 | °C |

Note:

Absolute maximum ratings are those values beyond which damage to the device may occur. Functional operation under these conditions is not implied. All values are referred to GND.

Table 4. Thermal data

| Symbol | Parameter | Value | Unit |
|-------------------|-------------------------------------|--------|------|
| R _{thJA} | Thermal resistance junction-ambient | 645.69 | °C/W |
| R _{thJC} | Thermal resistance junction-case | 116 | °C/W |

5 Electrical characteristics

 T_J = 25 °C, V_{IN} = $V_{OUT(NOM)}$ + 1 V, C_{IN} = C_{OUT} = 1 $\mu F,\,I_{OUT}$ = 1 mA, V_{EN} = $V_{IN},\,unless$ otherwise specified.

Table 5. Electrical characteristics (1)

| Symbol | Parameter | Test conditions | Min. | Тур. | Max. | Unit |
|-------------------|--|---|------|-------|------|--|
| V _{IN} | Operating input voltage | | 2.4 | | 5.5 | |
| \/ | Turn-on threshold | | | 2.0 | 2.15 | V |
| V _{UVLO} | Turn-off threshold | | 1.90 | 1.95 | | |
| V _{OUT} | V _{OUT} accuracy | I _{OUT} = 1 mA, -40 °C < T _J < 125 °C | -1.8 | | 1.8 | % |
| ΔV _{OUT} | Static line regulation | V_{OUT} +1 V \leq V _{IN} \leq 5.5 V, I _{OUT} = 1 mA | | 0.001 | | %/V |
| ΔV_{OUT} | Static load regulation | I _{OUT} = 1 mA to 150 mA | | 0.001 | | %/mA |
| V _{DROP} | Dropout voltage (2) | I _{OUT} = 150 mA, V _{OUT} > 2.2 V -40 °C < T _J < 125 °C | | 150 | 210 | mV |
| e _N | Output noise voltage | 10 Hz to 100 kHz, I _{OUT} = 10 mA, V _{OUT} = 1.5 V | | 20 | | μV _{RMS} /V _{OUT} |
| | Supply voltage rejection V _{OUT} = 1.5 V | $V_{IN} = V_{OUTNOM} + 1 V +/-V_{RIPPLE}$ $V_{RIPPLE} = 0.5 V$, frequency = 1 kHz $I_{OUT} = 1 \text{ mA}$ | | 76 | | dB |
| I SVR I | | V _{IN} = V _{OUTNOM} + 1 V +/-V _{RIPPLE} V _{RIPPLE} = 0.5 V, frequency =10 kHz I _{OUT} = 1 mA | | 76 | | |
| | | V _{IN} = V _{OUTNOM} + 1 V +/-V _{RIPPLE} V _{RIPPLE} = 0.5 V, frequency =100 kHz I _{OUT} = 1 mA | | 54 | | |
| | | I _{OUT} = 0 mA | | 31 | | |
| | Quiescent current | $I_{OUT} = 0 \text{ mA}, -40 \text{ °C} < T_{J} < 125 \text{ °C}$ | | | 60 | |
| | | I _{OUT} = 0 to 150 mA | | 75 | |] |
| IQ | | I _{OUT} = 0 to 150 mA -40 °C < T _J < 125 °C | | | 110 | μΑ |
| | | V_{IN} input current in OFF mode: $V_{EN} = GND$ | | 0.001 | 1 | |
| I _{SC} | Short-circuit current | $R_L = 0$ | 200 | | | mA |
| V | Enable input logic low | V _{IN} = 2.4 V to 5.5 V, -40 °C < T _J < 85 °C | | | 0.4 | V |
| V _{EN} | Enable input logic high | V _{IN} = 2.4 V to 5.5 V, -40 °C < T _J < 85 °C | 0.9 | | | V |



Electrical characteristics LD59015

Table 5. Electrical characteristics (continued)⁽¹⁾

| Symbol | Parameter | Test conditions | Min. | Тур. | Max. | Unit |
|------------------|--------------------------|-----------------------------|------|------|------|------|
| I _{EN} | Enable pin input current | V _{SHDN} = 5.5V | | 0.1 | 100 | nA |
| T _{ON} | Turn-on time (3) | | | 200 | | μs |
| т | Thermal shutdown | | | 160 | | °C |
| I SHDN | Hysteresis | | | 20 | | C |
| C _{OUT} | Output capacitor | Capacitance (see Section 6) | 1 | | 4.7 | μF |

^{1.} For $V_{OUT(NOM)}$ < 1.3 V, V_{IN} = 2.4 V.

Note: All transient values are guaranteed by design, not tested in production.





^{2.} Dropout voltage is the input-to-output voltage difference at which the output voltage is 100 mV below its nominal value. This specification does not apply to output voltages below 1.7 V.


^{3.} Turn-on time is time measured between the enable input just exceeding V_{EN} high value and the output voltage just reaching 95% of its nominal value.


6 Typical performance characteristics


$$C_{IN} = C_{OUT} = 1 \mu F$$


















577


DocID17488 Rev 5

















 C_{OUT} = 1 μ F; V_{IN} = V_{EN} = from 2.4 to 3.3 V; V_{OUT} = 0.8 V; I_{OUT} = 1 mA; t_{rise} = t_{fall} = 25 μ s

10/18 DocID17488 Rev 5









LD59015 Package information

7 Package information

In order to meet environmental requirements, ST offers these devices in different grades of ECOPACK[®] packages, depending on their level of environmental compliance. ECOPACK[®] specifications, grade definitions and product status are available at: www.st.com. ECOPACK[®] is an ST trademark.

7.1 SOT323-5L package information




Figure 21. SOT323-5L package outline

57/

DocID17488 Rev 5 13/18

Package information LD59015

Table 6. SOT323-5L package mechanical data

| Dim. | mm | | | | |
|------|------|------|------|--|--|
| | Min. | Тур. | Max. | | |
| А | 0.80 | | 1.10 | | |
| A1 | 0 | | 0.10 | | |
| A2 | 0.80 | 0.90 | 1 | | |
| b | 0.15 | | 0.30 | | |
| С | 0.10 | | 0.22 | | |
| D | 1.80 | 2 | 2.20 | | |
| E | 1.80 | 2.10 | 2.40 | | |
| E1 | 1.15 | 1.25 | 1.35 | | |
| е | | 0.65 | | | |
| e1 | | 1.30 | | | |
| L | 0.26 | 0.36 | 0.46 | | |
| < | 0° | | 8° | | |

LD59015 Package information

7.2 SOT323-5L packing information

A Po Note: Drawing not in scale

Figure 22. SOT323-5L tape and reel outline

Package information LD59015

Table 7. SOT323-5L tape and reel mechanical data

| Dim. | mm | | | |
|------|------|------|------|--|
| | Min. | Тур. | Max. | |
| А | 175 | 180 | 185 | |
| С | 12.8 | 13 | 13.2 | |
| D | 20.2 | | | |
| N | 59.5 | 60 | 60.5 | |
| Т | | | 14.4 | |
| Ao | | 2.25 | | |
| Во | | 3.17 | | |
| Ко | | 1.2 | | |
| Po | 3.9 | 4.0 | 4.1 | |
| Р | 3.9 | 4.0 | 4.2 | |

LD59015 Revision history

8 Revision history

Table 8. Document revision history

| Date | Revision | Changes |
|-------------|----------|--|
| 10-May-2010 | 1 | Initial release. |
| 21-Dec-2011 | 2 | Modified: operating input voltage (V _{IN}) min. value <i>Table 5 on page 7</i> . Availability LD59015C08R code <i>Table 1 on page 1</i> . |
| 06-Jul-2012 | 3 | Updated: Table 1 on page 1. |
| 24-Apr-2014 | 4 | Part number LD59015xx changed to LD59015. Updated the description in cover page and Section 7: Package mechanical data. Added Section 8: Packaging mechanical data. Minor text changes. |
| 05-Jul-2017 | 5 | Updated features and <i>Table 1: Device summary</i> . Minor text changes. |

IMPORTANT NOTICE - PLEASE READ CAREFULLY

STMicroelectronics NV and its subsidiaries ("ST") reserve the right to make changes, corrections, enhancements, modifications, and improvements to ST products and/or to this document at any time without notice. Purchasers should obtain the latest relevant information on ST products before placing orders. ST products are sold pursuant to ST's terms and conditions of sale in place at the time of order acknowledgement.

Purchasers are solely responsible for the choice, selection, and use of ST products and ST assumes no liability for application assistance or the design of Purchasers' products.

No license, express or implied, to any intellectual property right is granted by ST herein.

Resale of ST products with provisions different from the information set forth herein shall void any warranty granted by ST for such product.

ST and the ST logo are trademarks of ST. All other product or service names are the property of their respective owners.

Information in this document supersedes and replaces information previously supplied in any prior versions of this document.

© 2017 STMicroelectronics - All rights reserved

577

18/18 DocID17488 Rev 5