


MBT + I

Diamond cut
knurled knobs
with revolving handle



ELESA Original design



* Complete with colour index, example: 34398-C2 MBT.40+I B-6-C2

C9
 C2
 C3
 C4
 C5
 C6
 RAL9005 RAL2004 RAL7035 RAL1021 RAL5024 RAL3000

Elesa Standards		Main dimensions								Mounting hole		Handle	Weight
Code	Description	D	L	d ₁	l ₂	d ₂	l ₁	f	h ₂	d _{H9}	h	H	g
34398-*	MBT.40+I B-6-*	39.5	26.5	17	12.5	12	17	M4	4	6	14	20	34
34498-*	MBT.50+I B-6-*	50	33	20	16	15	23	M5	5	6	18	20	54
34598-*	MBT.60+I B-8-*	61	39	23	18.5	15	25	M5	6	8	20	23	65
34698-*	MBT.70+I B-10-*	70	42	24	20.5	16	30	M5	6	10	25	23	73
34798-*	MBT.85+I B-10-*	85	30.5	29	10.5	16	-	M5	6	10	22	23	84
34898-*	MBT.100+I B-10-*	100	31	35	11	16	-	M5	6	10	22	23	102

Material

High-resilience polypropylene based (PP) technopolymer. Resistant to solvents, oils, greases and other chemical agents.

Colour

Black, matte finish.

Coloured centre cap

Technopolymer, matte finish.

To order, add the index of the desired colour (C9, ..., C6) to the code and the description.

On request and for sufficient quantities, it can be supplied in other colours or with customised graphic symbols, marks or writings.

Revolving handle

Type [L.701+x](#) polyamide based (PA) technopolymer, black colour, matte finish.

Standard execution

Brass boss, plain hole. Assembly by means of a supplied transversal grub screw UNI 5929-85 (grub screw with hexagon socket and cup end).



STANDARD MACHINE ELEMENTS WORLDWIDE

ELESA models all rights reserved in accordance with the law. Always mention the source when reproducing our drawings.