

LT1521/LT1521-3 LT1521-3.3/LT1521-5

300mA Low Dropout Regulators with Micropower Quiescent Current and Shutdown

FEATURES

- Dropout Voltage: 0.5V
- **Output Current: 300mA**
- **Quiescent Current: 12uA**
- No Protection Diodes Needed
- Adjustable Output from 3.8V to 20V
- Fixed Output Voltages: 3V, 3.3V, 5V
- **Controlled Quiescent Current in Dropout**
- Shutdown $I_0 = 6\mu A$
- **Reverse Battery Protection**
- No Reverse Current
- Thermal Limiting

APPLICATIONS

- Low Current Regulator
- Regulator for Battery-Powered Systems
- Post Regulator for Switching Supplies


DESCRIPTION


The LT®1521/LT1521-3/LT1521-3.3/LT1521-5 are low dropout regulators with micropower guiescent current and shutdown. These devices are capable of supplying 300mA of output current with a dropout voltage of 0.5V. Designed for use in battery-powered systems, the low guiescent current, 12µA operating and 6µA in shutdown, makes them an ideal choice. The guiescent current is well controlled; it does not rise in dropout as it does with many other low dropout PNP regulators.

Other features of the LT1521/LT1521-3/LT1521-3.3/ LT1521-5 include the ability to operate with very small output capacitors. They are stable with only 1.5µF on the output while most older devices require between 10µF and 100µF for stability. Small ceramic capacitors can be used, enhancing manufacturability. Also, the input may be connected to voltages lower than the output voltage. including negative voltages, without reverse current flow from output to input. This makes the LT1521 series ideal for backup power situations where the output is held high and the input is low or reversed. Under these conditions only 5µA will flow from the output pin to ground.

All registered trademarks and trademarks are the property of their respective owners.

TYPICAL APPLICATION





150

OUTPUT CURRENT (mA)

0

50

Dropout Voltage

300

LT1521 • TA02


ABSOLUTE MAXIMUM RATINGS (Note 1)

Input Voltage	±20V*
Output Pin Reverse Current	10mA
Adjust Pin Current	10mA
Shutdown Pin Input Voltage (Note 1)6.5	/, –0.6V
Shutdown Pin Input Current (Note 1)	5mA
Output Short-Circuit Duration Ir	Idefinite

Storage Temperature Range	.–65°C to 150°C
Operating Junction Temperature Range	(Note 2)
Commercial	0°C to 125°C
Industrial	-40°C to 125°C
Lead Temperature (Soldering, 10 sec)	300°C
*For applications requiring input voltage ratings greater	ater than 20V, contact

the factory.

PIN CONFIGURATION



ORDER INFORMATION

LEAD FREE FINISH	TAPE AND REEL	PART MARKING*	PACKAGE DESCRIPTION	TEMPERATURE RANGE
LT1521CMS8#PBF	LT1521CMS8#TRPBF	LTEZ	8-Lead Plastic MSOP	0°C to 125°C
LT1521CMS8-3#PBF	LT1521CMS8-3#TRPBF	LTFB	8-Lead Plastic MSOP	0°C to 125°C
LT1521CMS8-3.3#PBF	LT1521CMS8-3.3#TRPBF	LTDU	8-Lead Plastic MSOP	0°C to 125°C
LT1521CMS8-5#PBF	LT1521CMS8-5#TRPBF	LTFA	8-Lead Plastic MSOP	0°C to 125°C
LT1521CS8#PBF	LT1521CS8#TRPBF	1521	8-Lead Plastic SOIC	0°C to 125°C
LT1521CS8-3#PBF	LT1521CS8-3#TRPBF	15213	8-Lead Plastic SOIC	0°C to 125°C
LT1521CS8-3.3#PBF	LT1521CS8-3.3#TRPBF	152133	8-Lead Plastic SOIC	0°C to 125°C
LT1521CS8-5#PBF	LT1521CS8-5#TRPBF	15215	8-Lead Plastic SOIC	0°C to 125°C
LT1521IS8#PBF	LT1521IS8#TRPBF	15211	8-Lead Plastic SOIC	-40°C to 125°C
LT1521IS8-3#PBF	LT1521IS8-3#TRPBF	152113	8-Lead Plastic SOIC	-40°C to 125°C
LT1521IS8-3.3#PBF	LT1521IS8-3.3#TRPBF	1521133	8-Lead Plastic SOIC	-40°C to 125°C
LT1521IS8-5#PBF	LT1521IS8-5#TRPBF	152115	8-Lead Plastic SOIC	-40°C to 125°C

ORDER INFORMATION

LEAD FREE FINISH	TAPE AND REEL	PART MARKING*	PACKAGE DESCRIPTION	TEMPERATURE RANGE
LT1521CST-3#PBF	LT1521CST-3#TRPBF	15213	3-Lead Plastic SOT-223	0°C to 125°C
LT1521CST-3.3#PBF	LT1521CST-3.3#TRPBF	152133	3-Lead Plastic SOT-223	0°C to 125°C
LT1521CST-5#PBF	LT1521CST-5#TRPBF	15215	3-Lead Plastic SOT-223	0°C to 125°C
LT1521IST-3#PBF	LT1521IST-3#TRPBF	152113	3-Lead Plastic SOT-223	-40°C to 125°C
LT1521IST-3.3#PBF	LT1521IST-3.3#TRPBF	1521133	3-Lead Plastic SOT-223	-40°C to 125°C
LT1521IST-5#PBF	LT1521IST-5#TRPBF	152115	3-Lead Plastic SOT-223	-40°C to 125°C

Contact the factory for parts specified with wider operating temperature ranges. *The temperature grade is identified by a label on the shipping container. Tape and reel specifications. Some packages are available in 500 unit reels through designated sales channels with #TRMPBF suffix.

ELECTRICAL CHARACTERISTICS The \bullet denotes the specifications which apply over the full operating temperature range, otherwise specifications are at T_A = 25°C.

PARAMETER	CONDITIONS			MIN	ТҮР	MAX	UNITS
Regulated Output Voltage (Note 4)	LT1521-3	V_{IN} = 3.5V, I_{OUT} = 1mA, T_J = 25°C 4V < V_{IN} < 20V, 1mA < I_{OUT} < 300mA	•	2.950 2.900	3.000 3.000	3.050 3.100	V V
	LT1521-3.3	V_{IN} = 3.8V, I_{OUT} = 1mA, T_J = 25°C 4.3V < V_{IN} < 20V, 1mA < I_{OUT} < 300mA	•	3.250 3.200	3.300 3.300	3.350 3.400	V V
	LT1521-5	V _{IN} = 5.5V, I _{OUT} = 1mA, T _J = 25°C 6V < V _{IN} < 20V, 1mA < I _{OUT} < 300mA	•	4.925 4.850	5.000 5.000	5.075 5.150	V V
	LT1521 (Note 5)	V _{IN} = 4.3V, I _{OUT} = 1mA, T _J = 25°C 4.8V < V _{IN} < 20V, 1mA < I _{OUT} < 300mA	•	3.695 3.640	3.750 3.750	3.805 3.860	V V
Line Regulation	LT1521-3	ΔV_{IN} = 4.5 to 20V, I _{OUT} = 1mA	٠		1.5	20	mV
	LT1521-3.3	ΔV_{IN} = 4.8 to 20V, I _{OUT} = 1mA			1.5	20	mV
	LT1521-5	ΔV_{IN} = 5.5 to 20V, I _{OUT} = 1mA			1.5	20	mV
	LT1521 (Note 5)	ΔV_{IN} = 4.3 to 20V, I _{OUT} = 1mA	٠		1.5	20	mV
Load Regulation	LT1521-3	ΔI_{LOAD} = 1mA to 300mA, $T_J \leq 25^\circ C$			-20	-30	mV
	LT1521-3.3	ΔI_{LOAD} = 1mA to 300mA, $T_J \leq 25^\circ\text{C}$			-20	-30	mV
	LT1521-5	ΔI_{LOAD} = 1mA to 300mA, T _J \leq 25°C			-25	-45	mV
	LT1521 (Note 5)	ΔI_{LOAD} = 1mA to 300mA, $T_J \leq 25^\circ C$			-20	-30	mV
	LT1521-3	ΔI_{LOAD} = 1mA to 300mA, T _J > 25°C			-20	-55	mV
	LT1521-3.3	ΔI_{LOAD} = 1mA to 300mA, T _J > 25°C			-20	-55	mV
	LT1521-5	ΔI_{LOAD} = 1mA to 300mA, T _J > 25°C			-25	-75	mV
	LT1521 (Note 5)	ΔI_{LOAD} = 1mA to 300mA, T _J > 25°C			-20	-55	mV
Dropout Voltage (Note 6)	$I_{LOAD} = 1mA, T_{J} = I_{LOAD} = 1mA$	25°C	•		130	170 250	mV mV
	I _{LOAD} = 50mA, T _J = I _{LOAD} = 50mA	= 25°C	•		290	350 450	mV mV
	I _{LOAD} = 100mA, T _J I _{LOAD} = 100mA	= 25°C	•		350	420 550	mV mV
	I _{LOAD} = 150mA, T _J I _{LOAD} = 150mA	= 25°C	•		400	470 600	mV mV
	I _{LOAD} = 300mA, T _J I _{LOAD} = 300mA	= 25°C	•		500	600 750	mV mV

ELECTRICAL CHARACTERISTICS The • denotes the specifications which apply over the full operating

temperature range, otherwise specifications are at $T_A = 25^{\circ}C$.

PARAMETER	CONDITIONS		MIN	ТҮР	MAX	UNITS
Ground Pin Current (Note 7)	I _{LOAD} = 0mA			12	25	μA
	I _{LOAD} = 1mA	•		65	100	μA
	I _{LOAD} = 10mA	٠		300	450	μA
	I _{LOAD} = 50mA			0.8	1.5	mA
	I _{LOAD} = 100mA	•		1.4	2.5	mA
	I _{LOAD} = 150mA	•		2.2	4.0	mA
	I _{LOAD} = 300mA	•		6.5	12.0	mA
Adjust Pin Bias Current (Notes 5, 8)	T _J = 25°C			50	100	nA
Shutdown Threshold	V _{OUT} = Off to On V _{OUT} = On to Off	•	0.25	1.20 0.75	2.80	V V
Shutdown Pin Current (Note 9)	V _{SHDN} = 0V	•		2.0	5.0	μA
Quiescent Current in Shutdown (Note 10)	$V_{IN} = V_{OUT} (NOMINAL) + 1V, V_{\overline{SHDN}} = 0V$	•		6	12	μA
Ripple Rejection	$V_{IN} - V_{OUT} = 1V(Avg), V_{RIPPLE} = 0.5V_{P-P}, f_{RIPPLE} = 120Hz, I_{LOAD} = 150mA$		50	58		dB
Current Limit	$_{IN} - V_{OUT} = 7V, T_J = 25^{\circ}C$ $_{IN} = V_{OUT} (NOMINAL) + 1.5V, \Delta V_{OUT} = -0.1V$		320	400 400	800	mA mA
Input Reverse Leakage Current	$V_{IN} = -20V, V_{OUT} = 0V$	•			1.0	mA
Reverse Output Current (Note 11)	$ \begin{array}{llllllllllllllllllllllllllllllllllll$			5 5 5 5	10 10 10 10	μΑ μΑ μΑ

Note 1: Stresses beyond those listed under Absolute Maximum Ratings may cause permanent damage to the device. Exposure to any Absolute Maximum Rating condition for extended periods may affect device reliability and lifetime.

Note 2: The shutdown pin input voltage rating is required for a low impedance source. Internal protection devices connected to the shutdown pin will turn on and clamp the pin to approximately 7V or -0.6V. This range allows the use of 5V logic devices to drive the pin directly. For high impedance sources or logic running on supply voltages greater than 5.5V, the maximum current driven into the shutdown pin must be limited to less than 5mA.

Note 3: For junction temperatures greater than 110°C, a minimum load of 1mA is recommended. For $T_J > 110$ °C and $I_{OUT} < 1$ mA, output voltage may increase by 1%.

Note 4: Operating conditions are limited by maximum junction temperature. The regulated output voltage specification will not apply for all possible combinations of input voltage and output current. When operating at maximum input voltage, the output current range must be limited. When operating at maximum output current, the input voltage range must be limited. **Note 5:** The LT1521 (adjustable version) is tested and specified with the adjust pin connected to the output pin.

Note 6: Dropout voltage is the minimum input/output voltage required to maintain regulation at the specified output current. In dropout the output voltage will be equal to: $(V_{IN} - V_{DROPOUT})$.

Note 7: Ground pin current is tested with $V_{IN} = V_{OUT}$ (nominal) and a current source load. This means the device is tested while operating in its dropout region. This is the worst-case ground pin current. The ground pin current will decrease slightly at higher input voltages.

Note 8: Adjust pin bias current flows into the adjust pin.


Note 9: Shutdown pin current at $V_{\overline{SHDN}} = 0V$ flows out of the shutdown pin.

Note 10: Quiescent current in shutdown is equal to the total sum of the shutdown pin current ($2\mu A$) and the ground pin current ($4\mu A$).

Note 11: Reverse output current is tested with the input pin grounded and the output pin forced to the rated output voltage. This current flows into the output pin and out of the ground pin.

LT1521/LT1521-3 LT1521-3.3/LT1521-5


TYPICAL PERFORMANCE CHARACTERISTICS









TYPICAL PERFORMANCE CHARACTERISTICS




TYPICAL PERFORMANCE CHARACTERISTICS




TYPICAL PERFORMANCE CHARACTERISTICS



Ripple Rejection







TIME (µs)

LT1521 • TPC33

Load Regulation





LT1521 • TPC34

PIN FUNCTIONS

OUT (Pin 1): The output pin supplies power to the load. A minimum output capacitor of 1.5μ F is required to prevent oscillations, but larger values of output capacitor will be necessary to deal with larger load transients. See the Applications Information section for more on output capacitance and reverse output characteristics.

SENSE (Pin 2): For fixed voltage versions of the LT1521 (LT1521-3, LT1521-3.3, LT1521-5), the sense pin is the input to the error amplifier. Optimum regulation will be obtained at the point where the sense pin is connected to the output pin of the regulator. In critical applications small voltage drops caused by the resistance (R_P) of PC traces between the regulator and the load, which would normally degrade regulation, may be eliminated by connecting the sense pin to the output at the load as shown in Figure 1 (Kelvin Sense Connection). Note that the voltage drops across the external PC traces will add to the dropout voltage of the regulator. The sense pin bias current is 5µA at the nominal regulated output voltage. This pin is internally clamped to -0.6V (one V_{BE}).




Figure 1. Kelvin Sense Connection

ADJ (Pin 2): For adjustable LT1521, the adjust pin is the input to the error amplifier. This pin is internally clamped to 6V and -0.6V (one V_{BE}). It has a bias current of 50nA which flows into the pin. See Adjust Pin Bias Current vs

Temperature in the Typical Performance Characteristics section. The adjust pin reference voltage is 3.75V referenced to ground. The output voltage range that can be produced by this device is 3.75V to 20V.


SHDN (Pin 5): The shutdown pin is used to put the device into shutdown. In shutdown the output of the device is turned off. This pin is active low. The device will be shut down if the shutdown pin is pulled low. The shutdown pin current with the pin pulled to ground will be 1.7µA. The shutdown pin is internally clamped to 7V and -0.6V (one V_{BF}). This allows the shutdown pin to be driven directly by 5V logic or by open collector logic with a pull-up resistor. The pull-up resistor is only required to supply the leakage current of the open collector gate, normally several microamperes. Pull-up current must be limited to a maximum of 5mA. A curve of the shutdown pin input current as a function of voltage appears in the Typical Performance Characteristics. If the shutdown pin is not used it can be left open circuit. The device will be active (output on) if the shutdown pin is not connected.


IN (Pin 8): Power is supplied to the device through the input pin. The input pin should be bypassed to ground if the device is more than six inches away from the main input filter capacitor. In general, the output impedance of battery rises with frequency, so it is advisable to include a bypass capacitor in battery-powered circuits. A bypass capacitor in the range of 1μ F to 10μ F is sufficient. The LT1521 is designed to withstand reverse voltages on the input pin with respect to ground and the output pin. In the case of reversed input, which can happen if a battery is plugged in backwards, the LT1521 will act as if there is a diode in series with its input. There will be no reverse current flow into the LT1521 and no reverse voltage will appear at the load. The device will protect both itself and the load.

The LT1521 is a 300mA low dropout regulator with micropower quiescent current and shutdown. The device is capable of supplying 300mA at a dropout of 0.5V and operates with very low quiescent current (12μ A). In shutdown, the quiescent current drops to only 6µA. In addition to the low quiescent current, the LT1521 incorporates several protection features which make it ideal for use in battery-powered systems. The device is protected against both reverse input voltages and reverse output voltages. In battery backup applications where the output can be held up by a backup battery when the input is pulled to ground, the LT1521 acts like it has a diode in series with its output and prevents reverse current flow.

Adjustable Operation

The adjustable version of the LT1521 has an output voltage range of 3.75V to 20V. The output voltage is set by the ratio of two external resistors as shown in Figure 2. The device servos the output voltage to maintain the voltage at the adjust pin at 3.75V. The current in R1 is then equal to 3.75V/R1. The current in R2 is equal to the sum of the current in R1 and the adjust pin bias current. The adjust pin bias current, 50nA at 25°C, flows through R2 into the adjust pin. The output voltage can be calculated using the formula in Figure 2. The value of R1 should be less than 400k to minimize errors in the output voltage caused by the adjust pin bias current. Note that in shutdown the output is turned off and the divider current will be zero. Curves of Adjust Pin Voltage vs Temperature and Adjust Pin Bias Current vs Temperature appear in the Typical Performance Characteristics. The reference voltage at the adjust pin has a positive temperature coefficient of





approximately 15ppm/°C. The adjust pin bias current has a negative temperature coefficient. These effects will tend to cancel each other.

The adjustable device is specified with the adjust pin tied to the output pin. This sets the output voltage to 3.75V. Specifications for output voltages greater than 3.75V will be proportional to the ratio of the desired output voltage to 3.75V; ($V_{OUT}/3.75V$). For example: load regulation for an output current change of 1mA to 300mA is –20mV typical at V_{OUT} = 3.75V. At V_{OUT} = 12V, load regulation would be:

(12V/3.75V)(-20mV) = -64mV

Thermal Considerations

The power handling capability of the device will be limited by the maximum rated junction temperature (125°C). The power dissipated by the device will be made up of two components:

- 1. Output current multiplied by the input/output voltage differential: $I_{OUT}(V_{IN} V_{OUT})$, and
- 2. Ground pin current multiplied by the input voltage: $(I_{GND})(V_{IN})$

The ground pin current can be found by examining the Ground Pin Current curves in the Typical Performance Characteristics. Power dissipation will be equal to the sum of the two components listed above.

The LT1521 series regulators have internal thermal limiting designed to protect the device during overload conditions. For continuous normal load conditions the maximum junction temperature rating of 125°C must not be exceeded. It is important to give careful consideration to all sources of thermal resistance from junction to ambient. Additional heat sources mounted nearby must also be considered.

For surface mount devices, heat sinking is accomplished by using the heat spreading capabilities of the PC board and its copper traces. Copper board stiffeners and plated through-holes can also be used to spread the heat generated by power devices.

The following tables list thermal resistance for each package. Measured values of thermal resistance for several

different board sizes and copper areas are listed for each package. All measurements were taken in still air on 3/32" FR-4 board with one ounce copper. All NC leads were connected to the ground plane.

Table	1.	MS8	Package
-------	----	-----	---------

	•		
COPPE	R AREA		THERMAL RESISTANCE
TOPSIDE**	BACKSIDE	BOARD AREA	(JUNCTION-TO-AMBIENT)
2500mm ²	2500mm ²	2500mm ²	110°C/W
1000mm ²	2500mm ²	2500mm ²	115°C/W
225mm ²	2500mm ²	2500mm ²	120°C/W
100mm ²	2500mm ²	2500mm ²	130°C/W

* Pin 4 is ground. ** Device is mounted on topside.

Table 2. S8 Package*

	-		
COPPE	R AREA		THERMAL RESISTANCE
TOPSIDE**	BACKSIDE	BOARD AREA	(JUNCTION-TO-AMBIENT)
2500mm ²	2500mm ²	2500mm ²	60°C/W
1000mm ²	2500mm ²	2500mm ²	60°C/W
225mm ²	2500mm ²	2500mm ²	68°C/W
100mm ²	2500mm ²	2500mm ²	74°C/W

* Pins 3, 6, 7 are ground. ** Device is mounted on topside.

Table 3. SOT-223 Package (Thermal Resistance Junction-to-Tab 20°C/W)

COPPE	R AREA		THERMAL RESISTANCE
TOPSIDE*	BACKSIDE	BOARD AREA	(JUNCTION-TO-AMBIENT)
2500mm ²	2500mm ²	2500mm ²	50°C/W
1000mm ²	2500mm ²	2500mm ²	50°C/W
225mm ²	2500mm ²	2500mm ²	58°C/W
100mm ²	2500mm ²	2500mm ²	64°C/W
1000mm ²	1000mm ²	1000mm ²	57°C/W
1000mm ²	0	1000mm ²	60°C/W

* Tab of device attached to topside copper.

Calculating Junction Temperature

Example: Given an output voltage of 3.3V, an input voltage range of 4.5V to 7V, an output current range of 0mA to 150mA and a maximum ambient temperature of 50°C, what will the maximum junction temperature be?

The power dissipated by the device will be equal to:

 $I_{OUT(MAX)}(V_{IN(MAX)} - V_{OUT}) + I_{GND}(V_{IN(MAX)})$

Where,

$$\begin{split} I_{OUT(MAX)} &= 150 mA \\ V_{IN(MAX)} &= 7V \\ I_{GND} \text{ at } (I_{OUT} = 150 mA, V_{IN} = 7V) = 2.1 mA \end{split}$$

S0,

P = 150mA(7V - 3.3V) + (2.1mA)(7V) = 0.57W

If we use a SOT-223 package, then the thermal resistance will be in the range of 50°C/W to 65°C/W depending on the copper area. So the junction temperature rise above ambient will be approximately equal to:

0.57W(60°C/W) = 34.2°C

The maximum junction temperature will then be equal to the maximum junction temperature rise above ambient plus the maximum ambient temperature or:

 $T_{JMAX} = 50^{\circ}C + 34.2^{\circ}C = 84.2^{\circ}C$

Output Capacitance and Transient Performance

The LT1521 is designed to be stable with a wide range of output capacitors. A minimum output capacitor of 1.5μ F is required to prevent oscillations. The LT1521 is a micropower device and output transient response will be a function of output capacitance. See the Transient Response curves in the Typical Performance Characteristics. Larger values of output capacitance will decrease the peak deviations and provide improved output transient response for larger load current deltas. Bypass capacitors, used to decouple individual components powered by the LT1521, will increase the effective value of the output capacitor.

Protection Features

The LT1521 incorporates several protection features which make it ideal for use in battery-powered circuits. In addition to the normal protection features associated with monolithic regulators, such as current limiting and thermal limiting, the device is protected against reverse input voltages, reverse output voltages and reverse voltages from output to input.

Current limit protection and thermal overload protection are intended to protect the device against current overload conditions at the output of the device. For normal operation, the junction temperatures should not exceed 125°C.

The input of the device will withstand reverse voltages of 20V. Current flow into the device will be limited to less than 1mA (typically less than 100 μ A) and no negative voltage will appear at the output. The device will protect both itself and the load. This provides protection against batteries that can be plugged in backward.

For fixed voltage versions of the device, the output can be pulled below ground without damaging the device. If the input is left open circuit or grounded, the output can be pulled below ground by 20V. The output will act like an open circuit, no current will flow out of the pin. If the input is powered by voltage source, the output will source the short-circuit current of the device and will protect itself by thermal limiting. For the adjustable version of the device, the output pin is internally clamped at one diode drop below ground. Reverse current for the adjustable device must be limited to 5mA.

In circuits where a backup battery is required, several different input/output conditions can occur. The output voltage may be held up while the input is either pulled to ground, pulled to some intermediate voltage or is left open circuit. Current flow back into the output will vary depending on the conditions. Many battery-powered circuits incorporate some form of power management. The following information will help optimize battery life. Table 4 summarizes the following information.

The reverse output current will follow the curve in Figure 3 when the input is pulled to ground. This current flows through the output pin to ground. The state of the shutdown pin will have no effect on output current when the input pin is pulled to ground.

In some applications it may be necessary to leave the input on the LT1521 unconnected when the output is held high. This can happen when the LT1521 is powered from a rectified AC source. If the AC source is removed, then the input of the LT1521 is effectively left floating. The reverse output current also follows the curve in Figure 3




Figure 3. Reverse Output Current

if the input pin is left open. The state of the shutdown pin will have no effect on the reverse output current when the input pin is floating.

When the input of the LT1521 is forced to a voltage below its nominal output voltage and its output is held high, the output current will follow the curve shown in Figure 3. This can happen if the input of the LT1521 is connected to a discharged (low voltage) battery and the output is held up by either a backup battery or by second regulator circuit. When the input pin is forced below the output pin or the output pin is pulled above the input pin, the input current will typically drop to less than $2\mu A$ (see Figure 4). The state of the shutdown pin will have no effect on the reverse output current when the output is pulled above the input.





Figure 4. Input Current

Table 4. Fault Conditions

INPUT PIN	SHDN PIN	OUTPUT/SENSE PINS	RESULTING CONDITIONS
< V _{OUT} (Nominal)	Open (High)	Forced to V _{OUT} (Nominal)	Reverse Output Current \approx 5µA (See Figure 3) Input Current \approx 1µA (See Figure 4)
< V _{OUT} (Nominal)	Grounded	Forced to V _{OUT} (Nominal)	Reverse Output Current \approx 5µA (See Figure 3) Input Current \approx 1µA (See Figure 4)
Open	Open (High)	> 1V	Reverse Output Current \approx 5µA (See Figure 3)
Open	Grounded	> 1V	Reverse Output Current ≈ 5µA (See Figure 3)
≤ 0.8V	Open (High)	≤ 0V	Output Current = 0
≤ 0.8V	Grounded	≤ 0V	Output Current = 0
> 1.5V	Open (High)	≤ 0V	Output Current = Short-Circuit Current
-20V < V _{IN} < 20V	Grounded	≤ 0V	Output Current = 0

PACKAGE DESCRIPTION



MS8 Package 8-Lead Plastic MSOP (Reference LTC DWG # 05-08-1660 Rev G)

1. DIMENSIONS IN MILLIMETER/(INCH)

2. DRAWING NOT TO SCALE

3. DIMENSION DOES NOT INCLUDE MOLD FLASH, PROTRUSIONS OR GATE BURRS.


MOLD FLASH, PROTRUSIONS OR GATE BURRS SHALL NOT EXCEED 0.152mm (.006") PER SIDE

4. DIMENSION DOES NOT INCLUDE INTERLEAD FLASH OR PROTRUSIONS.


INTERLEAD FLASH OR PROTRUSIONS SHALL NOT EXCEED 0.152mm (.006") PER SIDE

5. LEAD COPLANARITY (BOTTOM OF LEADS AFTER FORMING) SHALL BE 0.102mm (.004") MAX

PACKAGE DESCRIPTION




S8 Package 8-Lead Plastic Small Outline (Narrow .150 Inch) (Reference LTC DWG # 05-08-1610 Rev G)



S08 REV G 0212

PACKAGE DESCRIPTION



ST Package 3-Lead Plastic SOT-223 (Reference LTC DWG # 05-08-1630)

REVISION HISTORY (Revision history begins at Rev C)

REV	DATE	DESCRIPTION	PAGE NUMBER
С	12/20	Corrected the output voltage formula of the Adjustable Operation.	10

Information furnished by Analog Devices is believed to be accurate and reliable. However, no responsibility is assumed by Analog Devices for its use, nor for any infringements of patents or other rights of third parties that may result from its use. Specifications subject to change without notice. No license is granted by implication or otherwise under any patent or patent rights of Analog Devices.

RELATED PARTS

PART NUMBER	DESCRIPTION	COMMENTS
LTC®1174	425mA High Efficiency Step-Down Switching Regulator	>90% Efficiency, SO-8 Package
LT1175	500mA Micropower Low Dropout Negative Linear Regulator	Selectable Current Limit
LT1120A	125mA Micropower Low Dropout Linear Regulator	20µA Quiescent Current, Includes Comparator
LT1304	Micropower Step-Up DC/DC Converter	15µA Quiescent Current, 1.5 Minimum Input
LT1529	3A Micropower Low Dropout Regulator	50µA Quiescent Current
LT1761	100mA Low Noise Micropower Low Dropout Regulator	I_Q = 30µA, Low Noise 20µVRMS, V_{IN} = 1.8V to 20V, ThinSOT $^{\otimes}$
LT1762	150mA Low Noise Micropower Low Dropout Regulator	I_Q = 30µA, Low Noise 20µVRMS, V_{IN} = 1.8V to 20V, MSOP-8
LT1763	500mA Low Noise Micropower Low Dropout Regulator	I_Q = 30µA, Low Noise 20µVRMS, V_{IN} = 1.8V to 20V, SO-8
LT1962	300mA Low Noise Micropower Low Dropout Regulator	I_Q = 30µA, Low Noise 20µVRMS, V_{IN} = 1.8V to 20V, MSOP-8

