OPTOELECTRONICS





VAOL-3LSBY1

#### Feature

#### **Package Dimension**

0.25


- Low Power Consumption
- High Intensity
- I.C. compatible

### Applications

- Commercial Outdoor Sign Board
- Front Panel Indicator
- Dot-Matrix Module
- LED Bulb

#### Description

- These High Intensity LEDs are Based on InGaN/Sapphire Material Technology
- Emitted color:Blue
- Milkey Diffusion Lens



mm

## Absolute Maximum Ratings at Ta=25°C

Symbol	Parameter	Max.	Unit			
PD	Power Dissipation	120	mW			
VR	Reverse Voltage	5	V			
IAF	Average Forward Current	30	mA			
IPF	Peak Forward Current (Duty=0.1 , 1kHz)	100	mA			
	Derating Linear Form 25°C	0.4	mA / ℃			
Topr	Operating Temperature Range	-40 to $+80$	°C			
Tstg	Storage Temperature Range	-40 to $+100$	°C			
Lead Soldering Temperature [1.6mm (0.063inch) From Body] 260°C For 5 Seconds.						


### Electrical / Optical Characteristics and Curves at Ta=25°C

Symbol	Parameter	Test Condition	Min.	Тур.	Max.	Unit
VF	Forward Voltage	IF = 20 mA		3.5	4.0	V
IR	Reverse Current	VR = 5 V			50	$\mu A$
riangle  heta	Half Intensity Angle	IF = 20 mA		60		Deg.
IV	Luminous Intensity	IF= 20 mA		1200		mcd.
λd	Dominant Wavelength	IF = 20 mA		470		nm

190 bosstick blvd, ste 101 san marcos, ca 92069 phone 760.560.1300 fax 760.560.1301







### Electrical Characteristics at Ta=25℃

Intensity: Tolerance of minimum and maximum =  $\pm$  15%

Vf: Tolerance of minimum and maximum =  $\pm 0.05$ v

NOTE:


lighting:theway

1. Static electricity and surge damages the LED. It is recommend to use a anti-static wrist band or anti-electrostatic glove when handing the LEDs. All devices, equipment and machinery must be properly grounded.

2. Specific binning requirements- please contact our home office

#### **Radiation Diagram**

#### IF=20 mA 50% Power Angle Angle =60°









OPTOELECTRONICS




## BLUE

## Typical Electro-optical Characteristic Curves (25°C Free Air Temperature Unless Otherwise Specified)


Forward Current (mA DC)

Relative Intensity


Forward Current (mA)




Forward Current Vs. Forward Valtage





Relative Intensity Vs. Forward Current



Relative Intensity Vs. Lead Temperarture (Pulsed 20 mA; 300us pulse, 10ms period)







Peak Forward Voltage Vs. Forward Current (100us test pulse, 1% duty cycle) 100 75 50 25 0 25 0 0 1 2 3 4 5 6 Forward Voltage (V)

190 bosstick blvd, ste 101 san marcos, ca 92069 phone 760.560.1300 fax 760.560.1301





# **Mouser Electronics**

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

VCC: VAOL-3LSBY1