


TÜV MANAGEMENT SERVICE SERVICE

An ISO/TS16949 and ISO 9001 Certified Company

NPN SILICON PLANAR EPITAXIAL TRANSISTORS

2N5249 2N5249A



TO-92 Plastic Package

Designed for High Gain Amplifier Applications

ABSOLUTE MAXIMUM RATINGS (T_a=25°C unless specified otherwise)

DESCRIPTION	SYMBOL	VALUE	UNITS	
Collector Base Voltage	V _{CBO}	70	V	
Collector Emitter Voltage	V _{CEO}	50	V	
Emitter Base Voltage	V _{EBO}	5.0	V	
Collector Current	I _C	100	mA	
Power Dissipation	P _D	625	mW	
Operating And Storage Junction Temperature Range	T_{j},T_{stg}	- 65 to +150	°C	

ELECTRICAL CHARACTERISTICS (T_a=25°C unless specified otherwise)

DESCRIPTION	SYMBOL	TEST CONDITION	MIN	TYP	MAX	UNITS
Collector Cut off Current	I _{CBO}	V_{CB} =50V, I_E =0			30	nA
		$V_{CB}=50V, I_{E}=0, T_{a}=100^{\circ}C$			10	μΑ
Collector Cut Off Current	I _{CES}	V _{CE} =50V, V _{BE} =0			30	nA
Emitter Cut Off Current	I _{EBO}	$V_{EB} = 5V, I_{C} = 0$			50	nA
Collector Base Voltage	V_{CBO}	$I_{C}=10\mu A, I_{E}=0$	70			V
Collector Emitter Voltage	V_{CEO}	$I_C=10$ mA, $I_B=0$	50			V
Emitter Base Voltage	V_{EBO}	$I_{E}=10\mu A, I_{C}=0$	5.0			V
Collector Emitter Saturation Voltage	V _{CE (sat)}	I _C =10mA, I _B =1mA			0.125	V
Base Emitter On Voltage	V _{BE (on)}	$V_{CE}=10V$, $I_{C}=2mA$	0.5		0.90	V
Base Emitter Saturation Voltage	V _{BE (sat)}	I _C =10mA, I _B =1mA			0.78	V
DC Current Gain	h _{FE}	V_{CE} =5V, I_{C} =100 μ A		350		
		V_{CE} =5V, I_{C} =2mA	400		800	


DYNAMIC CHARACTERISTICS

BINAMIO CHARACIERIO 1100							
DESCRIPTION	SYMBOL	SYMBOL TEST CONDITION		TYP	MAX	UNITS	
Small Signal Current Gain	h _{fe}	V_{CE} =10V, I_{C} =2mA, f=1KHz	400		1200		
Collector Capacitance	C_cbo	$I_E=0$, $V_{CB}=10V$, $f=1MHz$			4	pF	
Noise Figure	NF	I _C =100μA, V _{CE} =5V f=1KHz, BW=15.7KHz Rg=5KΩ					
		only 2N5249A			5	dB	

2N5249_A Rev010303E

TO-92 Plastic Package

TO-92 Plastic Package



The TO-92 Package, Tape and Ammo Pack Drawings are correct as on the date of issue/revision of this Data Sheet.

The currently valid dimensions and information, may please be confirmed from the TO-92 Drawing in the Packages and Packing Section of the Product Catalogue.


Packing Details

PACKAGE	STANDARD PACK		INNER CARTON BOX		OUTER CARTON BOX		
	Details	Net Weight/Oty	Size	Qty	Size	Qty	Gr Wt
TO-92 Bulk	1K/polybag	200 gm/1K pcs	3" x 7.5" x 7.5"	5K	17" x 15" x 13.5"	80K	23 kgs
TO-92 T&A	2K/ammo box	645 gm/2K pcs	12.5" x 8" x 1.8"	2K	17" x 15" x 13.5"	32K	12.5 kgs

2N5249_A Rev010303E

TO-92 Plastic Package

TO-92 Tape and Ammo Pack



All dimensions are in mm

		SPECIFICATION					
ITEM	SYMBOL	MIN.	NOM.	MAX.	TOL.		
BODY WIDTH	A1	4.0		4.8			
BODY HEIGHT	А	4.8		5.2			
BODY THICKNESS	Т	3.9		4.2			
PITCH OF COMPONENT	Р		12.7		± 1.0		
*1FEED HOLE PITCH	Po		12.7		± 0.3		
*2 FEED HOLE CENTRE TO COMPONENT CENTRE	P2		6.35		+ 0.4		
DISTANCE BETWEEN OUTER							
LEADS	F		5.08		+ 0.6 - 0.2		
*3 COMPONENT ALIGNMENT SIDE VIEW	∆h		0	1.0			
*4 COMPONENT ALIGNMENT FRONT VIEW	△h1		0	1.3			
TAPE WIDTH	W		18		± 0.5		
HOLD-DOWN TAPE WIDTH	Wo		6		± 0.2		
HOLE POSITION	W1		9		+ 0.7		
					- 0.5		
HOLD-DOWN TAPE POSITION	W2		0.5		± 0.2		
LEAD WIRE CLINCH HEIGHT	Но		16		± 0.5		
COMPONENT HEIGHT	H1			23.25			
LENGTH OF SNIPPED LEADS	L			11.0			
FEED HOLE DIAMETER	Do		4		± 0.2		
*5 TOTAL TAPE THICKNESS	t			1.2			
LEAD - TO - LEAD DISTANCE	F1, F2		2.54		+ 0.4 - 0.1		
STAND OFF	H2	0.45		1.45	011		
CLINCH HEIGHT 0	Н3			3.0			
LEAD PARALLELISM	C1 - C2			0.22			
PULL - OUT FORCE	(p)	6N					

NOTES

- 1. Maximum alignment deviation between leads will not to be greater than 0.2mm.
- 2. Maximum non-cumulative variation between tape feed holes shall not exceed 1 mm in 20 pitches.
- 3. Holddown tape will not exceed beyond the edge(s) of carrier tape and there shall be no exposure of adhesive.
- 4. There will be no more than three (3) consecutive missing components in a tape.
- 5. A tape trailer, having at least three feed holes are provided after the last component in a tape.
- 6. Splices should not interfere with the sprocket feed holes.

REMARKS

- *1 Cumulative pitch error 1.0 mm/20 pitch
- *2 To be measured at bottom of clinch
- *3 At top of body
- *4 At top of body
- *5 t1 0.3 0.6 mm

2N5249_A Rev010303E

Notes 2N5249 2N5249A

TO-92 Plastic Package

Disclaimer

The product information and the selection guides facilitate selection of the CDIL's Discrete Semiconductor Device(s) best suited for application in your product(s) as per your requirement. It is recommended that you completely review our Data Sheet(s) so as to confirm that the Device(s) meet functionality parameters for your application. The information furnished in the Data Sheet and on the CDIL Web Site/CD are believed to be accurate and reliable. CDIL however, does not assume responsibility for inaccuracies or incomplete information. Furthermore, CDIL does not assume liability whatsoever, arising out of the application or use of any CDIL product; neither does it convey any license under its patent rights nor rights of others. These products are not designed for use in life saving/support appliances or systems. CDIL customers selling these products (either as individual Discrete Semiconductor Devices or incorporated in their end products), in any life saving/support appliances or systems or applications do so at their own risk and CDIL will not be responsible for any damages resulting from such sale(s).

CDIL strives for continuous improvement and reserves the right to change the specifications of its products without prior notice.



Continental Device India Limited
C-120 Naraina Industrial Area, New Delhi 110 028, India.
Telephone + 91-11-2579 6150, 5141 1112 Fax + 91-11-2579 5290, 5141 1119
email@cdil.com www.cdilsemi.com