Resistors

Electronics

General Purpose Cement Coated Wirewound Resistors

WA80 Series

Features

- Surface mount ZI-form option
- Flameproof protection
- Can replace carbon comp. in many applications
- Resistance values down to 0.01 ohms
- Ideal for pulse handling applications




All Pb-free parts comply with EU Directive 2011/65/EU amended by (EU) 2015/863 (RoHS3)

Electrical Data

		WA82	WA83	WA835	WA84	WA85
Power rating at 25°c	watts	1	2.0	2.5	3.0	5
Power rating at 70°c	watts	.86	1.6	2.0	2.5	4.3
Resistance range	ohms	0R068 to 430	0R05 to 900R	0R05 to 900R	0R01 to 2K2	0R015 to 6K8
Limiting element voltage	volts	50	50	75	100	150
Isolation voltage	volts	250	250	250	350	500
TCR	ppm/°C	<1Ω:350 >1Ω:200				
Resistance tolerance	%	<20R: 5, 10 ≥20R: 1, 2, 5, 10				
Values		E24 preferred				
Thermal impedance	°C/watt	140	110	90	82	54
Ambient temperature range	°C	- 55 to 155				

Physical Data

Dimensi	Dimensions (mm) and Weight (g)								
					PCB	Min			
					mounting	bend	Wt		
Туре	L max.	D max.	f min.	d nom.	centres	radius	nom.		
WA82	6.2	2.8	21.20	0.6	10.20	0.6	0.22		
WA83	9.0	3.6	19.80	0.8	12.70	1.2	0.50		
WA835	12.5	4.5	17.80	0.8	18.40	1.2	0.50		
WA84	14.5	5.2 (Note 1)	24.55	0.8	20.30	1.2	1.10		
WA85	16.5	7.0 (Note 2)	23.55	0.8	22.86	1.2	1.75		



Note 1: 5.4 for values ≤0R1 Note 2: 7.2 for values ≤0R1

Construction

A high quality ceramic substrate is assembled with interference fit end caps to which are welded the termination wires. The resistive element is wound on the substrate and welded to the caps. Cement protection is applied to the resistor body before marking with indelible ink.

Terminations

Material Hot tin dipped copper wire

Strength The terminations meet requirements of

IEC 68.2.21.

Solderability The terminations meet the requirements of IEC 115-1, Clause 4.17.3.2.

BI Technologies IRC Welwyn

General Purpose Cement Coated Wirewound Resistors

WA80 Series



Marking

WA85 resistors are legend marked with type reference, resistance value and tolerance. In conformance with IEC 62.

WA82, 83, 835 and 84 resistors 0R1 and above are colour coded with 4 bands in conformance with IEC 62. Values below 0R1 are 3 band marked, two digits and tolerance, there is no multiplier band.

Solvent Resistance

The body protection and marking are resistant to all normal industrial cleaning fluids suitable for printed circuits.

Flammability

The resistor coating will not burn under any condition of applied temperature or component overload.

Performance Data

		Maximum	Typical	
Load at rated power: 1000 hrs at 25 or 70°c	ΔR%	5.0 + .001Ω	3.0	
Dry heat: 1000 hrs at 200°c	ΔR%	5.0 + .001Ω	3.0	
Derating from rated power at 25°c		See derating curve		
Short term overload	ΔR%	5.0 + .001Ω	1.0	
Climatic	ΔR%	5.0 + .001Ω	2.0	
Climatic category	ΔR%	55/200/56Ω		
Long term damp Heat: 56 days	ΔR%	5.0 + .001Ω	1.0	
T.R.C. & Vibration	ΔR%	5.0 + .001Ω	1.0	
Robustness & Solder Heat	ΔR%	5.0 + .001Ω	1.0	
Pulse Handling		Data available by request		

Application Notes

Care must be taken when determining clearance between the resistor body and the P.C.B. or other components. Resistance is measured 6mm from body.

Packaging

All resistors are supplied tape packed ready for loading onto automatic sequencing and insertion machines. The critical dimensions are shown in figure 2.

Component wires will not protrude beyond the outside edge of the tapes.

All taped resistors will be supplied either on reels or in ammopacks, depending upon quantities orderded.

WA80 resistors can be supplied with radial, goalpost or lancet pre-formed leads- see

https://www.ttelectronics.com/TTElectronics/media/ProductFiles/Resistors/ApplicationNotes/TN008-resistors-Leadform-Capability.pdf.

WA83, 84 and 85 is also available in ZI-form SMD format packed in blister tape- see

https://www.ttelectronics.com/TTElectronics/media/ProductFiles/Resistors/Datasheets/ZI-form.pdf (a) and (b) and (b) and (b) are also as a finite of the control of the co





Figure 2



Туре	WA82	WA83	WA835	WA84	WA85
b	52	52	52	67	63
С	5	5	5	10	10

General Note

TT Electronics reserves the right to make changes in product specification without notice or liability.

All information is subject to TT Electronics' own data and is considered accurate at time of going to print.

BI Technologies IRC Welwyn

General Purpose Cement Coated Wirewound Resistors



WA80 Series

Ordering Procedure

Example: WA83-470RJI (WA83, 470 ohms ±5%, Pb-free)



ſ	1	2	3		4		
	Туре	Value	Tolerance	ce Packing			
	WA82	E24 = 3/4 characters	F = ±1%			WA82	5000/box
	WA83	R = ohms	G = ±2%		۸ mma	WA83	2500/box
	WA835	K = kilohms	J = ±5%	Ι	Ammo	WA835	1500/box
	WA84		K = ±10%			WA84	1000/box
	WA85				Tape	WA85	750/reel

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

TT Electronics:

 WA8510R0J
 WA8522R0J
 WA8522R0JTR
 WA84-10RJI
 WA83-820RKI
 WA83-390RJI
 WA84-30RJI
 WA84-2R2JI

 WA83-100RJI
 WA83-330RJI
 WA83-680RJI
 WA84-15RJI
 WA84-182JI
 WA84-47RJI
 WA8505-22RJI

 WA83-82RJI
 WA84-82RJI
 WA83-R05JI
 WA83-10RJI
 WA83-180RJI
 WA83-22RJI
 WA83-220RJI
 WA83-4R7JI

 WA83-47RJI
 WA83-470RJI
 WA8307-100RJI
 WA835-200RJI
 WA84-1R0JI
 WA84-1R5JI
 WA84-100RJI
 WA84-12RJI

 WA84-150RJI
 WA84-180RJI
 WA84-22RJI
 WA84-220RJI
 WA84-330RJI
 WA84-5R6JI
 WA84-68RJI

 WA83-2R7JI
 WA84-3R9JI
 WA84-4R7JI
 WA84-8R2JI
 WA8510-2K2JI
 WA84-18RJI
 WA84-560RJI
 WA84-270RJI

 WA84-120RJI
 WA84-1R8JI
 WA8505-6R2JI
 WA84-2R7JI
 WA8505-6R2JT075
 WA84-1K2JI
 WA84-820RJI
 WA84-820RJI