

Special Load PCB Relay RP3SL

- 1 pole 16A, 1 form A (NO) contact
- For high inrush currents up to 120A
- Mono- or bistable
- 4kV/8mm coil-contact

Typical applications

Lighting control, timers, motor control, building automation.







Approvals
VDE Cert. No. 40025448 (DC versions only), UL E214024
Technical data of approved types on request.

Comtact Data	
Contact Data	
Contact arrangement	1 form A (NO)
Rated voltage	250VAC
Max. switching voltage	400VAC
Rated current	
flux proof version	16A
wash tight version	12A
Limiting making current	
max. 4 s, duty factor 10 %	25A
max. 20 ms (incandescent lamp)	120A
Breaking capacity max.	
flux proof version	4000VA
wash tight version	3000VA
Contact material	AgSnO
Frequency of operation, with/without load	960/72000h ⁻¹
Operate/release time max., monostable	14/12ms
Set/reset time max., bistable	30/25ms
Bounce time max.	
monostable	5/7ms
bistable	5/15ms

bistable

Contact r	atings		
Type Contact		Load	Cycles
IEC61810			
RP3SL A (NO)		16A, 250VAC resistive, 70°C	50x10 ³
RP7SL	SL A (NO) 12A, 250VAC resistive, 70°C		100x10 ³
Mechanical endurance monostable		>20x10 ⁶ operatio	ns







>1x10⁶ operations

Coil Data	
Coil data, monostable coil	
Coil voltage range	5 to 110VDC
Operative range, IEC 61810	
flux proof version	2
wash tight version	1

Coil vers	sions, DC co	il			
Coil	Rated	Operate	Release	Coil	Rated coil
code	voltage	voltage	voltage	resistance	power
	VDC	VDC	VDC	$\Omega \pm 10\%^{1)}$	mW
005	5	3.8	0.5	54	500
006	6	4.5	0.6	68	500
012	12	9.0	1.2	270	500
024	24	18.0	2.4	11001)	500
048	48	36.0	4.8	44001)	500
060	60	45.0	6.0	6540 ¹⁾	500





Coil Data, bistable coil	1 coil	2 coils		
Coil voltage range	5 to 24VDC			
Operative range, IEC 61810	1			
Reset voltage min/max, % of Urtd	70/110%	75/120%		
Min./Max. energization duration	20ms/1min at < 50%DF			

	Coil	versions,	bistable
--	------	-----------	----------

Coil	Rated	Set	Reset	Reset	Coil	Rated coil
code	voltage	voltage	voltage	R1	resistance	power
	VDC	VDC	VDC	Ω/W	$\Omega \pm 10\%^{1)}$	mW
Coil ver	sions, bis	table 1 co	il			
A05	5	3.7	3.6	39/0.5	21	1250
A12	12	9.0	8.7	220/0.5	115	1250
A24	24	18.0	16.7	820/0.5	460	1250
Coil ver	sions, bis	table 2 co	ils			
F12	12	9.0	9.0		105 ¹⁾	1250
F24	24	18.0	18.0		460 ¹⁾	1250

1) Coil resistance ±15%.

All figures are given for coil without pre-energization, at ambient temperature +23°C, duty factor 20%. Other coil voltages on request.

10-2014, Rev. 1014 www.te.com © 2014 Tyco Electronics Corporation, a TE Connectivity Ltd. company.

Catalog and product specification according to IEC 61810-1 and to be used only together with the 'Definitions' section.

Catalog and product data is subject to the terms of the disclaimer and all chapters of the 'Definitions' section, available at http://relays.te.com/definitions

Catalog product data, 'Definitions' section, application notes and all specifications are subject to change.



Special Load PCB Relay RP3SL (Continued)

Insulation Data	
Initial dielectric strength	
between open contacts	2000V _{ms}
between contact and coil	4000V _{ms}
Clearance/creepage	1110
between contact and coil	≥8/8mm
Material group of insulation parts	Illa
Tracking index of relay base	PTI250V

Other Data

Material compliance: EU RoHS/ELV, China RoHS, REACH, Halogen content refer to the Product Compliance Support Center at www.te.com/customersupport/rohssupportcenter

Ambient temperature flux proof version

-40 to +70°C -40 to +35°C

wash tight version Category of environmental protection IEC 61810

RTII - flux proof, RTIII - wash tight

Vibration resistance (functional), form A contact Shock resistance (destructive) Terminal type Mounting distance, 12A/16A 20g 100g PCB-THT 0mm/≥3mm 18g


Weight
Resistance to soldering heat THT, IEC 60068-2-20
flux proof version 2

68-2-20 270°C/10s 260°C/5s

wash tight version
Packaging/unit


monostable and bistable 1coil version tube/20 pcs., box/500 pcs. bistable 2coil version tray/25 pcs., box/100 pcs.


Circuit scheme for bistable 1 coil



PCB layout / terminal assignment

Bottom view on solder pins






Bistable versions:

Indicated contact position during or after coil energization with reset voltage.

2-coil versions: Operate A2, A3 Reset A1, A3

b) for 2 coil version only

Dimensions





Special Load PCB Relay RP3SL (Continued)

Prod	uct code structure			Typical product	code	RP	3	SL	012
Туре						J			
	RP Special Load PCB Relay RP 3 SL								
Versio	on								
	3 Flux proof	7	Wash tight						
Conta	ct configuration / contact material							•	
	SL 1 form A contact (1 NO), AgSnO ₂								
Coil									-
	Coil code: please refer to coil versions table								

Product code	Version	Contact material	Coil version	Coil	Part number
RP3SL005	1 form A (NO) contact	AgSnO	DC coil	5VDC	1393230-7
RP3SL012	16A			12VDC	1393230-9
RP3SL018	flux proof			18VDC	1-1393230-0
RP3SL024				24VDC	1-1393230-1
RP3SL048				48VDC	1-1393230-2
RP3SL060				60VDC	1-1393230-3
RP3SLA06			Bistable 1 coil	6VDC	1393230-2
RP3SLA24				24VDC	1393230-4
RP3SLF12			Bistable 2 coils	12VDC	1393230-5

This list represents the most common types and does not show all variants covered by this datasheet. Other types on request.