

Han B Base Surface HC for central lever



Image is for illustration purposes only. Please refer to product description.

| | |
|--------------------|---|
| Part number | 09 30 016 0281 |
| Specification | Han B Base Surface HC for central lever |
| HARTING eCatalogue | https://b2b.harting.com/09300160281 |

Identification

| | |
|--------------------------|-------------------------|
| Category | Hoods/Housings |
| Series of hoods/housings | Han [®] B |
| Type of hood/housing | Surface mounted housing |
| Type | High construction |

Version

| | |
|----------------------|---|
| Locking type | Central locking lever (on the hood) |
| Size | 16 B |
| Version | Side entry |
| Cable entry | 2x Pg 29 |
| Field of application | Standard hoods/housings for industrial connectors |

Technical characteristics

| | |
|--|-----------------|
| Limiting temperature | -40 ... +125 °C |
| Degree of protection acc. to IEC 60529 | IP65 |
| Type rating acc. to UL 50 / UL 50E | 4 4X 12 |

Material properties

| | |
|-------------------------|----------------------|
| Material (hood/housing) | Aluminium die-cast |
| Surface (hood/housing) | Powder-coated |
| Colour (hood/housing) | RAL 7037 (dust grey) |
| Material (seal) | NBR |



Pushing Performance

Material properties

| | |
|-----------------------------|-----------|
| RoHS | compliant |
| ELV status | compliant |
| China RoHS | e |
| REACH Annex XVII substances | No |
| REACH ANNEX XIV substances | No |
| REACH SVHC substances | No |

Specifications and approvals

| | |
|-----------|--------|
| Approvals | DNV GL |
| CE | Yes |

Commercial data

| | |
|--------------------------------|--|
| Packaging size | 1 |
| Net weight | 334 g |
| Country of origin | Germany |
| European customs tariff number | 85389099 |
| eCl@ss | 27440202 Shell for industrial connectors |

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HARTING:](#)

[09300160281](#)