
Vishay BCcomponents



DC Film Capacitors MKT Radial Potted Type



FEATURES

- 5.08 mm lead pitch
- Supplied loose in box, taped on ammopack or reel
- AEC-Q200 qualified (rev. D)
- Material categorization: for definitions of compliance please see <u>www.vishay.com/doc?99912</u>


APPLICATIONS

Blocking and coupling, bypass and energy reservoir, telecom, industrial, consumer.

QUICK REFERENCE DATA					
Capacitance range (E12 series)	0.001 µF to 1.5 µF				
Capacitance tolerance	± 10 %, ± 5 %				
Rated DC voltage	50 V, 63 V, 250 V, 400 V, 630 V				
Rated AC voltage	32 V, 40 V, 63 V, 160 V, 220 V				
Climatic testing class acc. to IEC 60068-1	55/100/56 for rated voltage 50 V and 63 V 55/105/56 for rated voltage > 63 V				
Maximum application temperature	100 °C for rated voltage 50 V and 63 V 105 °C for rated voltage > 63 V				
Rated temperature	85 °C				
Reference standards	IEC 60384-2				
Dielectric	Polyester film				
Electrodes	Metallized				
	Mono construction				
Construction	Triple construction for 630 V, 0.00068 μ F to 0.0018 μ F				
Encapsulation	Flame retardant plastic case and epoxy resin (UL-class 94 V-0)				
Leads	Tinned wire				
Marking	C-value; tolerance; rated voltage; manufacturer's symbol; year and week of manufacture; manufacturer's type				
Performance grade	Grade 1 (long life)				

Note

• For more detailed data and test requirements, contact dc-film@vishay.com



Revision: 10-Apr-2019

1 For technical guestions, contact: dc-film@vishav.c Document Number: 28108

For technical questions, contact: <u>dc-film@vishay.com</u> THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. THE PRODUCTS DESCRIBED HEREIN AND THIS DOCUMENT ARE SUBJECT TO SPECIFIC DISCLAIMERS, SET FORTH AT <u>www.vishay.com/doc?91000</u>

ROHS COMPLIANT





COMPOSITION OF CATALOG NUMBER

	PITCHES	CAPACITAN (numerical									MULTIP	LIER
370	5.08 mm			(110	umenca	iiiy <i>)</i>					(nF)
						Ŀ				-	0.1	2
							Exam		0 = 100 nF		1	3
						Ľ	104 =	10 X 1	0 = 100 nF		10	4
											-	-
		BFC2	370		XX	Y١	Y	Υ			100	5
		2222 (*)	370		XX	Y٢	Y	Υ				
	(*) Old ordering number								· 			
TYPE	PACKAGING		LEAD CONFIGURATION		PREFERRED T					TYPE	ES	
	FACKAGING				C-TO		63		100 V		250 V	400 V
		Lead length 4.0 mm + 1.0 mm/- 0.5 mm Lead length 26.0 mm ± 2.0 mm			± 10		1		21		41	51
	Loose in box				± 5 %		1:		22		42	52
					± 10		1	-	25		45	55
370 (standard size)			10.7		<u>±5% 16</u> ±10% 18		-	26 28		46 48	56 58	
(Standard Size)	Taped on reel (1)	$H = 18.5 \text{ mm}; P_0 =$ Reel diameter = 35	12.7 mm; 6 mm		± 10 $\pm 5 \%$		19	-	28		48 49	58
	(-)				± 5 % 19 ± 10 % 75			85		35	65	
	Ammopack ⁽²⁾	$H = 18.5 \text{ mm}; P_0 =$	12.7 mm		$\pm 10\%$ 75 $\pm 5\%$ 76		-	86	-	36	66	
	1	1				-		-				
ТҮРЕ	PACKAGING	LEAD CONFI						PRE	EFERRED	TYPE	S	
ITPE	PACKAGING	LEAD CONFIC	JURATION		C-TO	L.	100		250 V		400 V	630 V
		Lead length			± 10		С		EE		FE	GE
	Loose in box	4.0 mm + 1.0 mm/-	0.5 mm		± 5 %		С	-	EF		FF	GF
	20000 11 000	Lead length 26.0 m	m + 2.0 mm		± 10		С		EH		FH	GH
370		3			± 5 %		C		El		FI	GI
(compact size)	Taped on reel (1)	$H = 18.5 \text{ mm}; P_0 =$	12.7 mm;		± 10		C		EL		FL	GL
		Reel diameter = 35	o mm		± 5 %		CI		EM		FM	GM
	Ammopack (2)	$H = 18.5 \text{ mm}; P_0 = 12.7 \text{ mm}$			± 10		C	_	EB	\rightarrow	FB FC	GB
					± 5 %	/o	U		EC		FC	GC

Notes

• For detailed tape specifications refer to packaging information: www.vishay.com/doc?28139 or end of catalog

⁽¹⁾ Reel diameter = 356 mm is available on request

⁽²⁾ H = in-tape height; P_0 = sprocket hole distance; for detailed specifications refer to packaging information



SPECIFIC REFERENCE DATA (Standard Size)								
DESCRIPTION		VAI	LUE					
Tangent of loss angle:	at 1	kHz	at 10 kHz	at 100 kHz				
$C \le 0.1 \ \mu F$	≤ 75 x	к 10 ⁻⁴	\leq 130 x 10 ⁻⁴	\leq 220 x 10 ⁻⁴				
$0.1 \ \mu F < C \le 0.47 \ \mu F$	≤ 75 2	к 10 ⁻⁴	\le 130 x 10 ⁻⁴	\leq 300 x 10 ⁻⁴				
$0.47 \ \mu F < C \le 1.5 \ \mu F$	≤ 75 2	k 10⁻⁴	\leq 130 x 10 ⁻⁴	-				
Rated voltage pulse slope $(dU/dt)_{B}$ at	50 V _{DC} /63 V _{DC}	100 V _{DC}	250 V _{DC}	400 V _{DC}				
nated voltage pulse slope (do/di)R at	60 V/µs	110 V/µs	330 V/µs	630 V/µs				
R between leads, for $C \leq 0.33 \ \mu F$								
at 10 V; 1 min	$>$ 15 000 M Ω							
at 100 V; 1 min		$>$ 15 000 M Ω	$>$ 30 000 M Ω	$>$ 30 000 M Ω				
RC between leads								
0.33 $\mu F < C \leq 1.0 \ \mu F$ at 10 V; 1 min	> 5000 s							
C > 1.0 μF at 10 V; 1 min	> 1000 s							
C > 0.33 μF at 100 V; 1 min		> 5000 s						
R between interconnecting leads and case (foil method)	> 30 000 MΩ	$>$ 30 000 M Ω	> 30 000 MΩ	$>$ 30 000 M Ω				
Withstanding (DC) voltage (cut off current 10 mA) $^{(1)}$; rise time \leq 1000 V/s rise time 100 V/s	100 V; 1 min	160 V; 1 min	400 V; 1 min	640 V; 1 min				
Withstanding (DC) voltage between leads and case	200 V; 1 min	200 V; 1 min	500 V; 1 min	800 V; 1 min				
Maximum application temperature	100 °C		105 °C					

Note

⁽¹⁾ See "Voltage Proof Test for Metallized Film Capacitors": <u>www.vishay.com/doc?28169</u>

SPECIFIC REFERENCE DATA (Compact Size)							
DESCRIPTION	VALUE						
Tangent of loss angle:	at 1	kHz	at 10 kHz	at 100 kHz			
$C \le 0.1 \ \mu F$	≤ 75 :	x 10 ⁻⁴	≤ 130 x 10 ⁻⁴	≤ 220 x 10 ⁻⁴			
0.1 μ F < C \leq 0.47 μ F	≤ 75 :	x 10 ⁻⁴	\leq 130 x 10 ⁻⁴	\leq 300 x 10 ⁻⁴			
C > 0.47 μF	≤ 75 :	x 10 ⁻⁴	\leq 130 x 10 ⁻⁴	-			
Deted veltage pulse alone (dLl(dt), et	100 V _{DC}	250 V _{DC}	400 V _{DC}	630 V _{DC}			
Rated voltage pulse slope (dU/dt) _R at	37 V/µs	44 V/µs	200 V/µs	540 V/µs			
R between leads, for $C \leq 0.33 \ \mu F$							
at 100 V; 1 min	$>$ 15 000 M Ω	$>$ 30 000 M Ω	$>$ 30 000 M Ω	$>$ 30 000 M Ω			
RC between leads							
C > 0.33 μF at 100 V; 1 min	> 5000 s						
R between interconnecting leads and case (foil method)	> 30 000 MΩ	> 30 000 MΩ	> 30 000 MΩ	> 30 000 MΩ			
Withstanding (DC) voltage (cut off current 10 mA) $^{(1)};$ rise time \leq 1000 V/s rise time 100 V/s	160 V; 1 min	400 V; 1 min	640 V; 1 min	1008 V; 1 min			
Withstanding (DC) voltage between leads and case	200 V; 1 min	500 V; 1 min	800 V; 1 min	1260 V; 1 min			
Maximum application temperature	100 °C 105 °C						

Note

⁽¹⁾ See "Voltage Proof Test for Metallized Film Capacitors": <u>www.vishay.com/doc?28169</u>



Vishay BCcomponents

ELE	ECTRI	ICAL DATA A	ND O	RDERIN	g infof	RMATIO	N (Standa	ard Size)				
					C	ATALOG N			(YYY AND	PACKAGIN	IG	
					PACK		LOOSE	IN BOX		RE	EL	
	CAP.	DIMENSIONS w x h x l	MASS	P ₀ = 12	.5 mm; 2.7 mm		LEADS	LONG	LEADS			C-VALUE
(V)	(µF)	(mm)	(g) ⁽¹⁾	C-TOL. = ± 10 %	C-TOL. = ± 5 %	C-TOL. = ± 10 %	C-TOL. = ± 5 %	C-TOL. = ± 10 %	C-TOL. = ± 5 %	C-TOL. = ± 10 %	C-TOL. = ± 5 %	
				XX (SPQ)								
	1.0		U		PITCH = 5							105
50	1.2 1.5	6.0 x 11.0 x 7.2	0.64	75 (750)	76 (750)	11 (2000)	12 (2000)	15 (1000)	16 (1000)	18 (1000)	19 (1000)	125 155
			U		PITCH = 5						, , ,	
	0.056 0.068 0.082 0.10 0.12 0.15 0.18	2.5 x 6.5 x 7.2	0.18	75 (2000)	76 (2000)	11 (2000)	12 (2000)	15 (1000)	16 (1000)	18 (2000)	19 (2000)	563 683 823 104 124 154 184
63	0.22 0.27 0.33 0.39 0.47	3.5 x 8.0 x 7.2	0.3	75 (1500)	76 (1500)	11 (2000)	12 (2000)	15 (1000)	16 (1000)	18 (1500)	19 (1500)	224 274 334 394 474
	0.56 0.68	4.5 x 9.0 x 7.2	0.42	75 (1000)	76 (1000)	11 (2000)	12 (2000)	15 (1000)	16 (1000)	18 (1000)	19 (1000)	564 684
	0.82	6.0 x 11.0 x 7.2	0.64	75	76	11	12	15	16	18	19	824
	1.0	0.0 X 11.0 X 1.2		(750)	(750) ; PITCH = 5	(2000)	(2000)	(1000)	(1000)	(1000)	(1000)	105
100	0.0010 0.0012 0.0015 0.0022 0.0027 0.0033 0.0039 0.0047 0.0056 0.0068 0.0082 0.010 0.012 0.015 0.018 0.022 0.027 0.033 0.027 0.033 0.039 0.047 0.056 0.068 0.082 0.010	2.5 x 6.5 x 7.2	0.18	85 (2000)	86 (2000)	21 (2000)	22 (2000)	25 (1000)	26 (1000)	28 (2000)	29 (2000)	102 122 152 182 222 272 332 392 472 562 682 822 103 123 153 183 223 273 333 393 473 563 683 823 104
	0.12 0.15 0.18 0.22 0.27	3.5 x 8.0 x 7.2 4.5 x 9.0 x 7.2	0.30	85 (1500) 85	86 (1500) 86	21 (2000) 21	22 (2000) 22	25 (1000) 25	26 (1000) 26	28 (1500) 28	29 (1500) 29	124 154 184 224 274
	0.33 0.39 0.47	6.0 x 11.0 x 7.2	0.64	(1000) 85 (750)	(1000) 86 (750)	(2000) 21 (2000)	(2000) 22 (2000)	(1000) 25 (1000)	(1000) 26 (1000)	(1000) 28 (1000)	(1000) 29 (1000)	334 394 474

Revision: 10-Apr-2019

4 For technical questions, contact: <u>dc-film@vishay.com</u> Document Number: 28108

THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. THE PRODUCTS DESCRIBED HEREIN AND THIS DOCUMENT ARE SUBJECT TO SPECIFIC DISCLAIMERS, SET FORTH AT www.vishay.com/doc?91000



Vishay BCcomponents

					C	ATALOG N	UMBER B	FC2 370 X)	(YYY AND	PACKAGI	NG	
					DPACK	LOOSE IN BOX				RE	EL	
URDC	CAP.	DIMENSIONS w x h x l	MASS (g) ⁽¹⁾	H = 18.5 mm; P ₀ = 12.7 mm		SHORT LEADS		LONG LEADS				C-VALUE
(V)	(µF)	(mm)		C-TOL. = ± 10 %	C-TOL. = ± 5 %	C-TOL. = ± 10 %	C-TOL. = ± 5 %	C-TOL. = ± 10 %	C-TOL. = ± 5 %	C-TOL. = ± 10 %	C-TOL. = ± 5 %	
				XX (SPQ)	XX (SPQ)	XX (SPQ)	XX (SPQ)	XX (SPQ)	XX (SPQ)	XX (SPQ)	XX (SPQ)	
			U _F	RAC = 160 V	; PITCH =	5.08 mm ±	0.30 mm; o	d _t = 0.50 m	m ± 0.05 m	m		
250	0.0010 0.0012 0.0015 0.0022 0.0027 0.0033 0.0039 0.0047 0.0056 0.0068 0.0082 0.010 0.012 0.015 0.018 0.022	2.5 x 6.5 x 7.2	0.18	35 (2000)	36 (2000)	41 (2000)	42 (2000)	45 (1000)	46 (1000)	48 (2000)	49 (2000)	102 122 152 222 272 332 392 472 562 682 822 103 123 153 183 223
	0.027 0.033	3.5 x 8.0 x 7.2	0.30	35 (1500)	36 (1500)	41 (2000)	42 (2000)	45 (1000)	46 (1000)	48 (1500)	49 (1500)	273 333
	0.039 0.047 0.056	4.5 x 9.0 x 7.2	0.42	35 (1000)	36 (1000)	41 (2000)	42 (2000)	45 (1000)	46 (1000)	48 (1000)	49 (1000)	393 473 563
	0.068 0.082 0.10	6.0 x 11.0 x 7.2	0.64	35 (750)	36 (750)	41 (2000)	42 (2000)	45 (1000)	46 (1000)	48 (1000)	49 (1000)	683 823 104
			U _F	RAC = 220 V	; PITCH =	5.08 mm ±	0.30 mm; o	d _t = 0.50 m	m ± 0.05 m	m		
	0.0010 0.0012 0.0015 0.0018 0.0022 0.0027 0.0033 0.0039 0.0047 0.0056 0.0068 0.0082	2.5 x 6.5 x 7.2	0.18	65 (2000)	66 (2000)	51 (2000)	52 (2000)	55 (1000)	56 (1000)	58 (2000)	59 (2000)	102 122 152 222 272 332 392 472 562 682 822
	0.010 0.012 0.015	3.5 x 8.0 x 7.2	0.30	65 (1500)	66 (1500)	51 (2000)	52 (2000)	55 (1000)	56 (1000)	58 (1500)	59 (1500)	103 123 153
	0.018 0.022 0.027	4.5 x 9.0 x 7.2	0.42	65 (1000)	66 (1000)	51 (2000)	52 (2000)	55 (1000)	56 (1000)	58 (1000)	59 (1000)	183 223 273
	0.033 0.039 0.047	6.0 x 11.0 x 7.2	0.64	65 (750)	66 (750)	51 (2000)	52 (2000)	55 (1000)	56 (1000)	58 (1000)	59 (1000)	333 393 473

Notes

• SPQ = Standard Packing Quantity

⁽¹⁾ Weight for short lead product only

Revision: 10-Apr-2019

Document Number: 28108



Vishay BCcomponents

					C	ATALOG N	IUMBER B	FC2 370 X)	YYY AND	PACKAGI	NG		
				AMMO	DPACK		LOOSE	IN BOX		RE	EL		
U _{RDC}	CAP.	wynyi	MASS	v		SHORT LEADS		LONG LEADS				C-VALUE	
(V)	(μF)	(mm)	(g) ⁽¹⁾	C-TOL. = ± 10 %	C-TOL. = ± 5 %	C-TOL. = ± 10 %	C-TOL. = ± 5 %	C-TOL. = ± 10 %	C-TOL. = ± 5 %	C-TOL. = ± 10 %	C-TOL. = ± 5 %		
				XX (SPQ)	XX (SPQ)	XX (SPQ)	XX (SPQ)	XX (SPQ)	XX (SPQ)	XX (SPQ)	XX (SPQ)		
			U	_{RAC} = 40 V	PITCH = 5	5.08 mm ± (0.30 mm; d	_t = 0.50 mr	n ± 0.05 m	m		-	
	0.12											124	
	0.15											154	
	0.18	3.5 x 8.0 x 7.2	0.30	CB	CC	CE	CF	CH	CI	CL	CM	184	
100	0.22		(1500)	(1500)	(2000)	(2000)	(1000)	(1000)	(1500)	(1500)	224		
100	0.27	0.27										274	
												334	
	0.39 0.47	4.5 x 9.0 x 7.2	0.42	CB (1000)	CC (1000)	CE (2000)	CF (2000)	CH (1000)	Cl (1000)	CL (1000)	CM (1000)	394 474	
	0.56	6.0 x 11.0 x 7.2	0.64	CB (750)	CC (750)	CE (2000)	CF (2000)	CH (1000)	CI (1000)	CL (1000)	CM (1000)	564	
	U _{RAC} = 63 V; PITCH = 5.08 mm ± 0.30 mm; d _t = 0.50 mm ± 0.05 mm												
	0.022 0.027	2.5 x 6.5 x 7.2	0.18	EB (2000)	EC (2000)	EE (2000)	EF (2000)	EH (1000)	El (1000)	EL (2000)	EM (2000)	223 273	
	0.033			· · ·	. ,	, ,	. ,	. ,	. ,	. ,	. ,	333	
	0.039											393	
	0.047	0.047 3.5 x 8.0 x 7.2 0.056	0.30	EB (1500)	EC (1500)	EE (2000)	EF (2000)	EH (1000)	EI (1000)	EL (1500)	EM (1500)	473	
250	0.056			(1300)	(1300)	(2000)	(2000)	(1000)	(1000)	(1300)	(1300)	563	
250	0.068											683	
	0.082	4.5 x 9.0 x 7.2	0.42	EB	EC	EE	EF	EH	El	EL	EM	823	
	0.10	4.5 × 9.0 × 7.2	0.42	(1000)	(1000)	(2000)	(2000)	(1000)	(1000)	(1000)	(1000)	104	
	0.12											124	
	0.15	6.0 x 11.0 x 7.2	0.64	EB	EC	EE	EF (2000)		EI (1000)	EL	EM	154	
	0.18		0.01	(750)	(750)	(2000)				(1000)	(1000)	184	
	0.22											224	
		T	U _F	_{AC} = 160 V	; PITCH = {	5.08 mm ±	0.30 mm; c	d _t = 0.50 m	m ± 0.05 m	Im	1	1	
	0.010											103	
	0.012	2.5 x 6.5 x 7.2	0.18	FB (2000)	FC	FE (2000)	FF (2000)	FH (1000)	FI (1000)	FL (2000)	FM	123	
	0.015			(2000)	(2000)	(2000)	(2000)	(1000)	(1000)	(2000)	(2000)	153	
	0.018											183	
	0.022 0.027				50						-14	223 273	
400	0.027	3.5 x 8.0 x 7.2	0.30	FB (1500)	FC (1500)	FE (2000)	FF (2000)	FH (1000)	FI (1000)	FL (1500)	FM (1500)	333	
	0.039			()	()	()	()	()	()	()	()	393	
	0.000			FB	FC	FE	FF	FH	Fl	FL	FM	473	
	0.056	4.5 x 9.0 x 7.2	0.42	(1000)	(1000)	(2000)	(2000)	(1000)	(1000)	(1000)	(1000)	563	
	0.068											683	
	0.082	6.0 x 11.0 x 7.2	0.64	FB	FC	FE	FF	FH	FI	FL	FM	823	
	0.10			(750)	(750)	(2000)	(2000)	(1000)	(1000)	(1000)	(1000)	104	

Revision: 10-Apr-2019

Document Number: 28108



Vishay BCcomponents

ELE	CTRIC	AL DATA AN	ND OF	DERINO) INFOR	MATION	(Compa	ict Size)						
					C	ATALOG N	UMBER B	FC2 370 X)	(YYY AND	PACKAGI	NG			
		DIMENSIONS w x h x l	MASS	AMMOPACK			LOOSE	IN BOX		REEL				
	CAP.			H = 18.5 mm; P ₀ = 12.7 mm		SHORT	SHORT LEADS		LONG LEADS					
(V)	(μF)	(mm)	(g) ⁽¹⁾	C-TOL. = ± 10 %	C-TOL. = ± 5 %	C-TOL. = ± 10 %	C-TOL. = ± 5 %	C-TOL. = ± 10 %	C-TOL. = ± 5 %	C-TOL. = ± 10 %	C-TOL. = ± 5 %			
				XX (SPQ)	XX (SPQ)	XX (SPQ)	XX (SPQ)	XX (SPQ)	XX (SPQ)	XX (SPQ)	XX (SPQ)	YYY		
			U _F	_{AC} = 220 V	; PITCH = {	5.08 mm ±	0.30 mm; d	d _t = 0.50 m	m ± 0.05 m	m				
	0.0010											102		
	0.0012											122		
	0.0015											152		
	0.0018													182
	0.0020			GB (1500)	GC (1500)				GI (1000)	GL (1500)		202		
	0.0022											222		
	0.0024		0.35			05	05	011			GM	242		
	0.0027	3.5 x 8.0 x 7.2				GE (2000)	GF (2000)	GH (1000)			(1500)	272		
	0.0033											332		
630	0.0039											392		
	0.0047											472		
	0.0056											562		
	0.0068											682		
	0.0082											822		
	0.010											103		
	0.012	4.5 x 9.0 x 7.2	0.45	GB	GC	GE	GF	GH	GI	GL	GM	123		
	0.015			(1000)	(1000)	(2000)	(2000)	(1000)	(1000)	(1000)	(1000)	153		
	0.018											183		
	0.022	6.0 x 11.0 x 7.2	0.65	0.65	GE	GF	GH		GL	GM	223			
	0.027		5.0 x 11.0 x 7.2 0.65		(750)	(2000)	(2000)	(1000)	(1000)	(1000)	(1000)	273		
	0.033											333		

Notes

• SPQ = Standard Packing Quantity

⁽¹⁾ Weight for short lead product only



MOUNTING

Normal Use

The capacitors are designed for mounting on printed-circuit boards. The capacitors packed in bandoliers are designed for mounting in printed-circuit boards by means of automatic insertion machines.

For detailed tape specifications refer to packaging information: <u>www.vishay.com/doc?28139</u> or end of catalog.

Specific Method of Mounting to Withstand Vibration and Shock

In order to withstand vibration and shock tests, it must be ensured that stand-off pips are in good contact with the printed-circuit board:


- For pitches \leq 15 mm capacitors shall be mechanically fixed by the leads
- For larger pitches the capacitors shall be mounted in the same way and the body clamped

Space Requirements on Printed Circuit Board

The maximum space for length ($I_{max.}$), width ($w_{max.}$) and height ($h_{max.}$) of film capacitors to take in account on the printed circuit board is shown in the drawings.

• For products with pitch \leq 15 mm, $\Delta w = \Delta I = 0.3$ mm; $\Delta h = 0.1$ mm

Eccentricity defined as in drawing. The maximum eccentricity is smaller than or equal to the lead diameter of the product concerned.



SOLDERING CONDITIONS

For general soldering conditions and wave soldering profile, we refer to the application note: **"Soldering Guidelines for Film Capacitors"**: <u>www.vishay.com/doc?28171</u>

Storage Temperature


 T_{stq} = -25 °C to +35 °C with with relative humidity of maximum 75 % without condensation

Ratings and Characteristics Reference Conditions


Unless otherwise specified, all electrical values apply to an ambient temperature of 23 °C \pm 1 °C, an atmospheric pressure of 86 kPa to 106 kPa and a relative humidity of 50 % \pm 2 %.


For reference testing, a conditioning period shall be applied over 96 h \pm 4 h by heating the products in a circulating air oven at the rated temperature and a relative humidity not exceeding 20 %.





www.vishay.com





(typical curve)

HI

10⁴

f (Hz)

10⁵


Standard size

TTIII


ПП

10³


Max. AC voltage as a function of frequency



Capacitance as a function of ambient temperature (typical curve) for voltages > 63 V



Impedance as a function of frequency



Max. AC voltage as a function of frequency

Revision: 10-Apr-2019

 $T_{amb} \le 85 \text{ °C}, 63 \text{ V}_{DC}$

10²

9

Document Number: 28108

For technical questions, contact: <u>dc-film@vishay.com</u> THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. THE PRODUCTS DESCRIBED HEREIN AND THIS DOCUMENT ARE SUBJECT TO SPECIFIC DISCLAIMERS, SET FORTH AT <u>www.vishay.com/doc?91000</u>

10²

AC Voltage (V)

10¹

10⁰


10¹








CHARACTERISTICS



Max. AC voltage as a function of frequency



Standard size

++++

10⁴

f (Hz)


10⁵

| | | | | | | |


1

10³


Max. AC voltage as a function of frequency



Max. AC voltage as a function of frequency



Max. AC voltage as a function of frequency



Max. AC voltage as a function of frequency

Revision: 10-Apr-2019

10

Document Number: 28108

For technical questions, contact: <u>dc-film@vishay.com</u> THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. THE PRODUCTS DESCRIBED HEREIN AND THIS DOCUMENT ARE SUBJECT TO SPECIFIC DISCLAIMERS, SET FORTH AT <u>www.vishay.com/doc?91000</u>

AC Voltage (V) 00

10²

10¹

10⁰

10¹

 $T_{amb} \le 85 \text{ °C}, 250 \text{ V}_{DC}$


10²

і ттни





www.vishay.com


CHARACTERISTICS





Max. AC voltage as a function of frequency














Max. AC voltage as a function of frequency







Max. AC voltage as a function of frequency

Revision: 10-Apr-2019


11 For technical questions, contact: dc-film@vishay.com Document Number: 28108

THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. THE PRODUCTS DESCRIBED HEREIN AND THIS DOCUMENT ARE SUBJECT TO SPECIFIC DISCLAIMERS, SET FORTH AT www.vishay.com/doc?91000



Vishay BCcomponents


CHARACTERISTICS




Maximum RMS current (sinewave) as a function of frequency

The maximum RMS current is defined by $I_{AC} = \omega \times C \times U_{AC}$.


U_{AC} is the maximum AC voltage depending on the ambient temperature in the curves "Max. RMS voltage and AC current as a function of frequency".



Tangent of loss angle as a function of frequency (typical curve)




Insulation resistance as a function of the ambient temperature (typical curve)




www.vishay.com

SHAY


Max. DC and AC voltage as a function of frequency for voltage 63 V




CHARACTERISTICS



www.vishay.com





Maximum allowed component temperature rise ($\Delta T)$ as a function of the ambient temperature (T_{amb}) for voltages >63~V

HEAT CONDUCTIVITY (G) AS A FUNCTION OF (ORIGINAL) PITCH AND CAPACITOR BODY THICKNESS IN mW/°C

W _{max.}	HEAT CONDUCTIVITY (mW/°C)				
(mm)	PITCH 5 mm				
2.5	2.5				
3.5	3.0				
4.5	4.0				
6.0	5.5				

POWER DISSIPATION AND MAXIMUM COMPONENT TEMPERATURE RISE

The power dissipation must be limited in order not to exceed the maximum allowed component temperature rise as a function of the free ambient temperature.


The power dissipation can be calculated according type detail specification "HQN-384-01/101: Technical Information Film Capacitors", <u>www.vishay.com/doc?28147</u>.

The component temperature rise (Δ T) can be measured (see section "Measuring the component temperature" for more details) or calculated by Δ T = P/G:

- ΔT = component temperature rise (°C)
- P = power dissipation of the component (mW)
- G = heat conductivity of the component (mW/°C)

MEASURING THE COMPONENT TEMPERATURE

A thermocouple must be attached to the capacitor body as in:



The temperature is measured in unloaded (T_{amb}) and maximum loaded condition (T_C).

The temperature rise is given by $\Delta T = T_C - T_{amb}$.

To avoid radiation or convection, the capacitor should be tested in a wind-free box.

Revision: 10-Apr-2019

Document Number: 28108





APPLICATION NOTE AND LIMITING CONDITIONS

These capacitors are not suitable for mains applications as across-the-line capacitors without additional protection, as described hereunder. These mains applications are strictly regulated in safety standards and therefore electromagnetic interference suppression capacitors conforming the standards must be used.

For capacitors connected in parallel, normally the proof voltage and possibly the rated voltage must be reduced. For information depending of the capacitance value and the number of parallel connections contact: <u>dc-film@vishay.com</u>

To select the capacitor for a certain application, the following conditions must be checked:

- 1. The peak voltage (U_P) shall not be greater than the rated DC voltage (U_{RDC})
- 2. The peak-to-peak voltage (U_{P-P}) shall not be greater than $2\sqrt{2} \times U_{RAC}$ to avoid the ionization inception level
- 3. The voltage peak slope (dU/dt) shall not exceed the rated voltage pulse slope in an RC-circuit at rated voltage and without ringing. If the pulse voltage is lower than the rated DC voltage, the rated voltage pulse slope may be multiplied by U_{RDC} and divided by the applied voltage.

For all other pulses following equation must be fulfilled:

$$2 \times \int_{0}^{1} \left(\frac{dU}{dt}\right)^{2} x dt < U_{RDC} \times \left(\frac{dU}{dt}\right)_{rated}$$

T is the pulse duration.

- 4. The maximum component surface temperature rise must be lower than the limits (see figure max. allowed component temperature rise).
- 5. Since in circuits used at voltages over 280 V peak-to-peak the risk for an intrinsically active flammability after a capacitor breakdown (short circuit) increases, it is recommended that the power to the component is limited to 100 times the values mentioned in the table: "Heat conductivity"
- 6. When using these capacitors as across-the-line capacitor in the input filter for mains applications or as series connected with an impedance to the mains the applicant must guarantee that the following conditions are fulfilled in any case (spikes and surge voltages from the mains included).

VOLTAGE CONDITIONS FOR 6 ABOVE								
ALLOWED VOLTAGES	T _{amb} ≤ 85 °C	85 °C < T _{amb} \leq 100 °C FOR 63 V						
ALLOWED VOLTAGES		85 °C < T _{amb} \leq 105 °C FOR > 63 V						
Maximum continuous RMS voltage	U _{RAC}	See "Max. AC voltage as function of temperature CBB952" per characteristics						
Maximum temperature RMS-overvoltage (< 24 h)	1.25 x U _{RAC}	U _{RAC}						
Maximum peak voltage (V _{O-P}) (< 2 s)	1.6 x U _{RDC}	1.3 x U _{RDC}						

EXAMPLE


C = 330 nF - 63 V used for the voltage signal shown in next drawing. $U_{P-P} = 40 V$; $U_P = 35 V$; $T_1 = 100 \mu$ s; $T_2 = 200 \mu$ s

The ambient temperature is $35 \,^{\circ}C$

Checking conditions:

- 1. The peak voltage $U_P = 35 \text{ V}$ is lower than 63 V_{DC}
- 2. The peak-to-peak voltage 40 V is lower than $2\sqrt{2} \times 40 V_{AC} = 113 U_{P-P}$
- 3. The voltage pulse slope (dU/dt) = 40 V/100 μ s = 0.4 V/ μ s This is lower than 60 V/ μ s (see specific reference data for each version)
- 4. The dissipated power is 16.2 mW as calculated with fourier terms The temperature rise for W_{max.} = 3.5 mm and pitch = 5 mm will be 16.2 mW/3.0 mW/°C = 5.4 °C This is lower than 15 °C temperature rise at 35 °C, according figure max. allowed component temperature rise
- 5. Not applicable
- 6. Not applicable

Voltage Signal



Revision: 10-Apr-2019

15

Document Number: 28108



INSPECTION REQUIREMENTS

General Notes

Sub-clause numbers of tests and performance requirements refer to the "Sectional Specification, Publication IEC 60384-2 and Specific Reference Data".

GROUP C INSPECTION REQ	UIREMENTS	
SUB-CLAUSE NUMBER AND TEST	CONDITIONS	PERFORMANCE REQUIREMENTS
SUB-GROUP C1A PART OF SAMPLE OF SUB-GROUP C1		
4.1 Dimensions (detail)		As specified in chapters "MKT 370 General Data" of this specification
4.3.1 Initial measurements	Capacitance Tangent of loss angle: for C ≤ 470 nF at 100 kHz or for C > 470 nF at 10 kHz	
4.3 Robustness of terminations	Tensile and bending	No visible damage
4.4 Resistance to soldering heat	Method: 1A Solder bath: 280 °C ± 5 °C Duration: 10 s	
4.14 Component solvent resistance	Isopropylalcohol at room temperature Method: 2 Immersion time: 5 min ± 0.5 min Recovery time: min. 1 h, max. 2 h	
4.4.2 Final measurements	Visual examination	No visible damage Legible marking
	Capacitance	$\left \Delta C/C \right \leq 2$ % of the value measured initially
	Tangent of loss angle	$\begin{array}{l} \mbox{Increase of tan } \delta \\ \leq 0.005 \mbox{ for: } C \leq 100 \mbox{ nF or } \\ \leq 0.010 \mbox{ for: } 100 \mbox{ nF } < C \leq 220 \mbox{ nF or } \\ \leq 0.015 \mbox{ for: } 220 \mbox{ nF } < C \leq 470 \mbox{ nF and } \\ \leq 0.003 \mbox{ for: } C > 470 \mbox{ nF } \\ \mbox{ Compared to values measured in } 4.3.1 \end{array}$
SUB-GROUP C1B OTHER PART OF SAMPLE OF SUB-GROUP C1		
4.6.1 Initial measurements	Capacitance Tangent of loss angle: for C ≤ 470 nF at 100 kHz or for C > 470 nF at 10 kHz	
4.6 Rapid change of temperature	$\theta A = -55 \ ^{\circ}C$ $\theta B = +100 \ ^{\circ}C$ for rated voltage 63 V $+105 \ ^{\circ}C$ for rated voltage > 63 V 5 cycles Duration t = 30 min	
4.7 Vibration	Visual examination Mounting: see section "Mounting" of this specification Procedure B4 Frequency range: 10 Hz to 55 Hz Amplitude: 0.75 mm or Acceleration 98 m/s ² (whichever is less severe) Total duration 6 h	No visible damage
4.7.2 Final inspection	Visual examination	No visible damage



GROUP C INSPECTION REQUIREMENTS									
SUB-CLAUSE NUMBER AND TEST	CONDITIONS	PERFORMANCE REQUIREMENTS							
SUB-GROUP C1B OTHER PART OF SAMPLE OF SUB-GROUP C1									
4.9 Shock	Mounting: see section "Mounting" of this specification Pulse shape: half sine Acceleration: 490 m/s ² Duration of pulse: 11 ms								
4.9.3 Final measurements	Visual examination	No visible damage							
	Capacitance	$ \Delta C/C \leq 3$ % of the value measured in 4.6.1							
	Tangent of loss angle	Increase of tan δ \leq 0.010 for: C \leq 220 nF or \leq 0.015 for: 220 nF < C \leq 470 nF and \leq 0.003 for: C > 470 nF Compared to values measured in 4.6.1							
	Insulation resistance	As specified in section "Specific Reference Data 370" of this specification							
SUB-GROUP C1 COMBINED SAMPLE OF SPECIMENS OF SUB-GROUPS C1A AND C1B									
4.10 Climatic sequence									
4.10.2 Dry heat	Temperature: +100 °C for rated voltage 63 V +105 °C for rated voltage > 63 V Duration: 16 h								
4.10.3 Damp heat cyclic Test Db, first cycle									
4.10.4 Cold	Temperature: -55 °C Duration: 2 h								
4.10.6 Damp heat cyclic Test Db, remaining cycles	Voltage proof = U_{RDC} for 1 min within 15 min after removal from testchamber	No breakdown of flash-over							
4.10.6.2 Final measurements	Visual examination	No visible damage Legible marking							
	Capacitance	$ \Delta C/C \le 5$ % of the value measured in 4.4.2 or 4.9.3							
	Tangent of loss angle	Increase of tan δ ≤ 0.010 for: C ≤ 220 nF or ≤ 0.015 for: 220 nF < C ≤ 470 nF and ≤ 0.005 for: C > 470 nF Compared to values measured in 4.3.1 or 4.6.1							
	Insulation resistance	\geq 50 % of values specified in section "Specific Reference Data 370" of this specification							
SUB-GROUP C2									
4.11 Damp heat steady state	56 days, 40 °C, 90 % to 95 % RH								
4.11.1 Initial measurements	Capacitance Tangent of loss angle at 1 kHz								

Revision: 10-Apr-2019

17 For technical questions, contact: dc-film@vishay.com Document Number: 28108

THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. THE PRODUCTS DESCRIBED HEREIN AND THIS DOCUMENT ARE SUBJECT TO SPECIFIC DISCLAIMERS, SET FORTH AT www.vishay.com/doc?91000



GROUP C INSPECTION REQUIREMENTS		
SUB-CLAUSE NUMBER AND TEST	CONDITIONS	PERFORMANCE REQUIREMENTS
SUB-GROUP C2		
4.11.3 Final measurements	Voltage proof = U_{RDC} for 1 min within 15 min after removal from testchamber	No breakdown of flash-over
	Visual examination	No visible damage Legible marking
	Capacitance	$ \Delta C/C \le 5$ % of the value measured in 4.11.1.
	Tangent of loss angle	Increase of tan $\delta \leq 0.005$ Compared to values measured in 4.11.1
	Insulation resistance	≥ 50 % of values specified in section "Specific Reference Data 370" of this specification
SUB-GROUP C3		
4.12 Endurance4.12.1 Initial measurements	Duration: 2000 h 1.25 x U_{RDC} at 85 °C 0.8 x 1.25 U_{RDC} at +100 °C for rated voltage 63 V 0.8 x 1.25 U_{RDC} at +105 °C for rated voltage > 63 V Capacitance	
	Tangent of loss angle: For C ≤ 470 nF at 100 kHz or for C > 470 nF at 10 kHz	
4.12.5 Final measurements	Visual examination	No visible damage Legible marking
	Capacitance	$ \Delta C/C \le 5$ % compared to values measured in 4.12.1
	Tangent of loss angle	Increase of tan δ ≤ 0.005 for at 85 °C ≤ 0.010 for at 100 °C for: C \leq 220 nF or ≤ 0.015 for: 220 nF < C \leq 470 nF and ≤ 0.003 for: C > 470 nF Compared to values measured in 4.12.1
	Insulation resistance	≥ 50 % of values specified in section "Specific Reference Data 370" of this specification
SUB-GROUP C4		
4.13 Charge and discharge	10 000 cycles Charged to U _{RDC} Discharge resistance: $R = \frac{U_R}{C \times (2.5 \times (dU/dt)_R)}$	
4.13.1 Initial measurements	Capacitance Tangent of loss angle: For C ≤ 470 nF at 100 kHz or for C > 470 nF at 10 kHz	
4.13.3 Final measurements	Capacitance	$ \Delta C/C \le 3$ % compared to values measured in 4.13.1
	Tangent of loss angle	Increase of tan δ ≤ 0.005 for: C ≤ 100 nF or ≤ 0.010 for: 100 nF < C ≤ 220 nF or ≤ 0.015 for: 220 nF < C ≤ 470 nF and ≤ 0.003 for: C > 470 nF Compared to values measured in 4.13.1
	Insulation resistance	\geq 50 % of values specified in section "Specific Reference Data 370" of this specification

Revision: 10-Apr-2019

18

Document Number: 28108



Vishay

Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.