

## P/N: T198821

### Copyright

© 2015, FLIR Systems, Inc.

All rights reserved worldwide. Names and marks appearing herein are either registered trademarks or trademarks of FLIR Systems and/or its subsidiaries. All other trademarks, trade names or company names referenced herein are used for identification only and are the property of their respective owners.

### Document identity

Publ. No.: T198821

Release:

Commit: 24749

Language: en-US

Modified: 2015-04-15

Formatted: 2015-04-22

### Corporate Headquarters

FLIR Systems, Inc.

27700 SW Parkway Ave.

Wilsonville, OR 97070

USA

Telephone: +1-503-498-3547

### Website

<http://www.flir.com>

### Customer support

<http://support.flir.com>

### Disclaimer


Specifications subject to change without further notice. Camera models and accessories subject to regional market considerations. License procedures may apply. Products described herein may be subject to US Export Regulations. Please refer to [exportquestions@flir.com](mailto:exportquestions@flir.com) with any questions.



<b>General description</b>	
Aluminum cooling bracket for FLIR AX8. See dimensional drawing for mounting holes.	
<b>Physical data</b>	
Weight	0.14 kg (0.31 lb.)
Size (L x W x H)	110 x 60 x 12 mm (4.3 x 2.4 x 0.5 in.)
Color	Blue anodizing
<b>Shipping information</b>	
Packaging, type	Cardboard box
List of contents	<ul style="list-style-type: none"><li>Cooling bracket</li><li>Screws</li></ul>
Packaging, weight	0.240 kg (0.53 lb.)
Packaging, size	157 x 130 x 65 mm (6.2 x 5.1 x 2.6 in.)
EAN-13	4743254002036
UPC-12	845188011161
Country of origin	Sweden

### Compatible with the following products

- 71201-0101; FLIR AX8 9 Hz



**Note 1**  
4x Ø2,6 used to hold the part during surface treatment.

**Note 2**  
Appearance according to FLIR Appearance standard 403093-B Class C, grade 2.

Additional geometry is taken from 3D-file: T128394 A

Konstr/Drawn <b>P. MARCUS</b>	Datum/Date 2014-09-18	Kontr/Check <b>JAMA</b>	Material <b>EN AW-6262 R</b>	FLIR
Där ej annat anges/Unless otherwise stated Gen tol ISO 2768-mk				Skala/Scale 1:1
0,5-6	+0,1	Hålkalibrer	0,1-0,3	BlackSheet 1(1)
(6)-30	+0,2	Fillet radii	0,1-0,3	Size <b>A3</b>
(120)-400	+0,5	Kanter brutna	0,1-0,3	Rev A
(400)-1000	+0,8	Edges broken	0,1-0,3	Ritn nr/Drawing No <b>T128394</b>

**Bracket cooling**