

## FEATURES

- Abrasive grit "anti-slip" tapes
- Additional grip underfoot on smooth surfaces
- Ideal for indicating hazardous areas or safe escape routes
- Hard wearing and easy to install
- Available in a range of grades, lengths and widths
- Long lasting colour
- Self-adhesive backing

## RS PRO Black 18.3m Hazard Tape, 50mm x

RS Stock No.: 762-1506



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

## Product Description

Anti-Slip tapes are designed to provide an extra comfort, confidence and safety on floor surfaces in hazardous areas such as warehouses, factories, stairs or even boats. They are ideal for use in any environment where slipping is a higher risk.

## General Specifications

<b>Colour</b>	Black
<b>Backing Material</b>	Polyethylene
<b>Installation Method</b>	Pressure sensitive self-adhesive tape
<b>Application</b>	Suitable for stairs, ladders, ramps, walkways, vehicles and boats

## Mechanical Specifications

<b>Width</b>	50mm
<b>Length</b>	183mm
<b>Thickness</b>	0.05mm
<b>Tensile Strength</b>	MD: 4.2 kg/15mm, CD: 3.1 kg/15mm
<b>Elongation at Break</b>	200±25%
<b>Adhesive Material</b>	Acrylic
<b>Surface finish</b>	Grit
<b>Grit Size</b>	46grit
<b>Rolling Ball Tack</b>	20cm
<b>Shear Resistance</b>	24hrs(1"X1"@1 kg)
<b>Coating Thickness</b>	0.05mm
<b>Solvent Residual</b>	>0.5%
<b>Adhesion</b>	2.5kg/1"
<b>Release Force</b>	13g/m <sup>2</sup>
<b>Dry Coating Weight</b>	37g/m <sup>2</sup>

## Operation Environment Specifications

<b>Minimum Operating Temperature</b>	10°C
<b>Environmental Resistance</b>	Suitable for an indoor and outdoor environment
<b>UV Resistance</b>	Yes
<b>Safe Temperature Range</b>	-10°C to +60°C
<b>Operation Temperature</b>	10°C +

## Approvals

<b>Compliance/Certifications</b>	EN13552
----------------------------------	---------

