
STPS1545-Y



Automotive power Schottky rectifier

Datasheet - production data



Features

- · Very small conduction losses
- · Negligible switching losses
- · Extremely fast switching
- Avalanche capability specified
- AECQ-101 qualified
- ECOPACK®2 compliant component

Description

Single chip Schottky rectifier suited for switch mode power supply and high frequency DC to DC converters.

Packaged in TO-220AC, this device is especially intended for use in low voltage, high frequency inverters, free wheeling and polarity protection in automotive applications.

Table 1. Device summary

Symbol	Value
I _{F(AV)}	15 A
V_{RRM}	45 V
T _j (max)	175 °C
V _F (typ)	0.50 V

This is information on a product in full production.

Characteristics STPS1545-Y

1 Characteristics

Table 2. Absolute ratings (limiting values)

Symbol	Paramete	Value	Unit	
V_{RRM}	Repetitive peak reverse voltage		45	V
I _{F(RMS)}	Forward rms current		30	Α
I _{F(AV)}	Average forward current δ = 0.5	$T_c = 155$ °C		Α
I _{FSM}	Surge non repetitive forward current	t _p = 10 ms sinusoidal	220	Α
I _{RRM}	Peak repetitive reverse current	epetitive reverse current $t_p = 2 \mu s \text{ square}$ F = 1 kHz		Α
I _{RSM}	Non repetitive peak reverse current $t_p = 100 \mu s square$		3	Α
P _{ARM} ⁽¹⁾	Repetitive peak avalanche power $T_j = 125$ °C, $t_p = 10 \mu s$		400	W
T _{stg}	Storage temperature range	-65 to + 175	°C	
T _j	Operating junction temperature (2)	-40 to + 175	°C	
dV/dt	Critical rate of rise of reverse voltage	10000	V/µs	

For pulse time duration deratings, please refer to Figure 3. More details regarding the avalanche energy
measurements and diode validation in the avalanche are provided in the STMicroelectronics Application
notes AN1768, "Admissible avalanche power of Schottky diodes" and AN2025, "Converter improvement
using Schottky rectifier avalanche specification".

Table 3. Thermal resistances

Symbo	Parameter	Value	Unit
R _{th(j-c)}	Junction to case	1.6	°C/W

Table 4. Static electrical characteristics (per diode)

Symbol	Parameter	Test conditions		Min.	Тур.	Max.	Unit
I _R ⁽¹⁾ F	Reverse leakage current	T _j = 25 °C	V _R =V _{RRM}	-	-	200	μΑ
		T _j = 125 °C		-	11	40	mA
		T _j = 125°C	I _F = 15A	-	0.5	0.57	
V _F ⁽¹⁾	Forward voltage drop	T _j = 25°C	I _F = 30 A	-	-	0.84	V
		T _j = 125 °C	I _F = 30 A	-	0.65	0.72	

^{1.} Pulse test: tp = 380 μ s, δ < 2%

To evaluate the conduction losses use the following equation:

$$P = 0.42 \text{ x I}_{F(AV)} + 0.01 \text{ I}_{F}^{2}_{(RMS)}$$



2/8 DocID023750 Rev 2

^{2.} $\frac{dPtot}{dTj} < \frac{1}{Rth(j-a)} \text{ condition to avoid thermal runaway for a diode on its own heatsink}$

STPS1545-Y Characteristics




Figure 2. Average forward current versus ambient temperature ($\delta = 0.5$) $I_{F(AV)}(A)$ 18 16 TO-220AC 14 12 10 8 6 4 2 T_{amb}(°C) $\delta = tp/T$ 0


Figure 3. Normalized avalanche power deratings versus pulse duration (Tj = 125 °C)


1 PARM(tp)/PARM(10 µs)


0.01

0.01

1 10 100 1000







Characteristics STPS1545-Y

100.0

T_{j=125}°C

(ypical values)

T_{j=25}°C

VFM(V)

0.0

0.1

0.0

0.2

0.4

0.6

0.8

1.0

1.2

1.4

1.6

Figure 7. Forward voltage drop versus forward current (maximum values)



STPS1545-Y **Package information**

Package information 2

Epoxy meets UL94, V0

Cooling method: by conduction (C) Recommended torque value: 0.55 N·m

Maximum torque value: 0.7 N.m

In order to meet environmental requirements, ST offers these devices in different grades of ECOPACK[®] packages, depending on their level of environmental compliance. ECOPACK[®] specifications, grade definitions and product status are available at: www.st.com. ECOPACK® is an ST trademark.

TO-220AC package information 2.1

H2 ØΙ L5 L7 L6 L2 D L9 F1 L4 Ε G

Figure 8. TO-220AC package outline

577

DocID023750 Rev 2

Package information STPS1545-Y

Table 5. TO-220AC package mechanical data

	Dimensions					
Ref.	Millimeters			Inches		
	Min.	Тур.	Max.	Min.	Тур.	Max.
Α	4.40		4.60	0.173		0.181
С	1.23		1.32	0.048		0.051
D	2.40		2.72	0.094		0.107
E	0.49		0.70	0.019		0.027
F	0.61		0.88	0.024		0.034
F1	1.14		1.70	0.044		0.066
G	4.95		5.15	0.194		0.202
H2	10.00		10.40	0.393		0.409
L2		16.40 typ.			0.645 typ.	
L4	13.00		14.00	0.511		0.551
L5	2.65		2.95	0.104		0.116
L6	15.25		15.75	0.600		0.620
L7	6.20		6.60	0.244		0.259
L9	3.50		3.93	0.137		0.154
М		2.6 typ.			0.102 typ.	
Diam. I	3.75		3.85	0.147		0.151

3 Ordering information

Table 6. Ordering information

Order codes	Marking	Package	Weight	Base qty	Delivery mode
STPS1545DY	STPS1545DY	TO-220AC	1.86 mg	50	Tube

4 Revision history

Table 7. Document revision history

Date	Revision	Changes
29-Oct-2012	1	First issue.
02-May-2016	2	Added pin name on package view and reformatted to current standards.



IMPORTANT NOTICE - PLEASE READ CAREFULLY

STMicroelectronics NV and its subsidiaries ("ST") reserve the right to make changes, corrections, enhancements, modifications, and improvements to ST products and/or to this document at any time without notice. Purchasers should obtain the latest relevant information on ST products before placing orders. ST products are sold pursuant to ST's terms and conditions of sale in place at the time of order acknowledgement.

Purchasers are solely responsible for the choice, selection, and use of ST products and ST assumes no liability for application assistance or the design of Purchasers' products.

No license, express or implied, to any intellectual property right is granted by ST herein.

Resale of ST products with provisions different from the information set forth herein shall void any warranty granted by ST for such product.

ST and the ST logo are trademarks of ST. All other product or service names are the property of their respective owners.

Information in this document supersedes and replaces information previously supplied in any prior versions of this document.

© 2016 STMicroelectronics – All rights reserved

57

8/8 DocID023750 Rev 2