



#### Features:

- · Universal AC input / Full range (up to 305VAC)
- Built-in active PFC function
- Protections: Short circuit / Overload / Over voltage / Over temperature
- Cooling by free air convection
- · OCP point adjustable through output cable or internal potential meter
- IP67 / IP65 design for indoor or outdoor installations
- Three in one dimming function (1~10Vdc or PWM signal or resistor)
- · Suitable for LED lighting and street lighting applications
- · Compliance to worldwide safety regulations for lighting
- Suitable for dry / damp / wet location
- 5 years warranty

# W SELV IP65 IP67 🕝 🔊 🕒 🛎 CBC E

HLG-320H-12 A Blank: IP67 rated. Cable for I/O connection.

- A: IP65 rated. Output voltage and constant current level can be adjusted through internal potential meter.
- B: IP67 rated. Constant current level adjustable through output cable with 1~10Vdc or PWM signal or resistor.
- C: Terminal block for I/O connection. Output voltage and constant current level can be adjusted through internal
- D: (option): IP67 rated. Timer dimming function, contact MEAN WELL for details.


#### **SPECIFICATION**


MODEL		HLG-320H-12	HLG-320H-15	HLG-320H-20	HLG-320H-24	HLG-320H-30	HLG-320H-36	HLG-320H-42	HLG-320H-48	HLG-320H-54			
	DC VOLTAGE	12V	15V	20V	24V	30V	36V	42V	48V	54V			
	CONSTANT CURRENT REGION Note.4		7.5 ~ 15V	10 ~ 20V	12 ~ 24V	15 ~ 30V	18 ~ 36V	21 ~ 42V	24 ~ 48V	27 ~ 54V			
	RATED CURRENT	22A	19A	15A	13.34A	10.7A	8.9A	7.65A	6.7A	5.95A			
	RATED POWER	264W	285W	300W	320.2W	321W	320.4W	321.3W	321.6W	321.3W			
	RIPPLE & NOISE (max.) Note.2	150mVp-p	150mVp-p	150mVp-p	150mVp-p	200mVp-p	250mVp-p	250mVp-p	250mVp-p	350mVp-p			
	VOLTAGE ADJ. RANGE Note.6			17 ~ 22V	21 ~ 26V	26 ~ 32V	32 ~ 39V	38 ~ 45V	43 ~ 52V	49 ~ 58V			
OUTPUT		Can be adjusted by internal potential meter or through output cable											
	CURRENT ADJ. RANGE	11 ~ 22A	9.5 ~ 19A	7.5 ~ 15A		5.35 ~ 10.7A	4.45 ~ 8.9A	3.8 ~ 7.65A	3.35 ~ 6.7A	2.97 ~ 5.95A			
	VOLTAGE TOLERANCE Note.3	±3.0%	±2.0%	±1.5%	±1.0%	±1.0%	±1.0%	±1.0%	±1.0%	±1.0%			
	LINE REGULATION	±0.5%	±0.5%	±0.5%	±0.5%	±0.5%	±0.5%	±0.5%	±0.5%	±0.5%			
	LOAD REGULATION	±2.0%	±1.5%	±1.0%	±0.5%	±0.5%	±0.5%	±0.5%	±0.5%	±0.5%			
	SETUP, RISE TIME Note.8	2500ms, 80m	s at full load	230VAC /115V	AC			1		-			
	HOLD UP TIME (Typ.)	15ms at full lo	ad 230VAC	/115VAC									
	VOLTAGE RANGE Note.5	90 ~ 305VAC 127 ~ 431VDC											
	FREQUENCY RANGE	47 ~ 63Hz											
INPUT	POWER FACTOR	PF≧0.95/230	VAC PF	≥0.98/115VAC	at full load and	d rated output v	oltage PF	= ≥ 0.9 at 50 ~	100% load				
	EFFICIENCY (Typ.) (230Vac)	91%	92.5%	93.5%	94%	94%	94.5%	95%	95%	95%			
	EFFICIENCY (Typ.) (277Vac)	91.5%	93%	94%	94.5%	94.5%	95%	95%	95%	95%			
	AC CURRENT	3.5A/115VAC 1.65A/230VAC 1.45A/277VAC											
	INRUSH CURRENT(Typ.)	COLD START 75A/230VAC											
	LEAKAGE CURRENT	<0.75mA/277VAC											
	OVER CURRENT Note.4	95~108%											
		Protection type : Constant current limiting, recovers automatically after fault condition is removed											
	SHORT CIRCUIT	Hiccup mode, recovers automatically after fault condition is removed.											
PROTECTION		14 ~ 17V	18 ~ 21V	23 ~ 27V	28 ~ 34V	34 ~ 38V	41 ~ 46V	47 ~ 53V	54 ~ 60V	59 ~ 65V			
	OVER VOLTAGE	Protection type: Shut down and latch off o/p voltage, re-power on to recover											
		100°C ±10°C (RTH2)											
	OVER TEMPERATURE	Protection type: Shut down and latch off o/p voltage, re-power on to recover											
	WORKING TEMP.	-40 ~ +60 °C (Refer to output load derating curve)											
	WORKING HUMIDITY	20 ~ 95% RH non-condensing											
ENVIRONMENT	STORAGE TEMP., HUMIDITY	-40 ~ +80℃, 10 ~ 95% RH											
	TEMP. COEFFICIENT	±0.03%/°C (0~50°C)											
	VIBRATION	10 ~ 500Hz, 5G 12min./1cycle, period for 72min. each along X, Y, Z axes											
	SAFETY STANDARDS Note.7	UL8750, EN61347-1, EN61347-2-13 independent (except for HLG-320H C type) approved; Design refer to UL60950-1, TU								UV EN60950-1			
	WITHSTAND VOLTAGE	I/P-O/P:3.75	KVAC I/P-F	G:1.88KVAC	O/P-FG:0.5K	CVAC							
SAFETY &	ISOLATION RESISTANCE	I/P-O/P, I/P-FG, O/P-FG:100M Ohms / 500VDC / 25°C / 70% RH											
EMC	EMI CONDUCTION & RADIATION	Compliance to	EN55015, EN	155022 (CISPF	R22) Class B								
	HARMONIC CURRENT	Compliance t	EN61000-3-2	Class C (≥5	0% load) ; EN6	1000-3-3							
	EMS IMMUNITY	Compliance to	DEN61000-4-2	2,3,4,5,6,8,11;	ENV50204, EN	61547, EN550	24, heavy indu	stry level (surg	e 4KV), criteri	аА			
	MTBF	157.1Khrs mi		K-217F (25°C)									
OTHERS	DIMENSION	252*90*43.8r	nm (L*W*H)(Hl	-G-320H-Blank	(/A/B) 256	6*90*43.8mm (	L*W*H)(HLG-3	20H-C)					
	PACKING	1.88Kg; 8pcs/	16Kg/0.83CUF	T									
NOTE	1. All parameters NOT special												
	Ripple & noise are measure     Tolorance : includes set up.					e terminated w	ith a 0.1uf & 4	7uf parallel cap	oacitor.				

- 3. Tolerance : includes set up tolerance, line regulation and load regulation.
  4. Constant current operation region is within 50% ~100% rated output voltage. This is the suitable operation region for LED related applications, but please reconfirm special electrical requirements for some specific system design.
- 5. Derating may be needed under low input voltages. Please check the static characteristics for more details.
- 6. Type A and type C only.
- 7. Safety and EMC design refer to EN60598-1, subject CNS15233, GB7000.1, FCC part18.
- 8. Length of set up time is measured at cold first start. Turning ON/OFF the power supply may lead to increase of the set up time.

  9. The power supply is considered as a component that will be operated in combination with final equipment. Since EMC performance will be affected by the complete installation, the final equipment manufacturers must re-qualify EMC Directive on the complete installation again.







※ IP65 rated. Output voltage and constant current level can be adjusted through internal potential meter. (Can access by removing the rubber stopper on the case.)



# 320W Single Output Switching Power Supply

# B Type:(HLG-320H-\_B) 252 225.2 8.9 300±20 300±20 +V(Red) AC/L(Brown) AC/N(Blue) FG (Green/Yellow) -V(Black) 40 SJTW 14AWG×2C DIM+(Blue) SJTW 18AWGx3C DIM-(White) SJTW 18AWG)×2C

- X IP67 rated. Output constant current level can be adjusted through output cable by connecting a resistor or 1 ∼ 10Vdc or 10V PWM signal between DIM+ and DIM-.
- ※ Please DO NOT connect "DIM-" to "-V".
- X Reference resistance value for output current adjustment (Typical)

Resistance value	<b>10K</b> Ω	<b>20K</b> Ω	30K $Ω$	<b>40K</b> Ω	<b>50K</b> Ω	<b>60K</b> Ω	<b>70K</b> Ω	<b>80K</b> Ω	90ΚΩ	<b>100K</b> Ω	OPEN
Percentage of rated current	10%	20%	30%	40%	50%	60%	70%	80%	90%	100%	98%~108%


# 


Dimming value	1V	2V	3V	4V	5V	6V	7V	8V	9V	10V	OPEN
Percentage of rated current	10%	20%	30%	40%	50%	60%	70%	80%	90%	100%	98%~108%

※ 10V PWM signal for output current adjustment (Typical): Frequency range :100HZ ~ 3KHz

Duty value	10%	20%	30%	40%	50%	60%	70%	80%	90%	100%	OPEN
Percentage of rated current	10%	20%	30%	40%	50%	60%	70%	80%	90%	100%	98%~108%

# C Type:(HLG-320H-\_C)





X Output voltage and constant current level can be adjusted through internal potential meter. (Can access by removing the rubber stopper on the case.)


## AC Input Terminal Pin No. Assignment

5	
Pin No.	Assignment
1	FG ±
2	AC/L
3	AC/N

# DC Output Terminal Pin No. Assignment


Pin No.	Assignment							
1	+V							
2	-V							






X IP67 rated. Timer dimming function, contact MEAN WELL for details.

# **■** Block Diagram



# ■ Derating Curve

# Static Characteristics






# **■** Power Factor Characteristic


Power factor will be higher than 0.9 when output loading is 50% or higher.





# **■** EFFICIENCY vs LOAD (48V Model)

HLG-320H series possess superior working efficiency that up to 95% can be reached in field applications.




# ■ DRIVING METHODS OF LED MODULE

There are two major kinds of LED drive method "direct drive" and "with LED driver".

A typical LED power supply may either work in "constant voltage mode (CV) or constant current mode (CC)" to drive the LEDs.

Mean Well's LED power supply with CV+ CC characteristic can be operated at both CV mode (with LED driver, at area (A) and CC mode (direct drive, at area (B).



Typical LED power supply I-V curve



## O Direct driving:

Under direct driving, the power supply will work in "constant current mode (CC)" and output voltage of the power supply will be clamped by sum of forward voltage (VF) of the LED strip.

The total forward voltage of series connecting LEDs is suggested for 75%~95% of power supply rated output voltage due to concern of the best PF value and efficiency.




## ○ With LED driver :


Using additional driver, the power supply will work in "constant voltage mode (CV)" and output voltage of the power supply will be kept in rated value. In this drive mode, several design issues need to be considered:

- 1.Output voltage of PSU must be higher than total forward voltage of series connecting LEDs by 3V minimum.
- 2.Input capacitor (Cin) of LED driver circuit should use 2.2uF ~ 22uF(typ.) of rating depends on the operating frequency of the LED driver.

  The higher the operating frequency is used, the smaller value of Cin should be chosen, and vice versa.



# **■** EMI DEBUG SUGGESTION




- A. Add a common mode ferrite choke on output wires to reduce the common emission between 10M ~ 300MHz per lighting EMI regulation.
- B. Chassis of LED lamp and chassis of HLG-320H or the FG wire should be connected to the safety ground to reduce the EMI noise, including the conduction and radiation emission.
- C. The additional X-Cap and discharge resistor can reduce the low frequency conduction noise between 9K ~ 1MHz per lighting EMI regulation.
- D. L-C filter should be added at the DC input of LED constant current driver to avoid the differential emission and high frequency noise generated by the CC driver.



# **■** DIMMING OPERATION(for B-type only)

Using the built-in dimming function on B-type model can't turn the lighting fixture totally dark. Please refer to the connection method below to achieve 0% brightness of the lighting fixture connecting to the LED power supply unit.

# O Dimming connection diagram for turning the lighting fixture ON/OFF:



Using a switch and relay can turn ON/OFF the lighting fixture.

- 1. Output constant current level can be adjusted through output cable by connecting a resistor or 1~10Vdc or 10V PWM signal between DIM+ and DIM-.
- 2. The LED lighting fixture can be turned ON/OFF by the switch.