Miniature Rocker Switches multicomp PRO

RoHS Compliant

Non-Illuminated Rocker Switch







MP004406/ MP004407



MP004408 / MP005716



MP005717

Illuminated Rocker Switch

Features

- 13mm × 19mm cut-out
- 4.8mm × 0.8mm faston tabs
- · UL, ENEC, CQC, CE approvals



MP004409





MP004429




MP004430

| Typical Specifications | Small Appliances |
|------------------------|-----------------------------------|
| Functions | SPST, Latching, SPDT, Latching |
| Cycle No. | 50.000 |
| Cut Out | 19mm × 13mm |
| Ambient Temperature | 125°C |
| GWT | 850°C |
| GWT No Flame (<2Sec) | 750°C on Demand |








| 1 | | |
|---|--|--|

| | 00.00. | | |
|-----------|--------------|-----------|--|
| Z | Υ | X | |
| 0.75-1.25 | 19 +0.2 -0 | 13 ±0.1 | |
| 1.25-2 | 19.3 +0.2 -0 | 13 ±0.1 | |
| 2-3 | 19.6 +0.2 -0 | 13 ±0.1 | |
| | 0.75-1.25 | 0.75-1.25 | |

Newark.com/multicomp-pro Farnell.com/multicomp-pro Element14.com/multicomp-pro

Miniature Rocker Switches multicomp PRO




Rocker Switch Cap



MP004424

Features

- · Splash Proof Cap
- Snap fits over 13mm × 19mm rocker switches
- · IP65 when fitted correctly
- · Black frame over moulded with PVC cap



Specifications Table

| Part No. | Rating | Actuator Colour | Body Colour | Marking | Drawing | Switch Action | Illumination Type |
|----------|------------------|--------------------|----------------|-----------|---------------|---------------|-----------------------------|
| MP004405 | 10(4)A / 250V AC | | | | | SPST Latching | |
| MP004406 | | Black | Black | ack - | - | Drawing 2 | SPDT Latching Changeover |
| MP004407 | | | | | | |] |
| MP004408 | | | 0 1 | Drawing 1 | DPST Latching | | |
| MP004409 | 10(4)A / 250V AC | Red | | - | | | |
| MP004429 | 12V DC | Green | Black | 0 1 | | | Illuminated |
| MP004430 | | Red | | | Drawing 2 | SDST Latabing | |
| MP005716 | 10/4) | Black | | | | SPST Latching | Non-Illuminated |
| MP005717 | 10(4)A / 250V AC | White | White | | | | Non-inuminated |

Important Notice: This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.

Newark.com/multicomp-pro Farnell.com/multicomp-pro Element14.com/multicomp-pro

