



Click [here](#) for the 3D model.

### Dimensions

|           |                 |
|-----------|-----------------|
| Chip Size | 0805            |
| L         | 2mm +/-0.25mm   |
| W         | 1.25mm +/-0.2mm |
| T         | 1.05mm MAX      |
| B         | 0.5mm +/-0.25mm |

### Packaging Specifications

|                    |      |
|--------------------|------|
| Packaging          | T&R  |
| Packaging Quantity | 3500 |

### General Information

|                |                         |
|----------------|-------------------------|
| Series         | VC                      |
| Type           | Varistors               |
| Style          | SMD Chip                |
| Description    | Surface Mount Varistors |
| Features       | Low Voltage             |
| Termination    | Nickel Tin              |
| RoHS           | Yes                     |
| Qualifications | IEC, UL, AEC-Q200       |
| AEC-Q200       | Yes                     |

### Specifications

|                           |                        |
|---------------------------|------------------------|
| Voltage DC                | 26 VDC (25C)           |
| Voltage AC                | 20 VAC                 |
| Temperature Range         | -55/+125°C             |
| Storage Temperature Range | -55/+150°C             |
| Varistor Voltage          | 33 VDC at 1 mA         |
| Clamping Voltage          | 54 V                   |
| Clamping Current          | 1 A (8/20 us MAX)      |
| Surge Current             | 120 A (8/20 us MAX)    |
| Energy                    | 0.4 J (10/1000 us MAX) |
| Capacitance               | 290 pf (1kHz)          |