

# **MCP1632**

# High-Speed, Low-Side PWM Controller

#### Features:

- High-Speed PWM Controller with Integrated Low-Side MOSFET Driver
- Multiple Switching Frequency Options (f<sub>SW</sub>):
  - 300 kHz
  - 600 kHz
- Adjustable Reference Voltage Generator
- Adjustable Soft Start
- Internal Slope Compensation
- Shutdown Input Pin (EN)
- Low Operating Current: < 5 mA (typical)</li>
- Undervoltage Lockout (UVLO) Protection
- · Output Short Circuit Protection
- Overtemperature Protection
- Operating Temperature Range:
  - -40°C to +125°C

#### **Applications:**

- Switch Mode Power Supplies
- Brick DC-DC Converters
- Battery Charger Applications
- LED Drivers

#### **Related Literature:**

 "MCP1632 300 kHz Boost Converter Demo Board User's Guide", Microchip Technology Inc., DS20005252A, 2013

#### **Description:**

The MCP1632 high-speed PWM controller is a pulse-width modulator developed for stand-alone power supply applications. The MCP1632 includes a high-speed analog control loop, a logic-level MOSFET driver, an internal oscillator, a reference voltage generator, and internal slope compensation. This high level of integration makes it an ideal solution for standalone SMPS applications. MCP1632 is suitable for use in topologies requiring a low-side MOSFET control, such as Boost, Flyback, SEPIC, Ćuk, etc. Typical applications include battery chargers, intelligent power systems, brick DC-DC converters, LED drivers. Due to its low power consumption, the MCP1632 PWM controller is recommended for battery-operated applications.

The MCP1632 offers a Peak Current mode control in order to achieve consistent performance regardless of the topology of the power train or the operating conditions. In addition, the MCP1632 can implement the Voltage Mode Control for cost-sensitive solutions.

The MCP1632 PWM controller can be easily interfaced with PIC microcontrollers in order to develop an intelligent power solution.


Additional features include: UVLO, overtemperature and overcurrent protection, shutdown capability (EN pin) and an adjustable soft start option.


#### Package Type

(2		Lead I Im x 3	DFN 8 mm)	8-Lead MSOP				
COMP	1				8 V <sub>REF</sub>			
FB	<u>2</u> ]	EP	[7] Vin	FB 2	7 V <sub>IN</sub>			
CS	<u>3</u> ]	9	[6] V <sub>EXT</sub>	CS 3	6 V <sub>EXT</sub>			
EN	47			) EN 4	5 GND			

# MCP1632


#### **Functional Block Diagram**





Typical Application Circuit – Peak Current Mode Control

### Typical Application Circuit – Voltage Mode Control



### 1.0 ELECTRICAL CHARACTERISTICS

#### Absolute Maximum Ratings †

V <sub>DD</sub> 6.0V	/
Maximum Voltage on Any Pin $\ .\ (V_{GND}-0.3)V$ to $(V_{IN}$ + 0.3)V	/
V <sub>EXT</sub> Short Circuit CurrentInternally Limited	I
Storage Temperature65°C to +150°C	;
Maximum Junction Temperature, T <sub>J</sub> +150°C	;
Continuous Operating Temperature Range40°C to +125°C	;
ESD protection on all pins, HBM 2 kV	/

**† Notice:** Stresses above those listed under "Maximum Ratings" may cause permanent damage to the device. This is a stress rating only and functional operation of the device at those or any other conditions above those indicated in the operational listings of this specification is not implied. Exposure to maximum rating conditions for extended periods may affect device reliability.

# AC/DC CHARACTERISTICS

**Electrical Specifications:** Unless otherwise noted,  $V_{IN}$  = 3.0V to 5.5V,  $F_{OSC}$  = 300 kHz,  $C_{IN}$  = 0.1  $\mu$ F,  $V_{IN}$  for typical values = 5.0V,  $T_A$  = -40°C to +125°C.

Parameters	Sym.	Min.	Тур.	Max.	Units	Conditions
Input Voltage						
Input Operating Voltage	V <sub>IN</sub>	3.0	_	5.5	V	
Input Quiescent Current	I(V <sub>IN</sub> )	—	5	7.5	mA	I <sub>EXT</sub> = 0 mA
Input Shutdown Current	I(V <sub>IN</sub> ) <sub>SHDN</sub>	—	_	2	μA	EN = 0V
EN Input						
EN Input Voltage Low	EN <sub>LOW</sub>	—	—	0.8	V	
EN Input Voltage High	EN <sub>HIGH</sub>	75	_	—	$\%$ of $V_{\text{IN}}$	
Delay Time	-	—	190	210	μs	EN goes from low to high (Note 1)
			40	60	μs	EN goes from high to low (Note 1)
Internal Oscillator						
Internal Oscillator Range	F <sub>OSC</sub>	250	300	350	kHz	Two options
		510	600	690		Refer to Section 4.8 "Internal Oscillator".
<b>Reference Voltage Section</b>						
Reference Voltage Input Range	V <sub>REF</sub>	0	_	V <sub>IN</sub>	V	Note 1 Refer to Section 4.7 "Reference Voltage Generator" for details.
Internal Constant Current Generator	I <sub>REF</sub>	48	50	52	μA	Refer to Section 4.7 "Reference Voltage Generator" for details.
Error Amplifier						
Input Offset Voltage	V <sub>OS</sub>	-4	0.1	+4	mV	
Error Amplifier	PSRR	65	80	—	dB	V <sub>IN</sub> = 3.0V to 5.0V, V <sub>CM</sub> = 1.2V (Note 1)
Common-Mode Input Range	V <sub>CM</sub>	GND - 0.3	_	V <sub>IN</sub>	V	Note 1
Common-Mode Rejection Ratio	CMRR	60	80	—	dB	V <sub>IN</sub> = 5V, V <sub>CM</sub> = 0V to 2.5V (Note 1)
Open-Loop Voltage Gain	A <sub>VOL</sub>	80	95	—	dB	$R_L = 5 k\Omega$ to V <sub>IN</sub> /2, 100 mV < V <sub>EAOUT</sub> < V <sub>IN</sub> - 100 mV, V <sub>CM</sub> = 1.2V (Note 1)
Low-Level Output	V <sub>OL</sub>	—	25	50	mV	$R_L = 5 \text{ k}\Omega \text{ to } V_{IN}/2$
Gain Bandwidth Product	GBWP	3.5	5	—	MHz	V <sub>IN</sub> = 5V ( <b>Note 1</b> )
Error Amplifier Sink Current	I <sub>SINK</sub>	4	8	_	mA	V <sub>IN</sub> = 5V, V <sub>REF</sub> = 1.2V, V <sub>FB</sub> = 1.4V, V <sub>COMP</sub> = 2.0V

**Note 1:** Ensured by design. Not production tested.

# **AC/DC CHARACTERISTICS (CONTINUED)**

Parameters	Sym.	Min.	Тур.	Max.	Units	Conditions
Error Amplifier Source Current	ISOURCE	4	6	_	mA	$V_{IN}$ = 5V, $V_{REF}$ = 1.2V, $V_{FB}$ = 1.0V, $V_{COMP}$ = 2.0V, Absolute Value
Current Sense Input						
Maximum Current Sense Signal	V <sub>CS_MAX</sub>	0.8	0.9	0.97	V	Set by maximum error amplifier clamp voltage, divided by 3 (Note 1)
Blanking Time	T <sub>BLANK</sub>	80	100	130	ns	Note 1
Delay from CS to V <sub>EXT</sub>	T <sub>CS_VEXT</sub>	_	-	35	ns	Excluding the blanking time (Note 1)
Current Sense Input Bias Current	I <sub>CS_B</sub>	—	-0.1	—	μA	Note 1
PWM Section						
Minimum Duty Cycle	DC <sub>MIN</sub>	—	_	0	%	$V_{FB} = V_{REF} + 0.1V, V_{CS} = GND$ (Note 1)
Maximum Duty Cycle	DC <sub>MAX</sub>	80	85	95	%	
Slope Compensation Ram	p Generator					
Ramp Amplitude	V <sub>RAMP</sub>	0.8	0.9	1	V <sub>PP</sub>	Refer to Section 4.6 "Slope Compensation" for details.
DC Offset Low	—	0.15	0.32	0.45	V	Refer to <b>Section 4.6 "Slope</b> <b>Compensation</b> " for details.
DC Offset High	—	1.12	1.22	1.32	V	Refer to Section 4.6 "Slope Compensation" for details.
Ramp Generator Output Impedance	Z <sub>RG</sub>	5.5	6	6.5	kΩ	Refer to <b>Section 4.6 "Slope</b> <b>Compensation</b> " for details.
Internal Driver						
R <sub>DSon</sub> P-channel	R <sub>DSon_P</sub>	—	10	30	Ω	
R <sub>DSon</sub> N-channel	R <sub>DSon_N</sub>	_	7	30	Ω	
V <sub>EXT</sub> Rise Time	T <sub>RISE</sub>	_	-	18	ns	C <sub>L</sub> = 100 pF Typical for V <sub>IN</sub> = 3V ( <b>Note 1</b> )
V <sub>EXT</sub> Fall Time	T <sub>FALL</sub>	_	_	18	ns	C <sub>L</sub> = 100 pF Typical for V <sub>IN</sub> = 3V ( <b>Note 1</b> )
Protection Features						
Undervoltage Lockout	UVLO	2.6	_	2.9	V	$V_{\text{IN}}$ falling, $V_{\text{EXT}}$ low state when in UVLO
Undervoltage Lockout Hysteresis	UVLO <sub>HYS</sub>	50	110	180	mV	
Thermal Shutdown	T <sub>SHD</sub>		150		°C	Note 1
Thermal Shutdown Hysteresis	T <sub>SHD_HYS</sub>	_	20		°C	Note 1

Note 1: Ensured by design. Not production tested.


# **TEMPERATURE SPECIFICATIONS**

Electrical Specifications: $V_{IN}$ = 3.0V to 5.5V, $F_{OSC}$ = 600 kHz, $C_{IN}$ = 0.1 µF. $T_A$ = -40°C to +125°C.								
Parameters	Sym.	Min.	Тур.	Max.	Units	Conditions		
Temperature Ranges								
Operating Junction Temperature Range	T <sub>A</sub>	-40	-	+125	°C	Steady state		
Storage Temperature Range	T <sub>A</sub>	-65	—	+150	°C			
Maximum Junction Temperature	TJ	—	—	+150	°C	Transient		
Thermal Package Resistances								
Thermal Resistance, 8L-DFN (2 mm x 3 mm)	θ <sub>JA</sub>	_	75	_	°C/W	Typical 4-layer board with two interconnecting vias.		
Thermal Resistance, 8L-MSOP	$\theta_{JA}$	—	211	—	°C/W	Typical 4-layer board.		


# 2.0 TYPICAL PERFORMANCE CURVES

**Note:** The graphs and tables provided following this note are a statistical summary based on a limited number of samples and are provided for informational purposes only. The performance characteristics listed herein are not tested or guaranteed. In some graphs or tables, the data presented may be outside the specified operating range (e.g., outside specified power supply range) and therefore outside the warranted range.


**Note:** Unless otherwise noted,  $V_{IN}$  = 5V,  $F_{OSC}$  = 300 kHz,  $C_{IN}$  = 0.1 µF,  $T_A$  = 25°C.




**FIGURE 2-1:** Input Quiescent Current vs. Input Voltage (EN = Low).




**FIGURE 2-2:** Input Quiescent Current vs. Input Voltage (EN = High).



**FIGURE 2-3:** Relative Oscillator Frequency Variation vs. Input Voltage.



**FIGURE 2-4:** Relative Oscillator Frequency Variation vs. Junction Temperature.



Voltage.

V<sub>REF</sub> Current vs. Input





FIGURE 2-6: Temperature.

V<sub>REF</sub> Current vs. Junction

Note: Unless otherwise noted, V\_IN = 5V, F\_{OSC} = 300 kHz, C\_IN = 0.1  $\mu$ F, T<sub>A</sub> = 25°C.











FIGURE 2-8: Error Amplifier Offset Voltage vs. Input Voltage.




Voltage.



**FIGURE 2-10:** V<sub>EXT</sub> Fall Time vs. Input Voltage.





**FIGURE 2-11:** Relative V<sub>EXT</sub> N-Channel MOSFET R<sub>DSon</sub> Variation vs. Input Voltage.




**FIGURE 2-12:** Relative V<sub>EXT</sub> P-Channel MOSFET R<sub>DSon</sub> Variation vs. Input Voltage.


Note: Unless otherwise noted, V<sub>IN</sub> = 5V, F<sub>OSC</sub> = 300 kHz, C<sub>IN</sub> = 0.1  $\mu$ F, T<sub>A</sub> = 25°C.







**FIGURE 2-14:** Relative V<sub>EXT</sub> N-Channel MOSFET R<sub>DSon</sub> Variation vs. Junction Temperature.



**FIGURE 2-15:** Relative V<sub>EXT</sub> P-Channel MOSFET R<sub>DSon</sub> Variation vs. Junction Temperature.

NOTES:

# 3.0 PIN DESCRIPTIONS

The descriptions of the pins are listed in Table 3-1.

Name	Function
COMP	Error Amplifier Output
FB	Error Amplifier Inverting Input
CS	Current Sense Input
EN	Enable Input
GND	Circuit Ground
$V_{EXT}$	External Driver Output
V <sub>IN</sub>	Input Bias
V <sub>REF</sub>	Reference Voltage Input/Internal Constant Current Generator Output
EP	Exposed Thermal Pad (EP); must be connected to GND
	Name       COMP       FB       CS       EN       GND       V <sub>EXT</sub> V <sub>IN</sub> V <sub>REF</sub>

#### TABLE 3-1: PIN FUNCTION TABLE

#### 3.1 Error Amplifier Output (COMP)

COMP is the internal error amplifier output pin. External compensation is connected from the FB pin to the COMP pin for control-loop stabilization. Type II or III compensation networks must be used depending on the application. An internal voltage clamp is used to limit the maximum COMP pin voltage to 2.7V (typical). This clamp is used to set the maximum peak current in the power system switch by setting a maximum limit on the CS input for Peak Current Mode control systems.

#### 3.2 Error Amplifier Inverting Input (FB)

FB is the internal error amplifier inverting input pin. The output (voltage or current) is sensed and fed back to the FB pin for regulation. Inverting or negative feedback is used.

#### 3.3 Current Sense Input (CS)

This is the input for the switch current used for Peak Current Mode control. A blanking period of 100 ns (typical) for CS signal is provided to avoid leading edge spikes that can cause false PWM reset. The normal PWM duty cycle will be terminated when the voltage on the CS pin (including the slope compensation ramp) is equal to the output of the error amplifier divided by 3. For Current Mode operation, the CS pin will control the PWM output on a cycle-by-cycle basis. The internal error amplifier output is clamped to 2.7V (nominal) and divided by 3, so the maximum voltage of the CS pin is 0.9V. By limiting the inverting pin of the high-speed comparator to 0.9V, a current sense limit is established for all input bias voltage conditions (cycle-by-cycle overcurrent protection). To avoid the instability of the Peak Current Mode control when the duty cycle is higher than 50%, a slope compensation ramp generator is internally provided. This circuit will add to the CS signal an artificially generated ramp to avoid

sub-harmonic oscillations. The amplitude of the slope compensation ramp is adjustable with one external resistor.

If this pin is left open, the PWM Controller will operate in Voltage Mode Control. In this mode, the external switching MOSFET transistor is not protected against overcurrent conditions. Certain limitations related to the stability of the closed-loop system must be taken into account by the designer when the part operates in Voltage Mode Control. Refer to Section 5.2 "Operation in Voltage Mode Control" for details about the operation in Voltage Mode Control.

#### 3.4 Enable Input (EN)

When this pin is connected to GND (logic "Low") for more than 50  $\mu$ s (typical), the chip will go into Shutdown state. A logic "High" enables the normal operation of the MCP1632 device. When the device is disabled, the V<sub>EXT</sub> output is held low. Do not let the EN pin float. If not used, connect EN to V<sub>IN</sub> through a 10 k $\Omega$ resistor.

# 3.5 Circuit Ground (GND)

Connect the circuit ground to the GND pin. For most applications, this should be connected to the analog (quiet) ground plane. Effort should be made to minimize the noise on this ground, as it can adversely affect the cycle-by-cycle comparison between the CS input and the error amplifier output.

# 3.6 External Driver Output (V<sub>EXT</sub>)

 $V_{EXT}$  is the internal MOSFET driver output pin, used to drive the external transistor. For high-power or high-side drives, this output should be connected to the logic-level input of an appropriate MOSFET driver. For low-power, low-side applications, the  $V_{EXT}$  pin can be used to directly drive the gate of an N-channel MOSFET.

#### 3.7 Input Bias (VIN)

 $V_{\text{IN}}$  is the input voltage pin. Connect the input voltage source to the  $V_{\text{IN}}$  pin. For normal operation, the voltage on the  $V_{\text{IN}}$  pin should range from +3.0V to +5.5V. A bypass capacitor of at least 0.1  $\mu\text{F}$  should be connected between the  $V_{\text{IN}}$  pin and the GND pin. This decoupling capacitor must be located as close as possible to the controller package.

#### 3.8 Reference Voltage Input/Internal Constant Current Generator Output (V<sub>REF</sub>)

This pin is the output of the internal Constant Current Generator (50  $\mu$ A typical). An external resistor must be connected between this pin and GND. The current flowing in this resistor will set the reference voltage. Optionally, a capacitor may also be connected between this pin and GND to set the soft start ramp behavior. This pin may be overdriven by an external voltage source, enabling the reference voltage to be controlled externally. Refer to Section 4.7 "Reference Voltage Generator" for details.

# 4.0 DETAILED DESCRIPTION

#### 4.1 Device Overview

The MCP1632 device is comprised of an internal oscillator, an internal constant current generator, a high-speed comparator, a high-bandwidth amplifier, an internal ramp generator for slope compensation and logic gates, and is intended to be used to develop a stand-alone switch-mode power supply. There are two (orderable) switching frequency options for this device: 300 kHz or 600 kHz. Refer to Functional Block Diagram for details about the internal functional blocks.

#### 4.2 **PWM Circuitry**

MCP1632 implements a typical Peak Current Mode control loop. The V<sub>EXT</sub> output of the MCP1632 device is determined by the output level of the internal high-speed comparator and the level of the internal CLK signal. When the CLK signal level is high, the PWM output (V<sub>EXT</sub>) is forced low, limiting the maximum duty cycle to approximately 85% (typical). When the CLK signal is low, the PWM output is determined by the output level of the internal high-speed comparator. During UVLO, the V<sub>EXT</sub> pin is held in low state. During overtemperature operation, the V<sub>EXT</sub> pin is high-impedance (10 k $\Omega$  to ground, typical).

## 4.3 Normal Cycle-by-Cycle Control

The beginning of a PWM cycle is defined by the internal CLK signal (a transition from high to low). Refer to Figure 4-1 for the detailed timing operation of the MCP1632 PWM controller.

For normal operation, the state of the high-speed comparator output (R) is low and the Q output of the latch is low. On the high-to-low transition of the CLK signal, the SR inputs to the high-speed latch are both low and the Q output will remain unchanged (low). The output of the OR gate (V<sub>DRIVE</sub>) will transition from high to low, turning on the P-Channel drive transistor in the output stage of the PWM. This will change the PWM output (V<sub>FXT</sub>) from low to high, turning on the power train MOSFET and ramping current in the power train magnetic device. The sensed current in the magnetic device is fed into the CS input, shown as a ramp, and increases linearly until it reaches the same level as the divided down output of the error amplifier at the non-inverting input of the high-speed comparator. The comparator output (R) changes state (low to high) and resets the PWM latch. The Q output transition from low to high turns off the V<sub>EXT</sub> drive to the external MOSFET driver, thus terminating the current conduction cycle. The CLK signal will transition from low to high while the V<sub>FXT</sub> pin remains unchanged. If the CS input pin never reaches the same level as the error amplifier output, the low-to-high transition on the CLK signal terminates the current switching cycle. This would be considered as the maximum duty cycle. In either case, while the CLK signal is high, the  $V_{EXT}$  drive pin is low, turning off the external power train switch. The next switching cycle will start on another transition of the CLK signal from high to low.

#### 4.4 Error Amplifier/Comparator Current Limit Function

The internal amplifier is used to create an error output signal that is determined by the  $\mathsf{V}_{\mathsf{REF}}$  input pin and the power supply output voltage fed back into the FB pin. The error amplifier output is rail-to-rail and is clamped by a precision 2.7V internal voltage source. The output of the error amplifier is then divided down 3:1 and connected to the inverting input of the high-speed comparator. The maximum output of the error amplifier is 2.7V, so the maximum input to the inverting pin of the high-speed comparator is 0.9V. As the output load current demand increases, the error amplifier output increases too, causing the inverting input pin of the high-speed comparator to increase. Eventually, the output of the error amplifier will hit the 2.7V clamp, limiting the input of the high-speed comparator to 0.9V maximum. Even if the FB input continues to decrease, calling for more current, the inverting input is limited to 0.9V. By limiting the inverting input to 0.9V, the current sense (CS) input is limited to 0.9V, thus limiting the current that flows in the main switch. Limiting the maximum peak current in the switch prevents the destruction of the semiconductor device and the saturation of the inductor during overloads. The resistor divider placed at the output of the error amplifier decreases the gain of the control loop by 9.5 dB. The designer must take into account this gain reduction during the compensation loop process. The error amplifier is rail-to-rail at the input and the common-mode range includes the GND and  $V_{IN}$ potentials.

#### 4.5 0% Duty Cycle Operation

The duty cycle of the V<sub>EXT</sub> output is capable of reaching 0% when the FB pin (inverting error amplifier) is held higher than the voltage present on the V<sub>RFF</sub> (Reference Voltage) pin. This is accomplished by the rail-to-rail output capability of the error amplifier and the offset voltage of the high-speed comparator. The minimum error amplifier output voltage, divided by 3, is less than the offset voltage of the high-speed comparator. In case the output voltage of the converter is above the desired regulation point, the FB input will be above the V<sub>REF</sub> input and the error amplifier will be pulled to the bottom rail (GND). This low voltage is divided down 3:1 by the 2R and 1R resistor, and is connected to the input of the high-speed comparator. This voltage will be low enough so that there is no triggering of the comparator, allowing narrow pulse widths at VEXT.





FIGURE 4-1: PWM Timing Diagram.

#### 4.6 Slope Compensation

In order to prevent sub-harmonic oscillations that occur when a Peak Current Mode converter exceeds a 50% duty cycle, the MCP1632 provides an internal ramp generator that can be used for slope compensation. Refer to Figure 4-2 for details about the slope generator circuit. The amplitude of the generated ramp signal is 0.9 V<sub>PP</sub> (typical) and the DC offset value is 770 mV (typical). The impedance of the internal ramp generator (R<sub>G</sub>) is 6 k $\Omega$  (typical). The amplitude of the slope compensation ramp can be adjusted by modifying the value of the R<sub>SLOPE</sub> resistor. Refer to Figure 4-3 for details about the slope compensation ramp signal applied to CS pin. The parameters of the slope compensation ramp signal can be calculated with the provided equations.

The MCP1632 device is equipped with a blanking circuit for the CS pin in order to prevent any false resets of the RS latch due to noise. However, for certain applications, it is recommended to place a small value capacitor ( $C_{FILTER}$ ) between the CS pin and GND to provide additional filtering for the current sense signal. The recommended value ranges from 10 pF to 30 pF. Use caution, because a higher value may affect the slope compensation ramp.






FIGURE 4-3: Slope Compensation Signal (CS) Pin.

## 4.7 Reference Voltage Generator

The internal precision constant current generator and an external resistor connected between the V<sub>RFF</sub> pin and GND form the reference voltage generator. Refer to Figure 4-4 for details. Optionally, a capacitor (C<sub>SS</sub>) can be connected in parallel with R<sub>VRFF</sub> to activate the soft start function that will minimize overshoots of the output voltage during start-up. The equations in Figure 4-4 calculate the value of the resistor ( $R_{VRFF}$ ) for a given reference voltage and the value of the soft start capacitor (CSS) based on the necessary time to reach 90% of the final value for V<sub>REF</sub>. An internal circuit of the MCP1632 device will discharge the capacitor during the shutdown period. This capacitor must be of good quality, with low leakage currents, in order to avoid any errors that can affect the reference voltage. The reference voltage should not exceed 80% of the bias input voltage (VIN pin) in order to avoid any errors that affect the internal constant current generator.

An external low-noise, low-impedance source can be used to overdrive the  $V_{\mathsf{REF}}$  pin in order to control the reference voltage. In this case, the resistor/capacitor group connected to GND is not necessary, and the soft start profile must be controlled by the external reference voltage generator.




FIGURE 4-4: Reference Voltage Generator.

#### 4.8 Internal Oscillator

The MCP1632 PWM controller provides two (orderable) switching frequency options: 300 kHz and 600 kHz.

#### 4.9 Undervoltage Lockout (UVLO)

When the input voltage ( $V_{IN}$ ) is less than the UVLO threshold, the  $V_{EXT}$  is held in low state. This will ensure that, if the voltage is not adequate to power the MCP1632 device, the main power supply switch will be held in off state. In order to prevent oscillations when the input voltage is near the UVLO threshold, the UVLO circuit offers 100 mV (typical) hysteresis. Typically, the MCP1632 device will not start until the input voltage at  $V_{IN}$  is between 2.8V and 2.9V (typical).

#### 4.10 Overtemperature Protection

To protect the V<sub>EXT</sub> output if shorted to V<sub>IN</sub> or GND, the V<sub>EXT</sub> output of the MCP1632 device will be high-impedance if the junction temperature is above the thermal shutdown threshold. An internal 10 k $\Omega$  pull-down resistor is connected from V<sub>EXT</sub> to ground to provide some pull-down during overtemperature conditions. The protection is set to 150°C (typical), with a hysteresis of 20°C.

NOTES:

## 5.0 APPLICATION CIRCUITS

#### 5.1 Typical Applications

The MCP1632 PWM controller can be used for applications that require low-side MOSFET control, such as Boost, Buck-Boost, Flyback, SEPIC or Ćuk converters. By using an external high-side MOSFET driver (e.g. MCP14628), the MCP1632 device is able to control the buck converter. The MCP1632 PWM controller can be easily interfaced with a microcontroller in order to develop intelligent solutions, such as battery chargers or LED drivers.


Figure 5-1 depicts the typical boost converter controlled by MCP1632. The input voltage applied on the V<sub>IN</sub> pin of the MCP1632 device should be kept below 5.5V. If the converter must operate with input voltages higher than 5.5V, a linear voltage regulator can be used to bias the MCP1632 controller. The Peak Current Mode control used in this case will ensure consistent performance over a wide range of operating conditions.

The Q1 MOSFET is protected against overcurrent by internally limiting the maximum voltage at the output of the error amplifier of the controller. If the voltage applied on the CS pin exceeds 0.9V, the MCP1632 device will reduce the duty cycle in order to prevent overcurrent in Q1 MOSFET. The maximum drain peak current in Q1 can be calculated using Equation 5-1. The slope compensation ramp amplitude may limit the maximum peak current and must be considered when calculating this parameter. The DC offset of the slope compensation ramp (DC<sub>HIGH</sub>) is calculated using the equations provided in Figure 4-3.

Note that the boost converter is not protected against the output short circuit.

**EQUATION 5-1:** 

$$I_{Peak}Max(A) = \frac{0.9V - D \times DC_{HIGH}(V)}{R_{SENSE}(\Omega)}$$



The single-ended primary inductor converter (SEPIC) used to drive an LED string is presented in Figure 5-2. This converter offers buck-boost functionality and is protected against the output short circuit. The inductors can share the same magnetic core (coupled inductors); in this case, the mutual inductance doubles the value of the inductor, reducing the ripple of the current. The LED string can be dimmed by driving the EN pin (PWM dimming) or by adjusting the value of the R<sub>VREF</sub> resistor (current dimming). The maximum allowable peak current into Q1 MOSFET can be calculated using Equation 5-1. The SEPIC converter exhibits poor dynamic performance and is recommended only for applications with low step response demands, like LED drivers or battery chargers.





FIGURE 5-2: MCP1632 SEPIC Converter.

A typical charger application for one- or two-cell Li-Ion batteries is presented in Figure 5-3. The PIC microcontroller handles all the necessary functions of the charger and the MCP1632 device controls the power train. Using the SEPIC converter allows developing a universal charger where the input voltage can be higher or lower than the battery voltage. The microcontroller can control the reference voltage across certain limits using its internal high-frequency PWM generator and the external circuit consisting of D2 and R1.

This circuit can be replaced with a digital-to-analog converter (DAC) for a better range and accuracy of the reference voltage control. The charging current is monitored using a low-side shunt ( $R_S$ ) and an inverting amplifier. The floating voltage of the charger is controlled by MCP1632 and can be adjusted by varying the value of the  $R_{VREF}$  resistor or the ratio of the feedback divider ( $R_5$ ,  $R_6$ ). Additional protection features can be implemented in the microcontroller's firmware.



MCP1632

#### 5.2 Operation in Voltage Mode Control

The MCP1632 PWM controller can operate in Voltage Mode Control using the internal slope compensation ramp to generate the PWM signal. The current sense resistor is not necessary for this application, thus the overall efficiency of the converter can be improved. Refer to Typical Application Circuit - Voltage Mode Control. Certain limitations occur in this operating mode. The compensation network for Voltage Mode Control must be of Type III, increasing the number of components. The closed-loop system is now a second order system and stability can be difficult to achieve over a wide range of operating conditions. The position of the dominant pole (double pole) in boost-derived converters varies with the operating conditions (input/output voltages); maintaining acceptable phase and gain margins across the entire operating range of the converter becomes a difficult task in this case.

Note that there is no inherent protection mechanism that can limit the inductor's current during transients or overloads. A resistor placed between the CS pin and GND allows adjusting the maximum duty cycle by controlling the amplitude of the ramp signal. Refer to Figure 5-4 for details. If the  $R_{DC Adj}$  resistor is not placed, the maximum duty cycle is set to approximately 60% (typical). The duty cycle can be increased up to 85% (typical) by adjusting the value of the  $R_{DC Adj}$  resistor. The designer must limit the maximum operating duty cycle of the converter to a safe value by adjusting the value of the ramp enables operation with 0% duty cycle if the output of the error amplifier divided by 3 is lower than  $DC_{LOW}$ .

The Voltage Mode Control should be used only for systems with low input voltages, low DC conversion ratios and limited dynamics of the load (e.g., LED drivers or battery chargers).




FIGURE 5-4:

Voltage Mode Operation Details.

#### 5.3 PCB Layout Recommendations

The PCB layout is critical for switch-mode power supplies. When developing the PCB, the designer must follow the general rules for switching converters in order to achieve consistent performance. The guidelines include:

- Identify the high-current, high-frequency loops before starting the PCB design. Figure 5-5 depicts these loops for boost converters.  $I_1$  and  $I_2$  are the main currents of the boost converter. The  $I_{RR}$  is the current produced by the reverse recovery of the output rectifier D1. The  $I_{RR}$  current is an important source of noise/EMI.
- Minimize the area of the high-current loops. Use copper planes or large traces for high-current connections in order to minimize the parasitic inductances.

- Four-layer PCBs with internal ground plane offer the best performance for switch-mode power supplies. For cost-sensitive applications, two-layer PCBs can be used. In this case, the bottom layer must be used like a ground plane.
- Use separate grounds for small-signal and power signals. These grounds must be connected (when possible) in a single point located near the GND pin of the MCP1632 controller.
- Keep the current sense (CS) and feedback (FB) signals away from noisy nodes, such as the drain of the main switch (Q1).
- Locate the compensation network components near the MCP1632 case.




FIGURE 5-5:

The Boost Converter's Current Loops.

NOTES:


# 6.0 PACKAGING INFORMATION

#### 6.1 Package Marking Information

8-Lead DFN (2x3x0.9 mm)



Part Number	Code
MCP1632-AAE/MC	ACD
MCP1632-BAE/MC	ACY
MCP1632T-AAE/MC	ACD
MCP1632T-BAE/MC	ACY



8-Lead MSOP (3x3 mm)




Example



Legend:	XXX Y YY WW NNN @3 *	Customer-specific information Year code (last digit of calendar year) Year code (last 2 digits of calendar year) Week code (week of January 1 is week '01') Alphanumeric traceability code Pb-free JEDEC designator for Matte Tin (Sn) This package is Pb-free. The Pb-free JEDEC designator ((e3))
	be carrie	can be found on the outer packaging for this package. In the full Microchip part number cannot be marked on one line, it will d over to the next line, thus limiting the number of available is for customer-specific information.

#### 8-Lead Plastic Dual Flat, No Lead Package (MC) – 2x3x0.9 mm Body [DFN]

Note: For the most current package drawings, please see the Microchip Packaging Specification located at http://www.microchip.com/packaging



	Units		MILLIMETERS		
	Dimension Limits	MIN	NOM	MAX	
Number of Pins	N	8			
Pitch	е		0.50 BSC		
Overall Height	A	0.80	0.90	1.00	
Standoff	A1	0.00	0.02	0.05	
Contact Thickness	A3	0.20 REF			
Overall Length	D	2.00 BSC			
Overall Width	E	3.00 BSC			
Exposed Pad Length	D2	1.30	-	1.55	
Exposed Pad Width	E2	1.50	-	1.75	
Contact Width	b	0.20	0.25	0.30	
Contact Length	L	0.30	0.40	0.50	
Contact-to-Exposed Pad	К	0.20	-	_	

NOTE 2

A1

#### Notes:

1. Pin 1 visual index feature may vary, but must be located within the hatched area.

- 2. Package may have one or more exposed tie bars at ends.
- 3. Package is saw singulated.

A3


- 4. Dimensioning and tolerancing per ASME Y14.5M.
  - BSC: Basic Dimension. Theoretically exact value shown without tolerances.

REF: Reference Dimension, usually without tolerance, for information purposes only.

Microchip Technology Drawing C04-123C

8-Lead Plastic Dual Flat, No Lead Package (MC) - 2x3x0.9mm Body [DFN]

**Note:** For the most current package drawings, please see the Microchip Packaging Specification located at http://www.microchip.com/packaging



#### RECOMMENDED LAND PATTERN

	Units			S
Dimensio	Dimension Limits		NOM	MAX
Contact Pitch	E	E 0.50 BSC		
Optional Center Pad Width	W2			1.45
Optional Center Pad Length	T2			1.75
Contact Pad Spacing	C1	2.90		
Contact Pad Width (X8)	X1			0.30
Contact Pad Length (X8)	Y1			0.75
Distance Between Pads	G	0.20		

Notes:


1. Dimensioning and tolerancing per ASME Y14.5M

BSC: Basic Dimension. Theoretically exact value shown without tolerances.

Microchip Technology Drawing No. C04-2123B

#### 8-Lead Plastic Micro Small Outline Package (MS) [MSOP]


**Note:** For the most current package drawings, please see the Microchip Packaging Specification located at http://www.microchip.com/packaging



Microchip Technology Drawing C04-111C Sheet 1 of 2

#### 8-Lead Plastic Micro Small Outline Package (MS) [MSOP]

**Note:** For the most current package drawings, please see the Microchip Packaging Specification located at http://www.microchip.com/packaging



DETAIL C

	Units			
Dimensior	Dimension Limits			MAX
Number of Pins	N	8		
Pitch	е		0.65 BSC	
Overall Height	A	-	-	1.10
Molded Package Thickness	A2	0.75	0.85	0.95
Standoff	A1	0.00	-	0.15
Overall Width	E	4.90 BSC		
Molded Package Width	E1	3.00 BSC		
Overall Length	D	3.00 BSC		
Foot Length	L	0.40	0.60	0.80
Footprint	L1	0.95 REF		
Foot Angle	φ	0°	-	8°
Lead Thickness	С	0.08	-	0.23
Lead Width	b	0.22	-	0.40

#### Notes:

1. Pin 1 visual index feature may vary, but must be located within the hatched area.

2. Dimensions D and E1 do not include mold flash or protrusions. Mold flash or protrusions shall not exceed 0.15mm per side.

3. Dimensioning and tolerancing per ASME Y14.5M.


BSC: Basic Dimension. Theoretically exact value shown without tolerances.

REF: Reference Dimension, usually without tolerance, for information purposes only.

Microchip Technology Drawing C04-111C Sheet 2 of 2

#### 8-Lead Plastic Micro Small Outline Package (UA) [MSOP]

**Note:** For the most current package drawings, please see the Microchip Packaging Specification located at http://www.microchip.com/packaging



#### RECOMMENDED LAND PATTERN

	Units	1	MILLIMETERS		
Dimensio	Dimension Limits		NOM	MAX	
Contact Pitch	E		0.65 BSC		
Contact Pad Spacing	С		4.40		
Overall Width	Z			5.85	
Contact Pad Width (X8)				0.45	
Contact Pad Length (X8)	Y1			1.45	
Distance Between Pads	G1	2.95			
Distance Between Pads	GX	0.20			

#### Notes:

1. Dimensioning and tolerancing per ASME Y14.5M

BSC: Basic Dimension. Theoretically exact value shown without tolerances.

Microchip Technology Drawing No. C04-2111A

## APPENDIX A: REVISION HISTORY

### **Revision A (December 2013)**

• Original Release of this Document.

NOTES:

# **PRODUCT IDENTIFICATION SYSTEM**

To order or obtain information, e.g., on pricing or delivery, refer to the factory or the listed sales office.

PART NO. X	<u>(X</u>	<u>×</u>	<u>/XX</u>	Exa	amples:	
Device Frequ	uency	 Temperat Range	•	a)	MCP1632-AAE/MC:	Extended temperature, 8LD 2x3 DFN package
Device:	MCP163 MCP163		peed, low-side PWM controller peed, low-side PWM controller	b)	MCP1632T-AAE/MC: MCP1632-BAE/MC:	Extended temperature, 8LD 2x3 DFN package
		5 1	(Tape and Reel)	c)	MCF 1032-BAE/MC.	Extended temperature, 8LD 2x3 DFN package
Frequency:	AA BA	= 300 kHz = 600 kHz		d)	MCP1632T-BAE/MC:	Tape and Reel, Extended temperature, 8LD 2x3 DFN package
Temperature Range:	E	= -40°C to +	+125°C	a)		Extended temperature, 8LD MSOP package
Package:	MC	<ul> <li>Plastic Du (DFN)</li> </ul>	ual Flat, No Lead – 2x3x0.9 mm body	b)	MCP1632T-AAE/MS:	Tape and Reel,
	MS :		icro Small Outline			Extended temperature, 8LD MSOP package
				c)	MCP1632-BAE/MS:	Extended temperature, 8LD MSOP package
				d)	MCP1632T-BAE/MS:	Tape and Reel, Extended temperature, 8LD MSOP package

NOTES:

#### Note the following details of the code protection feature on Microchip devices:

- · Microchip products meet the specification contained in their particular Microchip Data Sheet.
- Microchip believes that its family of products is one of the most secure families of its kind on the market today, when used in the intended manner and under normal conditions.
- There are dishonest and possibly illegal methods used to breach the code protection feature. All of these methods, to our knowledge, require using the Microchip products in a manner outside the operating specifications contained in Microchip's Data Sheets. Most likely, the person doing so is engaged in theft of intellectual property.
- Microchip is willing to work with the customer who is concerned about the integrity of their code.
- Neither Microchip nor any other semiconductor manufacturer can guarantee the security of their code. Code protection does not mean that we are guaranteeing the product as "unbreakable."

Code protection is constantly evolving. We at Microchip are committed to continuously improving the code protection features of our products. Attempts to break Microchip's code protection feature may be a violation of the Digital Millennium Copyright Act. If such acts allow unauthorized access to your software or other copyrighted work, you may have a right to sue for relief under that Act.

Information contained in this publication regarding device applications and the like is provided only for your convenience and may be superseded by updates. It is your responsibility to ensure that your application meets with your specifications. MICROCHIP MAKES NO REPRESENTATIONS OR WARRANTIES OF ANY KIND WHETHER EXPRESS OR IMPLIED, WRITTEN OR ORAL, STATUTORY OR OTHERWISE, RELATED TO THE INFORMATION, INCLUDING BUT NOT LIMITED TO ITS CONDITION, QUALITY, PERFORMANCE, MERCHANTABILITY OR FITNESS FOR PURPOSE. Microchip disclaims all liability arising from this information and its use. Use of Microchip devices in life support and/or safety applications is entirely at the buyer's risk, and the buyer agrees to defend, indemnify and hold harmless Microchip from any and all damages, claims, suits, or expenses resulting from such use. No licenses are conveyed, implicitly or otherwise, under any Microchip intellectual property rights.

# QUALITY MANAGEMENT SYSTEM CERTIFIED BY DNV = ISO/TS 16949=

#### Trademarks

The Microchip name and logo, the Microchip logo, dsPIC, FlashFlex, KEELOQ, KEELOQ logo, MPLAB, PIC, PICmicro, PICSTART, PIC<sup>32</sup> logo, rfPIC, SST, SST Logo, SuperFlash and UNI/O are registered trademarks of Microchip Technology Incorporated in the U.S.A. and other countries.

FilterLab, Hampshire, HI-TECH C, Linear Active Thermistor, MTP, SEEVAL and The Embedded Control Solutions Company are registered trademarks of Microchip Technology Incorporated in the U.S.A.

Silicon Storage Technology is a registered trademark of Microchip Technology Inc. in other countries.

Analog-for-the-Digital Age, Application Maestro, BodyCom, chipKIT, chipKIT logo, CodeGuard, dsPICDEM, dsPICDEM.net, dsPICworks, dsSPEAK, ECAN, ECONOMONITOR, FanSense, HI-TIDE, In-Circuit Serial Programming, ICSP, Mindi, MiWi, MPASM, MPF, MPLAB Certified logo, MPLIB, MPLINK, mTouch, Omniscient Code Generation, PICC, PICC-18, PICDEM, PICDEM.net, PICkit, PICtail, REAL ICE, rfLAB, Select Mode, SQI, Serial Quad I/O, Total Endurance, TSHARC, UniWinDriver, WiperLock, ZENA and Z-Scale are trademarks of Microchip Technology Incorporated in the U.S.A. and other countries.

SQTP is a service mark of Microchip Technology Incorporated in the U.S.A.

GestIC and ULPP are registered trademarks of Microchip Technology Germany II GmbH & Co. KG, a subsidiary of Microchip Technology Inc., in other countries.

All other trademarks mentioned herein are property of their respective companies.

© 2013, Microchip Technology Incorporated, Printed in the U.S.A., All Rights Reserved.

Rinted on recycled paper.

ISBN: 978-1-62077-770-1

Microchip received ISO/TS-16949:2009 certification for its worldwide headquarters, design and wafer fabrication facilities in Chandler and Tempe, Arizona; Gresham, Oregon and design centers in California and India. The Company's quality system processes and procedures are for its PIC® MCUs and dsPIC® DSCs, KEELOQ® code hopping devices, Serial EEPROMs, microperipherals, nonvolatile memory and analog products. In addition, Microchip's quality system for the design and mulfacture of development systems is ISO 9001:2000 certified.



# **Worldwide Sales and Service**

#### AMERICAS

Corporate Office 2355 West Chandler Blvd. Chandler, AZ 85224-6199 Tel: 480-792-7200 Fax: 480-792-7277 Technical Support: http://www.microchip.com/ support

Web Address: www.microchip.com

Atlanta Duluth, GA Tel: 678-957-9614 Fax: 678-957-1455

Austin, TX Tel: 512-257-3370

Boston Westborough, MA Tel: 774-760-0087 Fax: 774-760-0088

Chicago Itasca, IL Tel: 630-285-0071 Fax: 630-285-0075

**Cleveland** Independence, OH Tel: 216-447-0464 Fax: 216-447-0643

Dallas Addison, TX Tel: 972-818-7423 Fax: 972-818-2924

**Detroit** Novi, MI Tel: 248-848-4000

Houston, TX Tel: 281-894-5983

Indianapolis Noblesville, IN Tel: 317-773-8323 Fax: 317-773-5453

Los Angeles Mission Viejo, CA Tel: 949-462-9523 Fax: 949-462-9608

New York, NY Tel: 631-435-6000

San Jose, CA Tel: 408-735-9110

**Canada - Toronto** Tel: 905-673-0699 Fax: 905-673-6509

#### ASIA/PACIFIC

Asia Pacific Office Suites 3707-14, 37th Floor Tower 6, The Gateway Harbour City, Kowloon Hong Kong Tel: 852-2401-1200 Fax: 852-2401-3431

Australia - Sydney Tel: 61-2-9868-6733 Fax: 61-2-9868-6755

**China - Beijing** Tel: 86-10-8569-7000 Fax: 86-10-8528-2104

**China - Chengdu** Tel: 86-28-8665-5511 Fax: 86-28-8665-7889

China - Chongqing Tel: 86-23-8980-9588 Fax: 86-23-8980-9500

**China - Hangzhou** Tel: 86-571-2819-3187

Fax: 86-571-2819-3189 China - Hong Kong SAR

Tel: 852-2943-5100 Fax: 852-2401-3431

China - Nanjing Tel: 86-25-8473-2460

Fax: 86-25-8473-2470 China - Qingdao Tel: 86-532-8502-7355 Fax: 86-532-8502-7205

**China - Shanghai** Tel: 86-21-5407-5533 Fax: 86-21-5407-5066

China - Shenyang Tel: 86-24-2334-2829 Fax: 86-24-2334-2393

**China - Shenzhen** Tel: 86-755-8864-2200 Fax: 86-755-8203-1760

**China - Wuhan** Tel: 86-27-5980-5300 Fax: 86-27-5980-5118

**China - Xian** Tel: 86-29-8833-7252 Fax: 86-29-8833-7256

**China - Xiamen** Tel: 86-592-2388138 Fax: 86-592-2388130

**China - Zhuhai** Tel: 86-756-3210040 Fax: 86-756-3210049

#### ASIA/PACIFIC

India - Bangalore Tel: 91-80-3090-4444 Fax: 91-80-3090-4123

India - New Delhi Tel: 91-11-4160-8631 Fax: 91-11-4160-8632

India - Pune Tel: 91-20-3019-1500

**Japan - Osaka** Tel: 81-6-6152-7160 Fax: 81-6-6152-9310

**Japan - Tokyo** Tel: 81-3-6880- 3770 Fax: 81-3-6880-3771

**Korea - Daegu** Tel: 82-53-744-4301 Fax: 82-53-744-4302

Korea - Seoul Tel: 82-2-554-7200 Fax: 82-2-558-5932 or 82-2-558-5934

Malaysia - Kuala Lumpur Tel: 60-3-6201-9857 Fax: 60-3-6201-9859

**Malaysia - Penang** Tel: 60-4-227-8870 Fax: 60-4-227-4068

Philippines - Manila Tel: 63-2-634-9065 Fax: 63-2-634-9069

**Singapore** Tel: 65-6334-8870 Fax: 65-6334-8850

**Taiwan - Hsin Chu** Tel: 886-3-5778-366 Fax: 886-3-5770-955

Taiwan - Kaohsiung Tel: 886-7-213-7830

**Taiwan - Taipei** Tel: 886-2-2508-8600 Fax: 886-2-2508-0102

**Thailand - Bangkok** Tel: 66-2-694-1351 Fax: 66-2-694-1350

#### EUROPE

Austria - Wels Tel: 43-7242-2244-39 Fax: 43-7242-2244-393 Denmark - Copenhagen Tel: 45-4450-2828 Fax: 45-4485-2829

France - Paris Tel: 33-1-69-53-63-20 Fax: 33-1-69-30-90-79

Germany - Dusseldorf Tel: 49-2129-3766400

**Germany - Munich** Tel: 49-89-627-144-0 Fax: 49-89-627-144-44

Germany - Pforzheim Tel: 49-7231-424750

**Italy - Milan** Tel: 39-0331-742611 Fax: 39-0331-466781

Italy - Venice Tel: 39-049-7625286

Netherlands - Drunen Tel: 31-416-690399 Fax: 31-416-690340

Poland - Warsaw Tel: 48-22-3325737

**Spain - Madrid** Tel: 34-91-708-08-90 Fax: 34-91-708-08-91

**Sweden - Stockholm** Tel: 46-8-5090-4654

**UK - Wokingham** Tel: 44-118-921-5800 Fax: 44-118-921-5820

10/28/13

# **Mouser Electronics**

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Microchip:

MCP1632-BAE/MS MCP1632-BAE/MC MCP1632-AAE/MS MCP1632-AAE/MC MCP1632T-BAE/MC MCP1632T-BAE/MS MCP1632T-AAE/MC MCP1632T-AAE/MS