

J-CAP™ Series

Highest Joules/cc Conductive Polymer Solid Electrolytic Chip Capacitors



FEATURES


- Highest Energy per volume
- Fast DCL drop with Voltage applied after reflow
- Benign failure mode under recommended use conditions
- Low ESR
- Undertab terminations layout:
 - High Volumetric Efficiency
 - Low profile case sizes
 - High capacitance in smaller dimensions
 - Close positioning of several parts for efficient high density PCB layout
- 3x reflow 260°C compatible



LEAD-FREE
LEAD-FREE COMPATIBLE
COMPONENT




RoHS
COMPLIANT




APPLICATIONS

- Power backup for SSDs (MLC, SLC, EFD, PCIe), battery-powered portable equipment, industrial alarms, smart power meters, and mobile devices.

J-LEAD



UNDERTAB



CASE DIMENSIONS UNDERTAB: millimeters (inches)

| Code | EIA Code | EIA Metric | L±0.20 (0.008) | W+0.20 (0.008) -0.10 (0.004) | H max. | Wp±0.10 (0.004) | Wn±0.10 (0.004) | Ap±0.10 (0.004) | An±0.10 (0.004) | S Min. |
|------|----------|------------|----------------|------------------------------|--------------|-----------------|-----------------|-----------------|-----------------|--------------|
| L | 1210 | 3528-10 | 3.50 (0.138) | 2.80 (0.110) | 1.00 (0.039) | 2.50 (0.098) | 2.10 (0.083) | 1.15 (0.045) | 1.35 (0.053) | 1.00 (0.039) |
| T | 1210 | 3528-12 | 3.50 (0.138) | 2.80 (0.110) | 1.20 (0.047) | 2.50 (0.098) | 2.10 (0.083) | 1.15 (0.045) | 1.35 (0.053) | 1.00 (0.039) |
| X | 2917 | 7343-15 | 7.30 (0.287) | 4.30 (0.169) | 1.50 (0.059) | 3.25 (0.128) | 3.25 (0.128) | 2.00 (0.079) | 3.20 (0.126) | 2.10 (0.083) |
| 4 | 2924 | 7361-20 | 7.30 (0.287) | 6.10 (0.240) | 2.00 (0.079) | 4.75 (0.187) | 4.75 (0.187) | 2.00 (0.079) | 3.20 (0.126) | 2.10 (0.083) |

CASE DIMENSIONS J-LEAD: millimeters (inches)

| Code | EIA Code | EIA Metric | L±0.20 (0.008) | W+0.20 (0.008) -0.10 (0.004) | H±0.20 (0.008) -0.10 (0.004) | Wp±0.20 (0.008) | A+0.30 (0.012) -0.20 (0.008) | S Min. |
|------|----------|------------|----------------|------------------------------|------------------------------|-----------------|------------------------------|--------------|
| C | 2312 | 6032-28 | 6.00 (0.236) | 3.20 (0.126) | 2.60 (0.102) | 2.20 (0.087) | 1.30 (0.051) | 2.90 (0.114) |
| D | 2917 | 7343-31 | 7.30 (0.287) | 4.30 (0.169) | 2.90 (0.114) | 2.40 (0.094) | 1.30 (0.051) | 4.40 (0.173) |
| E | 2917 | 7343-43 | 7.30 (0.287) | 4.30 (0.169) | 4.10 (0.162) | 2.40 (0.094) | 1.30 (0.051) | 4.40 (0.173) |
| H | 1210 | 3528-15 | 3.50 (0.138) | 2.80 (0.110) | 1.50 (0.059) max. | 2.20 (0.087) | 0.80 (0.031) | 1.40 (0.055) |
| 5 | 2917 | 7343-40 | 7.30 (0.287) | 4.30 (0.169) | 3.80 (0.150) | 2.40 (0.094) | 1.30 (0.051) | 4.40 (0.173) |


W₁ dimension applies to the termination width for A dimensional area only.

MAXIMUM ENERGY PER CASE SIZE


| Case Size | H Max (mm) | Max Energy (mJ) |
|-----------|------------|-----------------|
| C | 2.8 | 5.8 |
| D | 3.1 | 21.8 |
| E | 4.3 | 11.9 |
| H | 1.5 | 3.3 |
| L | 1.0 | 1.8 |
| T | 1.2 | 6.5 |
| X | 1.5 | 18.2 |
| 4 | 2.0 | 43.0 |
| 5 | 4.0 | 46.6 |

MARKING

C, D, E, H, L, T, X, 5 CASE



4 CASE



HOW TO ORDER

| | | | | | | | |
|----------------------------------|--|--|-----------------------------------|--|---|--------------------------|---|
| TCN Type TCJ TCN | 4 Case Size See table above | 158 Capacitance Code pF code: 1st two digits represent significant figures, 3rd digit represents multiplier | M Tolerance M = ±20% | 006 Rated DC Voltage 006 = 6.3Vdc 020 = 20Vdc 010 = 10Vdc 025 = 25Vdc 016 = 16Vdc 035 = 35Vdc | R Packaging R = Pure Tin 7" Reel S = Pure Tin 13" Reel (J-Lead) | 0055 ESR in mΩ | E Additional Character E = Black resin |
|----------------------------------|--|--|-----------------------------------|--|---|--------------------------|---|

Part Numbers already changed to an "E" suffix will continue to be supplied with only black resin. Those Part Numbers currently produced with gold resin will eventually change to black before July, 2020.



The Important Information/Disclaimer is incorporated in the catalog where these specifications came from or available online at www.avx.com/disclaimer/ by reference and should be reviewed in full before placing any order.

TECHNICAL SPECIFICATIONS

| | | | | | | | | |
|------------------------------------|--|-----|----|----|----|----|----|----|
| Technical Data: | All technical data relate to an ambient temperature of +25°C | | | | | | | |
| Capacitance Range: | 4.7 μF to 1500 μF | | | | | | | |
| Capacitance Tolerance: | ±20% | | | | | | | |
| Leakage Current DCL: | 0.1CV | | | | | | | |
| Rated Voltage DC (V _R) | ≤ +85°C: | 6.3 | 10 | 16 | 20 | 25 | 35 | 50 |
| Surge Voltage (V _S) | ≤ +85°C: | 8 | 13 | 21 | 26 | 33 | 46 | 65 |
| Temperature Range: | -55°C up to +125°C | | | | | | | |
| Reliability: | 1% per 1000 hours at 85°C, V _R with 0.1Ω/V series impedance 60% confidence level | | | | | | | |

NOTE: Conductive Polymer Capacitors are designed to operate within the limits of the environmental conditions specified for each series. If operated continuously at their maximum temperature and / or humidity limit, or beyond these limits, capacitors may exhibit a parametric shift in capacitance and increases in ESR. These changes may occur earlier if the specified environmental conditions are exceeded. Similarly, their normal operational time period will be significantly extended if their general duty cycle includes operation below maximum temperature within humidity controlled environments. Careful attention should be paid to maximum temperature with associated high humidity environments as well as voltage derating, ripple current and current surges. Please reference the AVX Conductive Polymer Capacitor Guidelines for more information or contact factory for application assistance.

CAPACITANCE AND RATED VOLTAGE RANGE (LETTER DENOTES CASE SIZE)

| Capacitance | | Rated Voltage DC to 85°C, [mJ] | | | | | | |
|-------------|------|--------------------------------|--------------------------|--------------------------|----------------|--------------------------|--------------------------|---------------|
| μF | Code | 6.3V (J) | 10V (A) | 16V (C) | 20V (D) | 25V (E) | 35V (V) | 50V (T) |
| 4.7 | 475 | | | | | | L(300E) [1.8] T(200E) | |
| 6.8 | 685 | | | | | | | C(200E) [5.4] |
| 10 | 106 | | | | | | T(200E) [3.9] | D(120E) [8.0] |
| 15 | 156 | | | | | | C(200E) [5.8] | E(70E) [11.9] |
| 22 | 226 | | | | | T(200E) [4.3] | D(100E) [8.5] | |
| 33 | 336 | | | H(150E) [3.3] T(200E) | | T(250E) [6.5] | D(70E) [12.8] | |
| 47 | 476 | | C(100E) [1.7] H(100E) | T(200) [4.7] T(150E) | | X(100E) [9.2] | X(150E) [18.2] | |
| 68 | 686 | H(100E) [0.8] | D(45E) [2.5] | D(50E) [6.7] | D(55E) [8.4] | D(70E) [13.3] | | |
| 100 | 107 | | D(45E) [3.6] | D(50E) [9.9] | D(55E) [12.4] | D(70E) [19.6] 4(100E) | 4(100E) [38.8] | |
| 150 | 157 | T(200E) [1.7] | D(45E) [5.4] | X(100E) [14.9] | | 4(70E) [29.3] | | |
| 220 | 227 | H(170E) [2.6] | D(40E) [7.9] | D(50E) [21.8] 4(70E) | 4(100E) [27.2] | 4(100E) [43.0] | | |
| 330 | 337 | D(40E) [3.8] | 5(100E) [11.9] | 4(70E) [32.7] 5(100E) | | | | |
| 470 | 477 | X(50E) [5.4] | | 5(100E) [46.6] | | | | |
| 1000 | 108 | 4(55E) [11.6] | | | | | | |
| 1500 | 158 | 4(55E) [17.4] | | | | | | |

Note for designers - for the highlighted ratings, higher voltage options are now available in the same case size and are recommended for new designs.

Released ratings, (ESR ratings in mOhms in parentheses) [Energy in mJ]

Note: Voltage ratings are minimum values. AVX reserves the right to supply

higher voltage ratings in the same case size, to the same reliability standards.

RATINGS & PART NUMBER REFERENCE

| AVX Part No. | Case Size | Capacitance (µF) | Rated Voltage (V) | Maximum Operating Temperature (°C) | DCL Max. (µA) | DF Max. (%) | ESR Max. @ 100kHz (mΩ) | 1000kHz RMS Current (mA) 45°C | Product Category | MSL | ENERGY | | |
|-------------------|-----------|------------------|-------------------|------------------------------------|---------------|-------------|------------------------|-------------------------------|------------------|-----|-------------|------------------------|----------------------|
| | | | | | | | | | | | Energy (mJ) | Energy/volume (mJ/cm³) | Energy/area (mJ/cm²) |
| 6.3 Volt @ 85°C | | | | | | | | | | | | | |
| TCJH686M006#0100E | H | 68 | 6.3 | 105 | 40.8 | 6 | 100 | 1000 | 3 | 3 | 0.8 | 54 | 8.0 |
| TCNT157M006#0200E | T | 150 | 6.3 | 105 | 90 | 10 | 200 | 700 | 3 | 4 | 1.7 | 147 | 17.7 |
| TCJH227M006#0170E | H | 220 | 6.3 | 105 | 132 | 10 | 170 | 800 | 3 | 3 | 2.6 | 173 | 26 |
| TCJD337M006#0040E | D | 330 | 6.3 | 105 | 198 | 6 | 40 | 2400 | 2 | 3 | 3.8 | 42 | 12.2 |
| TCNX477M006#0050E | X | 470 | 6.3 | 85 | 282 | 10 | 50 | 1900 | 5 | 5 | 5.4 | 115 | 17.3 |
| TCN4108M006#0055E | 4 | 1000 | 6.3 | 85 | 600 | 20 | 55 | 1860 | 5 | 4 | 11.6 | 130 | 26 |
| TCN4158M006#0055E | 4 | 1500 | 6.3 | 85 | 900 | 20 | 55 | 1860 | 5 | 4 | 17.4 | 195 | 39 |
| 10 Volt @ 85°C | | | | | | | | | | | | | |
| TCJH476M010#0100E | H | 47 | 10 | 105 | 47 | 6 | 100 | 1000 | 3 | 3 | 1.7 | 115 | 17.3 |
| TCJC476M010#0100E | C | 47 | 10 | 125 | 47 | 6 | 100 | 1300 | 1 | 3 | 1.7 | 34 | 8.8 |
| TCJD686M010#0045E | D | 68 | 10 | 105 | 68 | 6 | 45 | 2200 | 3 | 3 | 2.5 | 27 | 7.8 |
| TCJD107M010#0045E | D | 100 | 10 | 105 | 100 | 6 | 45 | 2200 | 3 | 3 | 3.6 | 40 | 11.5 |
| TCJD157M010#0045E | D | 150 | 10 | 105 | 150 | 6 | 45 | 2200 | 3 | 3 | 5.4 | 59 | 17.2 |
| TCJD227M010#0040E | D | 220 | 10 | 105 | 220 | 6 | 40 | 2400 | 3 | 3 | 7.9 | 87 | 25.2 |
| TCJ5337M010#0100E | 5 | 330 | 10 | 105 | 330 | 10 | 100 | 1300 | 2 | 3 | 11.9 | 100 | 37.8 |
| 16 Volt @ 85°C | | | | | | | | | | | | | |
| TCJH336M016#0150E | H | 33 | 16 | 105 | 52.8 | 6 | 150 | 800 | 3 | 3 | 3.3 | 223 | 33.4 |
| TCNT336M016#0200E | T | 33 | 16 | 105 | 52.8 | 6 | 200 | 700 | 3 | 4 | 3.3 | 277 | 33.4 |
| TCNT476M016#0150E | T | 47 | 16 | 105 | 75.2 | 6 | 150 | 800 | 3 | 4 | 4.7 | 395 | 47.6 |
| TCNT476M016#0200E | T | 47 | 16 | 105 | 75.2 | 6 | 200 | 700 | 3 | 4 | 4.7 | 395 | 47.6 |
| TCJD686M016#0050E | D | 68 | 16 | 105 | 108.8 | 6 | 50 | 2100 | 2 | 3 | 6.7 | 74 | 21.5 |
| TCJD107M016#0050E | D | 100 | 16 | 105 | 160 | 6 | 50 | 2100 | 2 | 3 | 9.9 | 109 | 31.6 |
| TCNX157M016#0100E | X | 150 | 16 | 105 | 240 | 6 | 100 | 1300 | 3 | 4 | 14.9 | 316 | 47.4 |
| TCJD227M016#0050E | D | 220 | 16 | 105 | 352 | 10 | 50 | 2100 | 2 | 3 | 21.8 | 240 | 69.5 |
| TCN4227M016#0070E | 4 | 220 | 16 | 105 | 352 | 20 | 70 | 1650 | 2 | 4 | 21.8 | 245 | 49 |
| TCN4337M016#0070E | 4 | 330 | 16 | 105 | 528 | 20 | 70 | 1650 | 3 | 4 | 32.7 | 367 | 73.5 |
| TCJ5337M016#0100E | 5 | 330 | 16 | 105 | 528 | 10 | 100 | 1300 | 2 | 3 | 32.7 | 274 | 104.2 |
| TCJ5477M016#0100E | 5 | 470 | 16 | 105 | 752 | 10 | 100 | 1300 | 3 | 3 | 46.6 | 391 | 148.5 |
| 20 Volt @ 85°C | | | | | | | | | | | | | |
| TCJD686M020#0055E | D | 68 | 20 | 105 | 136 | 6 | 55 | 2000 | 3 | 3 | 8.4 | 92 | 26.7 |
| TCJD107M020#0055E | D | 100 | 20 | 105 | 200 | 6 | 55 | 2000 | 3 | 3 | 12.4 | 136 | 39.3 |
| TCN4227M020#0100E | 4 | 220 | 20 | 85 | 440 | 10 | 100 | 1380 | 5 | 4 | 27.2 | 305 | 61.1 |
| 25 Volt @ 85°C | | | | | | | | | | | | | |
| TCNT226M025#0200E | T | 22 | 25 | 105 | 55 | 6 | 200 | 700 | 3 | 4 | 4.3 | 364 | 43.9 |
| TCNT336M025#0250E | T | 33 | 25 | 105 | 82.5 | 10 | 250 | 600 | 3 | 4 | 6.5 | 547 | 65.8 |
| TCNX476M025#0100E | X | 47 | 25 | 105 | 117.5 | 6 | 100 | 1300 | 2 | 5 | 9.2 | 195 | 29.3 |
| TCJD686M025#0070E | D | 68 | 25 | 105 | 170 | 6 | 70 | 1800 | 2 | 3 | 13.3 | 146 | 42.3 |
| TCJD107M025#0070E | D | 100 | 25 | 105 | 250 | 6 | 70 | 1800 | 2 | 3 | 19.6 | 215 | 62.3 |
| TCN4107M025#0100E | 4 | 100 | 25 | 105 | 250 | 6 | 100 | 1380 | 2 | 4 | 19.6 | 219 | 43.9 |
| TCN4157M025#0070E | 4 | 150 | 25 | 105 | 375 | 6 | 70 | 1650 | 2 | 4 | 29.3 | 329 | 65.9 |
| TCN4227M025#0100E | 4 | 220 | 25 | 105 | 550 | 10 | 100 | 1380 | 3 | 4 | 43.0 | 483 | 96.7 |
| 35 Volt @ 85°C | | | | | | | | | | | | | |
| TCNL475M035#0300E | L | 4.7 | 35 | 105 | 16.5 | 6 | 300 | 600 | 2 | 5 | 1.8 | 186 | 18.6 |
| TCNT475M035#0200E | T | 4.7 | 35 | 105 | 16.5 | 10 | 200 | 700 | 3 | 4 | 1.8 | 154 | 18.6 |
| TCNT106M035#0200E | T | 10 | 35 | 105 | 35 | 10 | 200 | 700 | 3 | 4 | 3.9 | 328 | 39.5 |
| TCJC156M035#0200E | C | 15 | 35 | 105 | 52.5 | 6 | 200 | 900 | 3 | 3 | 5.8 | 116 | 30.3 |
| TCJD226M035#0100E | D | 22 | 35 | 105 | 77 | 6 | 100 | 1500 | 2 | 3 | 8.5 | 94 | 27.1 |
| TCJD336M035#0070E | D | 33 | 35 | 105 | 115.5 | 6 | 70 | 1800 | 2 | 3 | 12.8 | 141 | 40.7 |
| TCNX476M035#0150E | X | 47 | 35 | 105 | 165 | 10 | 150 | 1100 | 3 | 4 | 18.2 | 387 | 58.0 |
| TCN4107M035#0100E | 4 | 100 | 35 | 105 | 350 | 10 | 100 | 1380 | 2 | 3 | 38.8 | 435 | 87.1 |
| 50 Volt @ 85°C | | | | | | | | | | | | | |
| TCJC685M050#0200E | C | 6.8 | 50 | 105 | 34 | 8 | 200 | 900 | 3 | 3 | 5.4 | 108 | 28.2 |
| TCJD106M050#0120E | D | 10 | 50 | 105 | 50 | 10 | 120 | 1400 | 3 | 3 | 8.0 | 87 | 25.3 |
| TCJE156M050#0070E | E | 15 | 50 | 105 | 75 | 6 | 70 | 1900 | 3 | 3 | 11.9 | 93 | 38 |

Energy is calculated by this formula (consider derating factor):

$$\text{Energy} = \frac{1}{2} C \times ((V_r \times X)^2 - V_x^2)$$

where C = Capacitance

V_r = Rated Voltage

X = Recommended derating factor

V_x = 3V (invariable)

Moisture Sensitivity Level (MSL) is defined according to J-STD-020.

All technical data relates to an ambient temperature of +25°C. Capacitance is measured at 120Hz, 0.5RMS with DC bias of 2.2 volts. DCL is measured at rated voltage after 5 minutes.

ESR allowed to move up to 1.25 times catalog limit post mounting.

For typical weight and composition see page 276.

NOTE: AVX reserves the right to supply higher voltage ratings in the same case size, to the same reliability standards.

J-CAP™ Series


Highest Joules/cc Conductive Polymer Solid Electrolytic Chip Capacitors




RECOMMENDED DERATING FACTOR

Voltage and temperature derating as percentage of Vr


Product Category 1




Product Category 2



Product Category 3



Product Category 5



PRODUCT CATEGORY 1 (TEMPERATURE RANGE -55°C TO +125°C)

| TEST | Condition | Characteristics | | | | | | | | |
|------------------------------|---|--------------------|--|--------------|-------|-----------|-----------|-----------|------------|-----------|
| Endurance | Apply rated voltage (Ur) at 85°C and /or 2/3 rated voltage (Ur) at 125°C for 2000 hours through a circuit impedance of $\leq 0.1\Omega/V$. Stabilize at room temperature for 1-2 hours before measuring. | Visual examination | no visible damage | | | | | | | |
| | | DCL | 1.25 x initial limit | | | | | | | |
| | | $\Delta C/C$ | within $\pm 20\%$ of initial value | | | | | | | |
| | | DF | 1.5 x initial limit | | | | | | | |
| | | ESR | 2 x initial limit | | | | | | | |
| Storage Life | Store at 125°C, no voltage applied, for 2000 hours. Stabilize at room temperature for 1-2 hours before measuring. | Visual examination | no visible damage | | | | | | | |
| | | DCL | 2 x initial limit | | | | | | | |
| | | $\Delta C/C$ | within $\pm 20\%$ of initial value | | | | | | | |
| | | DF | 1.5 x initial limit | | | | | | | |
| | | ESR | 2 x initial limit | | | | | | | |
| Humidity | Store at 65°C and 95% relative humidity for 500 hours, with no applied voltage. Stabilize at room temperature and humidity for 1-2 hours before measuring. | Visual examination | no visible damage | | | | | | | |
| | | DCL | 3 x initial limit | | | | | | | |
| | | $\Delta C/C$ | within +30/-20% of initial value | | | | | | | |
| | | DF | 1.5 x initial limit | | | | | | | |
| | | ESR | 2 x initial limit | | | | | | | |
| Temperature Stability | Step | Temperature°C | Duration(min) | | | | | | | |
| | 1 | +20 | 15 | | +20°C | -55°C | +20°C | +85°C | +125°C | +20°C |
| | 2 | -55 | 15 | DCL | IL* | n/a | IL* | 10 x IL* | 12.5 x IL* | IL* |
| | 3 | +20 | 15 | $\Delta C/C$ | n/a | +0/-20% | $\pm 5\%$ | +20/-0% | +30/-0% | $\pm 5\%$ |
| | 4 | +85 | 15 | DF | IL* | 1.5 x IL* | IL* | 1.5 x IL* | 2 x IL* | IL* |
| | 5 | +125 | 15 | | | | | | | |
| | 6 | +20 | 15 | | | | | | | |
| Surge Voltage | Apply 1.3x 2.3x rated voltage (Ur) at 125°C for 1000 cycles of duration 6 min (30 sec charge, 5 min 30 sec discharge) through a charge / discharge resistance of 1000 Ω | Visual examination | no visible damage | | | | | | | |
| | | DCL | initial limit | | | | | | | |
| | | $\Delta C/C$ | within +10/-20% of initial value for Vr $\leq 10V$ within +20/-30% of initial value for Vr $\geq 16V$ | | | | | | | |
| | | DF | 1.25 x initial limit | | | | | | | |
| Mechanical Shock | MIL-STD-202, Method 213, Condition C | Visual examination | no visible damage | | | | | | | |
| | | DCL | initial limit | | | | | | | |
| | | $\Delta C/C$ | within $\pm 5\%$ of initial value | | | | | | | |
| | | DF | initial limit | | | | | | | |
| | | ESR | initial limit | | | | | | | |
| Vibration | MIL-STD-202, Method 204, Condition D | Visual examination | no visible damage | | | | | | | |
| | | DCL | initial limit | | | | | | | |
| | | $\Delta C/C$ | within $\pm 5\%$ of initial value | | | | | | | |
| | | DF | initial limit | | | | | | | |
| | | ESR | initial limit | | | | | | | |

*Initial Limit

Initial measurement max. 1hr after the removal from dry pack or after pretreatment at 85°C for 24 hours.

PRODUCT CATEGORY 2, 3 (TEMPERATURE RANGE -55°C TO +105°C)

| TEST | Condition | Characteristics | | | | | | | | |
|------------------------------|--|--------------------|--|--------------|-------|-----------|-----------|-----------|------------|-----------|
| Endurance | Apply rated voltage (Ur) at 85°C for 2000 hours through a circuit impedance of $\leq 0.1\Omega/V$ (all CATEGORIES). And / or apply rated voltage (Ur) (CATEGORY 2) or 0.8x rated voltage (CATEGORY 3) at 105°C for 2000 hours through a circuit impedance of $\leq 0.1\Omega/V$. Always stabilize at room temperature for 1-2 hours before measuring. | Visual examination | no visible damage | | | | | | | |
| | | DCL | 1.25 x initial limit | | | | | | | |
| | | $\Delta C/C$ | within +10/-20% of initial value for $V_r \leq 16V$ within $\pm 20\%$ of initial value for $V_r \geq 20V$ | | | | | | | |
| | | DF | 1.5 x initial limit | | | | | | | |
| | | ESR | 2 x initial limit | | | | | | | |
| Storage Life | Store at 105°C, no voltage applied, for 2000 hours. Stabilize at room temperature for 1-2 hours before measuring. | Visual examination | no visible damage | | | | | | | |
| | | DCL | 1.25 x initial limit | | | | | | | |
| | | $\Delta C/C$ | within +10/-20% of initial value for $V_r \leq 16V$ within $\pm 20\%$ of initial value for $V_r \geq 20V$ | | | | | | | |
| | | DF | 1.5 x initial limit | | | | | | | |
| | | ESR | 2 x initial limit | | | | | | | |
| Humidity | Store at 65°C and 95% relative humidity for 500 hours, with no applied voltage. Stabilize at room temperature and humidity for 1-2 hours before measuring. | Visual examination | no visible damage | | | | | | | |
| | | DCL | 3 x initial limit | | | | | | | |
| | | $\Delta C/C$ | within +30/-20% of initial value | | | | | | | |
| | | DF | 1.5 x initial limit | | | | | | | |
| | | ESR | 2 x initial limit | | | | | | | |
| Temperature Stability | Step | Temperature°C | Duration(min) | | | | | | | |
| | 1 | +20 | 15 | | +20°C | -55°C | +20°C | +85°C | +105°C | +20°C |
| | 2 | -55 | 15 | DCL | IL* | n/a | IL* | 10 x IL* | 12.5 x IL* | IL* |
| | 3 | +20 | 15 | $\Delta C/C$ | n/a | +0/-20% | $\pm 5\%$ | +20/-0% | +30/-0% | $\pm 5\%$ |
| | 4 | +85 | 15 | DF | IL* | 1.5 x IL* | IL* | 1.5 x IL* | 2 x IL* | IL* |
| | 5 | +105 | 15 | | | | | | | |
| | 6 | +20 | 15 | | | | | | | |
| Surge Voltage | Apply 1.3x rated voltage (Ur) at 105°C for CATEGORY 2, or apply 1.3x 0.8x rated voltage (Ur) at 105°C for CATEGORY 3 for 1000 cycles of duration 6 min (30 sec charge, 5 min 30 sec discharge) through a charge / discharge resistance of 1000 Ω | Visual examination | no visible damage | | | | | | | |
| | | DCL | initial limit | | | | | | | |
| | | $\Delta C/C$ | within +10/-20% of initial value for $V_r \leq 16V$ within +20/-30% of initial value for $V_r \geq 20V$ | | | | | | | |
| | | DF | 1.25 x initial limit | | | | | | | |
| | | ESR | initial limit | | | | | | | |
| Mechanical Shock | MIL-STD-202, Method 213, Condition C | Visual examination | no visible damage | | | | | | | |
| | | DCL | initial limit | | | | | | | |
| | | $\Delta C/C$ | within $\pm 5\%$ of initial value | | | | | | | |
| | | DF | initial limit | | | | | | | |
| | | ESR | initial limit | | | | | | | |
| Vibration | MIL-STD-202, Method 204, Condition D | Visual examination | no visible damage | | | | | | | |
| | | DCL | initial limit | | | | | | | |
| | | $\Delta C/C$ | within $\pm 5\%$ of initial value | | | | | | | |
| | | DF | initial limit | | | | | | | |
| | | ESR | initial limit | | | | | | | |

*Initial Limit

Initial measurement max. 1hr after the removal from dry pack or after pretreatment at 85°C for 24 hours.

PRODUCT CATEGORY 5 (TEMPERATURE RANGE -55°C TO +85°C)

| TEST | Condition | | | Characteristics | | | | | |
|------------------------------|--|---------------|---------------|--------------------|--|-----------|-----------|-----------|-----------|
| Endurance | Apply rated voltage (Ur) at 85°C for 2000 hours through a circuit impedance of $\leq 0.1\Omega/V$. Stabilize at room temperature for 1-2 hours before measuring. | | | Visual examination | no visible damage | | | | |
| | | | | DCL | 1.25 x initial limit | | | | |
| | | | | $\Delta C/C$ | within +10/-20% of initial value for $V_r \leq 16V$ within $\pm 20\%$ of initial value for $V_r \geq 20V$ | | | | |
| | | | | DF | 1.5 x initial limit | | | | |
| | | | | ESR | 2 x initial limit | | | | |
| Storage Life | Store at 85°C, no voltage applied, for 2000 hours. Stabilize at room temperature for 1-2 hours before measuring. | | | Visual examination | no visible damage | | | | |
| | | | | DCL | 1.25 x initial limit | | | | |
| | | | | $\Delta C/C$ | within +10/-20% of initial value for $V_r \leq 16V$ within $\pm 20\%$ of initial value for $V_r \geq 20V$ | | | | |
| | | | | DF | 1.5 x initial limit | | | | |
| | | | | ESR | 2 x initial limit | | | | |
| Humidity | Store at 65°C and 95% relative humidity for 500 hours, with no applied voltage. Stabilize at room temperature and humidity for 1-2 hours before measuring. | | | Visual examination | no visible damage | | | | |
| | | | | DCL | 5 x initial limit | | | | |
| | | | | $\Delta C/C$ | within +40/-20% of initial value | | | | |
| | | | | DF | 1.5 x initial limit | | | | |
| | | | | ESR | 2 x initial limit | | | | |
| Temperature Stability | Step | Temperature°C | Duration(min) | | +20°C | -55°C | +20°C | +85°C | +20°C |
| | 1 | +20 | 15 | | | | | | |
| | 2 | -55 | 15 | DCL | IL* | n/a | IL* | 10 x IL* | IL* |
| | 3 | +20 | 15 | $\Delta C/C$ | n/a | +0/-20% | $\pm 5\%$ | +20/-0% | $\pm 5\%$ |
| | 4 | +85 | 15 | DF | IL* | 1.5 x IL* | IL* | 1.5 x IL* | IL* |
| | 5 | +20 | 15 | | | | | | |
| Surge Voltage | Apply 1.3x rated voltage (Ur) at 85°C for 1000 cycles of duration 6 min (30 sec charge, 5 min 30 sec discharge) through a charge / discharge resistance of 1000 Ω | | | Visual examination | no visible damage | | | | |
| | | | | DCL | initial limit | | | | |
| | | | | $\Delta C/C$ | within +10/-20% of initial value for $V_r \leq 16V$ within +20/-30% of initial value for $V_r \geq 20V$ | | | | |
| | | | | DF | 1.25 x initial limit | | | | |
| | | | | ESR | initial limit | | | | |
| Mechanical Shock | MIL-STD-202, Method 213, Condition C | | | Visual examination | no visible damage | | | | |
| | | | | DCL | initial limit | | | | |
| | | | | $\Delta C/C$ | within $\pm 5\%$ of initial value | | | | |
| | | | | DF | initial limit | | | | |
| | | | | ESR | initial limit | | | | |
| Vibration | MIL-STD-202, Method 204, Condition D | | | Visual examination | no visible damage | | | | |
| | | | | DCL | initial limit | | | | |
| | | | | $\Delta C/C$ | within $\pm 5\%$ of initial value | | | | |
| | | | | DF | initial limit | | | | |
| | | | | ESR | initial limit | | | | |

*Initial Limit


Initial measurement max. 1hr after the removal from dry pack or after pretreatment at 85°C for 24 hours.

J-CAP™ Series


Highest Joules/cc Conductive Polymer Solid Electrolytic Chip Capacitors




SOLID ELECTROLYTIC CAPACITOR ROADMAP



FIVE CAPACITOR CONSTRUCTION STYLES



SERIES LINE UP : Conductive Polymer



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

AVX:

[TCJH157M006R0200](#) [TCJT476M006R0080](#) [TCJT336M010R0070](#) [TCJT476M006R0120](#) [TCJD106M050R0120](#)
[TCJT686M004R0080](#) [TCJC336M010R0100](#) [TCJC476M010R0100](#) [TCJT107M004R0150](#) [TCJT336M010R0150](#)
[TCJT476M004R0080](#) [TCJT226M006R0150](#) [TCJT336M006R0150](#) [TCJC686M006R0100](#) [TCJT226M010R0150](#)
[TCJT106M016R0150](#) [TCJC156M035R0200](#) [TCJC226M025R0100](#) [TCJC475M035R0200](#) [TCJC685M035R0200](#)
[TCJD156M035R0070](#) [TCJD156M035R0100](#) [TCJD226M025R0060](#) [TCJD226M025R0100](#) [TCJD226M035R0070](#)
[TCJD226M035R0100](#) [TCJD336M025R0060](#) [TCJD336M025R0100](#) [TCJD336M035R0070](#) [TCJD336M035R0100](#)
[TCJD476M025R0060](#) [TCJD476M025R0100](#) [TCJE106M050R0070](#) [TCJE156M050R0070](#) [TCJE336M035R0055](#)
[TCJE476M025R0050](#) [TCJE476M035R0055](#) [TCJE686M025R0050](#) [TCJC106M035R0200](#) [TCJT106M016R0200](#)
[TCJC155M050R0300](#) [TCJC225M050R0300](#) [TCJC475M050R0200](#) [TCJC685M050R0200](#) [TCJD685M050R0120](#)
[TCJC225M063R0200](#) [TCJC335M063R0200](#) [TCJD475M063R0120](#) [TCJD475M075R0150](#) [TCJD685M063R0120](#)
[TCJD685M075R0120](#) [TCJE106M063R0100](#) [TCJE685M063R0100](#) [TCJC475M063R0200](#) [TCJC105M063R0300](#)
[TCJC155M063R0300](#) [TCJE107M016R0040](#) [TCJE107M020R0045](#) [TCJE157M016R0040](#) [TCJE686M020R0045](#)
[TCJC105M063S0300](#) [TCJC155M063S0300](#) [TCJC225M063S0200](#) [TCJC335M063S0200](#) [TCJC475M063S0200](#)
[TCJD475M063S0120](#) [TCJD475M075S0150](#) [TCJD685M063S0120](#) [TCJD685M075S0120](#) [TCJE106M063S0100](#)
[TCJE107M016S0040](#) [TCJE107M020S0045](#) [TCJE157M016S0040](#) [TCJE685M063S0100](#) [TCJE686M020S0045](#)
[TCJT476M006R0070](#) [TCJT107M006R0200](#) [TCJT686M006R0200](#) [TCJD337M006R0050](#) [TCJD227M006R0050](#)
[TCJD337M006R0040](#) [TCJD337M004R0050](#) [TCJD477M004R0050](#) [TCJD107M020R0055](#) [TCJD477M002R0050](#)
[TCJD686M020R0055](#) [TCJD335M125R0250](#) [TCJD157M010R0045](#) [TCJD227M010R0050](#) [TCJD227M010R0040](#)
[TCJD157M010R0055](#) [TCJE107M025R0080](#) [TCJD107M010R0055](#) [TCJD477M004R0040](#) [TCJD477M002R0040](#)
[TCJT107M006R0070](#) [TCJD107M010R0045](#) [TCJD227M006R0040](#) [TCJD337M004R0040](#) [TCJD157M010R0040](#)