


KEMET Part Number: PME264NE5470MR30
(P264EF473M660A)

PME264/P264, Film, Metallized Paper, Safety, 0.047 uF, 20%, 660 VAC (X2), 1500 VDC, 85°C, Lead Spacing = 25.4mm



General Information	
Supplier:	KEMET
Series:	PME264/P264
Dielectric:	Metallized Paper
Style:	Radial
Features:	EMI Safety
RoHS:	Yes
Lead:	Wire Leads
Qualifications:	ENEC, UL, cUL
AEC-Q200:	No
Construction:	Molded

Dimensions	
L	30.5mm MAX
H	17mm MAX
T	10.5mm MAX
S	25.4mm +/-0.4mm
LL	30mm +5mm
F	1mm NOM

Specifications	
Capacitance:	0.047 uF
Capacitance Tolerance:	20%
Voltage AC:	660 VAC (X2)
Voltage DC:	1500 VDC
Temperature Range:	-40/+85°C
Rated Temperature:	85°C
Dissipation Factor:	1.30% 1kHz
Insulation Resistance:	12 GOhms
Max dV/dt:	1000 V/us
Safety Class:	X2

Packaging Specifications	
Packaging:	Bulk, Bag
Packaging Quantity:	100