




1 2 3 4 5 6


# DIMENSIONS




DATE PRINTING  
YY-YEAR XX-WEEK



# PCB LAYOUT



# TERMINATION



# ORDERING INFORMATION

SERIES	8609	3	4	8	7	6	14	7	4	5	ELF
ROWS FITTED WITH CONTACTS											
ROW a	b	c									
ROW a - c											
NO. OF CONTACTS											
TYPE OF INSULATOR											
3 ROW MALE INSULATOR											
METHOD OF MOUNTING											
REVERSE MOUNTING - STYLE R/2											
TERMINATION											
STRAIGHT SPILL											
OPTIONS											
NO OPTION WITH HARPOONS											
PERFORMANCE CLASS											
DIN 41612 CLASS 3											4
DIN 41612 CLASS 2											5
DIN 41612 CLASS 1											6
AS PER MIL C 55302 / JSS 50808											8
PITCH PER ROW											
2.54 mm											
LEAD FREE VERSION											5

Copyright AFCL

GENERAL CHARACTERISTICS & ROHS INFO

REFER DRAWING C-8609-0000A

mat'l. code	surface	tolerance	projection	product family
SEE DWG C-8609-0000A	ISO 1302	ISO 406 ISO 1101		8609
itr	ecn	no	dr	title
A	104-0053	MINI	2004-09-17	DIN REVERSE HEADER
B	105-0042	MINI	2005-05-19	DIN 41612 STYLE R/2
C	106-0061	MINI	2006-05-31	
D	108-0146	KR	2008-10-21	dwg no
E	ELX-I-31455	MJA	2018-10-06	sheet 1 of 1 size
F	ELX-I-40615	MJA	2021-04-12	A3
sheet index	revision		appd	type
	F		SANOJ	Product Customer Drawing
	sheet	1		

form: A3

1 2 3

4 5 6