


VSVA-B-... Solenoid valve



FESTO

Festo SE & Co. KG
Rüter Straße 82
73734 Esslingen
Deutschland
+49 711 347-0

www.festo.com

Addendum document | Operating conditions UL

8160337
2021-12c
[8160339]



Translation of the original instructions

© 2022 all rights reserved to Festo SE & Co. KG

1 Applicable documents

All available documents for the product → www.festo.com/sp.

2 UL approval

In combination with the UL inspection mark on the product, the information in this section must also be observed in order to comply with the certification conditions of Underwriters Laboratories Inc. (UL) for USA and Canada.

UL approval information	
Product category code	YIOZ2 (USA) YIOZ8 (Canada)
File number	MH19482
Considered standards	UL 429
UL mark	

Tab. 1: UL approval information

- Technical data for the product may have different values in other documents. The technical data in this document will always have priority for the UL-certified products.
- Only for connection to a NEC/CEC Class 2 supply.
- Fitting and commissioning is to be carried out by qualified personnel only in accordance with the operating instructions. The personnel must have several years of training and experience in installing and commissioning electrical and pneumatic industrial control systems.
- A retrofit or expansion of the product with modules for which the UL mark does not apply will result in loss of the UL certification.

Acceptance conditions

In determining the acceptability of these valves in the end-use, the following shall be determined:

- These valves have been evaluated for connection to an NEC Class 2 source only.
- These valves are only intended for use in indoor-dry locations only.
- The valve connectors are intended to be factory-wired only.
- The suitability of the factory-wiring, including mating connectors, for secureness, and grounding of dead-metal, shall be determined in the end-product.
- These valves are intended for use in an ultimate electrical enclosure, and the need for an electrical enclosure for the valves shall be determined in the end-product application.
- These valves are intended for use in a suitable enclosure or mounted in a guarded and protected location where the valve body will be protected against impact.
- The suitability of the grounding/bonding connection shall be evaluated in the endproduct application.
- The suitability of the fluid connections to these valves, with respect to securement and leakage, are to be determined in the end-product application.
- These valves are intended to be used in conjunction with air-tubes with the following fittings designation:

Port	Air tube diameter	Size thread
1, 2, 3, 4, 5	3 ... 18 mm, 1/8 ... 1", M3 ... M7	M3, M5, M7, G 1/8, G 1/4, G 3/8, G 3/4, 1/8 NPT, 1/4 NPT, 3/8 NPT, 3/4 NPT, 5/32 UMF, 5/16 UMF
12, 14, 82, 84		M3, M5, M7, G 1/8, G 3/8, G 3/4, 1/8 NPT, 1/4 NPT, 3/8 NPT, 3/4 NPT, 5/32 UMF, 5/16 UMF

Tab. 2: Valve size 10

3 Technical data for UL approval

VSVA-B-...	...-A1-... ...-A2-... with holding current reduction feature	...22-...-D1-... ...32-...-D1-...	...52-...-D1-... ...53-...-D1-...
Power single solenoid plug-in	1.6 W	1.6 W	1.6 W
Power single solenoid	2.6 W	1.3 W	1.6 W
Max. power	5.2 W	2.6 W	3.2 W
Operating pressure	0.2 ... 1 MPa 29 ... 145 psi		
Maximum fluid temperature/ambient	-5 ... 50 °C 23 ... 122 °F		
Insulation class	Class 105 (A)	Class 155 (F)	
Fluid	Air or inert gas		

Tab. 3: Technical data UL

VSVA-B-...	...-D2-... with holding current reduction feature	...C1 and VSCS2 cURus approval only
Power single solenoid plug-in	4.6 W	–
Power single solenoid	4.6 W	1.8 W
Max. power	9.2 W	3.2 W
Operating pressure	0.2 ... 1 MPa 29 ... 145 psi	
Maximum fluid temperature/ambient	-5 ... 50 °C 23 ... 122 °F	
Insulation class	Class 155 (F)	
Fluid	Air or inert gas	

Tab. 4: Technical data UL