


Overvoltage protected AC switch (ACS)

Datasheet - production data



Features

- Blocking voltage: V_{DRM} / V_{RRM} = +/- 700 V
- Avalanche controlled: V_{CL} typ. = 1100 V
- Nominal conducting current: I_{T(RMS)} = 2 A
- Gate triggering current: I_{GT} < 10 mA
- High noise immunity: static dV/dt > 500 V/μs
 - Needs no more external protection snubber or varistor
 - Enables equipment to meet IEC 61000-4-5
 - Reduces component count up to 80%
 - Interfaces directly with the micro controller
 - Eliminates any gate kick back on the microcontroller
 - Allows straightforward connection of several AC switches on same cooling pad

Applications


- AC static switching in appliance control systems
- Drive of low power high inductive or resistive loads like:
 - Relay, valve, solenoid, dispenser
 - Pump, fan, micro-motor
 - Defrost heater

Description

The ACS120 belongs to the AC line switch family. This high-performance switch circuit is able to control a load of up to 2 A.

The ACS switch embeds a high-voltage clamping structure to absorb the inductive turn-off energy and a gate level shifter driver to separate the digital controller from the main switch. It is triggered with a negative gate current flowing out of the gate pin.

Figure 1. Functional diagram



Characteristics ACS120

1 Characteristics

Table 1. Absolute ratings (limiting values) for either positive or negative polarity of pin OUT voltage in respect to pin COM voltage

Symbol	Parameter		Value	Unit	
V_{DRM}/V_{RRM}	Repetitive peak off-state voltage				V
		DPAK	T _C = 119 °C		
$I_{T(RMS)}$	On-state RMS current full cycle sine wave 50 to 60 Hz	TO-220FPAB	T _C = 117 °C	2	Α
		TO-220AB	T _C = 119 °C		
ı	Non repetitive surge peak on-state current		t _P = 20 ms	20	Α
I _{TSM}	T_J initial = 25 °C, full cycle sine wave	le sine wave		21	Α
I ² t	Fusing capability $t_P = 10 \text{ ms}$			2.6	A ² s
dI/dt	Repetitive on-state current critical rate of rise $I_G = 10 \text{ mA} (t_r < 100 \text{ ns})$ $T_j = 125 \text{ °C}$ $f = 120 \text{ Hz}$			50	A/µs
V_{PP}	Non repetitive line peak pulse voltage ⁽¹⁾	2	kV		
T _{stg}	Storage temperature range	- 40 to + 150	°C		
T _J	Operating junction temperature range	- 30 to + 125	°C		
T _L	Maximum lead soldering temperature during	260	°C		

^{1.} According to test described by IEC 61000-4-5 standard and *Figure 17*.

Table 2. Switch Gate characteristics (maximum values)

Symbol	Parameter	Value	Unit
$P_{G(AV)}$	Average gate power dissipation	0.1	W
I _{GM}	Peak gate current (t _P = 20 μs)	1	Α
V_{GM}	Peak positive gate voltage (in respect to pin COM)	5	V

Table 3. Thermal resistances

Symbol	Parameter		Value	Unit	
		$S = 0.5 \text{ cm}^{2(1)}$	DPAK	70	°C/W
R _{th (j-a)}	Junction to ambient	TO-220FPAB		60	°C/W
		TO-220AB		60	°C/W
	Junction to case	DPAK		2.6	°C/W
R _{th (j-c)}		TO-220FPAB		3.5	°C/W
		TO-220AB		2.6	°C/W

^{1.} S = Copper surface under tab

2/17 DS3279 Rev 5

ACS120 Characteristics

Table 4. Parameter description

Symbol	Parameter description
I _{GT}	Triggering gate current
V _{GT}	Triggering gate voltage
V _{GD}	Non-triggering gate voltage
I _H	Holding current
IL	Latching current
V _{TM}	Peak on-state voltage drop
V _{TO}	On-state threshold voltage
R _d	On-state dynamic resistance
I _{DRM} / I _{RRM}	Maximum forward or reverse leakage current
dV/dt	Critical rate of rise of off-state voltage
(dV/dt)c	Critical rate of rise of commutating off-state voltage
(dl/dt)c	Critical rate of decrease of commutating on-state current
V _{CL}	Clamping voltage
I _{CL}	Clamping current

Table 5. Electrical characteristics

Symbol	Test co			Values	Unit	
I _{GT}	V_{OUT} = 12V (DC), R_L = 140 Ω	QII -QIII	T _J = 25 °C	Max.	10	mA
V _{GT}	V_{OUT} = 12V (DC), R_L = 140 Ω	QII -QIII	T _J = 25 °C	Max.	1	V
V _{GD}	$V_{OUT} = V_{DRM}, R_L = 3.3 \text{ k}\Omega$		T _J = 125 °C	Min.	0.15	V
I _H	I _{OUT} = 100 mA gate open		T _J = 25 °C	Max.	45	mA
ΙL	I _G = 20 mA		T _J = 25 °C	Max.	65	mA
V _{TM}	I _{OUT} = 2.8 A, t _p = 380 μs		T _J = 25 °C	Max.	1.3	V
V _{TO}			T _J = 125 °C	Max.	0.85	V
R _d			T _J = 125 °C	Max.	200	mΩ
1 /1	V _{OUT} = 700 V		T _J = 25 °C	Max.	2	
I _{DRM} /I _{RRM}			T _J = 125 °C	Max.	200	μA
dV/dt	V _{OUT} = 460 V gate open		T _J = 110 °C	Min.	500	V/µs
(dl/dt)c	(dV/dt)c = 20 V/µs		T _J = 125 °C	Min.	1	A/ms
V _{CL}	I _{CL} = 1 mA, t _p = 1 ms		T _J = 25 °C	Тур.	1100	V

Characteristics ACS120

Figure 2. Maximum power dissipation versus RMS on-state current P(W) 2.4 2.2 2.0 1.8 1.6 1.4 1.2 1.0 0.8 0.6 0.4 0.2 1.0

Figure 3. On-state RMS current versus case temperature $I_{\underline{\mathsf{T}(\mathsf{RMS})}}(\mathsf{A})$ 2.4 2.2 α = 180 TO-220AB/DPAI 20 1.8 O-220FPAB 1.6 1.4 1.2 1.0 0.8 0.6 0.4 0.2 T_c(°C) 0.0 125

Figure 4. On-state RMS current versus ambient temperature $I_{T(RMS)}(A)$ 1.8 1.6 α = 180 1.4 Printed circuit board FR4 natural convection 1.2 $S = 0.5 \text{ cm}^2$ 1.0 0.8 0.6 0.4 0.2 Tamb (°C) 0.0 0 25 50 75 100

Figure 5. Relative variation of thermal impedance versus pulse duration

1.E+00

K = [Z_{tt}/R_{tt}]

DPAK

TO-220FPAB

TO-220FPAB

TO-220FPAB

TO-220FPAB

TO-220AB

1.E-02

1.E-02


1.E-01

1.E+00

1.E+01

1.E+02

1.E+03






Figure 7. Relative variation of static dV/dt

ACS120 Characteristics

Figure 8. Relative variation of critical rate of decrease of main current versus reapplied dV/dt (typical values)




Figure 9. Relative variation of critical rate of decrease of main current versus junction temperature




Figure 10. Surge peak on-state current versus number of cycles




Figure 11. Non repetitive surge peak on-state current for a sinusoidal pulse with width $t_p < 10 \text{ ms}$




Figure 12. On-state characteristics (maximum values)





Figure 13. Thermal resistance junction to ambient versus copper surface under tab





DS3279 Rev 5

2 AC line switch basic application

The ACS120 device is well adapted to washing machine, dishwasher, tumble drier, refrigerator, air-conditioning systems, and cookware. It has been designed especially to switch on and off low power loads such as solenoid, valve, relay, dispenser, micro-motor, pump, fan and defrost heaters.

This AC switch is triggered by a negative gate current flowing out of the gate pin G. It can be driven directly by the digital MCU through a resistor as shown on the typical application diagram.

Thanks to its thermal and turn-off commutation performance, the ACS120 switch can drive, with no additional turn-off snubber, an inductive load up to 2 A.




Figure 14. Typical application diagram

2.1 Protection against overvoltage: the best choice is ACS


In comparison with standard Triacs the ACS120 is over-voltage self-protected, as specified by the new parameter V_{CL} . This feature is useful in two operating conditions: in case of turn-off of very inductive load, and in case of surge voltage that can occur on the electrical network.

6/17 DS3279 Rev 5

2.2 High inductive load switch-off: turn-off overvoltage clamping

With high inductive and low RMS current loads the rate of decrease of the current is very low. An overvoltage can occur when the gate current is removed and the OUT current is lower than $I_{\rm H}$.

As shown in *Figure 15 and Figure 16*, at the end of the last conduction half-cycle, the load current decreases (1). The load current reaches the holding current level I_H (2), and the ACS turns off (3). The water valve, as an inductive load (up to 15 H), reacts as a current generator and an overvoltage is created, which is clamped by the ACS (4). The current flows through the ACS avalanche and decreases linearly to zero. During this time, the voltage across the switch is limited to the clamping voltage V_{CL} . The energy stored in the inductance of the load is dissipated in the clamping section that is designed for this purpose. When the energy has been dissipated, the ACS voltage falls back to the mains voltage value (230 V rms, 50 Hz) (5).



Note: Same working principle described in item 2.2 is valid for both current directions.

4

DS3279 Rev 5 7/17

Alternating current mains transient voltage ruggedness 2.3

The ACS120 switch is able to withstand safely the AC mains transients either by clamping the low energy spikes or by breaking-over when subjected to high energy shocks, even with high turn-on current rises. The test circuit shown in Figure 17 is representative of the final ACS120 application, and is also used to test the AC switch according to the IEC 61000-4-5 standard conditions. Thanks to the load limiting the current, the ACS120 switch withstands the voltage spikes up to 2 kV above the peak mains voltage. The protection is based on an overvoltage crowbar technology. Actually, the ACS120 breaks over safely as shown in Figure 18. The ACS120 recovers its blocking voltage capability after the surge (switch-off back at the next zero crossing of the current). Such non-repetitive tests can be done 10 times on each AC mains voltage polarity.






Figure 17. Overvoltage ruggedness test circuit for resistive and inductive loads






8/17 DS3279 Rev 5 **ACS120 Package information**

3 **Package information**

- Epoxy meets UL94-V0
- Lead-free package
- Recommended torque: 0.4 to 0.6 N·m (TO-220AB, TO-220FPAB)

In order to meet environmental requirements, ST offers these devices in different grades of ECOPACK packages, depending on their level of environmental compliance. ECOPACK specifications, grade definitions and product status are available at: www.st.com. ECOPACK is an ST trademark.

3.1 **TO-220FPAB** package information



Package information ACS120

Table 6. TO-220FPAB package mechanical data

	Dimensions					
Ref.	Millimeters		Inche	es ⁽¹⁾		
	Min.	Max.	Min.	Max.		
А	4.40	4.60 0.1732		0.1811		
В	2.50	2.70	0.0984	0.1063		
D	2.50	2.75	0.0984	0.1083		
E	0.45	0.70	0.0177	0.0276		
F	0.75	1.00	0.0295	0.0394		
F1	1.15	1.70	0.0453	0.0669		
F2	1.15	1.70	0.0453	0.0669		
G	4.95	5.20	0.1949	0.2047		
G1	2.40	2.70	0.0945	0.1063		
Н	10.00	10.40	0.3937	0.4094		
L2	16.00	Тур.	0.6299	Э Тур.		
L3	28.60	30.60	1.1260	1.2047		
L4	9.80	10.60	0.3858	0.4173		
L5	2.90	3.60	0.1142	0.1417		
L6	15.90	16.40	0.6260	0.6457		
L7	9.00	9.30	0.3543	0.3661		
Dia.	3.00	3.20	0.1181	0.1260		

^{1.} Inches only for reference.

3.2 DPAK package information

Figure 20. DPAK package outline

THERMAL PAD

DI

DI

SEATING PLANE

GAUGE PLANE

Note:

This package drawing may slightly differ from the physical package. However, all the specified dimensions are guaranteed.


Package information ACS120

Table 7. DPAK package mechanical data

			Dime	nsions		
Ref.		Millimeters			Inches ⁽¹⁾	
	Min.	Тур.	Max.	Min.	Тур.	Max.
Α	2.18		2.40	0.0858		0.0945
A1	0.9		1.10	0.0354		0.0433
A2	0.03		0.23	0.0012		0.0091
b	0.64		0.90	0.0252		0.0354
b4	4.95		5.46	0.1949		0.2150
С	0.46		0.61	0.0181		0.0236
c2	0.46		0.60	0.0181		0.0236
D	5.97		6.22	0.2350		0.2449
D1	4.95		5.60	0.1949		0.2205
E	6.35		6.73	0.2500		0.2650
E1	4.32		5.50	0.1701		0.2165
е		2.286			0.0900	
e1	4.40		4.70	0.1732		0.1850
Н	9.35		10.40	0.3681		0.4094
L	1.0		1.78	0.0394		0.0701
L2			1.27			0.0500
L4	0.6		1.02	0.0236		0.0402
V2	-8°		+8°	-8°		+8°

^{1.} Inches only for reference.

Figure 21. Footprint (dimensions in mm)



ACS120 Package information

3.3 TO-220AB package information




Figure 22. TO-220AB package outline

1. Resin gate position accepted in each of the two position as well as the symmetrical opposites.

Package information ACS120

Table 8. TO-220AB package mechanical data

	Dimensions					
Ref.	Millimeters		Inch	es ⁽¹⁾		
	Min.	Max.	Min.	Max.		
А	4.40	4.60 0.1732		0.1811		
b	0.61	0.88	0.0240	0.0346		
b1	1.14	1.70	0.0449	0.0669		
С	0.48	0.70	0.0189	0.0276		
D	15.25	15.75	0.6004	0.6201		
D1	1.27	typ.	0.05 typ.			
E	10.00	10.40	0.3937	0.4094		
е	2.40	2.70	0.0945	0.1063		
e1	4.95	5.15	0.1949	0.2028		
F	1.23	1.32	0.0484	0.0520		
H1	6.20	6.60	0.2441	0.2598		
J1	2.40	2.72	0.0945	0.1071		
L	13.00	14.00	0.5118	0.5512		
L1	3.50	3.93	0.1378	0.1547		
L20	16.40 typ.		0.6457 typ.			
L30	28.90 typ.		1.1378 typ.			
ØP	3.75	3.85	0.1476	0.1516		
Q	2.65	2.95	0.1043	0.1161		

^{1.} Inches only for reference.

ACS120 Ordering information

4 Ordering information

Figure 23. Ordering information scheme




Table 9. Ordering information

Order code	Marking	Package	Weight	Base qty	Packing mode
ACS120-7SB	ACS1207S	DPAK	0.32 g	75	Tube
ACS120-7SB-TR	ACS1207S	DPAK	0.32 g	2500	Tape and reel
ACS120-7SFP	ACS1207S	TO-220FPAB	1.9 g	50	Tube
ACS120-7ST	ACS1207S	TO-220AB	1.9 g	50	Tube

Revision history ACS120

5 Revision history

Table 10. Document revision history

Date	Revision	Changes
Apr-2004	1	Previous release.
28-Jan-2011	2	Added ECOPACK statement. Updated $T_{\mathbb{C}}$ values in Table 1.
28-May-2014	3	Updated DPAK package information and reformatted to current standard.
02-May-2016	4	Added pin name on cover page package view and reformatted to current standard.
24-Mar-2022	5	Updated Figure 20.

IMPORTANT NOTICE - PLEASE READ CAREFULLY

STMicroelectronics NV and its subsidiaries ("ST") reserve the right to make changes, corrections, enhancements, modifications, and improvements to ST products and/or to this document at any time without notice. Purchasers should obtain the latest relevant information on ST products before placing orders. ST products are sold pursuant to ST's terms and conditions of sale in place at the time of order acknowledgement.

Purchasers are solely responsible for the choice, selection, and use of ST products and ST assumes no liability for application assistance or the design of Purchasers' products.

No license, express or implied, to any intellectual property right is granted by ST herein.

Resale of ST products with provisions different from the information set forth herein shall void any warranty granted by ST for such product.

ST and the ST logo are trademarks of ST. For additional information about ST trademarks, please refer to www.st.com/trademarks. All other product or service names are the property of their respective owners.

Information in this document supersedes and replaces information previously supplied in any prior versions of this document.

© 2022 STMicroelectronics – All rights reserved



DS3279 Rev 5 17/17

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

STMicroelectronics:

ACS120-7SFP ACS120-7ST ACS120-7SB ACS120-7SB-TR