


45 V field-effect rectifier diode

Datasheet - production data



Description

This single rectifier is based on a proprietary technology that achieves the best in class V_F/I_R trade-off for a given silicon surface.

Therefore it can advantageously replace 45 V low voltage Schottky diodes.

Packaged in DPAK, this device is intended to be used in rectification and freewheeling operations in power supplies.

Table 1: Device summary

| Symbol | Value |
|--------------------|--------|
| $I_{F(AV)}$ | 20 A |
| V_{RRM} | 45 V |
| $V_F(\text{typ.})$ | 0.29 V |
| $T_J(\text{max.})$ | 150 °C |

Features

- ST advanced rectifier process
- Stable leakage current over reverse voltage
- Low forward voltage drop
- High frequency operation
- ECOPACK[®]2 compliant component for DPAK on demand

1 Characteristics

Table 2: Absolute ratings (limiting values at 25 °C, unless otherwise specified, anode terminals short-circuited)

| Symbol | Parameter | Value | Unit | |
|---------------------|---|-----------------------------------|------|---|
| V _{RRM} | Repetitive peak reverse voltage | 45 | V | |
| I _{F(RMS)} | Forward rms current | 40 | A | |
| I _{F(AV)} | Average forward current $\delta = 0.5$, square wave | T _C = 125 °C | 20 | A |
| I _{FSM} | Surge non repetitive forward current | t _p = 10 ms sinusoidal | 180 | A |
| T _{stg} | Storage temperature range | -65 to +175 | °C | |
| T _j | Maximum operating junction temperature range ⁽¹⁾ | -40 to +150 | °C | |

Notes:

⁽¹⁾(dP_{tot}/dT_j) < (1/R_{th(j-a)}) condition to avoid thermal runaway for a diode on its own heatsink.

Table 3: Thermal resistance parameters

| Symbol | Parameter | Value | Unit |
|----------------------|------------------|-------|------|
| R _{th(j-c)} | Junction to case | 1.4 | °C/W |

Table 4: Static electrical characteristics (anode terminals short circuited)

| Symbol | Parameter | Test conditions | Min. | Typ. | Max. | Unit | |
|-------------------------------|-------------------------|-------------------------|-----------------------------------|------|------|------|----|
| I _R ⁽¹⁾ | Reverse leakage current | T _j = 25 °C | V _R = 35 V | - | 100 | 300 | μA |
| | | T _j = 125 °C | | - | 12 | 24 | mA |
| | | T _j = 25 °C | V _R = V _{RRM} | - | 200 | 600 | μA |
| | | T _j = 125 °C | | - | 18 | 40 | mA |
| V _F ⁽²⁾ | Forward voltage drop | T _j = 25 °C | I _F = 5 A | - | 0.35 | | V |
| | | T _j = 125 °C | | - | 0.29 | | |
| | | T _j = 25 °C | I _F = 10 A | - | 0.41 | 0.45 | |
| | | T _j = 125 °C | | - | 0.38 | 0.42 | |
| | | T _j = 25 °C | I _F = 20 A | - | 0.51 | 0.55 | |
| | | T _j = 125 °C | | - | 0.52 | 0.57 | |

Notes:

⁽¹⁾Pulse test: t_p = 5 ms, $\delta < 2\%$

⁽²⁾Pulse test: t_p = 380 μs, $\delta < 2\%$

To evaluate the maximum conduction losses use the following equation:

$$P = 0.27 \times I_{F(AV)} + 0.015 \times I_{F(RMS)}^2$$

1.1 Characteristics (curves)










Figure 7: Thermal resistance junction to ambient versus copper surface under tab for DPAK




2 Package information

In order to meet environmental requirements, ST offers these devices in different grades of ECOPACK® packages, depending on their level of environmental compliance. ECOPACK® specifications, grade definitions and product status are available at: www.st.com. ECOPACK® is an ST trademark.

- Cooling method: by conduction (C)
- Epoxy meets UL 94,V0

2.1 DPAK package information

Figure 8: DPAK package outline




This package drawing may slightly differ from the physical package. However, all the specified dimensions are guaranteed.

Table 5: DPAK package mechanical data

| Ref. | Dimensions | | | |
|------|-------------|-------|------------|-------|
| | Millimeters | | Inches | |
| | Min. | Max. | Min. | Max. |
| A | 2.18 | 2.40 | 0.085 | 0.094 |
| A1 | 0.90 | 1.10 | 0.035 | 0.043 |
| A2 | 0.03 | 0.23 | 0.001 | 0.009 |
| b | 0.64 | 0.90 | 0.025 | 0.035 |
| b4 | 4.95 | 5.46 | 0.194 | 0.215 |
| c | 0.46 | 0.61 | 0.018 | 0.024 |
| c2 | 0.46 | 0.60 | 0.018 | 0.023 |
| D | 5.97 | 6.22 | 0.235 | 0.244 |
| D1 | 4.95 | 5.60 | 0.194 | 0.220 |
| E | 6.35 | 6.73 | 0.250 | 0.265 |
| E1 | 4.32 | 5.50 | 0.170 | 0.216 |
| e | 2.286 typ. | | 0.090 typ. | |
| e1 | 4.40 | 4.70 | 0.173 | 0.185 |
| H | 9.35 | 10.40 | 0.368 | 0.409 |
| L | 1.0 | 1.78 | 0.039 | 0.070 |
| L2 | | 1.27 | | 0.050 |
| L4 | 0.60 | 1.02 | 0.023 | 0.040 |
| V2 | -8° | +8° | -8° | +8° |

Figure 9: DPAK recommended footprint (dimensions in mm)



3 Ordering information

Table 6: Ordering information

| Order code | Marking | Package | Weight | Base qty. | Delivery mode |
|---------------|-----------|---------|--------|-----------|---------------|
| FERD2045SB-TR | FERD 2045 | DPAK | 0.32 g | 2500 | Tape and reel |

4 Revision history

Table 7: Document revision history

| Date | Revision | Changes |
|-------------|----------|------------------|
| 15-Jan-2018 | 1 | Initial release. |

IMPORTANT NOTICE – PLEASE READ CAREFULLY

STMicroelectronics NV and its subsidiaries ("ST") reserve the right to make changes, corrections, enhancements, modifications, and improvements to ST products and/or to this document at any time without notice. Purchasers should obtain the latest relevant information on ST products before placing orders. ST products are sold pursuant to ST's terms and conditions of sale in place at the time of order acknowledgement.

Purchasers are solely responsible for the choice, selection, and use of ST products and ST assumes no liability for application assistance or the design of Purchasers' products.

No license, express or implied, to any intellectual property right is granted by ST herein.

Resale of ST products with provisions different from the information set forth herein shall void any warranty granted by ST for such product.

ST and the ST logo are trademarks of ST. All other product or service names are the property of their respective owners.

Information in this document supersedes and replaces information previously supplied in any prior versions of this document.

© 2018 STMicroelectronics – All rights reserved

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[STMicroelectronics:](#)

[FERD2045SB-TR](#)