



Piezoelectric Sound Components

EU RoHS Compliant

- All the products in this catalog comply with EU RoHS.
- EU RoHS is "the European Directive 2011/65/EU on the Restriction of the Use of Certain Hazardous Substances in Electrical and Electronic Equipment."
- For more details, please refer to our website 'Murata's Approach for EU RoHS' (http://www.murata.com/eneu/support/compliance/rohs).

Contents

Product specifications are as of December 2015.

Part Numbering ·····		
1 Piezoelectric Sounders		
SMD Type Product Lineup ·····	p4	
Pin Type Product Lineup	р7	
Pin Type Taping Product Lineup ······	p10	
Drive Method ·····	p12	
\triangle Caution · Notice · · · · · · · · · · · · · · · · · · ·	p13	
2 Piezoelectric Buzzers		
Product Lineup ·····	p15	
\triangle Caution · Notice · · · · · · · · · · · · · · · · · · ·	p16	
3 Piezoelectric Diaphragms		
Product Lineup	p18	
Design Procedures · Drive Method ······	p19	
\triangle Caution · Notice · · · · · · · · · · · · · · · · · · ·	p20	
Oscillating System ·····	p22	
To Raise Sound Pressure Level (S.P.L.)	p23	
Characteristics and Measuring Method	p24	
Minimum Quantity ·····	p25	

Please check the MURATA website (http://www.murata.com/) if you cannot find a part number in this catalog.

muRata

2

3

Part Numbering

SMD Piezoelectric Sounder

(Part Number)	PK	LCS	1212	Е	40	**	-R1
	1	2	8	4	6	6	7

1Product ID

Product ID	
PK	Piezoelectric Sound Components

2 Product

Code	Product
LCS/MCS	SMD Sounder

Oimensions

Code	Outer Dimensions
1212	□12mm
0909	□9mm

4 Drive

Code	Drive
E	External Drive

Pin Type Piezoelectric Sounders/Piezoelectric Buzzers

(Part Number)	РК	Μ	13	Е	Ρ	YH	40	**	Ρ	-A0
	0	2	8	4	6	6	7	8	9	10
Product ID										_

Pro	oduct ID	
	РК	Piezoelectric Sound Components

2 Product

Code	Product
м	Sounder
В	Buzzer

3 Outer Dimensions

Expressed by two figures in mm.

Ex.)	Code	Outer Dimensions
	13	ø12.6mm

4Drive

Code	Drive
E	External-Drive
s	Self-Drive

GOuter Electrode Style

Code	Outer Electrode Style
Р	Pin Type

6 Structure

Code	Structure			
P	Flat Type Auto-assemble			
Υ□	Flat Type/Available for Taping			
C□	Flat Type/Semi-auto-assemble			
	Exclude above mentioned			

 \Box signifies specification of the outer electrode.

Oscillating Frequency Type

Expressed resonant frequency by two-digit alphanumerics. The unit is in 100 hertz (Hz.) 4kHz (4000Hz) is denoted as "**40**."

GIndividual Specification Code

Code	Individual Specification Code				
**	Two digits express specific specification in characteristics.				

Packaging

00	
Code	Packaging
-R1	Plastic Taping

Oscillating Frequency Type

Expressed resonant frequency by two-digit alphanumerics. The unit is in 100 hertz (Hz). In case of 4kHz (4000Hz), expressed as "40."

BIndividual Specification Code

Code	Individual Specification Code				
**	Two digits express custom specification in characteristics.				

Special Quality Guarantee

Code	Special Quality Guarantee			
Р	Post Plated Terminal			
 Not Post Plated Terminal (Blank) 				

Packaging

Code	Packaging			
-ВО	Bulk			
-A0	Radial Taping			

Radial taping is not available for all types.

Please contact us.

Piezoelectric Diaphragms				
(Part Number)	7 N B -**** -1R5 L 10 9 9 9 9 9 9 6 6 7			
Product ID				
Product ID				
7	Ceramic Material			

2 Metal Plate Material

Code	Metal Plate Material			
В	Brass			
N	Nickel Alloy			

OProduct

Code	Product	
В	Piezoelectric Diaphragms	

4 Metal Plate Diameter

Code	Metal Plate Diameter			
_****	A hyphen (-) plus from two to four-digit alphanumerics express metal plate outer dimensions. A decimal point is expressed by the capital letter " R ."			

BResonant Frequency Type

A hyphen (-) and three-digit alphanumerics express resonant frequency. A decimal point is expressed by the capital letter "R." If there is no decimal point, the decimal point code is omitted.

OProduct Specification

Code	Product Specification			
L	With lead (available for RoHS)			
-	No lead (omitted)			

Individual Specification Code

These digits express a lead length, lead number, and the presence/absence of a connector. If the product has no individual specification, the corresponding code is omitted.

P37E.pdf Dec.25,2015

RoHS

Piezoelectric Sound Components


Piezoelectric Sounders SMD Type

Taking advantage of extensive acoustic and mechanical design technology and high performance ceramics, Murata has developed SMD piezoelectric sounders that suit the thin, high-density design of electronic equipment.

Features


- 1. Small, thin and lightweight
- 2. High sound pressure level and clear sound
- 3. Reflowable
- 4. Tape & Reel supply













PKLCS1212E2400-R1 PKLCS1212E24A0-R1

PKMCS0909E4000-R1





(Note) The location of open hole is not specified. (in mm)

For Consumer

Part Number	Sound Pressure Level (dB)	Operating Voltage Range* (Vo-p)	Capacitance (nF) Ref. only	Operating Temp. Range (°C)	Storage Temp. Range (°C)
PKLCS1212E2000-R1	70 min.[±1.5Vo-p,2kHz,square wave,10cm]	±12.5 max.	(28.0)	-20 to +70	-30 to +80
PKLCS1212E2400-R1	75 min.[±1.5Vo-p,2.4kHz,square wave,10cm]	±12.5 max.	(28.0)	-20 to +70	-30 to +80
PKLCS1212E4001-R1	75 min.[±1.5Vo-p,4kHz,square wave,10cm]	±12.5 max. or 25.0 max.	(19.5)	-20 to +70	-30 to +80
PKMCS0909E4000-R1	65 min.[±1.5Vo-p,4kHz,square wave,10cm]	±12.5 max.	(9.0)	-40 to +85	-40 to +85

*Operating Voltage Range: Does not contain Direct Current bias.

For Automotive

Part Number	Sound Pressure Level (dB)	Operating Voltage Range* (Vo-p)	Capacitance (nF) Ref. only	Operating Temp. Range (°C)	Storage Temp. Range (°C)
PKLCS1212E20A0-R1	70 min.[±1.5Vo-p,2kHz,square wave,10cm]	±12.5 max.	(28.0)	-40 to +85	-40 to +85
PKLCS1212E24A0-R1	75 min.[±1.5Vo-p,2.4kHz,square wave,10cm]	±12.5 max.	(28.0)	-40 to +85	-40 to +85
PKLCS1212E40A1-R1	75 min.[±1.5Vo-p,4kHz,square wave,10cm]	±12.5 max. or 25.0 max.	(19.5)	-40 to +85	-40 to +85

*Operating Voltage Range: Does not contain Direct Current bias.





Note • Please read rating and ACAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.
 • This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.

P37E.pdf . Dec.25,2015


Standard Land Pattern Dimensions

PKLCS Series




1







(in mm)





(in mm)

Frequency Response











PKMCS0909E4000-R1 Conditions: 10cm, A-filter




Taping Dimension PKLCS Series

1



Taping Dimension PKMCS Series



muRata

Note • Please read rating and ①CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.
 • This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.

P37E.pdf Dec.25,2015

RoHS

1

Piezoelectric Sound Components

Piezoelectric Sounders Pin Type

Microcomputers are widely used for microwave ovens, air conditioners, cars, toys, timers, and alarm equipment. Externally driven piezoelectric sounders are used in digital watches, electronic calculators, telephones and other equipment. They are driven by a signal (ex.: 2048Hz or 4096Hz) from an LSI and provide melodious sound.

Features

- 1. Low power consumption
- 2. No contacts; therefore, semipermanent life; noiseless and highly reliability

Applications

- 1. Various office equipment such as PPCs printers and keyboards
- 2. Home appliances such as microwave oven, rice cookers etc.


R1.0

PKM17EP


3. Confirmation sound of various audio equipment



PKM13EPYH4002-B0








PKM17EPP-2002-B0



4






PKM22EPH2001



PKM17EPPH4001-B0

PKM22EPPH2001-B0




1001-B0 6.5


(in mm) Tol.: ±0.5



PKM22EPPH4001-B0



Note • Please read rating and ⁽/_LCAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.
 • This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.





Part Number	Sound Pressure Level (dB)	Operating Voltage Range* (Vo-p)	Capacitance (nF)	Operating Temp. Range (°C)	Storage Temp. Range (°C)
PKM13EPYH4002-B0	70 min.[±1.5Vo-p,4kHz, square wave,10cm]	±15.0 max. or 30.0 max.	5.5 ±30%[1kHz]	-40 to +85	-40 to +85
PKM17EPP-2002-B0	70 min.[3.0Vo-p,2kHz, square wave,10cm]	25.0 max. [with polarity]	34.0 ±30%[120Hz]	-20 to +70	-30 to +80
PKM17EPPH4001-B0	72 min.[±1.5Vo-p,4kHz,square wave,10cm]	±12.5 max. or 25.0 max.	7.0 ±30%[1kHz]	-20 to +70	-30 to +80
PKM22EPH2001	75 min.[±1.5Vo-p,2kHz,square wave,10cm]	±12.5 max. or 25.0 max.	17.0 ±30%[120Hz]	-20 to +70	-30 to +80
PKM22EPPH2001-B0	70 min.[±1.5Vo-p,2kHz,square wave,10cm]	±15.0 max. or 30.0 max.	19.0 ±30%[120Hz]	-20 to +70	-30 to +80
PKM22EPPH4001-B0	75 min.[±1.5Vo-p,4kHz,square wave,10cm]	±15.0 max. or 30.0 max.	12.0 ±30%[1kHz]	-20 to +70	-30 to +80
PKM22EPPH4005-B0	75 min.[±1.5Vo-p,4kHz,square wave,10cm]	±15.0 max. or 30.0 max.	12.0 ±30%[1kHz]	-20 to +70	-30 to +80
РКМ22ЕРРН4007-В0	85 min.[±1.5Vo-p,4kHz,square wave,10cm]	±15.0 max. or 30.0 max.	12.0 ±30%[1kHz]	-20 to +70	-30 to +80

*Operating Voltage Range: Does not contain Direct Current bias.

Frequency Response


1






PKM17EPP-2002-B0

.....



PKM22EPH2001 Conditions: 10cm, A-filter





Continued on the following page. 🖊


muRata


Continued from the preceding page. \searrow

Frequency Response










P37E.pdf Dec.25,2015

1





Note • Please read rating and ACAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.
 • This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.

P37E.pdf Dec.25,2015

RoHS

Piezoelectric Sound Components

Piezoelectric Sounders Pin Type Taping


Taking advantage of extensive automatic insertion design technology and materials experience, Murata has developed standard taping type piezoelectric sounders.

This Murata technology supports labor and cost saving measures.

Features

- 1. Lead dimension: Improved mounting reliability (cut & clinch) due to round terminal
- 2. High, stable mountability
- 3. Ammo packaging






Part Number	Sound Pressure Level (dB)	Operating Voltage Range* (Vo-p)	Capacitance (nF)	Operating Temp. Range (°C)	Storage Temp. Range (°C)
PKM13EPYH4000-A0	70 min.[±1.5Vo-p,4kHz,square wave,10cm]	±15.0max. or 30.0max.	5.5 ±30%[1kHz]	-40 to +85	-40 to +85
*Operating Voltage Bange: Do	pes not contain Direct Current bias				

^tOperating Voltage Range: Does not contain Direct Current bias.


Frequency Response



A Note
 Please read rating and A CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.
 This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.

1

Taping Dimension






Item	Code	Nominal Value	Tol.	Notes
Width of diameter	D	ø12.6	±0.5	
Height of component	A	6.9	±0.5	
Dimensions of terminal	d1	ø0.5	±0.1	
Lead length under the hold-down tape	L1	8.0 min.	_	
Pitch of component	Р	25.4	±0.5	
Pitch of sprocket	Po	12.7	±0.2	Tolerance for Pitches 10xP0=127±2mm
Length from hole center to lead	P1	3.85	±0.7	
Length from hole center to component center	P2	6.35	±0.7	
Lead spacing	F	5.0	±0.5	
Slant forward or backward	dh	0	±1.0	360°: 1mm max.
Width of carrier tape	W	18.0	±0.5	
Width of hold-down tape	Wo	12.5 min.	_	Hold-down tape does not exceed the carrier tap
Position of sprocket hole	W1	9.0	±0.5	
Gap of hold-down tape and carrier tape	W2	2.0 max.	_	
Distance between the center of sprocket hole and lead stopper	Но	18.0	±0.5	
Total height of component	H1	26.0 max.	_	
Diameter of sprocket hole	D0	ø4.0	±0.2	
Total thickness of tape	t	0.6	±0.2	
Body tilt	dS	0	±1.0	



Drive Method

Fig. 1 shows examples of the circuit to which the external drive method is applied.

- (i) Represents a circuit driven by output signals of the unstable multivibrator.
- (ii) Represents a circuit using 2 NAND gates, which is oscillated or stopped by ON/OFF operations of the input signals.
- (iii) Represents a circuit driven by output signals of CMOS LSI.



1

Caution · Notice

ACaution (Rating)

Do not use the product beyond the rated temperature range and the rated voltage range. If using it beyond this range, characteristics might degrade.

Notice (Storage and Operating Condition)

1. Product Storage Condition

Please store the products in a room where the temperature/humidity is stable and avoid places where there are large temperature changes. Please store the products under the following conditions. Temperature: -10 to +40°C Humidity: 15 to 85%R.H.

2. Expiration Date on Storage

Expiration date (shelf life) of the products is six months after delivery under the condition of a sealed and unopened package. Please use the products within six months after delivery. If you store the products for a long time (more than six months), use carefully because the products may be degraded in solderability due to storage under poor conditions.

Please confirm solderability and characteristics for the products regularly.

- 3. Notice on Product Storage
 - (1) Please do not store the products in a chemical atmosphere (Acids, Alkali, Bases, Organic gas, Sulfides and so on), because the characteristics may be reduced in quality, may be degraded in solderability due to storage in a chemical atmosphere.

Notice (Soldering and Mounting)

1. Mounting

When mounting a pin terminal type of product to the printed circuit board, please insert the pin terminal along the hole of the board. If the product is pressed so that the terminal is not in the hole, the pin terminal would be pushed into the inside of the product and the sounds might become unstable.

- Double-sided through-hole Board Please avoid using a double-sided through-hole board. If the melted solder touched the base of a pin terminal, a part of the plastic case would melt and the sounds might become unstable.
- 3. Soldering Conditions
 - (1) Flow soldering conditions for pin terminal type
 - \cdot Temperature: within 260°C±5°C
 - · Time: within 10±1 sec.
 - \cdot Soldering part is the lead terminals excluding 1.5mm from product body.


- (2) Please do not store the products directly on the floor without anything under them to avoid damp places and/or dusty places.
- (3) Please do not store the product in places such as in a damp heated place or any place exposed to direct sunlight or excessive vibration.
- (4) Please use the products immediately after the package is opened, because the characteristics may be reduced in quality, and/or be degraded in solderability due to storage under poor conditions.
- (5) Please be sure to consult with our sales representative or engineer whenever the products are to be used in conditions not listed above.
- 4. Operating Environment

This product is designed for application in an ordinary environment (normal room temperature, humidity and atmospheric pressure).

Do not use the products in a chemical atmosphere such as chlorine gas, acid or sulfide gas.

Characteristics might degrade by a chemical reaction with the material used in products.

- (2) Soldering condition by soldering iron for pin terminal type
 - · Temperature: within 350±5°C
 - · Time: within 3.0±0.5 sec.
 - \cdot Soldering part is the lead terminals excluding 1.5mm from product body
- (3) Reflow soldering condition for surface mounting type
 - · Temperature profile: Fig. 1
 - \cdot Number of times: Within 2 maximum





Caution · Notice


Continued from the preceding page. \searrow


- Washing Please avoid washing, since this product is not a sealed structure.
- 5. After Mounting the Product
 - (1) If the product is floating from the printed circuit board, please do not push it. When pressing, the pin terminal is pushed inside the product and the sounds might become unstable.
 - (2) Please do not apply force (shock) to the product. If force is applied, the case might come off.
 - (3) If the case comes off, please do not reassemble. Even if it seems to have returned to the original, the sounds might become unstable.
 - (4) Please do not blow air onto the product directly. Blown air applies force to the piezoelectric diaphragm through the sound emission hole; cracks could occur and then the sounds could become unstable. In addition, there is a possibility that the case could come off.
- Notice (Handling)
- 1. Piezoelectric ceramic is used in this product. Please use care in handling, because ceramic is broken when excessive force is applied.
- 2. Please do not apply force to the piezoelectric diaphragm from the sound emission hole. If applying force, cracks occur and the sounds might become unstable.
- Please do not drop the product or apply shock or temperature change to it. If so, the LSI might be destroyed by the charge (surge voltage) generated. Fig. 2 shows an example driving circuit using zener diode.

Notice (Driving)

- 1. Ag migration might occur if DC voltage is applied to the product under a high humidity environment. Please avoid using it under high humidity and design the circuit not to apply DC voltage.
- 2. When driving the product by IC, please insert the resistance of 1 to $2k\Omega$ in series. The purpose is to protect the IC and to obtain stable sound. (Please see Fig. 2a). Inserting a diode in parallel to the product has the same effect. (Please see Fig. 3b)

6. Flux or Coating Agent, etc., Various Solvents It is possible for a liquid solvent to penetrate inside the product, since this product is not a sealed structure. If a liquid penetrated inside and attached to the piezoelectric diaphragm, its vibration could be inhibited. If attaching to an electrical junction, the electric connection might fail. To prevent sound instability, please do not allow liquid to penetrate inside the product.





muRata

P37E.pdf Dec.25,2015

2

RoHS

Piezoelectric Sound Components


Piezoelectric Buzzers

This is a unified piezoelectric sounder that has a piezoelectric diaphragm of 3 terminals connected to a self-drive circuit, and it easily generates sound with only a DC power supply (DC3.0-15V). Using a suitably designed resonant system, this type can be used where large sound volumes are needed.

Applications


- 1. Gas alarms, burglar alarms
- 2. Air conditioners, microwave ovens and various types of microcomputer controlled home electronic appliances
- 3. Toys, games, and other simple electronic devices such as teaching aids

PKB24SPCH3601-B0



Part Number	Sound	Oscillating	Current	Operating	Operating	Storage
	Pressure Level	Frequency	Consumption	Voltage Range	Temp. Range	Temp. Range
	(dB)	(kHz)	(mA)	(Vdc)	(°C)	(°C)
PKB24SPCH3601-B0	90 min. [12Vdc,10cm]	3.6 ±0.5kHz [12Vdc]	16 max. [12Vdc]	3.0 to 15.0	-20 to +70	-30 to +80

Voltage-Sound Pressure Level/Voltage-Consumption Current



Caution · Notice

ACaution (Rating)

Do not use the product beyond the rated temperature range and the rated voltage range. If using it beyond this range, characteristics might degrade.

Notice (Storage and Operating Condition)

1. Product Storage Condition

Please store the products in a room where the temperature/humidity is stable and avoid places where there are large temperature changes. Please store the products under the following conditions. Temperature: -10 to +40°C Humidity: 15 to 85%R.H.

2. Expiration Date on Storage

Expiration date (shelf life) of the products is six months after delivery under the condition of a sealed and unopened package. Please use the products within six months after delivery. If you store the products for a long time (more than six months), use carefully because the products may be degraded in solderability due to storage under poor conditions.

Please confirm solderability and characteristics for the products regularly.

- 3. Notice on Product Storage
 - (1) Please do not store the products in a chemical atmosphere (Acids, Alkali, Bases, Organic gas, Sulfides and so on), because the characteristics may be reduced in quality, may be degraded in solderability due to storage in a chemical atmosphere.

Notice (Soldering and Mounting)

1. Mounting

When mounting a pin terminal type of product to the printed circuit board, please insert the pin terminal along the hole of the board. If the product is pressed so that the terminal is not in the hole, the pin terminal would be pushed into the inside of the product and the sounds might become unstable.

- 2. Double-sided through-hole Board Please avoid using a double-sided through-hole board. If the melted solder touched the base of a pin terminal, a part of the plastic case would melt and the sounds might become unstable.
- 3. Soldering Conditions
 - (1) Flow soldering conditions for pin terminal type
 - Temperature: within +260°C±5°C
 - · Time: within 10±1 sec.
 - \cdot Soldering part is the lead terminals excluding 1.5mm from product body.
 - (2) Soldering condition by soldering iron for pin terminal type
 - · Temperature: within 350±5°C

- (2) Please do not store the products directly on the floor without anything under them to avoid damp places and/or dusty places.
- (3) Please do not store the product in places such as in a damp heated place or any place exposed to direct sunlight or excessive vibration.
- (4) Please use the products immediately after the package is opened, because the characteristics may be reduced in quality, and/or be degraded in solderability due to storage under poor conditions.
- (5) Please be sure to consult with our sales representative or engineer whenever the products are to be used in conditions not listed above.
- 4. Operating Environment

This product is designed for application in an ordinary environment (normal room temperature, humidity and atmospheric pressure).

Do not use the products in a chemical atmosphere such as chlorine gas, acid or sulfide gas.

Characteristics might degrade by a chemical reaction with the material used in products.

- · Time: within 3.0±0.5 sec.
- · Soldering part is the lead terminals excluding 1.5mm from product body.
- 4. Washing

muRata

.....

Please avoid washing, since this product is not a sealed structure.

- 5. After Mounting the Product
 - (1) If the product is floating from the printed circuit board, please do not push it. When pressing, the pin terminal is pushed inside the product and the sounds might become unstable.
 - (2) Please do not apply force (shock) to the product. If force is applied, the case might come off.
 - (3) If the case comes off, please do not reassemble. Even if it seems to have returned to the original, the sounds might become unstable.
 - (4) Please do not blow air onto the product directly. Blown air applies force to the piezoelectric diaphragm through the sound emission hole; cracks could occur and then the sounds could become unstable.

16

▲Caution · Notice

Continued from the preceding page.


6. Flux or Coating Agent, etc., Various Solvents It is possible for a liquid solvent to penetrate inside the product, since this product is not a sealed structure. If a liquid penetrated inside and attached to the piezoelectric diaphragm, its vibration could be inhibited. If attaching to an electrical junction, the electric connection might fail. To prevent sound instability, please do not allow liquid to penetrate inside the product.

Notice (Handling)


- 1. Piezoelectric ceramic is used in this product. Please use care in handling, because ceramic is broken when excessive force is applied.
- 2. Please do not apply force to the piezoelectric diaphragm from the sound emission hole. If applying force, cracks occur and the sounds might become unstable.
- 3. Please do not drop the product or apply shock or temperature change to it. If so, the LSI might be destroyed by the charge (surge voltage) generated.

Notice (Driving)

- 1. When using a piezoelectric buzzer, there is no need to prepare the oscillation circuit; it has an oscillation circuit.
- 2. Please set the sounding time more than 200 msec., when driving the piezoelectric sounder of self-drive or the piezoelectric buzzer as an intermittent sound.
- 3. Please don't block the sound emission hole with tape to control the sound volume. The oscillation circuit condition is set so as to obtain a stable sounding (oscillating) state under the condition that the front of sound emission hole is in an open state. If the sound emission hole is blocked with tape, then the oscillation condition changes and the sounds might become unstable.
- 4. Please don't put a resistor between the oscillation circuit and power supply to control the sound volume of the piezoelectric sounder or the piezoelectric buzzer. Doing so could cause an unstable sounding state like an abnormal oscillation or the oscillation stopping because of the change in oscillation conditions. Please insert a capacitor (about 1µF) in parallel with the piezoelectric buzzer, if you need to control the sound volume. (Please see Fig. 2)
- 5. Please keep a distance of more than 15mm between the surface of sound emission hole and the surface of housing, when mounting the piezoelectric sounder of self-drive or the piezoelectric buzzer into your set. A shorter distance could cause an unstable sounding state like an abnormal oscillation or the oscillation stopping; because the oscillation conditions change, the acoustics are influenced by reflection.



.....



P37E.pdf Dec.25,2015

RoHS

Piezoelectric Sound Components

Piezoelectric Diaphragms

Features


- 1. Clear sound
- 2. Ultra thin and lightweight
- 3. No contacts; therefore, noiseless and highly reliable
- 4. Low power consumption for voltage type

Applications

3

Clocks/Calculators/Digital camera/Various alarms (Burglar alarms, etc.)

.....



External Drive Type

Part Number	Resonant Frequency (kHz)	Resonant Impedance (Ω)	Capacitance (nF)	Plate Size øD (mm)	Element Size øa (mm)	Electrode Size øb (mm)	Thickness T (mm)	Plate Thickness t (mm)	Plate Material
7BB-12-9	9.0 ±1.0kHz	1000 max.	8.0 ±30% [1kHz]	12.0	9.0	8.0	0.22	0.10	Brass
7BB-15-6	6.0 ±1.0kHz	800 max.	10.0 ±30% [1kHz]	15.0	10.0	9.0	0.22	0.10	Brass
7BB-20-3	3.6 ±0.6kHz	500 max.	20.0 ±30% [1kHz]	20.0	14.0	12.8	0.22	0.10	Brass
7BB-20-6	6.3 ±0.6kHz	350 max.	10.0 ±30% [1kHz]	20.0	14.0	12.8	0.42	0.20	Brass
7BB-20-6L0	6.3 ±0.6kHz	1000 max.	10.0 ±30% [1kHz]	20.0	14.0	12.8	0.42	0.20	Brass (with Lead Wire: AWG32 Length 50mm)
7BB-27-4	4.6 ±0.5kHz	200 max.	20.0 ±30% [1kHz]	27.0	19.7	18.2	0.54	0.30	Brass
7BB-27-4L0	4.6 ±0.5kHz	300 max.	20.0 ±30% [1kHz]	27.0	19.7	18.2	0.54	0.30	Brass (with Lead Wire: AWG32 Length 50mm)
7BB-35-3	2.8 ±0.5kHz	200 max.	30.0 ±30% [1kHz]	35.0	25.0	23.0	0.53	0.30	Brass
7BB-35-3L0	2.8 ±0.5kHz	200 max.	30.0 ±30% [1kHz]	35.0	25.0	23.0	0.53	0.30	Brass (with Lead Wire: AWG32 Length 50mm)
7BB-41-2	2.2 ±0.3kHz	250 max.	30.0 ±30% [1kHz]	41.0	25.0	23.0	0.63	0.40	Brass
7BB-41-2L0	2.2 ±0.3kHz	300 max.	30.0 ±30% [1kHz]	41.0	25.0	23.0	0.63	0.40	Brass (with Lead Wire: AWG32 Length 50mm)
7NB-31R2-1	1.3 ±0.5kHz	300 max.	40.0 ±30% [120Hz]	31.2	19.7	18.2	0.22	0.10	Nickel Alloy

Note • Please read rating and (LCAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.
 • This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.

Design Procedure · Drive Method

Design Procedure


In general, man's audible frequency range is about 20Hz to 20kHz.


Frequency ranges of 2kHz to 4kHz are most easily heard. For this reason, most piezoelectric sound components are used in this frequency range and the resonant frequency (fo) is generally selected in the same range. In general, the piezoelectric diaphragm is installed in a cavity to produce high sound pressure (Fig 1). The resonant frequency (fcav) of the cavity in Fig. 1 is obtained from Formula (1) (Helmholtz's Formula). Since the piezoelectric diaphragm and cavity have proper resonant frequencies, (fo) and (fcav) respectively, sound pressure in specific frequencies can be increased and a specific bandwidth can be provided by controlling both positions.




This method produces sound by driving the piezoelectric diaphragm with electric signals supplied from an external oscillating circuit such as a multivibrator.


Using this method, the piezoelectric buzzer can work as a speaker. In this method, a mechanical oscillation Qm of the piezoelectric diaphragm is damped properly to provide a wider frequency band of the sound pressure. This is applied to the switching sounds of home electric appliances, key-in sounds of OA equipment, because it can provide multiple sounds, not just a single sound. Fig. 3 shows examples of the circuit to which the external drive method is applied: (i) represents a circuit driven by output signals of the unstable multivibrator; (ii) represents a circuit using 2 NAND gates, which is oscillated or stopped by ON/OFF operations of the input signal; (iii) represents a circuit driven by output signals of the input signal; (iii) represents a circuit driven by output signals of CMOS LSI.















ACaution · Notice

∆Caution (Rating)

Do not use the product beyond the rated temperature range. If using it beyond this range, characteristics might degrade.

The rated voltage range is not specified; depending on the driving condition or the mounting method, the rated voltage range is different. In your evaluation, please use actual operating voltage.

Notice (Storage and Operating Condition)

- 1. Product Storage Condition
- Please store the products in a room where the temperature/humidity is stable and avoid places where there are large temperature changes. Please store the products under the following conditions. Temperature: -10 to +40°C Humidity: 15 to 85%R.H.
- 2. Expiration Date on Storage

Expiration date (shelf life) of the products is six months after delivery under the condition of a sealed and unopened package. Please use the products within six months after delivery. If you store the products for a long time (more than six months), use carefully because the products may be degraded in solderability due to storage under poor conditions.

Please confirm solderability and characteristics for the products regularly.

- 3. Notice on Product Storage
 - (1) Please do not store the products in a chemical atmosphere (Acids, Alkali, Bases, Organic gas, Sulfides and so on), because the characteristics may be reduced in quality, may be degraded in solderability due to storage in a chemical atmosphere.

- (2) Please do not store the products directly on the floor without anything under them to avoid damp places and/or dusty places.
- (3) Please do not store the product in places such as in a damp heated place or any place exposed to direct sunlight or excessive vibration.
- (4) Please use the products immediately after the package is opened, because the characteristics may be reduced in quality, and/or be degraded in solderability due to storage under poor conditions.
- (5) Please be sure to consult with our sales representative or engineer whenever the products are to be used in conditions not listed above.
- 4. Operating Environment
 - This product is designed for application in an ordinary environment (normal room temperature, humidity and atmospheric pressure).
 - Do not use the products in a chemical atmosphere such as chlorine gas, acid or sulfide gas.

Characteristics might degrade by a chemical reaction with the material used in products.

Notice (Soldering and Mounting)

1. Mounting

When mounting the product on your set, pressing force should be applied to only the supporting part. When force is applied to the non-supporting part, cracks might occur, causing unstable sounds.

2. Soldering

(1) Please consult with a Murata representative if you need to solder the lead wires to the product. We can deliver the products with soldered lead wires.
When soldering, it is recommended to solder by heating the product (from 60 to 80°C, more than 10 sec).
Including the presence or absence of heating, please use after a thorough evaluation about soldering.
Soldering condition is as follows.

- · Metal Plate
- Temperature of soldering iron: from 410 to 450°C Soldering Time: within 3 sec.
- · Ag electrode
- Temperature of soldering iron: from 320 to 350°C Soldering Time: within 0.5 sec.
- · Solder: Sn-Ag-Cu (Flux-cored solder)
- (2) Soldering condition of the lead wire to printed circuit board by using soldering iron.
 - · Temperature: 350±5°C
 - · Time: within 3.0±0.5 sec.

Caution · Notice


Continued from the preceding page. \searrow


Notice (Handling)

- 1. Piezoelectric ceramic is used in this product. Please use care in handling, because the ceramic is broken when excessive force is applied.
- 2. To avoid rusting, please do not touch the products with bare hands.
- 3. Please do not pull the lead wire of the product. Pulling may cause the lead wire to disconnect or to peel off the solder point.
- 4. When attaching a connector to the lead wires, please do not apply force to the soldering part. After attaching a connector, we recommend checking the connecting status.
- 5. Please do not bend the product or apply any force to it. Also, please do not press it with sharp objects. Applying force could cause cracks to occur in the piezoelectric ceramic, resulting in unstable sounds.
- 6. Please do not drop the product or apply shock or temperature change to it. If so, the LSI might be destroyed by the charge (surge voltage) generated. Fig.1 shows an example driving circuit using zener diode.

Notice (Driving)

- 1. Ag migration might occur if DC voltage is applied to the product under a high humidity environment. Please avoid using it under high humidity and design the circuit not to apply DC voltage.
- 2. When driving the product by IC, please insert the resistance of 1 to $2k\Omega$ in series. The purpose is to protect the IC and to obtain stable sound. (Please see Fig. 2a). Inserting a diode in parallel to the product has the same effect. (Please see Fig. 2b).







Oscillating System

Basically, the sound source of a piezoelectric sound component is a piezoelectric diaphragm. A piezoelectric diaphragm consists of a piezoelectric ceramic plate that has electrodes on both sides and a metal plate (brass or stainless steel, etc.).

A piezoelectric ceramic plate is attached to a metal plate with adhesives. Fig. 2 shows the oscillating system of a piezoelectric diaphragm.

Applying DC voltage between electrodes of a piezoelectric diaphragm causes mechanical distortion due to the piezoelectric effect. For a misshapen piezoelectric element, the distortion of the piezoelectric element expands in a radial direction, and the piezoelectric diaphragm bends toward the direction shown in Fig. 2 (a). The metal plate bonded to the piezoelectric element does not expand. Conversely, when the piezoelectric element shrinks, the piezoelectric diaphragm bends in the direction shown in Fig. 2 (b). Thus, when AC voltage is applied across electrodes, the bending shown in Fig. 2 (a) and Fig. 2 (b) is repeated as shown in Fig. 2 (c), producing sound waves in the air.





muRata

To Raise Sound Pressure Level (S.P.L.)

It is probable that the S.P.L. of Piezoelectric sound components is higher when the input voltage is higher because Piezoelectric sound components are driven by voltage. The relationship between S.P.L. and the input voltage is basically shown in the following fomula:

S.P.L. after increased input voltage(dB)=


previous S.P.L.+20Log(V2/V1) V1: previous input voltage V2: increased input voltage


Therefore, S.P.L. is theoretically getting 6dB higher as the input voltage is twice as high.

Fig. 1 represents S.P.L. - frequency characteristics for PKLCS1212E4001-R1 in which the input voltage is varied. We can see that S.P.L. is approximately getting 6dB higher as the input voltage is twice as high.

In summary, the following are typical examples of raising S.P.L.

- (1) (i), (ii), (iii) in Fig. 3 (Examples of the External Drive Circuit) (page 19), input DC voltage for Piezoelectric sound components should be getting higher. Variable range of input voltage should be less than maximum input voltage.
- (2) In a case that is driven by IC directly like as Fig. 2, input voltage of Piezoelectric sound components should be twice as high because of the BTL (Bridge Tied Load) drive circuit, which includes an inverter.







Characteristics and Measuring Method

Characteristics

Туре	Resonant Frequency	Resonant Impedance	Capacitance	Sound Pressure Level	Oscillating Frequency	Current Consumption	Input Voltage	Operating Voltage
Piezoelectric Diaphragm	0	0	0					
Piezoelectric Sounder (External Drive)			(O)	0			0	
Piezoelectric Buzzer				0	0	0		0
Remarks	Common Conditions: Operating Temp. Range / Storage Temp. Range Measurement Instruments: LCR Meter (Capacitance) / Freq. Counter (Oscillating Freq.) / Multi Meter (Current Consump					t Consumption)		

Measuring Procedure

Measurement of Resonant Frequency and Resonant Impedance

When the piezoelectric diaphragm oscillates freely in air, the node does not move as shown in Fig. 1. With this point held with a measuring terminal, the resonant frequency (fo) and resonant impedance (Ro) are measured in the constant-current circuit as shown in Fig. 2.

Measuring Procedure

- 1) Connect the switch to side "a" and adjust frequency of the oscillator to read the frequency and the voltage when the voltmeter indicates a minimum value.
- 2) Next connect the switch to side "b" and vary the variable resistor to have the same voltage as in 1). Then, read the value of the resistor.
- 3) The resonant frequency (f0) can be obtained from 1) and the resonant impedance (R0) from 2).
- Note: Actual measurement is performed using a measuring unit in accordance with the above principles.

Measurement of Sound Pressure Level (S.P.L.)


The sound pressure level is measured with a sound pressure level meter as shown in Fig. 3.

- Note: The relation between sound pressure level and distance between sound pressure level and voltage can be expressed with Formula (2). The value of the sound pressure level under different operating conditions can be easily calculated using values specified in the catalog.
 - S.P.L.(dB) [under actual operating conditions]
 - = S.P.L.(dB) [value specified in catalog]

-20 log A/B(dB)(2)


In case of relation with distance:


- A = Actual distance
- B = Distance specified in catalog
- In case of relation with voltage:
 - A = Voltage specified in catalog
 - B = Actual operating voltage



.....

Fig. 1 Measurement of Piezoelectric Diaphragm





Downloaded from Arrow.com.

muRata

Minimum Quantity

			Minimum Quantity (pcs.)					
Product Names	Part Number –	Ø330mm Reel	Bulk (Box)	Ammo Pack				
Piezoelectric Sounders	PKLCS1212E2000-R1	1000						
	PKLCS1212E20A0-R1	1000						
	PKLCS1212E2400-R1	1000						
	PKLCS1212E24A0-R1	1000						
	PKLCS1212E4001-R1	1000						
	PKLCS1212E40A1-R1	1000						
	PKMCS0909E4000-R1	2000						
	PKM13EPYH4000-A0			500				
	PKM13EPYH4002-B0		1980					
	PKM17EPP-2002-B0		1000					
	PKM17EPPH4001-B0		1200					
	PKM17EPPH4002-B0		1200					
	PKM22EPH2001		360					
	PKM22EPH2002		270					
	PKM22EPH2003		270					
	PKM22EPPH2001-B0		750					
	PKM22EPPH2002-B0		750					
	PKM22EPPH4001-B0		900					
	РКМ22ЕРРН4002-В0		900					
	PKM22EPPH4005-B0		750					
	РКМ22ЕРРН4007-В0		750					
	PKM22EPPH4012-B0		750					
Piezoelectric Buzzers	PKB24SPCH3601-B0		650					
Piezoelectric Diaphragms	7BB-12-9		5120					
	7BB-15-6		8000					
	7BB-20-3		3000					
	7BB-20-6		1800					
	7BB-20-6L0		600					
	7BB-27-4		1500					
	7BB-27-4L0		600					
	7BB-35-3		800					
	7BB-35-3L0		400					
	7BB-41-2		400					
	7BB-41-2L0		250					
	7NB-31R2-1		3000					

Global Locations

For details please visit www.murata.com



Note

1 Export Control

For customers outside Japan:

No Murata products should be used or sold, through any channels, for use in the design, development, production, utilization, maintenance or operation of, or otherwise contribution to (1) any weapons (Weapons of Mass Destruction [nuclear, chemical or biological weapons or missiles] or conventional weapons) or (2) goods or systems specially designed or intended for military end-use or utilization by military end-users.

For customers in Japan:

For products which are controlled items subject to the "Foreign Exchange and Foreign Trade Law" of Japan, the export license specified by the law is required for export. Please contact our sales representatives or product engineers before using the products in this catalog for the applications listed below, which require especially high reliability for the prevention of defects which might directly damage a third party's life, body or property, or when one of our products is intended for use in applications other than those specified in this catalog.

- (1) Aircraft equipment
- Aerospace equipment
- (3) Undersea equipment
- ④ Power plant equipment
- (5) Medical equipment
- Transportation equipment (vehicles, trains, ships, etc.)
- Traffic signal equipment
- B Disaster prevention / crime prevention equipment
- Data-processing equipment
- Application of similar complexity and/or reliability requirements to the applications listed above

Product specifications in this catalog are as of December 2015. They are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering. If there are any questions, please contact our sales representatives or product engineers.

Please read rating and ①CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.

This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.

Please note that unless otherwise specified, we shall assume no responsibility whatsoever for any conflict or dispute that may occur in connection with the effect of our and/or a third party's intellectual property rights and other related rights in consideration of your use of our products and/or information described or contained in our catalogs. In this connection, no representation shall be made to the effect that any third parties are authorized to use the rights mentioned above under licenses without our consent.

7 No ozone depleting substances (ODS) under the Montreal Protocol are used in our manufacturing process.

Murata Manufacturing Co., Ltd. WWW.MUrata.com

