





C0816X5R0J105M050AC

Applications	 Commercial Grade
Feature	 Low ESL Reverse Geometry
Series	C0816 [EIA CC0306]



Size	
Length(L)	0.80mm +/-0.15mm
Width(W)	1.60mm +/-0.20mm
Thickness(T)	0.50mm +/-0.10mm
Terminal Width(B)	0.10mm Min.


Electrical Characteristics	
Capacitance	1uF +/-20%
Rated Voltage	6.3Vdc
Temperature Characteristic	X5R(+/-15%)
Dissipation Factor	12% Max.
Insulation Resistance	100M Min.

Other	
Soldering Method	Reflow
AEC Q200	No
Packing	Blister (Plastic)Taping [180mm Reel]
Package Quantity	4000 Pcs Min.


•This PDF document was created based on the data listed on the TDK Corporation website.
 •All specifications are subject to change without notice.

C0816X5R0J105M050AC


Characteristic Graphs




C0816X5R0J105M050AC




C0816X5R0J105M050AC




C0816X5R0J105M050AC



C0816X5R0J105M050AC



C0816X5R0J105M050AC(DC Bias = 0V) C0816X5R0J105M050AC(DC Bias = 3.15V)



C0816X5R0J105M050AC(100kHz) C0816X5R0J105M050AC(500kHz)
C0816X5R0J105M050AC(1MHz)

•This PDF document was created based on the data listed on the TDK Corporation website.
•All specifications are subject to change without notice.