



## Insulation sleeves

| Nominal cross section mm <sup>2</sup> | Nominal size to DIN | Part No. | Colour | Typ | Dimension mm |      |     | Insulation material | for item                       | Weight/pcs. ~kg | Packing unit/pcs |
|---------------------------------------|---------------------|----------|--------|-----|--------------|------|-----|---------------------|--------------------------------|-----------------|------------------|
|                                       |                     |          |        |     | b1           | l    | h1  |                     |                                |                 |                  |
| 0.5 - 2.5                             | 6.3                 | 2770     |        | A   | 12.5         | 23.0 | 8.5 | PE                  | 1720,1730                      | 0.035           | 100              |
|                                       |                     | 2775     |        | A   | 9.5          | 25.0 | 5.0 | PE                  | 1820,1830                      | 0.030           | 100              |
| 0.5 - 4                               | 6.3                 | 2780     |        | A   | 9.5          | 25.0 | 6.0 | PE                  | 1720,1730, 1820,1830           | 0.030           | 100              |
| 0.5 - 6                               |                     | 2785     |        | B   | 9.2          | 24.5 | 5.6 | PA                  | 1720,1730,1750, 2720,2730,2750 | 0.055           | 100              |
|                                       |                     | 2790     |        | C   | 13.5         | 15.0 | 3.1 | PVC                 | 3720,3725, 3735                | 0.060           | 100              |

## Non-insulated tabs, angled version



### Characteristics


- To DIN 46342, part 1 and similar versions
- Dimensions in the plug sector to DIN 46244

### Material

- Brass (CuZn)

### Surface

- Tin-plated to protect against corrosion



| Nominal size to DIN | Part No. | Tab Thickn. | Tab Width | Typ | Dimension mm |     |     |      |      |     | Weight/pcs. ~kg | Packing unit/pcs |
|---------------------|----------|-------------|-----------|-----|--------------|-----|-----|------|------|-----|-----------------|------------------|
|                     |          |             |           |     | b1           | d2  | l2  | l3   | l4   | w   |                 |                  |
| --                  | 2040     | 0.8         | 2.8       | A   | 5.0          | 3.2 | 5.5 | 6.5  | --   | 60° | 0.040           | 100              |
|                     | 2045     | 0.8         | 6.3       | A   | 10.0         | 4.3 | 8.0 | 10.0 | --   | 45° | 0.160           | 100              |
|                     | 2060     | 0.8         | 6.3       | B   | 8.0          | 4.3 | 8.0 | 8.0  | 10.7 | 30° | 0.085           | 100              |
|                     | 2070     | 0.8         | 6.3       | B   | 8.0          | 3.2 | 8.0 | 8.0  | 10.7 | 45° | 0.085           | 100              |
|                     | 2075     | 0.8         | 6.3       | B   | 8.0          | 4.1 | 8.0 | 8.0  | 10.7 | 45° | 0.085           | 100              |
| B 6.3 - 0.8         | 2080     | 0.8         | 6.3       | B   | 8.0          | 4.3 | 8.0 | 8.5  | 10.7 | 45° | 0.085           | 100              |
|                     | 2083     | 0.8         | 6.3       | B   | 8.0          | 5.3 | 8.0 | 8.5  | 10.7 | 45° | 0.080           | 100              |
| --                  | 2090     | 0.8         | 6.3       | B   | 8.0          | 5.3 | 8.0 | 8.0  | 10.7 | 45° | 0.080           | 100              |
|                     | 2100     | 0.8         | 6.3       | B   | 7.5          | 2.5 | 8.0 | 5.7  | 11.5 | 90° | 0.075           | 100              |
|                     | 2105     | 0.8         | 6.3       | B   | 8.0          | 3.2 | 8.0 | 8.0  | 11.5 | 90° | 0.085           | 100              |
| C 6.3 - 0.8         | 2115     | 0.8         | 6.3       | B   | 8.0          | 4.3 | 8.0 | 8.5  | 11.5 | 90° | 0.090           | 100              |