



Fuse-link, low voltage, 6 A, AC 500 V, 120 kA, 10 x 38 mm, gL/gG, IEC



Part no. CYLINDRICAL FUSE 10 x 38 6A GG 500V AC
Catalog No. C10G6

EL-Nummer (Norway) 1600254

Delivery program

| | | | |
|------------------------------|---|----|--|
| Product range | | | Fuse |
| Basic function | | | Fuse-link |
| Field of application | | | low voltage |
| Rated current | I | A | 6 |
| Rated voltage | | | AC 500 V |
| Size | | | 10 x 38 mm |
| Utilization category | | | gL/gG |
| Breaking Capacity | | kA | 120 |
| usable for size/applications | | | for industrial applications for general purpose use |
| Standard/Approval | | | IEC |
| Shape | | | cylindrical |
| Standards/Regulations | | | IEC 60269-2 |

Technical data ETIM 7.0

| | | | |
|---|--|----|---|
| Circuit breakers and fuses (EG000020) / Cylindrical fuse (EC002704) | | | |
| Electric engineering, automation, process control engineering / Electrical installation, device / Safety fuse inserts / Cylindrical fuse (safety fuse) (ecl@ss10.0.1-27-14-20-02 [AFZ797013]) | | | |
| Size | | | 10x38 mm |
| Rated voltage | | V | 500 - 500 |
| Rated voltage | | | Other |
| Voltage type | | | AC |
| Utilization category | | | gL/gG (cable protection/equipment protection) |
| Rated operating frequency | | Hz | 45 - 62 |
| Nominal current | | A | 6 |
| With striker | | | No |
| Release characteristic | | | Other |
| Breaking capacity | | kA | 120 |